



SAW Filters - Surface Mount

Applications: The front-end SAW filter in the receiver eliminates interference from the incoming RF signal, thus increasing selectivity and sensitivity in short-range devices. Tighter tolerances are available upon request.




Fig.	Frequency (MHz)	Passband (MHz)	Insertion Loss (dB)	Digi-Key Part No.	Cut Tape Price Each			Digi-Key Part No.	Tape & Reel		Epcos Part No.
					1	10	100		Qty.	Pricing	
1	312.2	311.9 - 312.5	1.8	495-2354-1-ND	2.07	1.86	1.56	495-2354-2-ND	9,000	965.00/M	B39311B3712U410
	315	314.7 - 315.3	1.7	495-1667-1-ND	2.07	1.86	1.56	495-1667-2-ND	9,000	965.00/M	B39321B3711U410
	315	314.85 - 315.15	2.4	495-2619-1-ND	2.33	2.10	1.75	495-2619-2-ND	9,000	1164.00/M	B39321B3731H110
	433.92	433 - 434.71	2.0	495-1870-1-ND	2.07	1.86	1.56	495-1870-2-ND	9,000	916.00/M	B39431B3710U410
	433.92	433.70 - 434.14	2.4	495-3691-1-ND NEW!	2.33	2.10	1.75	495-3691-2-ND NEW!	9,000	1086.00/M	B39431B3730H110
	433.92	433.70 - 434.14	2.2	495-3693-1-ND NEW!	2.33	2.10	1.75	495-3693-2-ND NEW!	9,000	1086.00/M	B39431B3736H110
	864	862.5 - 865.5	4.0	495-2353-1-ND	1.50	1.35	1.13	495-2353-2-ND	9,000	700.00/M	B39861B3563U410
	868.30	868.15 - 868.45	3.2	495-3692-1-ND NEW!	2.33	2.10	1.75	495-3692-2-ND NEW!	9,000	1086.00/M	B39871B3734H110
	869	868 - 870	2.4	495-2361-1-ND	2.33	2.10	1.75	495-2361-2-ND	9,000	1086.00/M	B39871B3715U410
	915	902 - 928	2.9	495-1674-1-ND	1.08	.98	.81	495-1674-2-ND	9,000	503.00/M	B39921B3588U410
	916	914.25 - 917.75	2.4	495-3690-1-ND NEW!	2.33	2.10	1.75	495-3690-2-ND NEW!	9,000	1086.00/M	B39921B3718U410
	1575.42	1574.22 - 1576.62	1.3	495-2363-1-ND	2.33	2.10	1.75	495-2363-2-ND	9,000	1086.00/M	B39162B3520U410
1575.42	1574.42 - 1576.42	3.2	495-3689-1-ND NEW!	2.33	2.10	1.75	495-3689-2-ND NEW!	9,000	1086.00/M	B39162B3521U410	
1575.42	1574.22 - 1576.62	3.3	495-3699-1-ND NEW!	2.33	2.10	1.75	495-3699-2-ND NEW!	9,000	1396.00/M	B39162B4050U510	
2	1575.42	1574.22 - 1576.62	1.3	495-2341-1-ND	2.33	2.10	1.75	495-2341-2-ND	9,000	1086.00/M	B39162B4060U810
3	303.8	303.62 - 303.98	3.0	495-2325-1-ND	3.62	3.26	2.72	---	---	---	B39301B3553U310
	311.06	310.94 - 311.18	2.0	495-2326-1-ND	3.62	3.26	2.72	495-2326-2-ND	3,000	1808.00/M	B39311B3577U310
	315	314.84 - 315.16	2.1	495-2329-1-ND	3.36	3.03	2.52	495-2329-2-ND	3,000	1679.00/M	B39321B3751U310
	315	314.9 - 315.1	3.3	495-2327-1-ND	3.87	3.49	2.91	495-2327-2-ND	3,000	1937.00/M	B39321B3576U310
	345.03	344.9 - 345.1	2.0	495-2330-1-ND	3.62	3.26	2.72	495-2330-2-ND	3,000	1808.00/M	B39351B3559U310
	433.42	433.31 - 433.53	3.3	495-2332-1-ND	2.34	2.11	1.76	495-2332-2-ND	3,000	1170.00/M	B39431B3567U310
	433.92	433.76 - 434.08	2.0	495-2335-1-ND	3.36	3.03	2.52	495-2335-2-ND	3,000	1679.00/M	B39431B3750U310
	433.92	433.83 - 434.01	3.4	495-2289-1-ND	2.34	2.11	1.76	495-2289-2-ND	3,000	1170.00/M	B39431B3575U310
	433.96	433.8 - 434.12	2.2	495-2359-1-ND	1.86	1.68	1.40	495-2359-2-ND	3,000	930.00/M	B39431B3555U310
	434.42	434.26 - 434.58	2.0	495-2336-1-ND	3.36	3.03	2.52	495-2336-2-ND	3,000	1679.00/M	B39431B3757U310
	868.3	868.2 - 868.4	4.2	495-2337-1-ND	2.34	2.11	1.76	495-2337-2-ND	3,000	1170.00/M	B39871B3574U310
	868.39	868 - 868.78	2.7	495-1961-1-ND	2.34	2.11	1.76	495-1961-2-ND	3,000	1170.00/M	B39871B3570U310
868.69	868 - 869.38	3.1	495-2338-1-ND	3.87	3.49	2.91	495-2338-2-ND	3,000	1937.00/M	B39871B3571U310	
869.69	869.2 - 870.18	2.8	495-2339-1-ND	3.87	3.49	2.91	495-2339-2-ND	3,000	1937.00/M	B39871B3573U310	
4	312.2	312.05 - 312.35	1.9	495-2355-1-ND	3.10	2.79	2.33	495-2355-2-ND	3,000	1550.00/M	B39311B3768Z810
	313.85	313.7 - 314	1.9	495-2356-1-ND	3.10	2.79	2.33	495-2356-2-ND	3,000	1550.00/M	B39311B3768Z810
	315	314.5 - 315.5	2.7	495-2328-1-ND	1.77	1.60	1.33	495-2328-2-ND	3,000	885.00/M	B39321B3581Z810
	315	314.85 - 315.15	1.9	495-1668-1-ND	3.10	2.79	2.33	495-1668-2-ND	3,000	1550.00/M	B39321B3761Z810
	315.15	315 - 315.3	1.9	495-2357-1-ND	3.10	2.79	2.33	495-2357-2-ND	3,000	1550.00/M	B39321B3763Z810
	315.5	315.35 - 315.65	1.9	495-2358-1-ND	3.10	2.79	2.33	495-2358-2-ND	3,000	1550.00/M	B39321B3765Z810
	345	344.6 - 345.4	2.5	495-2352-1-ND	3.10	2.79	2.33	495-2352-2-ND	3,000	1550.00/M	B39351B3583Z810
	433.92	433 - 434.71	2.8	495-2334-1-ND	1.77	1.60	1.33	495-2334-2-ND	3,000	885.00/M	B39431B3580Z810
	433.92	433.76 - 434.08	1.9	495-1672-1-ND	3.10	2.79	2.33	495-1672-2-ND	3,000	1550.00/M	B39431B3760Z810
	433.92	433.645 - 434.195	2.0	495-3694-1-ND	3.36	3.03	2.52	495-3694-2-ND NEW!	3,000	1679.00/M	B39431B3780Z810
	433.92	433.86 - 433.98	3.6	495-3695-1-ND NEW!	3.36	3.03	2.52	495-3695-2-ND NEW!	3,000	1679.00/M	B39431B3790Z810
	868.3	868 - 868.6	3.1	495-1673-1-ND	3.36	3.03	2.52	495-1673-2-ND	3,000	1679.00/M	B39871B3572Z810
914.7	913.9 - 915.5	4.0	495-2340-1-ND	3.10	2.79	2.33	495-2340-2-ND	3,000	1550.00/M	B39921B3705Z810	
5	942.5	925 - 960	1.4	495-1875-1-ND	1.56	1.41	1.17	495-1875-2-ND	9,000	780.00/M	B39941B7837K410
	1575.42	1574.42 - 1576.42	5	495-1880-1-ND	1.59	1.44	1.20	495-1880-2-ND	9,000	742.00/M	B39162B9000C710
	2140	2110.0 - 2170	2.6	495-1873-1-ND	1.83	1.65	1.38	495-1873-2-ND	9,000	854.00/M	B39212B7835C710
6	2140	2110.0 - 2170.0	2.4	495-2629-1-ND	1.62	1.46	1.22	495-2629-2-ND	9,000	756.00/M	B39212B7750C810
	1575.42	1574.22 - 1576.62	2.8	495-3696-1-ND NEW!	2.33	2.10	1.75	495-3696-2-ND NEW!	9,000	1086.00/M	B39162B4059U810

D

SAW Resonators - Surface Mount

Applications:

In remote control applications, SAW resonators provide stable frequencies for the RF carrier signal to transmit data over a range of 10-300m or for the local oscillators of superhet receivers.

Tighter tolerances are available upon request.




Fig.	No. of Ports	Frequency (MHz)	Digi-Key Part No.	Cut Tape Price Each			Digi-Key Part No.	Tape & Reel		Epcos Part No.
				1	10	100		Qty.	Pricing	
1	1	315	495-3698-1-ND NEW!	1.71	1.54	1.29	495-3698-2-ND NEW!	9,000	797.00/M	B39321R961H110
		433.92	495-2380-1-ND	1.50	1.36	1.13	495-2380-2-ND	9,000	701.00/M	B39431R900U410
		433.92	495-2382-1-ND	1.71	1.54	1.29	495-2382-2-ND	9,000	854.00/M	B39431R960H110
1	1	314.875; 315.125	495-2368-1-ND*	4.54	4.09	3.41	495-2368-2-ND*	3,000	2271.00/M	B39311R771U310
		433.81; 434.06	495-2377-1-ND*	4.54	4.09	3.41	495-2377-2-ND*	3,000	2271.00/M	B39431R770U310
		311.063	495-2344-1-ND	2.43	2.19	1.83	495-2344-2-ND	3,000	1215.00/M	B39311R2710U310
2	1	315	495-2346-1-ND	2.43	2.19	1.83	495-2346-2-ND	3,000	1215.00/M	B39321R2704U310
		418.05	495-2375-1-ND	2.43	2.19	1.83	495-2375-2-ND	3,000	1215.00/M	B39421R2702U310
		433.92	495-2349-1-ND	2.43	2.19	1.83	495-2349-2-ND	3,000	1215.00/M	B39431R2701U310
	2	804.5	495-2384-1-ND	2.43	2.19	1.83	495-2384-2-ND	3,000	1215.00/M	B39801R2712U310
		868.35	495-2385-1-ND	2.43	2.19	1.83	495-2385-2-ND	3,000	1215.00/M	B39871R2711U310
		915	495-1675-1-ND	1.77	1.60	1.33	---	---	---	B39921R2706U310
3	1	303.825	495-2365-1-ND	1.50	1.36	1.13	495-2365-2-ND	3,000	752.00/M	B39301R807H210
		304.3	495-2343-1-ND	2.22	2.01	1.67	495-2367-2-ND	3,000	1112.00/M	B39311R854H210
		314.5	495-2367-1-ND	2.22	2.01	1.67	495-2367-2-ND	3,000	1112.00/M	B39311R854H210
		315	495-1669-1-ND	.99	.90	.75	495-1669-2-ND	3,000	495.00/M	B39321R801H210
		315	495-2372-1-ND	.99	.90	.75	495-2372-2-ND	3,000	495.00/M	B39321R821H210
		315.02	495-2345-1-ND	2.22	2.01	1.67	495-2345-2-ND	3,000	1112.00/M	B39321R851H210
	433.42	495-2348-1-ND	.99	.90	.75	495-2348-2-ND	3,000	495.00/M	B39431R806H210	
	433.92	495-2378-1-ND	.99	.90	.75	495-2378-2-ND	3,000	495.00/M	B39431R820H210	
	433.92	495-2350-1-ND	.90	.81	.68	495-2350-2-ND	3,000	450.00/M	B39431R880H210	
	433.94	495-2379-1-ND	2.22	2.01	1.67	495-2379-2-ND	3,000	1112.00/M	B39431R850H210	
	868.35	495-3697-1-ND NEW!	4.54	4.09	3.41	495-3697-2-ND NEW!	3,000	2271.00/M	B39871R858H210	

* 2 resonators in 1 housing

Digi-Reel® Most SMT cutdown parts are available on a Digi-Reel®. For Digi-Reel part number, change 1-ND to 6-ND or CT-ND to DKR-ND. See Digi-Key® Services on page 2 for additional information.

More Product Available Online: www.digikey.com

Toll-Free: 1-800-344-4539 • Phone 218-681-6674 • Fax: 218-681-3380

(T083) 1397