

Fig. 1 — Aluminum Chassis

• Welded at stress points for assured, maximum strength and rigidity • Sides folded in at bottom for additional support • Bottom plate easily attached • Natural finish
NOTE: Bottom plate sold separately.

Fig. 2 — Plastiboxes — Style G

• ABS plastic • UL94-HB flammability rating • Suggested service temperature -40°C - 60°C

Fig. 3 — Plastiboxes — Style I

• ABS plastic material • UL94-5VA flammability rating

Fig. 4 — Hand-Held Grabber Enclosures — Style B

• ABS plastic in a light gray finish • UL94V-0 flammability rating

Fig. 5 — Hand-Held Grabber Enclosures — Style K

• ABS plastic with UL94V-0 flammability rating

Fig. 6 — Hand-Held Grabber Enclosures — Style L

• High impact resistant black ABS plastic with UL94V-0 flammability rating

Fig. 7 — Hand-Held Grabber Enclosures — Style M

• Impact resistant black ABS plastic with UL94V-0 flammability rating

Fig. 8 — Hand-Held Grabber Enclosures — Style N

• Impact resistant black ABS plastic with UL94V-0 flammability rating

Fig. 9 — Utility Cabinets

• Sturdy, all-welded body • Available in .040" aluminum or 20 gauge steel: "AU" prefix - aluminum alloy in natural finish; "CU" prefix - steel in metallic gray finish

Fig. 10 — ABS Plastic Utiliboxes

• Aluminum or plastic cover

Color	Dimensions - Inch (mm)			Digi-Key Part No.	Price Each			Bud Ind. Part No.
	A	B	C		1	10	50	
Fig. 1 — Chassis								
Natural	1.50 (38.1)	4.00 (100.4)	6.00 (152.4)	377-1000-ND	9.80	8.22	7.38	AC-1405
	2.00 (50.8)	6.00 (152.4)	8.00 (203.2)	377-1001-ND	12.50	10.40	9.35	AC-1413
	2.50 (63.5)	8.00 (203.2)	10.00 (254)	377-1002-ND	20.20	16.89	15.21	AC-1418
	2.50 (63.5)	8.00 (203.2)	12.00 (304.8)	377-1003-ND	25.00	20.86	18.75	AC-1419
	5.00 (127)	10.00 (254)	17.00 (431.8)	377-1004-ND	57.40	47.91	43.13	AC-1422
	5.00 (127)	13.00 (330.2)	17.00 (431.8)	377-1005-ND	66.20	55.28	49.76	AC-1426
	3.00 (76.2)	14.00 (355.6)	17.00 (431.8)	377-1006-ND	48.20	40.22	36.18	AC-1427
	4.00 (101.6)	15.00 (381)	17.00 (431.8)	377-1007-ND	65.40	54.59	49.13	AC-1428
	6.00 (152.4)	15.00 (381)	17.00 (431.8)	377-1008-ND	92.60	77.33	69.61	AC-1429
	3.00 (76.2)	17.00 (431.8)	17.00 (431.8)	377-1009-ND	56.10	46.86	42.19	AC-1430
	4.00 (101.6)	17.00 (431.8)	17.00 (431.8)	377-1010-ND	65.70	54.89	49.38	AC-1431
	2.00 (50.8)	5.00 (127)	7.00 (177.8)	377-1011-ND	10.90	9.07	8.18	AC-402
	2.00 (50.8)	5.00 (127)	9.50 (241.3)	377-1012-ND	13.20	10.95	9.85	AC-403
	3.00 (76.2)	5.00 (127)	10.00 (254)	377-1013-ND	16.80	14.02	12.60	AC-404
	2.00 (50.8)	7.00 (177.8)	7.00 (177.8)	377-1014-ND	11.40	9.42	8.48	AC-405
	2.00 (50.8)	7.00 (177.8)	9.00 (228.6)	377-1015-ND	13.80	11.49	10.33	AC-406
	2.00 (50.8)	7.00 (177.8)	11.00 (279.4)	377-1016-ND	16.00	13.32	12.00	AC-407
	3.00 (76.2)	7.00 (177.8)	12.00 (304.8)	377-1017-ND	21.20	17.69	15.90	AC-408
	2.00 (50.8)	7.00 (177.8)	13.00 (330.2)	377-1018-ND	17.40	14.57	13.11	AC-409
	3.00 (76.2)	7.00 (177.8)	15.00 (381)	377-1019-ND	27.60	23.04	20.73	AC-411
	3.00 (76.2)	8.00 (203.2)	17.00 (431.8)	377-1020-ND	28.70	24.03	21.61	AC-412
	3.00 (76.2)	10.00 (254)	12.00 (304.8)	377-1021-ND	32.20	26.96	24.29	AC-413
	3.00 (76.2)	10.00 (254)	14.00 (355.6)	377-1022-ND	32.80	27.50	24.76	AC-414
	2.00 (50.8)	10.00 (254)	17.00 (431.8)	377-1023-ND	29.20	24.43	22.01	AC-415
3.00 (76.2)	10.00 (254)	17.00 (431.8)	377-1024-ND	34.20	28.54	25.71	AC-416	
3.00 (76.2)	12.00 (304.8)	17.00 (431.8)	377-1025-ND	36.10	30.07	27.08	AC-418	
2.00 (50.8)	13.00 (330.2)	17.00 (431.8)	377-1026-ND	37.00	30.86	27.75	AC-419	
3.00 (76.2)	13.00 (330.2)	17.00 (431.8)	377-1027-ND	42.60	35.57	32.01	AC-420	
3.00 (76.2)	5.00 (127)	9.50 (241.3)	377-1028-ND	16.70	13.92	12.56	AC-421	
3.00 (76.2)	8.00 (203.2)	12.00 (304.8)	377-1029-ND	25.40	21.21	19.11	AC-424	
4.00 (101.6)	10.00 (254)	17.00 (431.8)	377-1030-ND	49.20	41.13	37.04	AC-427	
4.00 (101.6)	13.00 (330.2)	17.00 (431.8)	377-1031-ND	51.90	43.29	38.98	AC-428	
3.00 (76.2)	5.00 (127)	7.00 (177.8)	377-1032-ND	14.00	11.69	10.53	AC-429	
3.00 (76.2)	4.00 (101.6)	6.00 (152.4)	377-1033-ND	12.45	10.30	9.25	AC-430	
2.00 (50.8)	4.00 (101.6)	6.00 (152.4)	377-1034-ND	10.10	8.47	7.63	AC-431	

Color	Dimensions - Inch (mm)			Digi-Key Part No.	Price Each			Bud Ind. Part No.	
	A	B	C		1	10	50		
Fig. 2 — Plastiboxes — Style G									
Gray	1.50 (38.10)	2.25 (57.15)	3.62 (91.95)	377-1161-ND	6.70	5.59	5.00	PT-11308-G	
	1.50 (38.10)	3.25 (82.55)	5.62 (142.75)	377-1157-ND	12.20	10.19	9.00	PBS-11327-G	
	2.48 (62.99)	3.25 (82.55)	5.62 (142.75)	377-1162-ND	11.30	9.46	8.50	PT-11388-G	
	1.52 (38.61)	3.25 (82.55)	4.37 (111)	377-1158-ND	5.20	4.34	3.90	PBS-11532-G	
	1.52 (38.61)	3.25 (82.55)	5.62 (142.75)	377-1159-ND	5.50	4.60	4.20	PS-11543-G	
	2.52 (64.01)	4.87 (123.70)	6.87 (174.50)	377-1160-ND	6.80	5.65	5.10	PS-11553-G	
			377-1163-ND	7.20	6.00	5.50	PT-11557-G		
Fig. 3 — Plastiboxes — Style I									
Black	7.50 (190.50)	5.00 (127.00)	1.75 (44.45)	377-1572-ND	12.10	10.10	9.00	PT-11785-MP	
Fig. 4 — Hand-Held Grabber Enclosures — Style B									
Gray	1.71 (43.43)	5.16 (131.06)	9.33 (236.98)	377-1170-ND	19.00	15.85	14.50	HH-3420	
Fig. 5 — Hand-Held Grabber Enclosures — Style K									
Black	4.63 (117.60)	2.85 (72.39)	1.00 (25.40)	377-1550-ND	9.80	8.20	7.50	HH-3524	
	5.50 (139.70)	3.25 (82.55)	1.00 (25.40)	377-1551-ND	11.00	9.20	8.50	HH-3535	
Fig. 6 — Hand-Held Grabber Enclosures — Style L									
Black	5.71 (145.03)	3.54 (89.92)	1.26 (32.00)	377-1552-ND	7.10	5.90	5.40	HH-3580-B	
				377-1553-ND†	8.20	6.85	6.30	HH-3580-BCB	
Fig. 7 — Hand-Held Grabber Enclosures — Style M									
Black	3.26 (82.80)	5.98 (151.89)	1.31 (33.27)	377-1554-ND	7.40	6.20	5.70	HH-3600-B	
Fig. 8 — Hand-Held Grabber Enclosures — Style N									
Black	6.69 (169.93)	5.16 (131.06)	1.38 (35.05)	377-1555-ND	8.10	6.75	6.20	HH-3610-B	
				377-1556-ND†	9.20	7.70	7.10	HH-3610-BCB	
Accessories for Hand-Held Grabber Enclosures									
Tilt Stand for HH-3420				377-1171-ND	9.00	7.50	6.80	HH-3440-TS	
Gasket for HH-3420				377-1172-ND	1.00	0.85	0.75	HH-3441-G	
Fig. 9 — Utility Cabinets									
Natural	5.00 (127)	6.00 (152.40)	4.00 (101.60)	377-1056-ND	14.10	11.75	10.75	AU-1029	
	6.00 (152.40)	6.00 (152.40)	6.00 (152.40)	377-1057-ND	20.60	17.20	15.75	AU-1039	
	9.00 (228.60)	6.00 (152.40)	5.00 (127)	377-1058-ND	22.40	18.70	17.25	AU-1040	
Metallic Gray	6.00 (152.40)	6.00 (152.40)	6.00 (152.40)	377-1059-ND	33.00	27.50	25.00	CU-1098	
	9.00 (228.60)	6.00 (152.40)	5.00 (127)	377-1060-ND	37.30	31.10	28.75	CU-1099	
	12.00 (304.80)	7.00 (177.80)	6.00 (152.40)	377-1061-ND	58.50	48.85	45.00	CU-1124	
	4.00 (101.60)	5.00 (127)	3.00 (76.20)	377-1062-ND	18.20	15.25	14.00	CU-728	
	5.00 (127)	6.00 (152.40)	4.00 (101.60)	377-1063-ND	22.40	18.65	17.25	CU-729	
	10.00 (254)	8.00 (203.20)	7.00 (177.80)	377-1064-ND	56.40	47.10	43.75	CU-879	
	15.00 (381)	9.00 (228.60)	7.00 (177.80)	377-1065-ND	80.10	66.95	61.50	CU-882	
	Fig. 10 — ABS Plastic Utiliboxes								
	Black	5.30 (134.62)	2.94 (74.68)	1.95 (49.53)	377-1165-ND	3.00	2.50	2.25	CU-1874-B
	Gray	5.30 (134.62)	2.94 (74.68)	1.95 (49.53)	377-1166-ND	3.00	2.50	2.25	CU-1874-G
Black	4.10 (104.14)	2.23 (57.40)	2.00 (50.80)	377-1167-ND	4.30	3.57	3.25	CU-793	
	5.59 (141.99)	4.34 (110.27)	1.84 (46.77)	377-1168-ND	7.20	6.00	5.50	CU-387	
	4.31 (109.47)	3.06 (77.72)	1.46 (37.08)	377-1169-ND	5.80	4.85	4.50	CU-388	
	4.60 (116.84)	3.10 (78.74)	1.87 (47.50)	377-1216-ND	7.20	6.00	5.50	CU-3281	
	4.60 (116.84)	4.60 (116.84)	2.37 (60.20)	377-1217-ND	8.00	6.69	6.10	CU-3282	
	6.10 (154.94)	4.60 (116.84)	2.37 (60.20)	377-1218-ND	9.20	7.70	7.10	CU-3283	
	7.60 (193.04)	4.60 (116.84)	2.37 (60.20)	377-1219-ND	11.10	9.27	8.50	CU-3284	
	5.07 (128.78)	3.57 (90.68)	1.59 (40.39)	377-1220-ND	6.70	5.60	5.10	CU-389	
	6.10 (154.94)	4.60 (116.84)	1.37 (34.80)	377-1536-ND	10.00	8.35	7.75	CU-3287	
	6.10 (154.94)	4.60 (116.84)	1.37 (34.80)	377-1537-ND	10.00	8.35	7.75	CU-3287-MB	
	6.10 (154.94)	4.60 (116.84)	1.37 (34.80)	377-1538-ND	10.00	8.35	7.75	CUR-3287	
	6.10 (154.94)	4.60 (116.84)	1.37 (34.80)	377-1539-ND	10.70	8.90	8.20	CUR-3287-C	
	6.10 (154.94)	4.60 (116.84)	1.37 (34.80)	377-1540-ND	10.70	8.94	8.20	CUR-3287-MB	
	6.10 (154.94)	4.60 (116.84)	1.37 (34.80)	377-1541-ND	10.00	8.32	7.75	CUR-3287-CMB	

† With Battery Compartment

(Continued)

Chassis Bottom Plates

Color	Dimensions - Inch (mm)		Digi-Key Part No.	Price Each			Bud Ind. Part No.
	Fits Width	Chassis Length		1	10	100	
Natural	4.00 (101.60)	6.00 (152.40)	377-1035-ND	5.00	4.17	3.75	BPA-1505
	6.00 (152.40)	8.00 (203.20)	377-1036-ND	7.10	5.85	5.28	BPA-1513
	8.00 (203.20)	10.00 (254)	377-1037-ND	8.80	7.34	6.60	BPA-1518
	8.00 (203.20)	12.00 (304.80)	377-1038-ND	10.70	8.97	8.08	BPA-1519
	8.00 (203.20)	17.00 (431.80)	377-1039-ND	11.00	9.22	8.28	BPA-1520
	10.00 (254)	12.00 (304.80)	377-1040-ND	10.70	8.97	8.08	BPA-1523
	10.00 (254)	14.00 (355.60)	377-1041-ND	10.70	8.97	8.08	BPA-1524
	12.00 (304.80)	17.00 (431.80)	377-1042-ND	15.30	12.79	11.53	BPA-1528
	14.00 (355.60)	17.00 (431.80)	377-1043-ND	16.20	13.52	12.15	BPA-1529
	15.00 (381)	17.00 (431.80)	377-1044-ND	20.30	16.94	15.26	BPA-1530
	17.00 (431.80)	17.00 (431.80)	377-1045-ND	24.70	20.61	18.56	BPA-1531
	5.00 (127)	7.00 (177.80)	377-1046-ND	4.90	4.07	3.65	BPA-1589
	5.00 (127)	9.50 (241.30)	377-1047-ND	5.00	4.17	3.75	BPA-