



| Description | Dimensions Width x Length | Digi-Key Part No. | Price Each | | 3M Part No. |
|--|---------------------------|-----------------------|------------|--------|----------------------|
| | | | 1 | 5 | |
| 3M Laminating Adhesives | | | | | |
| Adhesive Transfer Tape, 100MP Adhesive, Clear, .005", Dual-lined for Prototyping | 8.5" x 8.5" | 3M6446-ND | 8.13 | 6.50 | F9469PC |
| Adhesive Transfer Tape, 200MP Adhesive, Clear, .005", Dual-lined for Prototyping | 8.5" x 8.5" | 3M6447-ND | 6.63 | 5.30 | 468MP |
| Double Coated Tape, 200MP Adhesive, Clear, .0057", Dual-lined for Prototyping | 8.5" x 8.5" | 3M6448-ND | 7.50 | 6.00 | 9495MP |
| Double Coated Tape, 300LSE Adhesive, Clear, .0067", Dual-lined for Prototyping | 8.5" x 8.5" | 3M6449-ND | 7.75 | 6.20 | 9495LE |
| Double Coated Tape, 300MP Adhesive, Tan, .0055", Dual-lined for Prototyping | 8.5" x 8.5" | 3M6450-ND | 6.25 | 5.00 | 9786 |
| Double Coated Tape, 300MP Adhesive, Clear, .0067", Dual-lined for Prototyping | 8.5" x 8.5" | 3M6451-ND | 7.00 | 5.60 | 9490LE |
| Aluminum Foil Tape | | | | | |
| Aluminum Foil Tape, 2.8-mil, Acrylic Adhesive, Thermally Conductive, Heat & Light Reflective | 1" x 60 yds. | 3M5613-ND | 20.93 | 17.94 | 425-1"X60YD-BULK |
| Aluminum Foil Tape, 2.8-mil, Acrylic Adhesive, Thermally Conductive, Heat & Light Reflective | 3" x 60 yds. | 3M5614-ND | 62.81 | 53.84 | 425-3"X60YD-BULK |
| Aluminum Foil Tape, 2.8-mil, Acrylic Adhesive, Thermally Conductive, Heat & Light Reflective | 2" x 60 yds. | 3M5615-ND | 63.77 | 54.66 | 427-2"X60YD |
| Aluminum Foil Tape, 2.0-mil, Silicone Adhesive, Thermally Conductive, Heat & Light Reflective | 1" x 60 yds. | 3M5617-ND | 63.16 | 54.14 | 433-1"X60YD |
| Aluminum Foil Tape, 2.0-mil, Silicone Adhesive, Thermally Conductive, Heat & Light Reflective | 2" x 60 yds. | 3M5616-ND | 126.32 | 108.27 | 433-2"X60YD |
| Aluminum Foil Tape, 2.0-mil, Silicone Adhesive, Thermally Conductive, Heat & Light Reflective, Lined | 1" x 60 yds. | 3M5632-ND | 75.08 | 64.35 | 433L-1"X60YD |
| Aluminum Foil Tape, 2.0-mil, Silicone Adhesive, Thermally Conductive, Heat & Light Reflective, Lined | 1" x 60 yds. | 3M5631-ND | 167.24 | 143.36 | 433L-2"X60YD |
| Aluminum Foil Tape, 5.0-mil, Acrylic Adhesive, Thermally Conductive, Heat and Light Reflective | 2" x 60 yds. | 3M5633-ND | 76.16 | 65.28 | 438 |
| Double Coated Foam Tape | | | | | |
| Attachment Tape, .045", Acrylic Plus Adhesive, High Performance, Black, Automotive Grade | 1/4" x 20 yds. | 3M6411-ND† | 17.83 | — | 06386 |
| Attachment Tape, .045", Acrylic Plus Adhesive, High Performance, Black, Automotive Grade | 1/2" x 5 yds. | 3M6410-ND | 9.92 | — | 06384 |
| Attachment Tape, .045", Acrylic Plus Adhesive, High Performance, Black, Automotive Grade | 1/2" x 20 yds. | 3M6408-ND | 31.13 | — | 06382 |
| Attachment Tape, .045", Acrylic Plus Adhesive, High Performance, Black, Automotive Grade | 7/8" x 20 yds. | 3M6409-ND | 47.29 | — | 06383 |
| Attachment Tape, .060", Acrylic Plus Adhesive, High Performance, Black, Automotive Grade | 7/8" x 10 yds. | 3M6412-ND | 34.53 | — | 06395 |
| Attachment Tape, .090", Acrylic Plus Adhesive, High Performance, Gray, Automotive Grade | 1/2" x 10 yds. | 3M6413-ND | 22.84 | — | 06394 |
| Double Coated Foam Tape, .125", Pressure Sensitive Acrylic Adhesive, Off-White Urethane Foam | 1" x 36 yds. | 3M4008-ND | 57.57 | — | 4008 1" |
| Double Coated Foam Tape, .062", Pressure Sensitive Acrylic Adhesive, Off-White Urethane Foam | 1" x 36 yds. | 3M40161-ND | 38.74 | — | 4016 1" |
| Double Coated Foam Tape, .062", Pressure Sensitive Acrylic Adhesive, Neutral Urethane Foam | 1" x 36 yds. | 3M4026-ND | 33.29 | — | 4026 1" |
| Double Coated Foam Tape, .125", Pressure Sensitive Acrylic Adhesive, Black Vinyl Foam | 1" x 36 yds. | 3M44081-ND | 79.94 | — | 4408 1" |
| Double Coated Foam Tape, .062", Pressure Sensitive Acrylic Adhesive, Black Vinyl Foam | 1" x 36 yds. | 3M44161B-ND | 57.80 | — | 4416 1" BLACK |
| Double Coated Foam Tape, .062", Pressure Sensitive Acrylic Adhesive, White Vinyl Foam | 1" x 36 yds. | 3M44161W-ND | 57.80 | — | 4416 1" WHITE |
| Double Coated Foam Tape, .045", Pressure Sensitive VHB™ Acrylic Adhesive, Dark Gray | 1/2" x 36 yds. | 3M6462-ND NEW! | 30.00 | 25.71 | 4611 1/2 IN X 36 YD |
| Double Coated Foam Tape, .020", Pressure Sensitive VHB Acrylic Adhesive, Clear | 1" x 72 yds. | 3M6463-ND NEW! | 132.48 | 113.55 | 4905-1"X72YD |
| Double Coated Foam Tape, .020", Pressure Sensitive VHB Acrylic Adhesive, Clear | 1/2" x 72 yds. | 3M6464-ND NEW! | 70.95 | 60.81 | 4905-1/2"X72YD |
| Double Coated Foam Tape, .020", Pressure Sensitive VHB Acrylic Adhesive, Clear | 3/4" x 72 yds. | 3M6465-ND NEW! | 94.61 | 81.09 | 4905-3/4"X72YD |
| Double Coated Foam Tape, .040", Pressure Sensitive VHB Acrylic Adhesive, Clear (small pack) | 1/2" x 36 yds. | 3M6466-ND NEW! | 41.91 | 35.93 | 4910-1/2"X36YD |
| Double Coated Foam Tape, .040", Pressure Sensitive VHB Acrylic Adhesive, Clear | 1/2" x 36 yds. | 3M6467-ND NEW! | 37.42 | 32.07 | 4910-CLEAR-1/2"X36YD |
| Double Coated Foam Tape, .040", Pressure Sensitive VHB Acrylic Adhesive, Clear | 3/4" x 15 yds. | 3M5648-ND | 30.59 | 26.22 | 4910 3/4"X15YD |
| Double Coated Foam Tape, .040", Pressure Sensitive VHB Acrylic Adhesive, Clear | 1" x 36 yds. | 3M5650-ND | 62.37 | 53.46 | 4910-CLEAR-1"X36YD |
| Double Coated Foam Tape, .045", Pressure Sensitive VHB Acrylic Adhesive, White Acrylic Foam | 1/2" x 36 yds. | 3M5625-ND | 56.19 | 48.17 | 4950-1/2"X36YD-SMPK |
| Double Coated Foam Tape, .045", Pressure Sensitive VHB Acrylic Adhesive, White Acrylic Foam | 3/4" x 36 yds. | 3M5626-ND | 74.95 | 64.25 | 4950-3/4"X36YD-SMPK |
| Double Coated Foam Tape, .045", Pressure Sensitive VHB Acrylic Adhesive, White Acrylic Foam | 1" x 36 yds. | 3M5627-ND | 93.64 | 80.27 | 4950-1"X36YD-SMPK |
| Double Coated Foam Tape, .045", Pressure Sensitive VHB Modified Acrylic Adhesive, Black | 1/2" x 36 yds. | 3M5648-ND NEW! | 30.59 | 26.22 | 5952-1/2"X36YD |
| Double Coated Foam Tape, .045", Pressure Sensitive VHB Modified Acrylic Adhesive, Black | 3/4" x 15 yds. | 3M5647-ND | 30.59 | 26.22 | 5952 3/4"X15YD |
| Double Coated Foam Tape, .045", Pressure Sensitive VHB Modified Acrylic Adhesive, Black | 1" x 36 yds. | 3M5649-ND | 78.79 | 67.53 | 5952 1"X36YD |
| Duct Tape | | | | | |
| Duct Tape Clean Remove, 12.6-mil, Slate Blue Polyethylene Film, Synthetic Rubber Adhesive | 1.88" x 60 yds. | 3M5630-ND | 12.57 | 10.77 | 8979-BLUE-48MMX54.8M |
| Duct Tape Industrial Grade, 10.7-mil, Black Polyethylene Film, Rubber Adhesive | 1.88" x 60 yds. | 3M69692B-ND | 11.52 | — | 6969 2" BLACK |
| Duct Tape Industrial Grade, 10.7-mil, Silver Polyethylene Film, Rubber Adhesive | 1.88" x 60 yds. | 3M69692S-ND | 11.52 | — | 6969 2" SILVER |
| Electrical Tape - Black | | | | | |
| Vinyl Mastic Pad, All-Weather Grade, 125-mil, Black Vinyl Film, Rubber Mastic | 3-1/4" x 4-1/2" | 3M11008-ND | 4.00 | — | 2200 (3-1/4"X4-1/2") |
| Electrical Tape, General Purpose, 7-mil, Black PVC, Flame-Retardant | 3/4" x 66' | 3M1700-ND | 1.16 | — | 1700 TEMFLEX |
| Electrical Tape, Premium Grade, All-Weather, 7-mil, Black PVC, Pressure-Sensitive Adhesive | 3/4" x 66' | 3M33+A-ND | 5.82 | — | 33+ SUPER (3/4"X66') |
| Electrical Tape, Premium Grade, All-Weather, 8.5-mil, Black PVC, Pressure-Sensitive Adhesive | 3/4" x 66' | 3M88A-ND | 6.54 | — | 88 SUPER (3/4"X66') |
| Electrical Color Coding Tape - Colored | | | | | |
| Electrical Color Coding Tape, Red PVC, 7-mil, Pressure-Sensitive Adhesive | 3/4" x 66' | 3M35-RD-ND | 5.40 | — | 35 RED (3/4"X66') |
| Electrical Color Coding Tape, Orange PVC, 7-mil, Pressure-Sensitive Adhesive | 3/4" x 66' | 3M35-OR-ND | 5.40 | — | 35 ORANGE (3/4"X66') |
| Electrical Color Coding Tape, Yellow PVC, 7-mil, Pressure-Sensitive Adhesive | 3/4" x 66' | 3M35-YL-ND | 5.40 | — | 35 YELLOW (3/4"X66') |
| Electrical Color Coding Tape, Green PVC, 7-mil, Pressure-Sensitive Adhesive | 3/4" x 66' | 3M35-GN-ND | 5.40 | — | 35 GREEN (3/4"X66') |
| Electrical Color Coding Tape, Blue PVC, 7-mil, Pressure-Sensitive Adhesive | 3/4" x 66' | 3M35-BL-ND | 5.40 | — | 35 BLUE (3/4"X66') |
| Electrical Color Coding Tape, Violet PVC, 7-mil, Pressure-Sensitive Adhesive | 3/4" x 66' | 3M35-VL-ND | 5.40 | — | 35 VIOLET (3/4"X66') |
| Electrical Color Coding Tape, Gray PVC, 7-mil, Pressure-Sensitive Adhesive | 3/4" x 66' | 3M35-GY-ND | 5.40 | — | 35 GRAY (3/4"X66') |
| Electrical Color Coding Tape, White PVC, 7-mil, Pressure-Sensitive Adhesive | 3/4" x 66' | 3M35-WH-ND | 5.40 | — | 35 WHITE (3/4"X66') |
| Glass and Aluminum/Glass Cloth Tape | | | | | |
| Glass Cloth Tape, White, 5.4-mil, Silicone Adhesive, High Tensil Strength, General Purpose | 1" x 60 yds. | 3M5609-ND | 60.83 | 52.14 | 361-1"X60YD |
| Glass Cloth Tape, White, 5.4-mil, Silicone Adhesive, High Tensil Strength, General Purpose | 2" x 60 yds. | 3M5610-ND | 121.68 | 104.30 | 361-2"X60YD |
| Aluminum/Glass Cloth Tape, 7.3-mil, Silicone Adhesive, Flame/Tear/Puncture-Resistant | 1" x 36 yds. | 3M5611-ND | 99.30 | 85.11 | 363-1"X36YD |
| Aluminum/Glass Cloth Tape, 7.3-mil, Silicone Adhesive, Flame/Tear/Puncture-Resistant | 2" x 36 yds. | 3M5612-ND | 198.59 | 170.22 | 363-2"X36YD |
| High Temperature Tape | | | | | |
| High Temperature Kapton Tape, 2.7-mil, Amber KAPTON Polyimide Film, Silicone Adhesive | 1/2" x 36 yds. | 3M541312-ND | 25.84 | — | 5413 1/2" |
| High Temperature Kapton Tape, 2.7-mil, Amber KAPTON Polyimide Film, Silicone Adhesive | 3/4" x 36 yds. | 3M541334-ND | 38.77 | — | 5413 3/4" |
| Wave Solder Tape, Low Static, 2.7-mil, Amber Polyimide Film, Silicone Adhesive | 1/2" x 36 yds. | 3M591912-ND | 27.84 | — | 5419 1/2" |
| Wave Solder Tape, Low Static, 2.7-mil, Amber Polyimide Film, Silicone Adhesive | 3/4" x 36 yds. | 3M591934-ND | 39.77 | — | 5419 3/4" |
| Wave Solder Tape, Water-Soluble, PVA Film Backing, Water-soluble Synthetic Adhesive | 1/2" x 36 yds. | 3M541412-ND | 26.31 | — | 5414 1/2" |
| Wave Solder Tape, Water-Soluble, PVA Film Backing, Water-soluble Synthetic Adhesive | 3/4" x 36 yds. | 3M541434-ND | 41.43 | — | 5414 3/4" |

† Recommended for wheel flares or other less demanding applications due to a narrower width.

(Continued)

More Product Available Online: www.digikey.com

Toll-Free: 1-800-344-4539 • Phone 218-681-6674 • Fax: 218-681-3380

(T083) 2213

