



Fig.	Min. Loop Tensile Strength (Lbs)	Length Inch (mm)	Width Inch (mm)	Max. Bundle Diameter Inch (mm)	Digi-Key Part No.	Pkg. Qty.	Price/Pkg.	Panduit Part No.
PAN-TY® Clamp Tie With Mounting Hole - Nylon — RoHS Compliant								
1	18	4.3 (109.2)	0.100 (2.5)	0.75 (19.1)	298-1000-ND	100	34.03	PLC1M-S4-C
	40	6.1 (154.9)	0.135 (3.4)	1.25 (31.8)	298-1001-ND	100	34.21	PLC1.5I-S8-C
	50	7.9 (200.7)	0.190 (4.8)	1.84 (46.7)	298-1002-ND	100	36.20	PLC2S-S10-C
	50	12.0 (304.8)	0.190 (4.8)	3.00 (76.2)	298-1003-ND	100	83.59	PLC3S-S10-C
	50	15.0 (381.0)	0.190 (4.8)	4.00 (101.6)	298-1004-ND	100	94.50	PLC4S-S10-C
PAN-TY Clamp Tie With Mounting Hole - Weather Resistant - Black — RoHS Compliant								
1	18	4.3 (109.2)	0.100 (2.5)	0.75 (19.1)	298-1005-ND	100	60.61	PLC1M-S4-C0
	40	6.1 (154.9)	0.135 (3.4)	1.25 (31.8)	298-1006-ND	100	43.67	PLC1.5I-S8-C0
	50	7.9 (200.7)	0.190 (4.8)	1.84 (46.7)	298-1007-ND	100	45.46	PLC2S-S10-C0
	50	12.0 (304.8)	0.190 (4.8)	3.00 (76.2)	298-1008-ND	100	96.91	PLC3S-S10-C0
	50	15.0 (381.0)	0.190 (4.8)	4.00 (101.6)	298-1009-ND	100	109.28	PLC4S-S10-C0
PAN-TY Locking Clamp Tie - Nylon — RoHS Compliant								
1	50	7.9 (200.7)	.190 (4.8)	1.84 (47)	298-9973-ND	100	45.46	PLC2S-S6-C0
PAN-TY Cable Tie - Nylon — RoHS Compliant								
1	12	2.8 (71.1)	0.070 (1.8)	0.60 (15.2)	298-1016-ND	100	13.64	PLT6SM-C
	12	2.8 (71.1)	0.070 (1.8)	0.60 (15.2)	298-1017-ND	1,000	28.38	PLT6SM-M
	18	3.1 (78.7)	0.090 (2.3)	0.68 (17.3)	298-1018-ND	100	14.27	PLT7M-C
	18	3.1 (78.7)	0.090 (2.3)	0.68 (17.3)	298-1019-ND	1,000	26.99	PLT7M-M
	18	3.9 (99.1)	0.098 (2.5)	0.87 (22.1)	298-1020-ND	100	15.35	PLT1M-C
	18	3.9 (99.1)	0.098 (2.5)	0.87 (22.1)	298-1021-ND	1,000	30.83	PLT1M-M
	40	5.6 (142.2)	0.142 (3.6)	1.38 (35.1)	298-1022-ND	100	17.78	PLT1.5I-C
	40	5.6 (142.2)	0.142 (3.6)	1.38 (35.1)	298-1023-ND	1,000	47.57	PLT1.5I-M
	18	5.6 (142.2)	0.098 (2.5)	1.25 (31.8)	298-1024-ND	100	19.99	PLT1.5M-C
	18	5.6 (142.2)	0.098 (2.5)	1.25 (31.8)	298-1025-ND	1,000	46.55	PLT1.5M-M
	50	7.4 (188.0)	0.190 (4.8)	1.88 (47.8)	298-1030-ND	100	22.67	PLT2S-C
	50	7.4 (188.0)	0.190 (4.8)	1.88 (47.8)	298-1031-ND	1,000	65.06	PLT2S-M
	40	8.0 (203.2)	0.142 (3.6)	2.00 (50.8)	298-1026-ND	100	27.05	PLT2I-C
	40	8.0 (203.2)	0.142 (3.6)	2.00 (50.8)	298-1027-ND	1,000	61.85	PLT2I-M
	18	8.0 (203.2)	0.098 (2.5)	2.00 (50.8)	298-1028-ND	100	21.37	PLT2M-C
	18	8.0 (203.2)	0.098 (2.5)	2.00 (50.8)	298-1029-ND	1,000	47.25	PLT2M-M
	40	11.4 (289.6)	0.145 (3.7)	3.00 (76.2)	298-1032-ND	100	33.03	PLT3I-C
	50	11.5 (292.1)	0.190 (4.8)	3.00 (76.2)	298-1033-ND	100	45.33	PLT3S-C
	50	11.5 (292.1)	0.190 (4.8)	3.00 (76.2)	298-1034-ND	1,000	169.31	PLT3S-M
	50	14.5 (368.3)	0.190 (4.8)	4.00 (101.6)	298-1035-ND	100	51.60	PLT4S-C
	50	14.5 (368.3)	0.190 (4.8)	4.00 (101.6)	298-1036-ND	1,000	189.20	PLT4S-M
	50	17.5 (445.0)	0.190 (4.8)	5.00 (127.0)	298-1360-ND	100	77.42	PLT5S-C
	50	17.5 (445.0)	0.190 (4.8)	5.00 (127.0)	298-1361-ND	1,000	267.69	PLT5S-M
	120	21.9 (556.0)	0.300 (7.6)	6.00 (152.0)	298-1366-ND	100	76.68	PLT6LH-L
120	21.9 (556.0)	0.300 (7.6)	6.00 (152.0)	298-1367-ND	100	59.69	PLT6LH-C	
120	24.7 (627.0)	0.300 (7.6)	7.00 (178.0)	298-1368-ND	50	65.15	PLT7LH-L	
120	24.7 (627.0)	0.300 (7.6)	7.00 (178.0)	298-1369-ND	50	50.94	PLT7LH-C	
120	27.6 (701.0)	0.300 (7.6)	8.00 (203.0)	298-1373-ND	100	124.40	PLT8LH-C	
PAN-TY Cable Tie High Temperature - Poly — RoHS Compliant								
1	150	7.4 (188)	.190 (4.8)	1.88 (48)	298-9956-ND	1,000	1103.70	PLT2S-M71
CONTOUR-TY™ Cable Tie - Nylon — RoHS Compliant								
2	18	4.1 (104)	0.100 (2.5)	1.00 (25.4)	298-9908-ND	1,000	35.46	CBR1M-M
	40	5.9 (150)	0.140 (3.6)	1.50 (38.1)	298-9904-ND	1,000	54.74	CBR1.5I-M
	18	7.2 (183)	0.100 (2.5)	2.00 (50.8)	298-9912-ND	1,000	54.38	CBR2M-M
	50	7.6 (193)	0.190 (4.8)	2.00 (50.8)	298-9914-ND	1,000	74.78	CBR2S-M

Fig.	Min. Loop Tensile Strength (Lbs)	Length Inch (mm)	Width Inch (mm)	Max. Bundle Diameter Inch (mm)	Digi-Key Part No.	Pkg. Qty.	Price/Pkg.	Panduit Part No.
2	85	8.0 (203)	0.250 (6.4)	2.00 (50.8)	298-9910-ND	500	147.34	CBR2HS-D
	40	10.4 (264)	0.140 (3.6)	3.00 (76.2)	298-9916-ND	1,000	149.88	CBR3I-M
	50	10.8 (274)	0.190 (4.8)	3.00 (76.2)	298-9918-ND	1,000	194.81	CBR3S-M
	120	14.6 (371)	0.300 (7.6)	4.00 (101.6)	298-9922-ND	250	151.94	CBR4LH-TL
	120	20.9 (531)	0.300 (7.6)	6.00 (152.4)	298-9926-ND	100	97.59	CBR6LH-C
Double Hose Clamp - Nylon — RoHS Compliant								
3	100	11.0 (279)	.280 (7.1)	1.12 (28.4)†	298-9962-ND	50	64.86	DHC1.12X1.75-D0
CONTOUR-TY Cable Tie - Weather Resistant - Black — RoHS Compliant								
2	18	4.1 (104)	0.100 (2.5)	1.00 (25.4)	298-9909-ND	1,000	55.55	CBR1M-M0
	18	5.6 (142)	0.100 (2.5)	1.50 (38.1)	298-9907-ND	1,000	76.91	CBR1.5M-M0
	40	5.9 (150)	0.140 (3.6)	1.50 (38.1)	298-9905-ND	1,000	73.94	CBR1.5I-M0
	18	7.2 (183)	0.100 (2.5)	2.00 (50.8)	298-9913-ND	1,000	80.34	CBR2M-M0
	50	7.6 (193)	0.190 (4.8)	2.00 (50.8)	298-9915-ND	1,000	83.51	CBR2S-M0
	50	10.8 (274)	0.190 (4.8)	3.00 (76.2)	298-9919-ND	1,000	231.48	CBR3S-M0
	40	13.6 (345)	0.140 (3.6)	4.00 (101.6)	298-9921-ND	1,000	309.35	CBR4I-M0
	50	14.0 (356)	0.190 (4.8)	4.00 (101.6)	298-9925-ND	1,000	245.81	CBR4S-M0
	120	14.6 (371)	0.300 (7.6)	4.00 (101.6)	298-9923-ND	250	174.42	CBR4LH-TL0
	120	20.9 (531)	0.300 (7.6)	6.00 (152.4)	298-9927-ND	100	118.90	CBR6LH-C0
STA-STRAP® Panel Mount Tie - Nylon — RoHS Compliant								
4	120	10.1 (257)	.300 (7.6)	2.76 (70)	298-9963-ND	50	65.24	SSPM2.5HP-L300
	120	14.8 (376)	.300 (7.6)	4.0 (102)	298-9964-ND	50	83.26	SSPM4HP-L300
SUPER-GRIP™ Cable Tie - Nylon — RoHS Compliant								
5	18	4.2 (106)	0.118 (3.0)	1.00 (25)	298-9928-ND	100	15.51	SG100M-C
	18	4.2 (106)	0.118 (3.0)	1.00 (25)	298-9930-ND	1,000	31.44	SG100M-M
	40	6.2 (157)	0.168 (4.3)	1.50 (38)	298-9934-ND	1,000	48.08	SG150I-M
	50	8.3 (211)	0.225 (5.7)	2.00 (51)	298-9936-ND	100	22.67	SG200S-C
	50	8.3 (211)	0.225 (5.7)	2.00 (51)	298-9938-ND	1,000	65.04	SG200S-M
	70	12.4 (315)	0.225 (5.7)	3.20 (81)	298-9940-ND	100	46.25	SG300S-C
	70	12.4 (315)	0.225 (5.7)	3.20 (81)	298-9942-ND	1,000	172.68	SG300S-M
	120	15.3 (389)	0.330 (8.4)	4.13 (105)	298-9944-ND	50	39.74	SG350LH-L
	120	15.3 (389)	0.330 (8.4)	4.13 (105)	298-9946-ND	250	132.18	SG350LH-TL
	70	15.3 (389)	0.225 (5.7)	4.20 (107)	298-9948-ND	100	52.12	SG370S-C
70	15.3 (389)	0.225 (5.7)	4.20 (107)	298-9950-ND	1,000	192.99	SG370S-M	
SUPER-GRIP Cable Tie - Weather Resistant - Black — RoHS Compliant								
5	18	4.2 (106)	0.118 (3.0)	1.00 (25)	298-9929-ND	100	20.35	SG100M-C0
	18	4.2 (106)	0.118 (3.0)	1.00 (25)	298-9931-ND	1,000	49.23	SG100M-M0
	40	6.2 (157)	0.168 (4.3)	1.50 (38)	298-9933-ND	100	22.05	SG150I-C0
	50	8.3 (211)	0.225 (5.7)	2.00 (51)	298-9937-ND	100	24.22	SG200S-C0
	50	8.3 (211)	0.225 (5.7)	2.00 (51)	298-9939-ND	1,000	72.63	SG200S-M0
	70	12.4 (315)	0.225 (5.7)	3.20 (81)	298-9941-ND	100	49.56	SG300S-C0
	70	12.4 (315)	0.225 (5.7)	3.20 (81)	298-9943-ND	1,000	205.19	SG300S-M0
120	15.3 (389)	0.330 (8.4)	4.13 (105)	298-9945-ND	50	43.20	SG350LH-L0	

◆ RoHS Compliant

* VELCRO is a registered trademark of the Velcro Companies † See datasheet for additional dimensions (Continued)

More Product Available Online: www.digkey.com



Wire Ties and Accessories (Cont.)

Fig.	Min. Loop Tensile Strength (Lbs)	Length Inch (mm)	Width Inch (mm)	Max. Bundle Diameter Inch (mm)	Digi-Key Part No.	Pkg. Qty.	Price/Pkg.	Panduit Part No.
5	70	15.3 (389)	0.225 (5.7)	4.20 (107)	298-9949-ND	100	55.74	SG370S-C0
	70	15.3 (389)	0.225 (5.7)	4.20 (107)	298-9951-ND	1,000	218.06	SG370S-M0
	175	18.6 (471)	0.380 (9.7)	5.20 (132)	298-9953-ND	100	92.15	SG450H-C0
PAN-TY Push Mount - Nylon - RoHS Compliant								
1	40	6.1 (156.0)	0.135 (3.4)	1.25 (32.0)	298-1357-ND	1,000	157.97	PLP1.5I-M
	50	7.9 (200.0)	0.180 (4.6)	1.75 (45.0)	298-1358-ND	100	40.81	PLP2S-C
	50	7.9 (200.0)	0.180 (4.6)	1.75 (45.0)	298-1359-ND	1,000	184.58	PLP2S-M
PAN-TY Wing Push Mount - Nylon - RoHS Compliant								
6	18	4.3 (109.0)	0.098 (2.5)	0.87 (22.0)	298-1351-ND	100	33.08	PLWP1M-C
	18	4.3 (109.0)	0.098 (2.5)	0.87 (22.0)	298-1352-ND	500	94.96	PLWP1M-D
	50	5.2 (132.0)	0.190 (4.8)	1.00 (25.0)	298-1353-ND	100	39.65	PLWP1S-C
	40	6.0 (152.0)	0.135 (3.4)	1.25 (32.0)	298-1349-ND	100	37.45	PLWP1.5I-C
	40	6.0 (152.0)	0.135 (3.4)	1.25 (32.0)	298-1350-ND	500	101.90	PLWP1.5I-D
	50	7.8 (198.0)	0.190 (4.8)	1.75 (45.0)	298-1355-ND	100	45.67	PLWP2S-C
50	7.8 (198.0)	0.190 (4.8)	1.75 (45.0)	298-1356-ND	500	110.17	PLWP2S-D	
PAN-TY Wing Push Mount Offset - Nylon - RoHS Compliant								
6	50	6.97 (177)	.190 (4.8)	1.57 (40)	298-9957-ND	50	16.50	PLUP40SE-D
PAN-TY Cable Tie - Weather Resistant - Black - RoHS Compliant								
1	12	2.8 (71.1)	0.070 (1.8)	0.60 (15.2)	298-1037-ND	100	18.79	PLT6SM-C0
	12	2.8 (71.1)	0.070 (1.8)	0.60 (15.2)	298-1038-ND	1,000	40.50	PLT6SM-M0
	18	3.1 (78.7)	0.090 (2.3)	0.68 (17.3)	298-1039-ND	1,000	37.33	PLT7M-M0
	18	3.9 (99.1)	0.098 (2.5)	0.87 (22.1)	298-1040-ND	100	20.13	PLT1M-C0
	18	3.9 (99.1)	0.098 (2.5)	0.87 (22.1)	298-1041-ND	1,000	48.27	PLT1M-M0
	40	5.6 (142.2)	0.142 (3.6)	1.38 (35.1)	298-1042-ND	100	21.86	PLT1.5I-C0
	40	5.6 (142.2)	0.142 (3.6)	1.38 (35.1)	298-1043-ND	1,000	64.31	PLT1.5I-M0
	18	5.6 (142.2)	0.098 (2.5)	1.25 (31.8)	298-1044-ND	100	23.02	PLT1.5M-C0
	18	5.6 (142.2)	0.098 (2.5)	1.25 (31.8)	298-1045-ND	1,000	66.90	PLT1.5M-M0
	50	7.4 (188.0)	0.190 (4.8)	1.88 (47.8)	298-1050-ND	100	24.22	PLT2S-C0
	50	7.4 (188.0)	0.190 (4.8)	1.88 (47.8)	298-1051-ND	1,000	72.63	PLT2S-M0
	40	8.0 (203.2)	0.142 (3.6)	2.00 (50.8)	298-1046-ND	100	32.54	PLT2I-C0
	40	8.0 (203.2)	0.142 (3.6)	2.00 (50.8)	298-1047-ND	1,000	88.07	PLT2I-M0
	18	8.0 (203.2)	0.098 (2.5)	2.00 (50.8)	298-1048-ND	100	28.69	PLT2M-C0
	18	8.0 (203.2)	0.098 (2.5)	2.00 (50.8)	298-1049-ND	1,000	71.70	PLT2M-M0
	40	11.4 (289.6)	0.145 (3.7)	3.00 (76.2)	298-1052-ND	100	44.13	PLT3I-C0
	50	11.5 (292.1)	0.190 (4.8)	3.00 (76.2)	298-1053-ND	100	48.60	PLT3S-C0
	50	11.5 (292.1)	0.190 (4.8)	3.00 (76.2)	298-1054-ND	1,000	201.18	PLT3S-M0
	50	14.5 (368.3)	0.190 (4.8)	4.00 (101.6)	298-1055-ND	100	54.11	PLT4S-C0
	50	14.5 (368.3)	0.190 (4.8)	4.00 (101.6)	298-1056-ND	1,000	213.78	PLT4S-M0
	50	17.5 (445.0)	0.190 (4.8)	5.00 (127.0)	298-1362-ND	100	85.78	PLT5S-C0
	50	17.5 (445.0)	0.190 (4.8)	5.00 (127.0)	298-1363-ND	1,000	341.31	PLT5S-M0
	120	21.9 (556.0)	0.300 (7.6)	6.00 (152.0)	298-1364-ND	50	65.48	PLT6LH-L0
	120	21.9 (556.0)	0.300 (7.6)	6.00 (152.0)	298-1365-ND	100	84.53	PLT6LH-C0
120	27.6 (701.0)	0.300 (7.6)	8.00 (203.0)	298-1374-ND	100	130.46	PLT8LH-L0	
120	27.6 (701.0)	0.300 (7.6)	8.00 (203.0)	298-1375-ND	100	99.33	PLT8LH-C0	
BOW-TY Cable Tie Two Loop - Nylon - RoHS Compliant								
1	50	7.6 (193)	.190 (4.8)	1.8 (45.7)	298-9958-ND	100	53.56	PLB2S-C0
	50	11.8 (300)	.190 (4.8)	3.0 (76.2)	298-9959-ND	100	56.52	PLB3S-C0
	50	14.8 (376)	.190 (4.8)	4.1 (104.1)	298-9960-ND	1,000	285.21	PLB4S-M0
BOW-TY Cable Tie Three Loop - Nylon - RoHS Compliant								
1	125	20.0 (508)	.500 (12.7)	5.0 (127.0)	298-9961-ND	100	294.57	PLB35EH-C0
BARB-TY Cable Tie - Nylon Tie With Metal Clip								
1	18	4.0 (101.6)	0.095 (2.4)	0.90 (22.9)	298-1063-ND	100	15.55	BT1M-C
	40	6.1 (154.9)	0.141 (3.6)	1.50 (38.1)	298-1064-ND	100	17.94	BT1.5I-C
	18	6.1 (154.9)	0.095 (2.4)	1.50 (38.1)	298-1071-ND	100	20.81	BT1.5M-C
	18	7.7 (195.6)	0.095 (2.4)	2.00 (50.8)	298-1072-ND	100	21.81	BT2M-C
	40	8.0 (203.2)	0.141 (3.6)	2.00 (50.8)	298-1065-ND	100	27.05	BT2I-C
	50	8.0 (203.2)	0.185 (4.7)	2.00 (50.8)	298-1068-ND	100	22.67	BT2S-C
	40	11.1 (281.9)	0.141 (3.6)	3.00 (76.2)	298-1066-ND	100	33.35	BT3I-C
	18	14.0 (355.6)	0.095 (2.4)	4.00 (101.6)	298-1074-ND	100	31.47	BT4M-C
	40	14.3 (363.2)	0.141 (3.6)	4.00 (101.6)	298-1067-ND	100	47.06	BT4I-C
	120	24.4 (619.8)	0.275 (7.0)	7.00 (177.8)	298-1077-ND	50	65.78	BT7LH-L
	120	27.5 (698.5)	0.275 (7.0)	8.00 (203.2)	298-1078-ND	50	79.66	BT8LH-L
	BARB-TY Cable Tie - Weather Resistant Tie With Metal Clip - Black - RoHS Compliant							
1	18	4.0 (101.6)	0.095 (2.4)	0.90 (22.9)	298-1080-ND	100	20.37	BT1M-C0
	40	6.1 (154.9)	0.141 (3.6)	1.50 (38.1)	298-1081-ND	100	22.05	BT1.5I-C0
	18	6.1 (154.9)	0.095 (2.4)	1.50 (38.1)	298-1088-ND	100	24.37	BT1.5M-C0
	18	7.7 (195.6)	0.095 (2.4)	2.00 (50.8)	298-1089-ND	100	27.46	BT2M-C0
	40	8.0 (203.2)	0.141 (3.6)	2.00 (50.8)	298-1082-ND	100	32.50	BT2I-C0
	50	8.0 (203.2)	0.185 (4.7)	2.00 (50.8)	298-1085-ND	100	24.22	BT2S-C0
40	11.1 (281.9)	0.141 (3.6)	3.00 (76.2)	298-1083-ND	100	44.52	BT3I-C0	
50	11.2 (284.5)	0.185 (4.7)	3.00 (76.2)	298-1086-ND	100	49.56	BT3S-C0	

Fig.	Min. Loop Tensile Strength (Lbs)	Length Inch (mm)	Width Inch (mm)	Max. Bundle Diameter Inch (mm)	Digi-Key Part No.	Pkg. Qty.	Price/Pkg.	Panduit Part No.
1	18	14.0 (355.6)	0.095 (2.4)	4.00 (101.6)	298-1091-ND	100	41.76	BT4M-C0
	4.0	14.3 (363.2)	0.141 (3.6)	4.00 (101.6)	298-1084-ND	100	58.65	BT4I-C0
	50	14.4 (365.8)	0.185 (4.7)	4.00 (101.6)	298-1087-ND	100	55.74	BT4S-C0
	120	18.1 (459.7)	0.275 (7.0)	5.00 (127.0)	298-1092-ND	50	55.24	BT5LH-L0
	120	24.4 (619.8)	0.275 (7.0)	7.00 (177.8)	298-1094-ND	50	76.88	BT7LH-L0
120	27.5 (698.5)	0.275 (7.0)	8.00 (203.2)	298-1095-ND	50	92.53	BT8LH-L0	
PAN-TY Releasable Tie - Nylon - RoHS Compliant								
1	50	7.4 (188.0)	0.190 (4.8)	1.88 (47.8)	298-1057-ND	100	42.04	PRT2S-C
	50	11.5 (292.1)	0.190 (4.8)	3.00 (76.2)	298-1058-ND	100	71.17	PRT3S-C
	50	14.5 (368.3)	0.190 (4.8)	4.00 (101.6)	298-1059-ND	100	86.61	PRT4S-C
PAN-TY Releasable Tie - Weather Resistant - Black - RoHS Compliant								
1	50	7.4 (188.0)	0.190 (4.8)	1.88 (47.8)	298-1060-ND	100	44.56	PRT2S-C0
	50	11.5 (292.1)	0.190 (4.8)	3.00 (76.2)	298-1061-ND	100	79.59	PRT3S-C0
	50	14.5 (368.3)	0.190 (4.8)	4.00 (101.6)	298-1062-ND	100	95.10	PRT4S-C0
PAN-TY Marker Tie With Write On Area - Nylon - RoHS Compliant								
1	18	3.9 (99.1)	0.098 (2.5)	0.75 (19.1)	298-1011-ND	100	35.43	PLM1M-C
	18	4.3 (109.2)	0.098 (2.5)	0.87 (22.1)	298-1010-ND	100	35.15	PLF1M-C
	50	7.4 (188.0)	0.190 (4.8)	1.75 (45.0)	298-1012-ND	100	67.01	PLM2S-C
PAN-TY Marker Tie With Write On Area - Weather Resistant - Black - RoHS Compliant								
1	18	3.9 (99.1)	0.098 (2.5)	0.75 (19.1)	298-1014-ND	100	46.12	PLM1M-C0
	18	4.3 (109.2)	0.098 (2.5)	0.87 (22.1)	298-1013-ND	100	48.43	PLF1M-C0
	50	7.4 (188.0)	0.190 (4.8)	1.75 (45.0)	298-1015-ND	100	81.64	PLM2S-C0
Cushion Sleeve For Use With Metal Locking Tie - Black - RoHS Compliant								
—	—	100ft. (30.48m)	0.330 (8.0)	—	298-1103-ND	1 Reel	188.61	PCSS-B-CR
TAK-TY® (VELCRO®) Easy Release And Reuse Brand Cable Tie - Black - RoHS Compliant								
1	50	6.0 (152.4)	0.75 (19.1)	1.50 (38.1)	298-1110-ND	10	11.86	HLS1.5S-X0
	40	8.0 (203.2)	0.50 (12.7)	1.90 (48.3)	298-1113-ND	10	13.68	HLT2I-X0
	40	12.0 (304.8)	0.50 (12.7)	3.20 (81.3)	298-1114-ND	10	17.77	HLT3I-X0
	50	12.0 (304.8)	0.75 (19.1)	3.00 (76.2)	298-1108-ND	10	20.08	HLC3S-X0
	50	12.0 (304.8)	0.75 (19.1)	3.00 (76.2)	298-1111-ND	10	19.79	HLS3S-X0
	50	18.0 (457.2)	0.75 (19.1)	5.00 (127.0)	298-1109-ND	10	24.60	HLC5S-X0
	50	18.0 (457.2)	0.75 (19.1)	5.00 (127.0)	298-1112-ND	10	28.83	HLS5S-X0
	50	15ft. (4.572m)	0.75 (19.1)	Various	298-1115-ND	1 Reel	18.98	HLS-15R0

♦ RoHS Compliant

* VELCRO is a registered trademark of the Velcro Companies † See datasheet for additional dimensions

Fig.	Max. Bundle Diameter Inch (mm)	Length Inch (mm)	Thickness & Width In. (mm)	Min. Loop Tensile Strength Lbs.	Recommend Installation Tools	Digi-Key Part No.	Pkg. Qty.	Price/Pkg.	Panduit Part No.
Metal Locking Tie - Stainless Steel - RoHS Compliant									
1	1.00 (25.4)	5.0 (127.0)	.010 x .18	100	GS4MT	298-1100-ND	100	74.51	MLT1S-CP
	2.00 (50.8)	7.9 (200.7)	(.25 x 4.4)	100	ST2MT or HTMT	298-1101-ND	100	72.59	MLT2S-CP
	4.00 (101.6)	14.2 (360.7)		100	HTMT	298-1102-ND	100	86.90	MLT4S-CP
WAVE-TY™ Superior Grip Stainless Steel Ties - RoHS Compliant									
7	6.00 (152)	20.5 (521)	.010 x .31	200	GS4MT	298-1332-ND	50	96.44	MLT6WH-LP
	8.00 (203)	26.8 (681)	(.25 x 7.9)	200	ST2MT or HTMT	298-1333-ND	50	123.21	MLT8WH-LP
	10.00 (254)	33.0 (838)		200	HTMT	298-1334-ND	50	154.01	MLT10WH-LP
Metal Locking Tie - Nylon Coated - RoHS Compliant									
8	2 (51)	7.9 (201)	.010 x .31	250	GS4MT, HTMT	298-9970-ND	50	158.49	MLT2CH-LP316
	4 (102)	14.3 (362)	(7.9 x .25)	250	ST2MT or PPTMT	298-9971-ND	50	186.00	MLT4CH-LP316
	6 (152)	20.5 (521)		250	PPTMT	298-9972-ND	50	278.50	MLT6CH-LP316

Fig.	Length Inch (mm)	Width Inch (mm)	Digi-Key Part No.	Pkg. Qty.	Price/Pkg.	Panduit Part No.
Tie Holder With Adhesive - Nylon - RoHS Compliant						