

E-Z-HOOK Electronic Test Accessories

Hooks

(Set/10: 1 each of: Brown, Black, Red, Orange, Yellow, Green, Blue, Violet, Gray, White)



Dimensions in Inches

Fig. 1 – Double Hook, .025" Spacing 	Fig. 2 – Pico-Hook
Fig. 3 – Micro-Hook 	Fig. 4 – Double Micro-Hook
Fig. 5 – Mini-Hook 	Fig. 6 – Macro-Hook
Fig. 7 – Macro-Hook, Insulation Piercing 	Fig. 8 – Insulation Piercing

Fig.	Description	Color	Digi-Key Part No.	Price Each			E-Z-Hook Part No.	
				1	100	250		
1	.006" Dia. Wire Double Hook, .025" Spacing	Black	461-1000-ND	17.43	15.75	13.97	X2015 BLK	
		Red	461-1001-ND	17.43	15.75	13.97	X2015 RED	
2	Pico-Hook with .025" Square Pin Gold Plated	Black	461-1002-ND	3.47	3.14	2.78	P25 BLK	
		Red	461-1003-ND	3.47	3.14	2.78	P25 RED	
3	Micro-Hook Test Connector	Black	461-1004-ND	1.93	1.74	1.55	XM BLK	
		Red	461-1005-ND	1.93	1.74	1.55	XM RED	
		Gray	461-1006-ND	19.09	17.25	15.30	XM-S	
		Set/10	461-1007-ND	3.30	2.99	2.65	XM25 BLK	
4	E-Z-Micro Double Gripper	Black	461-1009-ND	2.66	2.40	2.13	XKM BLK	
		Red	461-1010-ND	2.66	2.40	2.13	XKM RED	
5	Mini-Hook Test Connector	Black	461-1013-ND	1.74	1.58	1.40	X100W BLK	
		Red	461-1014-ND	1.74	1.58	1.40	X100W RED	
	Gray	461-1015-ND	17.26	15.60	13.84	X100W-S		
	Set/10	461-1016-ND	3.65	3.30	2.93	XL1 BLK		
	6	Macro-Hook Test Connector	Black	461-1020-ND	5.61	5.07	4.50	XH BLK
			Red	461-1021-ND	5.61	5.07	4.50	XH RED
7	Macro-Hook Piercing Connector	Black	461-1024-ND	6.81	6.15	5.46	XJL BLK	
		Red	461-1025-ND	6.81	6.15	5.46	XJL RED	
8	Insulation Piercing Test Connector	Black	461-1026-ND	7.45	6.74	5.98	XJL BLK	
		Red	461-1027-ND	7.45	6.74	5.98	XJL RED	
9	Standard Banana Jack	Black	461-1028-ND	11.70	10.58	9.38	XL BLK	
		Red	461-1029-ND	11.70	10.58	9.38	XL RED	

Panel Mounts

(Set/10: 1 each of: Brown, Black, Red, Orange, Yellow, Green, Blue, Violet, Gray, White)



Dimensions in Inches

Fig. 1 – Banana Jack 	Fig. 2 – Double Banana Jack
---------------------------------	--

Fig.	Description	Color	Digi-Key Part No.	Price Each			E-Z-Hook Part No.
				1	100	250	
1	Standard Banana Jack	Red/Black	461-1215-ND	3.25	2.94	2.61	9284 R/B
	Standard Banana Jack	Set/10	461-1216-ND	16.27	14.70	13.04	9284-S
2	Double Standard Banana Jack with Binding Post	Red/Black	461-1217-ND	6.89	6.23	5.52	9406

Adapters

Dimensions in Inches

Fig. 1 – Jack to Alligator 	Fig. 2 – Banana Jack to .080 Tip Pin
Fig. 3 – BNC to Double Banana Plug 	Fig. 4 – Double Banana Jack to Plug
Fig. 5 – Hook to Banana Jack 	Fig. 6 – Banana Jack to Flexible Pin or Socket

Fig.	Description	Color	Digi-Key Part No.	Price Each			E-Z-Hook Part No.
				1	100	250	
1	Standard Tip Jack to Standard Alligator Clip	Red/Black	461-1207-ND	4.15	3.75	3.33	8014 R/B
	Standard Banana Jack to Standard Alligator Clip	Red/Black	461-1208-ND	1.56	1.41	1.26	8016 R/B
2	Standard Banana Jack to Tip Pin	Red/Black	461-1206-ND	3.95	3.57	3.17	8018 R/B
	BNC Female to Standard Double Banana Plug	Black	461-1278-ND	7.24	6.54	5.80	9225
3	BNC Male to Standard Double Banana Plug	Black	461-1279-ND	8.02	7.25	6.43	9248
	Stacking Double Banana Plug	Black	461-1237-ND	4.37	3.95	3.50	DB750BLK
4	Mini-Hook w/ Standard Banana Jack Plunger	Red/Black	461-1218-ND	8.63	7.80	6.92	8036 R/B
	Mini-Hook XR w/ Standard Banana Jack Plunger	Red/Black	461-1219-ND	9.33	8.43	7.48	8037 R/B
5	Mini-Hook XL w/ Standard Banana Jack Plunger	Red/Black	461-1220-ND	13.15	11.88	10.54	8038 R/B

E-Z-Flex™ Test

Banana socket end is brass tin plated. All other contact ends are gold plated.

Fig.	AWG	Contact Dia. Inches	Type Contact	Color	Digi-Key Part No.	Price Each			E-Z-Hook Part No.
						1	100	250	
6	22	.030	Socket	Red	461-1221-ND	5.43	4.91	4.35	9334 RED
			Pin	Red	461-1229-ND	4.08	3.69	3.28	9338 RED
			Socket	Black	461-1222-ND	5.43	4.91	4.35	9334 BLK
			Pin	Black	461-1230-ND	4.08	3.69	3.28	9338 BLK
			Socket	Red	461-1223-ND	4.08	3.69	3.28	9335 RED
			Pin	Red	461-1231-ND	4.52	4.08	3.62	9339 RED
6	20	.040	Socket	Black	461-1224-ND	4.08	3.69	3.28	9335 BLK
			Pin	Black	461-1232-ND	4.52	4.08	3.62	9339 BLK

RoHS Compliant

Connectors



(Set/10: 1 each of: Brown, Black, Red, Orange, Yellow, Green, Blue, Violet, Gray, White)

Dimensions in Inches

Fig. 1 – Shrouded Banana Plug 	Fig. 2 – Banana Plug
--	---------------------------------

Fig.	Description	Color	Digi-Key Part No.	Price Each			E-Z-Hook Part No.
				1	100	250	
1	Shrouded Right Angle Std. Banana Plug	Red/Black	461-1204-ND	8.98	8.12	7.20	9302 R/B
2	Standard Banana Plug	Red/Black	461-1214-ND	2.86	2.58	2.29	9202 R/B
		Set/10	461-1213-ND	14.11	12.75	11.31	9202-S

Probes

Features: • Lead Wire: 18AWG, (65 x 36) T.C. Flexible PVC insulation.

Dimensions in Inches

Description	Length (Inches)	Color	Digi-Key Part No.	Price Each			E-Z-Hook Part No.
				1	100	250	
Pin Tip Probe	—	Red/Black	461-1209-ND	6.21	5.61	4.98	30 R/B
Needle Tip Probe	—	Red/Black	461-1211-ND	6.21	5.61	4.98	34 R/B
Needle Tip with Standard Banana Jack	—	Red/Black	461-1212-ND	7.60	6.87	6.10	35 R/B
Test Probe to Standard Banana Plug	36	Red/Black	461-1183-ND	12.75	11.52	10.22	658-36 R/B
Test Probe to Shrouded Std. Banana Plug	36	Red/Black	461-1184-ND	15.17	13.71	12.16	666-36 R/B
Test Probe to Shrouded Std. Banana Plug	36	Red/Black	461-1186-ND	15.94	14.40	12.77	63334-36 R/B

(Continued)

More Product Available Online: www.digkey.com