

Items listed as digikey.com do not appear in the catalog, but appear on the Digi-Key Web Site.

Thin Film..... 1424	Card Edge ..... 34, 265, 466-471, 476, 482-483, 2235	0.0197" (0.5mm) ..... 121	Mini D Ribbon (MDR) ..... 56-57
Toroidal ..... 1406, 1432-1434, 1447, 1462, 1472, 1474-1476, 1484, 2317-2318, 2321	Centronics ..... 285, 293	0.0787" (2.00mm) ..... 125, 138	Mini-Fit ..... 205
Variable..... 1469	C-Grid® ..... 185-189	0.156" (3.96mm) ..... 137, 182-183, 194, 197	BMI ..... 206
Voltage Step-Up..... 1425	Champ® ..... 257, 263-264	2mm ..... 108, 138, 155-156, 159-161, 164-166, 511	HCS ..... 206
Wirewound ..... 1410, 1413-1422, 1431, 1436-1440, 1465-1466, 1468	Circular	..... Latching ..... 59	Jr. .... 203-204, 206
<b>CompactPCI® Products</b> ..... 478-479, 2235-2236	8D/D38999 Aluminum and Composite Series ..... 398	..... Shrouded..... 59	SMC ..... 206
<b>Computer Equipment</b>	44 Series ..... 392	Female	Sr. .... 207
Cable Assemblies ..... 60-66	97 Series ..... 386-388	0.0197" (0.5mm) ..... 121	MiniSAS ..... 480, 499
Keyboards..... 2009-2010	851 Series ..... 399	0.025" (0.635mm) ..... 121	Modular..... 65, 69, 297-298, 301-311, 313-316, 485
KVM Switches ..... 2278	Accessories ..... 387-388, 399-400, 421	0.031" (0.80mm) ..... 121-122	70AA ..... 485
Trackballs ..... 2009	Bayonet Lock..... 402	0.050" (1.27mm) ..... 122-123, 138	70AD ..... 486
<b>Concentric Scale Dials</b> ..... 1870	C16 ..... 390	0.0787" (2.00mm) ..... 125-127, 138	Adapters, Filtered..... 315-316
<b>Connectors</b>	C091 ..... 391	0.100" (2.54mm) ..... 127-132, 136, 170-173, 176, 180, 237, 509-511, 513	Adapters, IBM Equivalent ..... 304
0.2mm..... 77	Coaxial..... 420	..... 0.156" (3.96mm) ..... 137	DSL Filter ..... 315
0.3mm..... 77, 80, 83, 89	DIN ..... 420-421, 423-424	IDC ..... 31, 52-53, 59	Ethernet ..... 69, 297-298, 301-309, 315-316
0.4mm..... 77, 90, 118, 202, 486	IP67 ..... 389	IDC Dip ..... 52-53	Industrial..... 69, 304, 311, 313-314
SlimStack™ ..... 202	M8 and M12 Series ..... 422	Pin/Plug ..... 51-52	Modular Jacks, Filtered..... 316
0.5mm..... 76-81, 83-84, 87-88, 91-92, 118-119, 139, 202	Medical ..... 414	Protected ..... 37-38, 45, 137-138	Power Over Ethernet (PoE) ..... 309, 316
SlimStack™ ..... 202	Metal..... 383-388, 400-407, 411, 421, 423	Hoods, D-Sub ..... 274-275, 290-293	Spring-Loaded Contacts ..... 512
0.6mm..... 93	MIL-C-5015 ..... 386-387, 422	HSSDC2 ..... 497	M-Series ..... 255-256
0.8mm..... 84, 94, 119-120, 139, 148-149, 215	MIL-C-26482 ..... 383-385, 399	ICCON ..... 238-239	MT 100" ..... 238-239
0.65mm..... 93-94	MIL-C-38999 ..... 398	IDC Discrete	MTA 100" and 156" ..... 190-197
1.0mm ..... 76, 78-80, 84-86, 88-89, 95, 98, 139-140, 149, 152, 265, 484, 486	Miniature ..... 402-403, 405-407, 411, 413-414	D-Sub ..... 270	MTE 100" ..... 241-242, 247-248
1.5mm..... 141-142, 153	Mini-DIN ..... 423-424	Socket..... 190-192, 194-196, 241-242	MX150L ..... 394
Pico SPOX™ ..... 153	MS Series ..... 384, 388	Strip ..... 215	Parallel Interface ..... 257-259, 263-264, 293
1.20mm ..... 140	Plastic..... 390, 393, 398-400, 402, 407-408, 420, 422-424	IC Ribbon Cable	PCI Express ..... 471, 482-483, 493
1.25mm ..... 99-100, 140-141, 152-153	PT Series..... 383-385	2mm Socket..... 159, 161, 167-168	PC Pins/Receptacles ..... 504, 514-515
1.27mm ..... 162-163	Push-Pull Lock..... 399, 401, 406-408	Card Edge ..... 34	Phono Jacks/Plugs ..... 458-460, 466
2mm..... 100-108, 136-137, 142-143, 154-157, 159-161, 164-169, 478-479, 481-482, 511	RADSOK® ..... 382	DIP ..... 29, 33, 48, 54	Power ..... 136, 151, 197, 207-209, 214, 216-217, 349, 460-465, 475-476, 1514
Hard Metric ..... 479, 481-482	Screw Lock ..... 390, 400-401, 403-407	D-Sub ..... 28, 32, 48	Power Edge™ ..... 468
Metral® ..... 482	Sealed ..... 391-392, 398-399	Mini D (MDR)..... 56-57	Power Supply..... 113
Milli-Grid™ ..... 155-156	.125" Powerband Contact ..... 420	PCB ..... 34, 44	Rack and Panel ..... 218, 262
Millipacs® ..... 482	Wire Entry Seal Kits ..... 400	Pin/Plug ..... 31, 52-53	RADSOK® ..... 382
Mini-Clamp ..... 169	Video	Socket..... 30, 34, 50, 59, 159, 161, 167-168	RAPID LOCK ..... 476
Mintek™ ..... 159-161	Waterproof..... 389, 409-410, 412	IEEE 1394 (Firewire)..... 65, 68, 307, 312	Rectangular ..... 210-212
Sherlock™ ..... 154	Compact Flash ..... 489	Waterproof ..... 312	Heavy Duty ..... 210-212
Socket..... 511	CompactPCI® ..... 478-479	Industrial Ethernet ..... 69, 304, 349	146E Series ..... 212
Z-Pack ..... 478-479	CROWN CLIP..... 476	Interconnect Systems ..... 250-254, 497	IP65 ..... 210-211
2.5mm..... 109-112, 137-138, 158, 261	CROWN EDGE..... 476	Interface Modules ..... 357	Retention Modules..... 265
SPOX™ ..... 158	DIN, Rectangular ..... 468, 472-475, 477, 484, 504	Intra-Connector™ ..... 504	Reverse Polarity SMA ..... 449, 548-549
3.96mm ..... 158	DisplayPort® ..... 213	I/O ..... 120, 214-217, 496, 498	RF ..... 445
4.2mm..... 219	D-Sub ..... 28, 32, 48, 266-297, 305, 338	Jig Assemblies ..... See digikey.com	Accessories ..... 438, 2269
5.0mm ..... 113-114	Accessories ..... 274-275, 277-279, 294	Jones ..... See digikey.com	Adapters ..... 432, 438, 441, 452-453, 2269
5.08mm ..... 206	Adapters ..... 290	Jumpers	AMC ..... 430
7.5mm ..... 207	Backshells ..... 279, 290-293, 295, 297	Jumpers..... See Connectors - Shunts	BNC ..... 425, 431-432, 436-440, 453-454, 2269
7.92mm ..... 114	Combination ..... 279, 296	Jumpers Wires..... 115-116	Board-to-Board ..... 436
0.050" (1.27mm) ..... 58, 96-97, 149, 257-260, 510	Dual Port ..... 284	Termination Jumpers ..... 28-29, 32-35, 44, 48-50, 53-54	Coaxial ..... 436, 456-458
Picoflex™ ..... 58	Filtered ..... 294	LAN..... 304, 316	Decoupled ..... 440
0.062" ..... 208	Gender Changers..... 62, 290, 296	LED..... 2504	F ..... 442
0.084" ..... 208	Hardware Kits ..... 272-273, 276-277, 279, 294	Light-N-Lok™ ..... 2474	FL (Finger Lock) ..... 456
0.093" ..... 209	High Density ..... 271, 279-282, 284, 294, 297, 305	LVDS ..... 98, 118	H.FL. .... 456
0.100" (2.54mm) ..... 107, 180, 184-193, 238-242, 245, 247-249	VGA ..... 279	Mate-N-Lok® ..... 221-234	MCX/MMCX Type ..... 427, 441, 443, 445-446, 449, 454
0.156" (3.96mm) ..... 112-113, 139, 184, 194-197	Interface Modules and Cables ..... 338	Memory	SMP ..... 430
AC ..... 1514	Press Fit ..... 284	CardBus ..... 495	N Type ..... 427, 432, 442, 453
ATCA ..... 484	Water Resistant ..... 296, 305	Card Connectors..... 468, 489, 491-495	SHV ..... 442
Audio ..... 459-466	Dynamic..... 250-254	Compact Flash ..... 488, 490, 492, 494	SMA/SMB ..... 425-426, 429-430, 433, 435, 443-445, 447-449
Backplane ..... 467, 476	Edgecard ..... See Connectors - Card Edge	DDR ..... 490	FAKRA (SMB) ..... 429-430
Backshells ..... 290-293, 295	ELCON ..... 475	DIMM ..... 468, 491, 493	QMA (SMA) ..... 430
Ballast ..... 2474	Ethernet..... See Connectors - Modular	Memory Stick® ..... 492	Waterproof ..... 443-444
Banana Plugs/Jacks ..... 411, 2271, 2273-2274	Eurocard ..... 472-475, 477	MicroSD™/Transflash ..... 489, 492, 496	SMK ..... 449
Barrier Blocks ..... 349	ExpressCard™ ..... 487, 493, 496	PCMCIA Memory Card..... 488-489, 491-492, 495	Terminator Plugs ..... 440
Battery ..... 488	FFC/FPC (Flat Flex) ..... 74, 77-81, 83-89	SD™ ..... 489	TNC ..... 428, 432, 443, 453
Binding Posts..... 411, 2232, 2271	Fiber Optic ..... 317-319, 322	Secure Digital ... 488, 490, 492, 494, 496	Tools, Crimp ..... 428, 430, 442
Blind Mate (BMI)..... 199, 201, 205	Flexi-Block ..... 349	SIM ..... 496	Twinaxial ..... 432
Board-to-Board ..... 45, 81, 90-99, 104, 106-107, 118, 121-123, 125-137, 139, 141, 148-151, 155, 159-160, 164, 259-261, 476, 483, 486	F Type ..... 445, 2269	SIMM ..... 493	UH ..... 434, 442, 453
Floating..... 150	GBIC ..... 497	TransFlash ..... 494	UMCC ..... 434
Bus Bar..... 476	Hard Metric ..... 479, 481	MetPak™	W.FL ..... 456
	Hardware ..... 263, 265, 293	2-FB..... 480	Ribbon Shielded (SCR) ..... 57
	HDI (High Density Interconnect)..... 261	CP2 ..... 481	RITS ..... 250
	HDMI ..... 213, 468, 485	HSHM ..... 481	RJ45 ..... See Connectors - Modular
	Headers ..... 212	Metrimate ..... 219-220	Sabre™ ..... 207
	0.025" (0.635mm) ..... 121	Mezzanine ..... 201-202	SAS (Serial Attached SCSI)..... 483
	0.031" (0.80mm) ..... 121-122	MicroCross™ DVI ..... 213	SATA ..... 57, 484
	0.040" (1.00mm) ..... 122	Micro-Fit 3.0™ ..... 198-201	SCA2 ..... 487
	0.050" (1.27mm) ..... 122-123, 137, 511	Microphone ..... 405	
	0.100" (2.54mm) ..... 37-38, 45, 51-53, 128-136, 174-182, 188-190, 192-193, 212, 237, 243-246, 509-510, 513	Micro TCA ..... 484	
		Mictor ..... 485	
		Miniature Rectangular (MR)..... 236	

More Product Available Online: [www.digikey.com](http://www.digikey.com)

Toll-Free: 1-800-344-4539 • Phone 218-681-6674 • Fax: 218-681-3380