

Items listed as digikey.com do not appear in the catalog, but appear on the Digi-Key Web Site.

Scotchlok™ 362-363
 SCSI 257-258, 480, 498
 SCSI Terminator 64, 271
 SDR 57
 Serial ATA 213
 SFP (Small Form Pluggable) 495, 498-499
 Shunts/Jumpers... 108, 159, 161, 164, 166, 174-175, 179-180, 189, 197, 237
 SIM Card 486-487
 Smart Card 487, 493, 500
 SmartMedia 486
 SMP 448
 Sockets, IC See IC Sockets
 Soft Shell .062" and .093" 234-235
 Switch 2083
 System 50 260
 Telecom 262
 Television, "F" Type 453
 Terminal Blocks
 Accessories 337-340, 342
 Barrier Blocks 354-357
 DIN Rail 338-339, 341-342, 1983
 DIN Rail Mounted 337-341
 Eurostyle® 350-353, 356-357
 PCB Mounted 323-334, 343-353, 356-357
 Pluggable 333-334
 Terminals/Splices
 Board-in-Crimp 139
 Butt Splice 359-363, 368-370, 380
 Closed End 363, 368
 Crimp 182-183, 358-363, 365-381, 418-419
 Disconnect 364
 Faston 371-377, 381
 Knife Disconnect 368
 PC Quick-Fit 2226
 Quick Connect... 358-359, 361-363, 371, 381, 406-408, 411
 Ring Tongue 359-366, 369-370, 378-381
 See and Splice™ 360
 Snap Plug 361, 363, 381
 Spade Lugs 359, 361-363, 367, 369-370, 380-381, 2226
 Spade Plug 359
 Spring Push 354
 Test Points 2226, 2232
 Wire Nut 361-362
 Wire Pin 359
 Wire Tap 360
 Termination Plugs 101
 Tip Jacks/Plugs 411
 Toy Car Battery 185
 Trim Trio 395-397
 Accessories 397
 Circular Harsh Environment Bayonet 395-396
 Circular Quick Mate 396-397
 Rectangular Panel/Cable 396-397
 USB 64-65, 67-70, 297, 304-305, 307, 311, 316, 511
 Bluetooth® Adapters 311
 Waterproof 311-312
 VHDCI 497
 Water Resistant/Waterproof 143, 296-297, 394, 402-405
 Weathertight 393-394
 XFP 496-497
 Z-Pack 478-479
Contacts See Connectors
Controllers
 Brushless Fan Motor Controller .. 1171-1172
 Relays 2483
 Temperature 2482-2483
Converters, AC-DC See Power Supplies
Converters, DC-DC See Power Supplies
Cordless Soldering Irons 2173

Cords
 Fan 2301
 Power 1510-1511
Counters 2477-2478, 2482, 2485, 2489
 Accessories 2482
Crystals 1338-1350, 1354, 1356-1360, 1369-1374, 1379-1383, 1386-1390, 2282, 1359-1360, 1369-1370, 1379
 Cylinder Type 1359-1360, 1369-1370, 1379
 Kits 2282
 Microprocessor 1374
 Oscillators 1382-1383
 Tuning Fork 1379-1380
Current Indicators 2437
D
DC Block 1383
Delay Lines 1423
Detectors
 CO See digikey.com
 Combustible Gas Leak See digikey.com
 Refrigeration Leak See digikey.com
Development Kits and Tools
 Accessories 670, 673, 678, 680, 682-683
 Adapters 581-582, 609, 624, 646, 673, 675, 744
 BASIC Stamp Kits 626
 Configuration Devices 595
 Daughter Boards 527, 539, 646, 728
 Debug Tools 645, 688, 712, 719, 722
 Demo Kits 527-528, 596, 605, 677, 679, 683, 689, 709-710, 719
 Development/Starter Kits 527-530, 533, 535, 554-556, 563, 567, 570, 575, 579, 585, 596, 599, 602, 606, 609-615, 620, 622-623, 625, 661, 677, 679-680, 682, 700-703, 710, 717, 720-722, 2450
 Emulators 606, 609, 646, 673-676, 688, 700, 712, 728, 744
 EPROM 646, 676
 Flash 646
 PIC 646
 Evaluation Boards and Kits 523-524, 526-527, 539, 552-561, 563-564, 567, 569-570, 573, 575, 578-579, 585, 596, 602, 606, 609, 622-623, 670, 677, 679, 682-683, 688-689, 700-703, 705, 709-710, 717, 719, 722, 726, 728-729, 744-746, 750-751, 1171, 2433, 2449-2451, 2462
 DSP 726, 728
 RF 523-524, 526-527, 539, 554-561, 563, 567, 569, 575, 579
 Sensors 2433, 2449, 2451, 2462
 FPGA/CPLD Kits 597-598
 LED Discovery Kit 2510
 Oscillator 1361, 1363
 PCI 598
 Programmable 539, 554, 570, 581-582, 585, 587, 596, 599, 602, 605, 609, 626, 646, 673-676, 679-680, 682-683, 700, 702-703, 712, 717, 719, 726, 728, 744
 Programming Cable 586, 596
 Reference Design Kits 527, 621
 Remote Control Design 676
 Software 645, 670, 719, 722, 744, 746
 C-Complier 645, 679, 722, 744
 Library See digikey.com
 Module See digikey.com
 Speech Recognition Kit 624
 Programmable Interactive Module ... 624
 Voice Record/Playback 625
 Web Server Kit 675
Diacs 1202, 1238, 1321, 1939

Dials, Concentric Scale 1890, 1895, 1897
DIN Rail 338-339, 341-342
Diodes/Rectifiers 1163-1164, 1176, 1185-1190, 1194-1202, 1217-1224, 1231-1236, 1243-1248, 1251-1252, 1258-1275, 1285-1287, 1293-1295, 1298-1305, 1307-1308, 1318-1319, 1321, 1324-1327
 Arrays 1251, 1275, 1302, 1319
 Bridge 1220, 1264-1265, 1287, 1303-1305, 1325-1327
 ESD Protection 1197, 1935, 1937
 FREDs/HexFREDs 1221, 1295
 Hyperabrupt Varactors 1163
 Kits 1197, 2282
 PIN (RF) 1186, 1196-1197, 1308
 Schottky 1163-1164, 1185-1186, 1195, 1217-1220, 1231-1233, 1246-1248, 1252, 1266-1269, 1271, 1274-1275, 1293-1295, 1318, 1324-1327
 Super Barrier 1269
 Switching 1164, 1187-1188, 1194, 1248, 1251, 1272-1273, 1293-1294, 1307, 1319, 1324
 TVS See Transient Voltage Suppressors
 Varactors 1324
 Variable Capacitance 540, 1176, 1196
 Varistors See Varistors
 Zener 1164, 1188-1190, 1196, 1198-1200, 1243-1244, 1251-1252, 1258-1263, 1266, 1285-1287, 1305, 1308, 1319, 1324
 PolyZen Micro Assembly 1951
Diplexers
 Multilayer 1481
Displays
 Backlights 2470
 Dot Matrix 2542
 LCD See LCDs
 LED See LEDs
 Vacuum Fluorescent 2471, 2475
Duct Wiring See digikey.com
E
EMI Suppression
 Absorber Pads 523
 Arrays 1494, 1497-1499, 1504
 Capacitors 1672
 Common Mode Chokes 1497-1499
 Ferrite Cable Cores 1450, 1502-1503
 Ferrite Chips 1492-1497, 1509
 Filter Capacitor Type 1495
 Filters 1480, 1495, 1497-1500, 1502-1506, 1520, 1522-1523
 High Current 1496-1499
 LC Combined Chip 1495, 1504
Emulators See Development Tools
Enclosures/Boxes/Racks
 Accessories and Hardware 2196-2198, 2200, 2202, 2205-2207, 2209-2210
 Cabinets 2199-2202, 2204
 Conductive 2199
 Cases/Boxes 2196-2204, 2208-2211, 2269-2270
 Aluminum 2196, 2200-2203, 2208-2211, 2269-2270
 E.M.I. 2197-2198
 Plastic 2196-2200, 2202, 2204, 2208-2211, 2269-2270
 Soft-Sided 2211
 Nema 2203-2204
 Racks 2205-2207
 Watertight/Airtight Cases 2197-2199, 2211
Encoders
 Digital Contacting 2101
 Magnetic 2085
 Mechanical 2099-2100

Modular 2099
 Optical 2098-2099, 2101
 Rotary 2098-2101
 Square/Sealed 2101
 Universal 2009
EPROM Eraser 2266
ESD Products
 Suppression 1252, 1505, 1910, 1951, 1956-1957, 1969
 Arrays 1505, 1951, 1956
 Multilayer Chip 1910
 Surgelets See digikey.com
 TVS See Transient Voltage Suppressors
 Varistors/ZNRs 1906-1910, 1915
F
Fans/Blowers
 AC 2300, 2302, 2307, 2309-2310
 Accessories 2300-2301
 Blowers 2305, 2308-2312
 Chip Cooler 2307
 DC 2298-2299, 2302-2312
 Axial 2303-2306, 2311
 Brushless DC 2298-2299, 2306-2309
 Hydro-wave Bearing (HWB) 2303-2305
 Tachometer Output 2298-2299
 Therma Pro-V 2300
 Finger Guards 2298-2305, 2311-2312
 Mini 2307
Fastening Systems
 Hook and Loop 2214
 Velcro® 2215
Ferrites
 Bead Cores 1479, 1487-1488, 1497-1498, 1503-1504, 1509
 Chip Arrays 1488, 1494, 1497-1499
 Chips 1486, 1492-1494, 1496-1498
 Clamp-On 1485, 1501, 1503
 Common Mode Chokes 1497-1499
 Cylinder 1486, 1502-1503
 Differential Mode 1497, 1499
 EMI Discs and Plates 1500
 Flat Core 1509
 Flexible Ferrite Material 1450, 1487
 High Current 1497
 High Frequency Cores 1503
 Kits 1500, 1503-1504
 Low Frequency 1500
 Ribbond Cable 1501
 Ring Core 1502-1503, 1509
 Split Cores 1501, 1503
 Toroids 1483, 1500, 1502
Ferrules
 Crimp 273, 275
 Fiber Optic 317
 Split-Ring 275
 Wire 336
Fiber Optic
 Accessories 317-319
 Adapters 317-318, 320
 Amplifiers 2448
 Attenuators 318
 Bare Cable See digikey.com
 Cable 317, 319, 322, 2448
 Connectors 317-319, 322
 Emitters/Detectors 320
 Ferrules 317
 Inspection Tool 2267
 Kits 319
 LEDs 320, 322
 Receivers 317, 320, 322
 Sensors 320
 Switches 317-318
 Terminators 317-318
 Test Equipment 318
 Tools 319
 Transmitters 320, 322
 Transmitting/Receiving Modules 321-322

More Product Available Online: www.digikey.com

Toll-Free: 1-800-344-4539 • Phone 218-681-6674 • Fax: 218-681-3380