

Items listed as digikey.com do not appear in the catalog, but appear on the Digi-Key Web Site.

Controllers 659, 1044, 1046	Multiplexers/Demultiplexers 913, 1105, 1120-1121	Thyristor Triac 1009	Resistors 1796-1800, 1809-1813, 1817-1818, 2281-2282
Ethernet 843-844	Op Amps 972, 1024, 1108	Timekeeping 1124	Sensors 2440-2441
Ethernet Protocol 659, 750	Optical Sensor 913	Timers 800, 960, 974, 1034, 1172	Spacers/Standoffs 2227-2228
Hot Swap Control 652	PCI Bridge 1027	Tone Decoder See digikey.com	Switches 2061, 2108, 2282
HVS 844	PCI-to PCI Bridges 781	TOPFET 799	Terminals, Insulated 362-363
I2C 786-788, 1100	Peripheral Controllers 784	TriCore™ 722	Test Equipment 2260
IEEE 1394 788	Peripheral Interface Products 782	TVS 981	Test Lead 2273
LCD 844	PFC/PWM Controllers 1024	UARTs 1076	Thermistors 1944, 2282, 2460
LVDS 788, 844-845	Potentiometers, Digital 654-655, 1035-1038, 1122, 1136	USB	Knobs 1896-1897, 2087
LVDT 845	Power Amps 750-751, 998	Host Controllers 627	
LV/LVCP/LVDM 844	Power Control/Management 647-650, 653, 782-783, 798-799, 913-914, 962, 980, 983-984, 987, 998-1001, 1012-1013, 1041-1042, 1083-1093, 1101-1102, 1105-1106, 1171-1172	UART 627	
LVP 845-846	Power Conversion 979	USB/General Purpose Switches 974	
MLVD 846	Power Linear 980	USB to Serial Converters 628	
Multiprotocol 1100	Power Management 769-772	USB Transceivers 974	
PBW 788	Power Supply Products 750, 798-799, 914-958, 1001-1003	Video Communication 1043	
PCI Express 788	Power Switches 972	Video Switch Products 1027	
Peripherals 658-659	Precision Ground Reference 958	Vipower 1009	
PWM (Pulse Width Modulator) 651	Processors 779, 782	Voice Record/Playback 624-625	
RS232/422/423/485 788, 846-853, 1098-1100	Programmable Gate Arrays 958	Voltage Detectors 648, 1109, 1137	
SCSI 853	Programmable Logic	Voltage Monitors 1119-1120, 1124-1125	
SMBus 1100	CPLDs 586, 593-595, 599, 680	Voltage References 972, 1044, 1169-1170	
Specialty 1027	FPGAs 584, 586-587, 589-593, 600-601	Voltage Regulators 648-650, 1009-1012, 1015, 1044, 1077-1078, 1103, 1108, 1138, 1168-1169, 1938	
Transmitters/Receivers 621, 843, 1038-1041	FPSLIC 602	Volt-to-Freq/Freq-to-Volt Converters 655	
UARTs 788-789	SPLDs 601	Waveform Generators 772	
I/O Controllers 1136	ProSLIC 622		
I/O Expanders 797, 910-912	Protection 1003-1004, 1077		
IPAD 996	Q Filter, Variable 1171		
Latched Drivers 964	Radio Frequency 799		
LCD/LED Drivers 961	Real Time Clocks 799, 958, 1042, 1123-1124		
LDO Regulators 965-971, 976-977, 982-983, 1023-1024, 1106-1107, 1112-1113	References 1093-1094		
LED Ballasts 782	Regulators 964-965		
LED Drivers/DC-to-DC 1030-1031	Relays 2146		
Light Applications 1077	Reset Circuits See ICs - Supervisors		
Lighting 1171	RF Products See RF/IF		
Linear 656-658, 1004-1008, 1020-1023, 1031, 1049-1076, 1172	Sensor 783		
Linear Peripheral Drivers 912	Sensor/Signal Conditioning 772-773, 980		
Logic Translation 797-799	Serial Communication Controllers 784		
Memory	Signal Controllers 799		
EEPROM, Parallel 777	Signal Controllers/Processors 958-959, 1004		
EEPROM, Serial 777	Signal/Interface 980-981		
Flash 777	Signal Processors 773		
Memory Products See Memory	Small Signal 981		
Microcontrollers	Smart Power 1008		
8051 Architecture 607-609, 616-620, 683, 685-688, 720	Smart Power Modules 1024-1025		
ARM 602, 685-687, 701-703, 748-749	Sound Modules See digikey.com		
Cortex™ 660-661	Specialized 783, 799, 914, 1025, 1042, 1100, 1106, 1121-1122, 1136, 1171-1172		
AVR 603-606	Specialized IC 773		
BASIC Stamp 626	Supervisors/Reset Circuits 647-648, 973-974, 1033-1034, 1119-1120, 1123		
BlueStreak 624	Supervisory Circuits/Reset Generators 773, 981		
C166S V1 720-721	Switches 774-775, 975, 1106		
C166S V2 720-721	Analog 853-855, 975, 1120-1121		
CAN 607	Arrays 1042-1043		
Cortex™ 703	Bus 788		
Flash 607-608, 616-620, 631-644, 662, 664-673, 678, 680, 682-683, 689, 697-699, 705-710, 717, 719, 728-729, 731-744	DC-DC Power Management 975		
MCS@51 780	Discrete Arrays 975		
MCS@96 780	High Frequency 975		
MP3 607	Power Distribution 1949-1950		
OTP 629-630, 662-665, 674-676, 704	RF 788		
PIC 629-644	Thermal Management 975		
ProC 532	Switching 981		
Propeller 626	Switching Controllers 1112-1113		
Smart Card 607	Switching Regulators 651, 1109, 2334		
USB 607, 617-618, 681	System Management 961		
Micro-Integration 977	Telecom Broadband 781		
Microprocessors 612-615, 712-717, 778-781, 784	Telecommunications 779, 1076		
Modules 612, 614-615	TFT Displays 1136		
Mixed Signal Product 653-655, 678, 775-777, 992	Thermal Management 658-659, 799, 959-960, 1008, 1124		
MMIC 560, 564, 1187	Fan Controllers 658		
Modem Chipsets, Controllers, DSPs, AFEs 782	MICA Insulators 1153		
MOS Logic 977-979	Temperature Sensors 658, 799, 959-960, 1008		
Motion/Motor Control 768			
Motor Drivers 986-987			
Motor Drivers/Controllers 1031			

L

Labels	
Computer Printable 2225	
Heat Shrink 2225	
Safety See digikey.com	
Thermal Transfer 2225	
Wire Marker 2225	
Dispenser 2225	
Lamps	
Assemblies 2474	
Bracket 2277	
Bulbs 2277, 2381	
CCFL 2474	
Magnifiers 2277, 2381	
UV 2474	
Laser	
Accessories See digikey.com	
Diodes Modules	
Adjustable Focus 2492	
Infrared 2492	
Laser Line Generator 2492	
HE NE (Helium Neon) See digikey.com	
Receivers See digikey.com	
WBS See digikey.com	
LCDs	
7-Segment Displays 2470, 2476, 2493	
Bezel Displays 2008	
Character Display Modules 2469-2471	
Controller Boards and Accessories 2466	
Dot Matrix Modules 2476	
Graphic Display Modules 2468-2469, 2471, 2476	
Organic (OLED) Displays 2465	
TFT Displays 2466, 2468-2469, 2476	
Development Kits 2468-2469	
LEDs 2405-2406, 2412-2414, 2417-2418, 2423-2424, 2490, 2493-2504, 2510-2520, 2524-2560	
7-Segment Displays 2493, 2505, 2524, 2528, 2550, 2557	
Accessories 2518	
Alphanumeric Displays 2528, 2553	
Arrays/Light Bars 2501, 2503, 2510-2511, 2518, 2524, 2548-2549	
Arrays/Light Engine 2510-2511	
Assemblies 2534, 2537	
Bar Graph Array 2505, 2527, 2550, 2560	
Based 2504, 2512	
Bi-Color 2495-2499, 2501, 2513-2517, 2519-2520, 2525-2527, 2529-2533, 2536-2537, 2556-2557, 2560	
Blue 2494, 2498-2500, 2510-2517, 2519-2520, 2525-2526, 2529-2530, 2532, 2538-2539, 2547-2548, 2552, 2554-2557	
Circuit Board Indicators 2535	
Cluster 2501, 2504	
Connectors 2504	
Design Kits 2548	
Dot Matrix Display 2527	
Driver 2519	
DSP 2494	
Fiber Optic 322	
Flashing/Blinking 2496, 2501, 2534	
Heat Sinks 2510	
Hexadecimal Displays 2553	
High Brightness 2494, 2501, 2519, 2522-2523, 2529-2530, 2532, 2535, 2547-2548, 2554-2557, 2560	
High Power 2532	

J

K

Inverters	
CCFL and UV 2472-2474	
EL Backlighting 2474	
Power 2279	
I/O Modules 2144-2145, 2158-2159	
Isolators See Optoisolators	
Jumper Wire Kits 2232	
Keyboards 2009-2010	
Keypads 2008-2010	
Kits	
Adapters	
RF 444	
BASIC Stamp Kits 626	
Bead Cores 1504	
Buzzers 2183	
Capacitors	
Aluminum Electrolytic 1531, 1533, 1542, 1582, 2280	
Ceramic 1700, 1720, 1749, 2280	
Film 1669, 1685-1686, 1701, 2280, 2282	
Polyester 1668, 1670, 2280	
RF/Microwave 1734	
CeraDiodes 1913	
Chokes 1499	
Connector 185, 208-209, 264, 362	
Crimp Wire Ferrules 336	
Crystal 2282	
Diodes 1261-1262, 2282	
Zener 1261-1262, 2282	
EEPROM Kits 2280	
EMI Components 1500-1503	
ESD 2282	
Fabri-Level™ Switch 2463	
Ferrite Cable Cores 1502-1503	
Ferrite Chips Beads 1497	
Fiber Optic 319	
Fuses 1957-1962, 1966-1968, 2280	
Hardware 2231, 2282	
Heat Shrink Tubing 2174-2177, 2282	
Inductors 1436, 1443-1445, 1450, 2280, 2282, 2321	
Integrated Circuits 2282	
LEDs 2282, 2548	
PC Prototyping Boards 2240	
Potentiometers 1879, 1881-1883, 1885-1886, 1892, 1894, 1901, 1905, 2280	

More Product Available Online: www.digikey.com

Toll-Free: 1-800-344-4539 • Phone 218-681-6674 • Fax: 218-681-3380