

Items listed as digikey.com do not appear in the catalog, but appear on the Digi-Key Web Site.

Holders/Mounts 2222, 2227, 2503
Incandescent Replacement 2504, 2512, 2521
Infrared 2391, 2405-2406, 2412, 2415, 2417-2418, 2423-2424, 2490
Lenses/Caps 2535, 2542, 2549
Level Meters 2560
Low Battery Indicators 2501
Modular 2534
Modules 2222
Multi-Color 2514-2517, 2519, 2537
Numeric Displays 2553, 2557
Panel Mount 2502-2503
RGB (Red/Green/Blue) 2495, 2500, 2510-2511, 2513, 2537, 2548
Smart Displays 2553
Spacers 2215, 2227
Surface Mount 2508-2509, 2549
Through-Hole 2506-2507
White 2494, 2512-2513, 2515, 2519-2520, 2526, 2530-2532, 2535, 2538-2539, 2547-2548, 2555-2557
Wide Angle 2560

Lighting
Connectors 2474, 2504

Light Pipes 2222, 2497, 2521, 2535

Lights
Flashlights 2291
Worklights 2277

Line Conditioners 2278

Lockouts See digikey.com

M

Magnetic Card Readers 2223

Magnets 2107-2108

Magnifiers 2276-2277, 2381

Memory
Cards 1139-1140
Compact Flash 1139-1140
Flash Disks 1139
iDOC 1139
PCMCIA 1140
Secure Digital 1139-1140
uDOC 1139
DiskOnChip 1136
EEPROM 997-998
EEPROM, CMOS 798
EEPROM, Parallel 1041, 1134
EEPROM, Serial 1110-1111, 1133-1135
EPROM 996-998, 1134
FIFO 909-910
Flash 997-998, 1134-1136
INAND 1136
Integrated Circuits
DDR 1125-1126
DDR2 1126
DDR3 1126
EEPROM, Serial 1127-1131
FIFO 1132
Flash 781-782, 1126-1127
PSRAM 1127
SDRAM 1125, 1127
SRAM 1127, 1131-1132
Integrated Circuits/Semiconductors
DDR 1140
DDR2 1140
PROM, Serial 587
SDRAM 1140
Magnetoresistive RAM 778
Modules 1139-1140
NVRAM 998, 1123
SDRAM 1135
Serial Dataflash 1135
SRAM 798, 1135-1136

MESFETs 530

Meters See Test Equipment

Microcontrollers
 See ICs - Microcontrollers

Microphones
Cable 2167
Electret Condenser 2191-2193
Holders 2191, 2193
Magnetic 2194
Silicon 2195

Microprocessors
 See ICs - Microprocessors

Microscopes 2276

MOSFET/MOSFET Drivers 560, 652-653, 971-972, 1164-1167, 1179-1180, 1193, 1205-1216, 1226-1228, 1239, 1253-1255, 1278-1283, 1288-1292, 1295-1297, 1301, 1307, 1309-1311, 1323, 1328-1334

Motor Control
Modular Boards 661

Motors
Geared 1141
Stepper 1141

MOVs See Varistors

O

Optical Enhancement Films 2464

Optoelectronics
Ambient Light Sensor 2408, 2419
Infrared Detectors 2406
Infrared Emitters 2405, 2407, 2409-2410, 2412, 2415, 2417-2418, 2423, 2490
Interrupter Modules 2406
IrDA Transceiver Modules 2423, 2491
Lenses, Spherical 2492
Light Detectors 2405
Logic Detectors 2406
Optical Sensors 2408, 2413, 2415-2416, 2418, 2424, 2490
Reflective 2418-2419, 2424
Orientation Sensor 2412
Photoconductive Cells 2409-2410
Photo Detectors 2406-2407, 2409-2410, 2415, 2424
Photo Diodes 2391, 2405, 2407, 2409-2411, 2417, 2423-2424
Photo ICs 2411, 2424
Photointerrupters 2404, 2418-2419, 2424
Reflective 2404, 2424
Photo Transistors 2391, 2405, 2411, 2415, 2417-2418, 2423
Remote Control Receivers 2491, 2523
Touch Screens 2465-2466

Optoisolators/Photocouplers
Digital 2398, 2402-2403
High Speed Output 2385, 2394, 2401-2402
IREd 2394
Logic Output 2387, 2390, 2394, 2399-2402
Magnetic 2398
Optocouplers 2385-2386
Photo-IC Output 2387
Photo-Transistor Output 2384-2385, 2387-2390, 2392, 2394, 2396-2397, 2399
Photovoltaic 1212, 2394
SCR/Triac Output 2387, 2390
Thyristor Output 2393, 2395

Oscillators 1335-1338, 1344, 1350-1355, 1361-1369, 1374-1379, 1381, 1386-1389
Clock 1335-1338, 1374-1376, 1388
Crystal 1338-1347, 1355, 1365-1369, 1381, 1388
Ovenized (OCXO) 1379, 1382
Programmable 1361-1364
Real Time Clock 1364
SAW (Surface Acoustic Wave) 1382
Silicon 1379
Sockets 1368-1369, 1376

Spread Spectrum 1386
Synchronous Clock Generators 1378
Temperature Compensated (TCXO), (TCVCXO) 1337, 1353, 1363, 1379, 1381-1382, 1387
Voltage Controlled Saw (VCXO) 1382
Voltage Controlled (VCO) 1383-1385
Voltage Controlled (VCXO), (VCTCXO) 1337, 1352, 1354, 1367, 1374, 1378, 1382

P

Panel Meters See Test Equipment

Paper
Thermal Printer 2224
Toner Transfer 2239

PC Board Prototyping
Adapters, Application Specific 2240
Backplanes 2235
Etching Equipment 2238-2239
Extender Cards 2234, 2236
Prototyping Accessories 2212, 2227, 2233-2240, 2250, 2256, 2258
Cleaners and Cloths 2212, 2250, 2256
Etch Resist Pens 2239
PCB Drill Bits 2239
Swabs and Brushes 2238, 2256
Wipes 2250, 2256
Prototyping Boards 2227, 2233, 2235-2240
Copper Clad Boards 2237-2239
Solderless Breadboards 2232, 2236-2237
Terminal/Distribution Strips 2237
Toner Transfer Paper 2239

Photocouplers See Optoisolators

Photo Detectors See Optoelectronics

Photodiodes See Optoelectronics

Phototransistors See Optoelectronics

Potentiometers
Angle Sensing/Positioning 1874, 1899
Audio 1898
Carbon 1882, 1885, 1888, 1894-1895, 1905
Ceramic 1903-1904
Cermet 1864-1869, 1875-1890, 1893, 1899, 1905
Conductive Plastic 1869, 1883, 1889-1891
Digital 654-655
Digital Readout Dial 1895
Joystick Controller 1892
Kits 1879, 1881-1882, 1884-1886, 1894, 1901, 1905, 2280
Panel Control 1869, 1883, 1890
Position Sensor 1900
Rotary 1874, 1899
Slide 1900
Stock Pot™ 1893
Thumbwheel 1899
Trimmer 1864-1868, 1871-1890, 1892-1893, 1899, 1901-1905
Two-Axis Controller 1892
Wirewound 1869-1870, 1880-1883, 1885, 1890, 1894-1895

Power Cords 62-63, 1510-1511
EMI Filters 1502-1503

Power Dividers 1482, 1796

Power Entry Modules 1513, 1515-1517, 1520

Power Outlet 1512

Power Strips 2278-2279

Power Supplies
AC Adapters 2371-2372, 2382-2383
Accessories 2355-2356, 2370

AC-DC Converters 2338-2339, 2345, 2352-2353, 2356, 2363-2367, 2369-2370, 2373-2376, 2381-2383
Configurable 2340
DC-DC Converters 2325-2337, 2346-2347, 2349-2350, 2357-2360, 2365, 2368, 2376-2380
Adjustable Output 2357
Point of Load (POL) 2336, 2357, 2376
Programmable 2345, 2379-2380
Desktop Switchers 2371-2373, 2381-2383
DIN-Rail Mount 2365-2367
Dual Output 2336, 2346, 2358-2360, 2374-2379
Energy Star 2351
External 2264, 2279, 2352-2353, 2355-2356, 2371-2373, 2381-2383
Filters 2335, 2348
Hook-Up Cables 2264
Linear 2353-2354, 2361-2362, 2372, 2381
Medical Grade 2362-2383
Multiple Output 2338-2340, 2358-2360, 2374-2375, 2378, 2382-2383
Power Modules 2340, 2358
Power over Ethernet (PoE) 2351
Single Output 2334, 2336-2341, 2346, 2357-2360, 2374-2380
Switching 2339, 2341-2345, 2351-2353, 2355-2356, 2363-2367, 2369-2379, 2381-2383
Universal Input 2339, 2341, 2352-2354, 2356, 2369-2370, 2381-2383
UPS Systems 2278
Wall Transformers See Transformers

Printers
Accessories 2225
Labels 2225
Thermal 2224-2225
Thermal Paper 2225
Wire Marker 2225

Privacy Filters 2464-2465

Probes
Accessories 2266-2268, 2273
Clips 2268, 2273
Differential 2267
Logic 2266
Oscilloscope 2267, 2270
Pulser 2266
Temperature 2456
Thermocouple 2266, 2268

Programmable and Programming Tools See Development Tools

Prototyping See PC Board Prototyping

Protractors, Digital 2445

R

Raceway
Wire Duct and Accessories 2221

Racks and Accessories
 See Enclosures

Rectifiers See Diodes/Rectifiers

Reference Books See digikey.com

Relays
BGA 2105
Control 2482, 2484
Current Sensing 2438
High Frequency 2105, 2113-2114, 2121
I/O Modules 2144-2145, 2162
Mechanical 2111-2143
Power IC 2146
Reed 2102-2106, 2109
Safety 2144, 2463
Sockets and Accessories 2116, 2118, 2120, 2127-2132, 2137, 2143
Solid State 2144, 2147-2161
Time Delay 2483, 2485

More Product Available Online: www.digikey.com

Toll-Free: 1-800-344-4539 • Phone 218-681-6674 • Fax: 218-681-3380