

Items listed as digikey.com do not appear in the catalog, but appear on the Digi-Key Web Site.

Resistor/Capacitor Networks 1853

Resistors

- Aluminum Housed 1832, 1847
- Anti-Sulfurated See digikey.com
- Arrays 1851, 1853-1858, 1860
- Audio 1822
- Capacitor Discharge 1835
- Capacitor Mount 1822
- Carbon Composition 1827, 1830
- Carbon Film 1815, 1817
- Carbon Film 1847
- Ceramic Composition 1831, 1833
- Chassis Mount 1820-1821, 1823
- Current Sense 1828
- Current Sensing 1819, 1822-1823, 1827, 1829, 1846, 1848
- Heat Sink, Mountable 1825-1826, 1844, 1846, 1850
- High Voltage 1824, 1827, 1834
- Kits 1796-1800, 1809-1813, 1817-1818, 2281
- Metal Element 1823, 1829
- Metal Film 1797, 1814-1816, 1818, 1836-1841, 1843
- Metal Foil 1848
- Metal Oxide Film 1816-1818, 1833, 1842
- Mounting Hardware 1835
- Corrib® 1835
- Networks 1796, 1852-1853, 1857-1859, 1861-1863
- Non-Inductive 1829-1830, 1832
- Power 1820-1827, 1833-1835, 1840-1842, 1844, 1846-1850
- Power RF Terminators 529, 1800
- Precision Thick Film 1849
- Precision Thin Film 1849
- Pulse 1829
- Rheostats 1835
- Surge Capable 1832
- Thermistors See Thermistors
- Thick Film 1801-1807, 1809-1813, 1824-1825, 1827, 1832-1834, 1844, 1846-1847, 1849, 1852, 1860
- Thin Film 1796-1800, 1808, 1819, 1857-1858
- Vitreous Enamel 1831, 1834-1835
- Wide Terminal See digikey.com
- Wire Element 1833
- Wirewound 1789, 1817, 1820-1822, 1826, 1828, 1830-1832, 1839-1843, 1845, 1849-1850
- Zerohm Jumper Wires 1817, 1851

Resonators

- Ceramic 1390-1394, 1396
- SAW 1391, 1393-1394, 1397

RF/Hybrid

- Attenuators 1852
- Balun 1482
- Directional Coupler 1482
- Power Dividers 1482, 1796

RFid See RF/IF

RF/IF

- 3-Phase 1517
- Amplifiers 528-529, 540, 553, 561, 564, 568, 571-572, 579
- Antennas 527-528, 532, 534, 542, 546, 548-552, 574-575, 577
- Attenuators 444, 539
- Baluns 542-543
- Bluetooth® Devices 311, 528, 531, 538-539, 546, 557, 564-565, 569, 573-575
- Modules 539, 546, 557, 569, 573-575
- Serial Modem Adapter/Cord See digikey.com
- USB Adapters 311
- DC Filters 1520
- DDCs 525
- DDS 526
- Development Tools 524, 526-528, 532-533, 539-540, 553-554, 567, 569-570, 572-573, 575, 579
- Diodes 540

- Diplexers 543
- Multilayer 543
- Encoders/Decoders 553, 567
- Ethernet Bridge 532
- Filters 542-544, 574, 579-580
- FM/IF Systems 564
- Frequency Down/Up Converters 560
- Gain Blocks 524, 564
- Gain Phase Detectors 524
- General Purpose 1517-1519
- GPS 528
- Hardware 536-537
- IEC Inlet Line Filters 1520-1521
- IF Receivers 525
- Interface 528, 532
- Line Filters 1517-1521
- Log Amps/Detectors 547
- Medical Grade Filters 1519
- Mixers/Multipliers 547, 564
- Modems 533, 555-556, 622-623
- Modulator/Demodulator 524, 528, 547, 568
- OEM/RF Modules 528, 533, 552-554, 566-567, 570, 573
- ZigBee™ Modules 554
- PC Board Mountable Filters 1520
- PLL Synthesizers and VCOs 525, 557-558, 565
- Prescalers 560
- Reader Modules 535-536, 563, 578
- RFid 580
- Antenna 535-536
- Base Station IC 528, 578
- Development Kits 554, 572, 579
- Modules 572, 577, 580
- Readers 578, 1004
- Transmitters/Receivers 554, 565-566
- Transponders 576-577
- RF Modules 526, 545-546
- RMS Detectors 524
- Shielding 538
- Splitter 524
- Switches 539, 560
- Synthesizers 557, 570, 575
- Terminators 1819
- Test Equipment 544
- Transistors 529, 539-540, 559, 562
- Transmitters/Receivers 525, 527-528, 539-540, 554-555, 565, 567, 569, 575, 579, 659, 779
- RX/TX Subsystems 525
- WiMAX Power Amp 524
- Wireless Modules 541
- Wireless Networking Tools 532-533, 567, 570
- WLAN 530, 546, 565
- ZigBee™ Devices 538-539, 555, 561, 566, 573

RFI Suppression... 1496-1499, 1501-1503

Ribbon Cable, Filters 1501

RTDs (Resistance Temperature Detectors) 2456

S

- SCRs** 1225, 1236, 1250, 1296, 1321-1322, 1929
- Security Guards** 2012
- Semiconductors** See Integrated Circuits
- Sensors/Controllers**
- Accelerometer 2194, 2432-2433, 2450-2453
- Air Flow 2413-2414, 2426
- Ambient Light 2407
- Clinometers 2445
- Current 621, 1172, 2421, 2435, 2437-2439, 2441
- Digital Compass 2440-2442
- Distance Measuring 2405
- Electromechanical Controls 2464

- Evaluation Kits and Modules 2449, 2451, 2462
- Flow 2463
- Flow Switch 2431, 2463
- Fluid 2416, 2449
- Force 2446
- Gas See digikey.com
- Gas Flow 2414
- Gear Tooth 2462
- Hall Effect 2420-2421, 2423, 2439-2440
- Programmable 2420
- Humidity 2446-2447
- Illumination 2404
- Image 723
- Evaluation Kits 723
- Inclinometer 2452-2453
- Infrared Receivers 2490
- Liquid Level 320, 2108, 2421, 2431, 2462
- Load Cells 2446
- Magnetic 1172, 2106-2107, 2110, 2440-2441, 2462
- Magnetoresistive (MR) ... 2421, 2441, 2462
- Motion 2416
- Optical/Light 2408, 2411, 2413, 2415-2416, 2418, 2423
- Oxygen 2421
- Interface Boards 2421
- Packard™ Harnesses 2443
- Photoelectric 2448
- Piezo 2452
- Position/Proximity 1874, 1899, 2106-2108, 2408, 2414, 2434, 2447, 2449
- Magnetic 2106-2108
- Pressure 2414, 2425-2431, 2433-2435, 2442-2447, 2452
- Smoke Detection 779
- Switch 2421
- Temperature 2421, 2446
- Thermal 1978
- Thermopile See digikey.com
- Touch 2449
- Ultrasonic 2195, 2450
- Vacuum 2427
- Variable Reluctance Sensor (VRS) ... 2422
- Vibration 2414, 2452

Sidacs 1321

Sidactors 1940-1941

Socket Modems 555-556, 622-623

Sockets See also IC Sockets

- DIMM 468, 491, 493
- Lamp 2535
- Oscillator 1376, 1368-1369
- SIM Card 486
- SIMM 493
- Strip 509-511, 513, 517
- Transistor 1153
- Zig-Zag 515

Socket Wrap ID 504

Solar Cell Photovoltaic 2148

Solder/Desolder

- Accessories 2238, 2251-2258
- Desolder Braid 2238, 2256, 2258
- Desolder Pump 2255
- Flux Pens 2238, 2254, 2256, 2258
- Paste and Dispensers 2258
- Pocket Dispensers 2256
- Replacement Tips 2251-2254, 2258
- Solders 2257-2258
- Solvent Dispensers 2254
- Sponges 2258
- Thermal Tweezers 2252
- Vacuum Pickup Tool 2253
- Equipment 2251-2255
- Cordless Solder Iron 2254
- Fume/Smoke Absorbers 2254-2255
- Rework/Repair 2251-2254
- SMD Removal Kits 2255
- Solder Irons 2254

Solenoids 1141

Speakers

- Balanced Armature 2195
- General Purpose 2179
- Headset/Handset 2195
- Hi-Fi 2178
- Mini 2178
- Miniature Monitor 2179
- Notebook 2180
- Specialty 2195

Static Control Products 2247-2250

Stepper Motors 1141

Surface Mount Products See specific product listing

Surge Protection Components

- Surge Absorbers
- Arrays 1908
- Multilayer Chip 1908
- SiBar Thyristors 1950, 1952
- ZNRs 1906-1907, 1909
- Surge Arresters (GDTs) 1911, 1914, 1916-1917
- Surge Suppressors 1922, 1954, 1956, 2278-2279, 2365
- Arrays 1956
- Multilayer Chip 1915, 1954

Swabs and Applicators 2238, 2256

Switches

- Accessories 1998, 2002-2003, 2005-2006, 2012, 2015, 2017-2019, 2022-2026, 2037, 2041-2044, 2053-2054, 2057, 2059-2060, 2074, 2080
- Caps 1998, 2006, 2018, 2025, 2041-2044
- Frames 2042
- Seals 2012
- Splashproof Boots 2006, 2017, 2022, 2024-2025, 2037
- Basic Limit 2071-2072, 2075-2078
- Detector 1992-1994, 1996
- DIP 2087-2097
- Disconnect, DIN Rail Mount 2057
- Door 2070, 2072, 2084
- Emergency Stop 2049-2051, 2053, 2055-2057
- Fiber Optic 318
- Illuminated 1996, 2001, 2023, 2037-2038, 2041, 2053-2056, 2058-2060
- Interlocks 2084
- Intra-Switch™ 504
- Joysticks 2048
- Keylock 2034, 2049, 2051, 2053, 2055-2056, 2066-2067
- Keypads 2008-2010
- Key Switch 2001, 2004-2005, 2010, 2053, 2056, 2060, 2066-2067
- Kits 2061, 2282
- Knob Switches 2054, 2056, 2087
- Limit 2071-2074
- Magnetic 2107, 2109-2110, 2420
- Matrix Selector See digikey.com
- Microswitch 2083
- Navigation 1998, 2003
- Paddle See Toggle
- Pilot Lights 2053-2054
- Power 1986, 2043, 2148
- Pressure 2447
- Pushbutton 1986-1991, 1994, 2002, 2004-2006, 2008, 2018, 2025-2026, 2033, 2037-2051, 2053, 2055, 2058-2060, 2070
- Push/Pull 2066
- Pushwheel 2011
- Reed 2107, 2109-2110
- Rocker 2006-2007, 2026-2031, 2033-2038

More Product Available Online: www.digikey.com
 Toll-Free: 1-800-344-4539 • Phone 218-681-6674 • Fax: 218-681-3380