

Items listed as digikey.com do not appear in the catalog, but appear on the Digi-Key Web Site.

3M

- Adhesives
 - Clean-Walk 2212
 - Command™ 2212
 - Hot Melt 2212
 - Scotch-Weld™ 2212
- Breadboards 2232
- Bumpers 2212
- Cable
 - Flat 47
 - Ribbon 47, 56-57, 168
 - Round Jacketed/Shielded 47, 2165
 - Ties 2226
- Cable Assemblies 44
- PCB 44
- Termination Jumpers 44
- Cleaning Cloth 2212
- Connector Hardware 265
- Connectors
 - 0.1" 45
 - 2mm 167-169
 - Mini-Clamp 169
 - IDC 44, 56
 - Intra-Connector™ 504
 - Intra-Switch™ 504
- Memory
 - Compact Flash 490
 - DDR 490
 - microSD™ 489
 - SD™ 489
 - Secure Digital 490
- MetPak™
 - 2FP 480
 - CP2 481
 - HSHM 481
 - miniSAS 480
 - PCB 44
- Ribbon
 - Mini D 56-57
 - Shielded 57
- SATA 57
- Scotchlok™ 362-363
- SCSI 480
- EMI Suppression
 - Absorber Pads 523
- Headers 45, 167
- Heat Shrink Tubing 2174
- Hook and Loop Fasteners
 - Dual Lock™ 2215
 - Scotchmate™ 2215
- IC Sockets
 - DIP 521
 - PLCC Carrier 522
 - Type 'A' LCC 522
 - ZIF 490, 520-521
 - ZIP DIP 520-521
- IC Test Clips 522
- Jumper Wire 2232
- Kits
 - Heat Shrink Tubing 2174, 2282
 - Insulated Terminals 362
- Optical Enhancement Films 2464
- Optoelectronics 2465
- Touch Screens 2465
- Patch Cords 2272
- Privacy Filters 2464-2465
- Probe-It Clips 2273
- Shorting Jumpers 237
- Static Control Products 2247-2250
- Tape
 - Attachment 2213
 - Duct 2213
 - Electrical 523, 2213
 - Fabric 523
 - Foam 2213
 - Foil Shielding 523, 2213
 - Low Static 2213
 - Splicing 2214
 - Water Soluble 2213-2214
- Terminal Connectors 361-362
- Terminal Strips 2237
- Tools, Crimp 362
- Vacuum 2232
- Wire Marker Tape Dispensers 2214

A

- Aavid Thermalloy**
 - Heat Sinks 1142-1145
 - BGA 1145
 - Thermal Compound 1142
- Abrakon Corporation**
 - Crystals 1348-1350
 - Filters, SAW 1391
 - Oscillators 1350-1352, 1362
 - Programmable 1362
 - Resonators
 - Ceramic 1391
 - SAW 1391
- ACL Staticide, Inc.**
 - Cleaning Wipes 2250
 - Static Control Equipment See digikey.com
 - Static Control Products 2247, 2250
 - Static Dissipative Soap 2250
- ADI** See Analog Devices, Inc.
- Advanced Photonix, Inc.**
 - Photo Diodes/Emitters 2409-2410
- Advanced Thermal Solutions, Inc.**
 - Heat Sinks
 - BGA 1148-1151
 - LED 1151
 - LGA 1151
 - Tools 1149
- Airpax** See Sensata Technologies, Airpax
- Alcoswitch Tyco** See Tyco Electronics
- Alcoswitch
- AlfaMag Electronics, LLC**
 - Inductors 1462
- Allegro MicroSystems, Inc.**
 - Integrated Circuits
 - Hall Effect Sensors 985-986
 - Motor Drivers 986-987
 - Power Management 987
- All Sensors Corporation**
 - Pressure Sensors 2435
- Alpha & Omega Semiconductor, Inc.**
 - MOSFET/MOSFET Drivers 1333-1334
 - Transient Voltage Suppressors (TVS) 1938
 - Voltage Regulators 1938
- Alpha Wire Company**
 - Cable
 - Bus Bar 2171
 - Coaxial 2172
 - Ethernet 2172
 - Hook-Up 2170-2172
 - Multiconductor 2169-2170
 - Multi-paired 2168
 - Sleeving 2171
 - Spiral Wrap 2172
 - Test Lead 2171
 - Tinned Copper Flat Braid 2171
 - Heat Guns 2173
 - Tubing
 - Fabric 2173
 - Heat Shrink 2173
 - Teflon 2171
- Altera**
 - Cables/Programming Hardware 595
 - Development Kits and Tools 596-598
 - Evaluation Kits 596
 - Integrated Circuits/Semiconductors
 - CPLDs 593-595
 - FPGAs 589-593
- American Electrical, Inc.**
 - Cable Grips 2165
 - Circuit Breakers, DIN Rail Mount 1981
 - DIN Rail Mount 338
 - Disconnect Switches 2057
 - Accessories 2057

- Interface Modules and Cables 338
- Terminal Blocks
 - Accessories 337-338
 - DIN Rail Mount 337-338
 - Tools, Crimp 336
 - Wire Ferrules 336
- Ametherm**
 - Inrush Current Limiters 1947
 - Thermistors, NTC 2456
- Amphenol Commercial Products**
 - Connectors
 - D-Sub 297-298
 - Backshells 298
 - High Density 298
 - Infinity 499
 - Modular, Ethernet 297-298
 - SAS 499
 - SFP 499
 - USB 297
 - RF Adapters 425-428
 - RF Connectors
 - BNC 425
 - MCX/MMCX 427
 - N Type 427
 - SMA/SMB 425-426
 - TNC 428
 - Tools, Crimp 428
- Amphenol - Connex**
 - RF Adapters 425-428
 - RF Connectors
 - 97 Series 386-388
 - Accessories 387-388
 - IP67 389
 - MS Series 384, 388
 - PT Series 383-385
 - RADSOK® 382
 - Waterproof 389
 - Cord Grips 2165
- Amphenol - PCD**
 - Connectors
 - IEEE 1394 307
 - Modular, Ethernet (RJ11) 306-307
 - Terminal Splices 333-335
 - DIN Rail Mounted 335
 - PCB Mounted 333-335
 - Pluggable 333-334
 - USB 307
- Amphenol - RF Division**
 - Adapters, RF Coaxial 432, 434
 - RF Connectors
 - AMC 430
 - BNC 431-432
 - N Type 432
 - SMA/SMB 429-430, 433
 - FAKRA (SMB) 429-430
 - QMA (SMA) 430
 - SMP 430
 - TNC 432
 - Twinaxial 432
 - UHF 434
 - Tools, Crimp 430, 434
- Amphenol - Tuchel Electronics**
 - Cable Assemblies
 - eco/mate™ 390
 - Connectors
 - Backshell Kit See digikey.com
 - Circular
 - 44 Series 392
 - C16 390
 - C091 391-392
 - eco/mate™ 390
 - Hand Tools 391-392
 - Rectangular, Heavy Duty 212
 - Smart Card 500
- Amprobe**
 - Test Equipment
 - Accessories 2262-2263
 - Clamp Meters 2262-2263
 - Data Logger 2262
 - Hygrometer 2263
 - Kits 2262-2263

- Megohmmeter 2263
- Multimeters 2262-2263
- Power Recorder 2263
- Psychrometer 2263
- Relay Switch 2263
- Resistivity Tester 2263
- Rotation 2263
- Test Leads 2262
- Voltage Detection 2263
- Wire Tracer 2263
- AMP Tyco** See Tyco Electronics AMP
- Amulet Technologies LLC**
 - Graphic LCD Tool Kits 2469
- Amveco Magnetics**
 - Transformers
 - Current Sense 2439
 - Medical Grade 2318
 - Power 2318
 - Toroidal 2317-2318
- Analog Devices, Inc.**
 - DSP Emulators/Programmers 726-728
 - Gyroscopes 2451
 - ICs/Semiconductors 773
 - Amplifiers 752-758
 - Analog Computation Circuits 758
 - Analog/Digital Audio 758
 - ATE and Time Domain 758
 - Audio/Video 758
 - CCD 758
 - Clock Generation and Distribution 758
 - Data Communication 758-759
 - Data Conversion 759-765
 - Digital Potentiometers 765-766
 - Display and Video Converters 766
 - Evaluation Boards 766
 - Fiber Optics and Networks 766
 - Hardware Monitors and Thermal Management 766-767
 - Interface 767-768
 - Microcontrollers 728-729
 - MicroConverter® 728-729
 - Motion/Motor Control 768
 - Power Management 769-772
 - Sensor/Signal Conditioning 772-773
 - Specialized IC 773
 - Supervisory Circuits/Reset Generators 773
 - Switches 774-775
 - Waveform Generators 772
 - Isolators, Digital 2403
 - RF/IF Products 523-526
 - DDCs 525
 - DDSS 526
 - IF Receivers 525
 - Sensors, Accelerometers 2451
 - Evaluation Boards 2451
- Antenna**
 - Antennas 526
- APEM Components, Inc.**
 - Security Guards 2012
 - Switches
 - Emergency Stop 2049
 - Joysticks 2048
 - Keylock 2034, 2049
 - Pushbutton 2045, 2047-2049
 - Rocker 2034
 - Toggle 2024, 2034
- API Delevan**
 - Bead Cores 1450
 - Cable EMI Ferrite Cores 1450
 - EMI Suppression Cable Cores 1450
 - Ferrites, Flexible Material/Tubing 1450
 - Inductors
 - Air Core 1450
 - Chip See digikey.com
 - Coils 1442
 - Common Mode Choke 1449-1450
 - Filter 1442
 - Fixed 1442-1450
 - High Current 1442, 1445-1448
 - Kits 1443-1445, 1450
 - Power Choke 1446-1448
 - Shielded 1442-1448
 - Toroidal See digikey.com

MANUFACTURER'S INDEX

More Product Available Online: www.digikey.com

Toll-Free: 1-800-344-4539 • Phone 218-681-6674 • Fax: 218-681-3380