



**Termination Jumpers**

**Socket Connector — Single Ended (Cont.)**



No. of Cont.	Cont. Finish	Length Inch(cm)	Ribbon Cable*	Digi-Key Part No.	Price Each 1 10
14	Gold	36(91.44)	MC	C1AXG-1436M-ND	5.35 4.06
	Tin	36(91.44)	MC	C1AXS-1436M-ND	5.10 3.87
	Gold	36(91.44)	GR	C1AXG-1436G-ND	2.80 2.13
	Tin	36(91.44)	GR	C1AXS-1436G-ND	2.55 1.94
16	Gold	36(91.44)	MC	C1AXG-1636M-ND	5.87 4.45
	Tin	36(91.44)	MC	C1AXS-1636M-ND	5.56 4.22
	Gold	36(91.44)	GR	C1AXG-1636G-ND	3.23 2.45
	Tin	36(91.44)	GR	C1AXS-1636G-ND	2.92 2.21
20	Gold	36(91.44)	MC	C1AXG-2036M-ND	6.92 5.25
	Tin	36(91.44)	MC	C1AXS-2036M-ND	6.61 5.02
	Gold	36(91.44)	GR	C1AXG-2036G-ND	3.82 2.90
	Tin	36(91.44)	GR	C1AXS-2036G-ND	3.51 2.67
26	Gold	36(91.44)	MC	C1AXG-2636M-ND	8.77 6.65
	Tin	36(91.44)	MC	C1AXS-2636M-ND	8.40 6.37
	Gold	36(91.44)	GR	C1AXG-2636G-ND	4.63 3.51
	Tin	36(91.44)	GR	C1AXS-2636G-ND	4.26 3.23
34	Gold	36(91.44)	MC	C1AXG-3436M-ND	11.28 8.56
	Tin	36(91.44)	MC	C1AXS-3436M-ND	10.82 8.20
	Gold	36(91.44)	GR	C1AXG-3436G-ND	5.39 4.09
	Tin	36(91.44)	GR	C1AXS-3436G-ND	4.92 3.74
40	Gold	36(91.44)	MC	C1AXG-4036M-ND	13.04 9.89
	Tin	36(91.44)	MC	C1AXS-4036M-ND	12.51 9.49
	Gold	36(91.44)	GR	C1AXG-4036G-ND	6.61 5.01
	Tin	36(91.44)	GR	C1AXS-4036G-ND	6.08 4.61
50	Gold	36(91.44)	MC	C1AXG-5036M-ND	16.12 12.23
	Tin	36(91.44)	MC	C1AXS-5036M-ND	15.50 11.76
	Gold	36(91.44)	GR	C1AXG-5036G-ND	7.45 5.66
	Tin	36(91.44)	GR	C1AXS-5036G-ND	6.83 5.19
60	Gold	36(91.44)	MC	C1AXG-6036M-ND	19.43 14.73
	Tin	36(91.44)	MC	C1AXS-6036M-ND	18.68 14.17
	Gold	36(91.44)	GR	C1AXG-6036G-ND	9.54 7.24
	Tin	36(91.44)	GR	C1AXS-6036G-ND	8.80 6.68


Also available in the following versions:

- C3BB□-□□□□-ND — Socket Connector with Strain Relief.
- C1CX□-□□□□-ND — Socket Connector with Central Polarizing Key.
- C1DX□-□□□□-ND — Socket Connector with Strain Relief and Central Polarizing Key.

Call for complete part number and pricing!

**PCB Connector — Single Ended**

\* MC = Multi-Color, GR = Gray



PCB connector without strain relief shown.

No. of Cont.	Cont. Finish	Length Inch(cm)	Ribbon Cable*	Digi-Key Part No.	Price Each 1 10
10	Tin	36(91.44)	MC	C1PXS-1036M-ND	3.77 2.86
	Tin	36(91.44)	GR	C1PXS-1036G-ND	2.12 1.61
20	Tin	36(91.44)	MC	C1PXS-2036M-ND	6.39 4.85
	Tin	36(91.44)	GR	C1PXS-2036G-ND	3.30 2.50
26	Tin	36(91.44)	MC	C1PXS-2636M-ND	8.30 6.30
	Tin	36(91.44)	GR	C1PXS-2636G-ND	4.16 3.16
34	Tin	36(91.44)	MC	C1PXS-3436M-ND	10.69 8.11
	Tin	36(91.44)	GR	C1PXS-3436G-ND	6.05 4.59
40	Tin	36(91.44)	MC	C1PXS-4036M-ND	12.48 9.46
	Tin	36(91.44)	GR	C1PXS-4036G-ND	6.05 4.59
50	Tin	36(91.44)	MC	C1PXS-5036M-ND	15.60 11.83
	Tin	36(91.44)	GR	C1PXS-5036G-ND	6.93 5.26
60	Tin	36(91.44)	MC	C1PXS-6036M-ND	18.53 14.05
	Tin	36(91.44)	GR	C1PXS-6036G-ND	8.64 6.56

**Card Edge Connector — Single Ended**

\* MC = Multi-Color, GR = Gray




Card Edge connector without strain relief shown.

No. of Cont.	Cont. Finish	Length Inch(cm)	Ribbon Cable*	Digi-Key Part No.	Price Each 1 10
10	Gold	36(91.44)	MC	C1EXG-1036M-ND	5.07 3.85
	Tin	36(91.44)	MC	C1EXS-1036M-ND	4.67 3.54
	Gold	36(91.44)	GR	C1EXG-1036G-ND	3.42 2.60
	Tin	36(91.44)	GR	C1EXS-1036G-ND	3.02 2.29
20	Gold	36(91.44)	MC	C1EXG-2036M-ND	8.38 6.36
	Tin	36(91.44)	MC	C1EXS-2036M-ND	7.85 5.96
	Gold	36(91.44)	GR	C1EXG-2036G-ND	5.28 4.01
	Tin	36(91.44)	GR	C1EXS-2036G-ND	4.75 3.61
26	Gold	36(91.44)	MC	C1EXG-2636M-ND	10.50 7.97
	Tin	36(91.44)	MC	C1EXS-2636M-ND	9.85 7.47
	Gold	36(91.44)	GR	C1EXG-2636G-ND	6.36 4.83
	Tin	36(91.44)	GR	C1EXS-2636G-ND	5.71 4.34
34	Gold	36(91.44)	MC	C1EXG-3436M-ND	13.45 10.20
	Tin	36(91.44)	MC	C1EXS-3436M-ND	12.68 9.61
	Gold	36(91.44)	GR	C1EXG-3436G-ND	7.56 5.73
	Tin	36(91.44)	GR	C1EXS-3436G-ND	6.78 5.15

No. of Cont.	Cont. Finish	Length Inch(cm)	Ribbon Cable*	Digi-Key Part No.	Price Each 1 10
40	Gold	36(91.44)	MC	C1EXG-4036M-ND	15.79 11.98
	Tin	36(91.44)	MC	C1EXS-4036M-ND	14.86 11.27
	Gold	36(91.44)	GR	C1EXG-4036G-ND	9.37 7.11
	Tin	36(91.44)	GR	C1EXS-4036G-ND	8.44 6.40
50	Gold	36(91.44)	MC	C1EXG-5036M-ND	18.98 14.39
	Tin	36(91.44)	MC	C1EXS-5036M-ND	17.92 13.59
	Gold	36(91.44)	GR	C1EXG-5036G-ND	10.31 7.82
	Tin	36(91.44)	GR	C1EXS-5036G-ND	9.25 7.02

**Socket Connector to Socket Connector**

\* MC = Multi-Color, GR = Gray



Socket connector without strain relief shown.

No. of Cont.	Cont. Finish	Length Inch(cm)	Ribbon Cable*	Digi-Key Part No.	Price Each 1 10
10	Gold	6(15.24)	MC	C3AAG-1006M-ND	2.88 2.19
	Tin	6(15.24)	MC	C3AAS-1006M-ND	2.51 1.91
	Gold	6(15.24)	GR	C3AAG-1006G-ND	2.61 1.98
	Tin	6(15.24)	GR	C3AAS-1006G-ND	2.23 1.70
14	Gold	18(45.72)	MC	C3AAG-1018M-ND	3.68 2.80
	Tin	18(45.72)	MC	C3AAS-1018M-ND	3.31 2.51
	Gold	18(45.72)	GR	C3AAG-1018G-ND	2.86 2.17
	Tin	18(45.72)	GR	C3AAS-1018G-ND	2.49 1.89
16	Gold	36(91.44)	MC	C3AAG-1036M-ND	4.89 3.71
	Tin	36(91.44)	MC	C3AAS-1036M-ND	4.51 3.43
	Gold	36(91.44)	GR	C3AAG-1036G-ND	3.24 2.46
	Tin	36(91.44)	GR	C3AAS-1036G-ND	2.87 2.18
14	Gold	6(15.24)	MC	C3AAG-1406M-ND	4.07 3.09
	Tin	6(15.24)	MC	C3AAS-1406M-ND	3.58 2.72
	Gold	6(15.24)	GR	C3AAG-1406G-ND	3.65 2.77
	Tin	6(15.24)	GR	C3AAS-1406G-ND	3.15 2.39
14	Gold	18(45.72)	MC	C3AAG-1418M-ND	5.28 4.00
	Tin	18(45.72)	MC	C3AAS-1418M-ND	4.78 3.63
	Gold	18(45.72)	GR	C3AAG-1418G-ND	4.00 3.04
	Tin	18(45.72)	GR	C3AAS-1418G-ND	3.51 2.66
14	Gold	36(91.44)	MC	C3AAG-1436M-ND	7.08 5.37
	Tin	36(91.44)	MC	C3AAS-1436M-ND	6.59 5.00
	Gold	36(91.44)	GR	C3AAG-1436G-ND	4.53 3.44
	Tin	36(91.44)	GR	C3AAS-1436G-ND	4.04 3.07
16	Gold	6(15.24)	MC	C3AAG-1606M-ND	4.67 3.55
	Tin	6(15.24)	MC	C3AAS-1606M-ND	4.05 3.08
	Gold	6(15.24)	GR	C3AAG-1606G-ND	4.23 3.21
	Tin	6(15.24)	GR	C3AAS-1606G-ND	3.61 2.74
16	Gold	18(45.72)	MC	C3AAG-1618M-ND	5.96 4.52
	Tin	18(45.72)	MC	C3AAS-1618M-ND	5.34 4.05
	Gold	18(45.72)	GR	C3AAG-1618G-ND	4.64 3.52
	Tin	18(45.72)	GR	C3AAS-1618G-ND	4.02 3.05
16	Gold	36(91.44)	MC	C3AAG-1636M-ND	7.98 5.98
	Tin	36(91.44)	MC	C3AAS-1636M-ND	7.26 5.51
	Gold	36(91.44)	GR	C3AAG-1636G-ND	5.24 3.98
	Tin	36(91.44)	GR	C3AAS-1636G-ND	4.62 3.51
20	Gold	6(15.24)	MC	C3AAG-2006M-ND	5.02 3.81
	Tin	6(15.24)	MC	C3AAS-2006M-ND	4.40 3.34
	Gold	6(15.24)	GR	C3AAG-2006G-ND	4.50 3.42
	Tin	6(15.24)	GR	C3AAS-2006G-ND	3.88 2.95
20	Gold	18(45.72)	MC	C3AAG-2018M-ND	6.62 5.02
	Tin	18(45.72)	MC	C3AAS-2018M-ND	6.00 4.55
	Gold	18(45.72)	GR	C3AAG-2018G-ND	5.07 3.85
	Tin	18(45.72)	GR	C3AAS-2018G-ND	4.45 3.38
20	Gold	36(91.44)	MC	C3AAG-2036M-ND	9.03 6.85
	Tin	36(91.44)	MC	C3AAS-2036M-ND	8.41 6.38
	Gold	36(91.44)	GR	C3AAG-2036G-ND	5.93 4.50
	Tin	36(91.44)	GR	C3AAS-2036G-ND	5.31 4.03
26	Gold	6(15.24)	MC	C3AAG-2606M-ND	6.06 4.60
	Tin	6(15.24)	MC	C3AAS-2606M-ND	5.32 4.04
	Gold	6(15.24)	GR	C3AAG-2606G-ND	5.37 4.08
	Tin	6(15.24)	GR	C3AAS-2606G-ND	4.63 3.51
26	Gold	18(45.72)	MC	C3AAG-2618M-ND	8.15 6.18
	Tin	18(45.72)	MC	C3AAS-2618M-ND	7.41 5.62
	Gold	18(45.72)	GR	C3AAG-2618G-ND	6.08 4.61
	Tin	18(45.72)	GR	C3AAS-2618G-ND	5.34 4.05
26	Gold	36(91.44)	MC	C3AAG-2636M-ND	11.28 8.55
	Tin	36(91.44)	MC	C3AAS-2636M-ND	10.53 7.99
	Gold	36(91.44)	GR	C3AAG-2636G-ND	7.14 5.42
	Tin	36(91.44)	GR	C3AAS-2636G-ND	6.39 4.85
34	Gold	6(15.24)	MC	C3AAG-3406M-ND	7.56 5.74
	Tin	6(15.24)	MC	C3AAS-3406M-ND	6.63 5.03
	Gold	6(15.24)	GR	C3AAG-3406G-ND	6.58 4.99
	Tin	6(15.24)	GR	C3AAS-3406G-ND	5.65 4.29
34	Gold	18(45.72)	MC	C3AAG-3418M-ND	10.29 7.81
	Tin	18(45.72)	MC	C3AAS-3418M-ND	9.36 7.10
	Gold	18(45.72)	GR	C3AAG-3418G-ND	9.34 5.57
	Tin	18(45.72)	GR	C3AAS-3418G-ND	6.41 4.87
34	Gold	36(91.44)	MC	C3AAG-3436M-ND	14.38 10.91
	Tin	36(91.44)	MC	C3AAS-3436M-ND	13.45 10.20
	Gold	36(91.44)	GR	C3AAG-3436G-ND	8.49 6.44
	Tin	36(91.44)	GR	C3AAS-3436G-ND	7.56 5.73
40	Gold	6(15.24)	MC	C3AAG-4006M-ND	8.42 6.39
	Tin	6(15.24)	MC	C3AAS-4006M-ND	7.37 5.59
	Gold	6(15.24)	GR	C3AAG-4006G-ND	7.35 5.58
	Tin	6(15.24)	GR	C3AAS-4006G-ND	6.30 4.78
40	Gold	18(45.72)	MC	C3AAG-4018M-ND	11.63 8.82
	Tin	18(45.72)	MC	C3AAS-4018M-ND	10.58 8.02
	Gold	18(45.72)	GR	C3AAG-4018G-ND	8.42 6.39
	Tin	18(45.72)	GR	C3AAS-4018G-ND	7.36 5.59

No. of Cont.	Cont. Finish	Length Inch(cm)	Ribbon Cable*	Digi-Key Part No.	Price Each 1 10
40	Gold	36(91.44)	MC	C3AAG-4036M-ND	16.45 12.47
	Tin	36(91.44)	MC	C3AAS-4036M-ND	15.39 11.67
	Gold	36(91.44)	GR	C3AAG-4036G-ND	10.02 7.60
	Tin	36(91.44)	GR	C3AAS-4036G-ND	8.96 6.80
50	Gold	6(15.24)	MC	C3AAG-5006M-ND	10.19 7.73
	Tin	6(15.24)	MC	C3AAS-5006M-ND	8.95 6.79
	Gold	6(15.24)	GR	C3AAG-5006G-ND	8.74 6.63
	Tin	6(15.24)	GR	C3AAS-5006G-ND	7.50 5.69
50	Gold	18(45.72)	MC	C3AAG-5018M-ND	14.20 10.77
	Tin	18(45.72)	MC	C3AAS-5018M-ND	12.96 9.83
	Gold	18(45.72)	GR	C3AAG-5018G-ND	9.87 7.48
	Tin	18(45.72)	GR	C3AAS-5018G-ND	8.63 6.54
50	Gold	36(91.44)	MC	C3AAG-5036M-ND	20.22 15.33
	Tin	36(91.44)	MC	C3AAS-5036M-ND	18.98 14.39
	Gold	36(91.44)	GR	C3AAG-5036G-ND	11.55 8.76
	Tin	36(91.44)	GR	C3AAS-5036G-ND	10.31 7.82
60	Gold	6(15.24)	MC	C3AAG-6006M-ND	12.39 9.40
	Tin	6(15.24)	MC	C3AAS-6006M-ND	10.90 8.27
	Gold	6(15.24)	GR	C3AAG-6006G-ND	10.74 8.15
	Tin	6(15.24)	GR	C3AAS-6006G-ND	9