




Dip Plug Cable Assemblies
Single Ended Style 2 (Cont.)



No. of Contacts	Contact Finish	Length Inch (cm)	Rib-on-Cable	Digi-Key Part No.	Price Each 1 10
10	Gold	6 (15.24)	GR	H2PXH-1036G-ND	3.98 3.02
	Tin	6 (15.24)	GR	H2PXS-1036G-ND	3.98 3.02
14	Gold	6 (15.24)	MC	H2PXH-1406M-ND	4.32 3.28
	Gold	6 (15.24)	GR	H2PXS-1406G-ND	3.90 2.96
	Gold	6 (15.24)	GR	H2PXS-1406G-ND	3.90 2.96
	Gold	18 (45.72)	MC	H2PXH-1418M-ND	5.52 4.19
	Tin	18 (45.72)	MC	H2PXS-1418M-ND	5.52 4.19
	Tin	18 (45.72)	GR	H2PXS-1418G-ND	4.25 3.23
16	Gold	6 (15.24)	MC	H2PXH-1606M-ND	4.32 3.28
	Gold	6 (15.24)	GR	H2PXS-1606G-ND	3.90 2.96
	Gold	6 (15.24)	GR	H2PXS-1606G-ND	3.92 2.98
	Gold	18 (45.72)	MC	H2PXH-1618M-ND	5.65 4.28
	Tin	18 (45.72)	MC	H2PXS-1618M-ND	5.65 4.28
	Tin	18 (45.72)	GR	H2PXS-1618G-ND	4.33 3.28
20	Gold	6 (15.24)	MC	H2PXH-2006M-ND	5.20 3.95
	Gold	6 (15.24)	GR	H2PXS-2006G-ND	4.69 3.56
	Gold	6 (15.24)	GR	H2PXS-2006G-ND	4.69 3.56
	Gold	18 (45.72)	MC	H2PXH-2018M-ND	6.81 5.17
	Tin	18 (45.72)	MC	H2PXS-2018M-ND	6.81 5.17
	Tin	18 (45.72)	GR	H2PXS-2018G-ND	5.26 3.99
24	Gold	6 (15.24)	MC	H2PXH-2406M-ND	9.21 6.99
	Gold	6 (15.24)	GR	H2PXS-2406G-ND	6.12 4.64
	Gold	6 (15.24)	GR	H2PXS-2406G-ND	6.12 4.64
	Gold	18 (45.72)	MC	H2PXH-2418M-ND	11.72 8.85
	Tin	18 (45.72)	MC	H2PXS-2418M-ND	11.72 8.85
	Tin	18 (45.72)	GR	H2PXS-2418G-ND	9.03 6.85
40	Gold	6 (15.24)	MC	H2PXH-4006M-ND	15.45 11.72
	Gold	6 (15.24)	GR	H2PXS-4006G-ND	10.67 8.09
	Gold	6 (15.24)	GR	H2PXS-4006G-ND	10.67 8.09
	Gold	18 (45.72)	MC	H2PXH-4018M-ND	16.64 12.49
	Tin	18 (45.72)	MC	H2PXS-4018M-ND	16.64 12.49
	Tin	18 (45.72)	GR	H2PXS-4018G-ND	12.31 9.33

Single Ended Style 4

*MC=Multi-Color, GR=Gray




Dip Connector without Strain Relief Shown
Pin #1 on connector is connected to 2nd conductor on cable

No. of Contacts	Contact Finish	Length Inch (cm)	Rib-on-Cable	Digi-Key Part No.	Price Each 1 10
10	Gold	6 (15.24)	MC	H4PXH-1006M-ND	3.63 2.75
	Tin	6 (15.24)	MC	H4PXS-1006M-ND	3.63 2.75
	Gold	6 (15.24)	GR	H4PXH-1006G-ND	3.35 2.54
	Gold	6 (15.24)	GR	H4PXS-1006G-ND	3.35 2.54
	Gold	18 (45.72)	MC	H4PXH-1018M-ND	4.43 3.36
	Tin	18 (45.72)	MC	H4PXS-1018M-ND	4.43 3.36
14	Gold	6 (15.24)	MC	H4PXH-1406M-ND	4.43 3.36
	Gold	6 (15.24)	GR	H4PXS-1406G-ND	3.60 2.74
	Gold	6 (15.24)	GR	H4PXS-1406G-ND	3.60 2.74
	Gold	18 (45.72)	MC	H4PXH-1418M-ND	5.63 4.27
	Tin	18 (45.72)	MC	H4PXS-1418M-ND	5.63 4.27
	Tin	18 (45.72)	GR	H4PXS-1418G-ND	3.98 3.02
20	Gold	6 (15.24)	MC	H4PXH-2006M-ND	4.32 3.28
	Gold	6 (15.24)	GR	H4PXS-2006G-ND	3.90 2.96
	Gold	6 (15.24)	GR	H4PXS-2006G-ND	3.90 2.96
	Gold	18 (45.72)	MC	H4PXH-2018M-ND	5.52 4.19
	Tin	18 (45.72)	MC	H4PXS-2018M-ND	5.52 4.19
	Tin	18 (45.72)	GR	H4PXS-2018G-ND	4.25 3.23
24	Gold	6 (15.24)	MC	H4PXH-2406M-ND	7.33 5.56
	Gold	6 (15.24)	GR	H4PXS-2406G-ND	7.33 5.56
	Gold	6 (15.24)	GR	H4PXS-2406G-ND	4.78 3.63
	Gold	18 (45.72)	MC	H4PXH-2418M-ND	11.29 8.56
	Tin	18 (45.72)	MC	H4PXS-2418M-ND	11.29 8.56
	Tin	18 (45.72)	GR	H4PXS-2418G-ND	8.65 6.56
40	Gold	6 (15.24)	MC	H4PXH-4006M-ND	9.61 7.29
	Gold	6 (15.24)	GR	H4PXS-4006G-ND	9.09 6.90
	Gold	6 (15.24)	GR	H4PXS-4006G-ND	9.09 6.90
	Gold	18 (45.72)	MC	H4PXH-4018M-ND	12.31 9.33
	Tin	18 (45.72)	MC	H4PXS-4018M-ND	12.31 9.33
	Tin	18 (45.72)	GR	H4PXS-4018G-ND	9.66 7.33

No. of Contacts	Contact Finish	Length Inch (cm)	Rib-on-Cable	Digi-Key Part No.	Price Each 1 10
16	Gold	6 (15.24)	MC	H4PXH-1606M-ND	4.36 3.31
	Tin	6 (15.24)	MC	H4PXS-1606M-ND	4.36 3.31
	Gold	6 (15.24)	GR	H4PXH-1606G-ND	3.92 2.98
	Gold	6 (15.24)	GR	H4PXS-1606G-ND	3.92 2.98
	Gold	18 (45.72)	MC	H4PXH-1618M-ND	5.65 4.28
	Tin	18 (45.72)	MC	H4PXS-1618M-ND	5.65 4.28
20	Gold	6 (15.24)	MC	H4PXH-2006M-ND	5.20 3.95
	Gold	6 (15.24)	GR	H4PXS-2006G-ND	4.69 3.56
	Gold	6 (15.24)	GR	H4PXS-2006G-ND	4.69 3.56
	Gold	18 (45.72)	MC	H4PXH-2018M-ND	6.81 5.17
	Tin	18 (45.72)	MC	H4PXS-2018M-ND	6.81 5.17
	Tin	18 (45.72)	GR	H4PXS-2018G-ND	5.26 3.99
24	Gold	6 (15.24)	MC	H4PXH-2406M-ND	9.21 6.99
	Gold	6 (15.24)	GR	H4PXS-2406G-ND	6.12 4.64
	Gold	6 (15.24)	GR	H4PXS-2406G-ND	6.12 4.64
	Gold	18 (45.72)	MC	H4PXH-2418M-ND	11.72 8.85
	Tin	18 (45.72)	MC	H4PXS-2418M-ND	11.72 8.85
	Tin	18 (45.72)	GR	H4PXS-2418G-ND	9.03 6.85
40	Gold	6 (15.24)	MC	H4PXH-4006M-ND	15.45 11.72
	Gold	6 (15.24)	GR	H4PXS-4006G-ND	10.67 8.09
	Gold	6 (15.24)	GR	H4PXS-4006G-ND	10.67 8.09
	Gold	18 (45.72)	MC	H4PXH-4018M-ND	16.64 12.49
	Tin	18 (45.72)	MC	H4PXS-4018M-ND	16.64 12.49
	Tin	18 (45.72)	GR	H4PXS-4018G-ND	12.31 9.33

Double Ended Style 6

*MC=Multi-Color, GR=Gray




Dip Connector without Strain Relief Shown
Pin #1 on connector is connected to 2nd conductor on cable

No. of Contacts	Contact Finish	Length Inch (cm)	Rib-on-Cable	Digi-Key Part No.	Price Each 1 10
10	Gold	6 (15.24)	MC	H6PPH-1006M-ND	6.85 5.20
	Tin	6 (15.24)	MC	H6PPS-1006M-ND	6.85 5.20
	Gold	6 (15.24)	GR	H6PPH-1006G-ND	6.57 4.99
	Gold	6 (15.24)	GR	H6PPS-1006G-ND	6.57 4.99
	Gold	18 (45.72)	MC	H6PPH-1018M-ND	7.65 5.80
	Tin	18 (45.72)	MC	H6PPS-1018M-ND	7.65 5.80
14	Gold	6 (15.24)	MC	H6PPH-1406M-ND	8.04 6.10
	Gold	6 (15.24)	GR	H6PPS-1406G-ND	7.62 5.78
	Gold	6 (15.24)	GR	H6PPS-1406G-ND	7.62 5.78
	Gold	18 (45.72)	MC	H6PPH-1418M-ND	9.24 7.01
	Tin	18 (45.72)	MC	H6PPS-1418M-ND	9.24 7.01
	Tin	18 (45.72)	GR	H6PPS-1418G-ND	7.97 6.05
20	Gold	6 (15.24)	MC	H6PPH-2006M-ND	11.05 8.38
	Gold	6 (15.24)	GR	H6PPS-2006G-ND	11.05 8.38
	Gold	6 (15.24)	GR	H6PPS-2006G-ND	8.50 6.45
	Gold	18 (45.72)	MC	H6PPH-2018M-ND	13.62 10.33
	Tin	18 (45.72)	MC	H6PPS-2018M-ND	13.62 10.33
	Tin	18 (45.72)	GR	H6PPS-2018G-ND	10.52 7.98
24	Gold	6 (15.24)	MC	H6PPH-2406M-ND	13.62 10.33
	Gold	6 (15.24)	GR	H6PPS-2406G-ND	10.52 7.98
	Gold	6 (15.24)	GR	H6PPS-2406G-ND	10.52 7.98
	Gold	18 (45.72)	MC	H6PPH-2418M-ND	15.32 11.61
	Tin	18 (45.72)	MC	H6PPS-2418M-ND	15.32 11.61
	Tin	18 (45.72)	GR	H6PPS-2418G-ND	12.31 9.33
40	Gold	6 (15.24)	MC	H6PPH-4006M-ND	15.32 11.61
	Gold	6 (15.24)	GR	H6PPS-4006G-ND	12.31 9.33
	Gold	6 (15.24)	GR	H6PPS-4006G-ND	12.31 9.33
	Gold	18 (45.72)	MC	H6PPH-4018M-ND	18.12 13.81
	Tin	18 (45.72)	MC	H6PPS-4018M-ND	18.12 13.81
	Tin	18 (45.72)	GR	H6PPS-4018G-ND	13.25 10.05

No. of Contacts	Contact Finish	Length Inch (cm)	Rib-on-Cable	Digi-Key Part No.	Price Each 1 10
20	Gold	36 (91.44)	GR	H6PPH-2036G-ND	10.52 7.98
	Tin	36 (91.44)	GR	H6PPS-2036G-ND	10.52 7.98
24	Gold	6 (15.24)	MC	H6PPH-2406M-ND	10.30 7.81
	Gold	6 (15.24)	GR	H6PPS-2406G-ND	10.30 7.81
	Gold	6 (15.24)	GR	H6PPS-2406G-ND	9.57 7.26
	Gold	6 (15.24)	GR	H6PPS-2406G-ND	9.57 7.26
	Gold	18 (45.72)	MC	H6PPH-2418M-ND	12.31 9.33
	Tin	18 (45.72)	MC	H6PPS-2418M-ND	12.31 9.33
40	Gold	6 (15.24)	MC	H6PPH-4006M-ND	13.26 10.06
	Gold	6 (15.24)	GR	H6PPS-4006G-ND	12.19 9.24
	Gold	6 (15.24)	GR	H6PPS-4006G-ND	12.19 9.24
	Gold	18 (45.72)	MC	H6PPH-4018M-ND	16.47 12.49
	Tin	18 (45.72)	MC	H6PPS-4018M-ND	16.47 12.49
	Tin	18 (45.72)	GR	H6PPS-4018G-ND	13.25 10.05

Double Ended Style 8

*MC=Multi-Color, GR=Gray



Dip Connector without Strain Relief Shown
Pin #1 on connector is connected to 2nd conductor on cable

No. of Contacts	Contact Finish	Length Inch (cm)	Rib-on-Cable	Digi-Key Part No.	Price Each 1 10
10	Gold	6 (15.24)	MC	H8PPH-1006M-ND	6.85 5.20
	Tin	6 (15.24)	MC	H8PPS-1006M-ND	6.85 5.20
	Gold	6 (15.24)	GR	H8PPH-1006G-ND	6.57 4.99
	Gold	6 (15.24)	GR	H8PPS-1006G-ND	6.57 4.99
	Gold	18 (45.72)	MC	H8PPH-1018M-ND	7.65 5.80
	Tin	18 (45.72)	MC	H8PPS-1018M-ND	7.65 5.80
14	Gold	6 (15.24)	MC	H8PPH-1406M-ND	8.04 6.10
	Gold	6 (15.24)	GR	H8PPS-1406G-ND	7.62 5.78
	Gold	6 (15.24)	GR	H8PPS-1406G-ND	7.62 5.78
	Gold	18 (45.72)	MC	H8PPH-1418M-ND	9.24 7.01
	Tin	18 (45.72)	MC	H8PPS-1418M-ND	9.24 7.01
	Tin	18 (45.72)	GR	H8PPS-1418G-ND	7.97 6.05
20	Gold	6 (15.24)	MC	H8PPH-2006M-ND	11.05 8.38
	Gold	6 (15.24)	GR	H8PPS-2006G-ND	11.05 8.38
	Gold	6 (15.24)	GR	H8PPS-2006G-ND	8.50 6.45
	Gold	18 (45.72)	MC	H8PPH-2018M-ND	13.62 10.33
	Tin	18 (45.72)	MC	H8PPS-2018M-ND	13.62 10.33
	Tin	18 (45.72)	GR	H8PPS-2018G-ND	10.52 7.98
24	Gold	6 (15.24)	MC	H8PPH-2406M-ND	13.62 10.33
	Gold	6 (15.24)	GR	H8PPS-2406G-ND	10.52 7.98
	Gold	6 (15.24)	GR	H8PPS-2406G-ND	10.52 7.98
	Gold	18 (45.72)	MC	H8PPH-2418M-ND	15.32 11.61
	Tin	18 (45.72)	MC	H8PPS-2418M-ND	15.32 11.61
	Tin	18 (45.72)	GR	H8PPS-2418G-ND	12.31 9.33
40	Gold	6 (15.24)	MC	H8PPH-4006M-ND	15.32 11.61
	Gold	6 (15.24)	GR	H8PPS-4006G-ND	12.31 9.33
	Gold	6 (15.24)	GR	H8PPS-4006G-ND	12.31 9.33
	Gold	18 (45.72)	MC		