


A



USB Standard Features:
 • Broad industry support from computer and telecom leaders • 12 Mbit/sec low-cost data transfer rates
 • Provides PC/telephone integration and digital connectivity • Standard serial port connector for all devices
 • Supports daisy chaining and up to 127 devices • Windows '95 Operating Driver support **Applications:**
 • Desktop and Notebook PCs • Peripherals • Keyboard, Mouse • Telephony, ISDN, PBX's, Handsets

USB Connectors:

Electrical: • Voltage: 30V • Current: Up to 1.5A • Contact Resistance: 30mΩ maximum • Dielectric Withstanding Voltage: 750VAC • Insulation Resistance: 1000MΩ minimum • Housing: Glass fiber-filled polyester, UL94V-0 • Metal Shell: Copper Alloy • Plating: Gold

USB On-the-Go (OTG) Connectors:

• Approximately 1/8th the size of standard USB-B connectors • Fully compliant with current USB 2.0 specifications • Compact and lightweight design meets various portable and mobile equipment needs
 • Operates at speeds up to 480Mbps • Rugged durability up to 5,000 cycles

Micro-USB Connectors:

The interconnect solutions for the Molex Micro-USB system include OTG compatible, Micro-B and Micro AB receptacles. **Features and Benefits:** • Stainless steel shell • Multi-snap shield design • Pick and place area **Applications:** • Mobile Phone • MP3 Players • Portable Digital Video Players • Digital Still Cameras • Digital Video Cameras

Fig.	Description	Operating Temperature Range (°C)	Digi-Key Part No.	Price Each			Digi-Key Part No.	Tape and Reel		Molex Part No.
				1	10	100		Qty.	Pricing	
1	Type "A" Upright, Right Angle, Gold Flash	0 - 40	WM17112-ND	2.14	1.89	1.26	—	—	89485-8000	
	Type "A" Upright, Right Angle, 30 micro-inch, Gold	0 - 40	WM17138-ND NEW!	2.31	1.85	1.24	—	—	89485-8001	
2	Type "A" Dual Stacked, Right Angle, White	0 - 50	WM17130-ND♦	1.26	1.11	.74	—	—	67298-4090	
3	Type "A" 4 Stacked, Right Angle, Black	0 - 40	WM17111-ND	7.13	6.29	4.20	—	—	67857-0011	
4	Type "B" Single, Right Angle, Black, Gold Flash	0 - 50	WM17113-ND♦	2.00	1.77	1.18	—	—	67068-8000	
	Type "B" Single, Right Angle, Black, 30 micro-inch, Gold	0 - 50	WM17123-ND♦	2.69	2.37	1.59	—	—	67068-8001	
	Type "B" Single, Right Angle, White	0 - 50	WM17131-ND♦	1.87	1.66	1.11	—	—	67068-9000	
5	Type "B" Vertical with Paired Board Locks and Grounding Pins	0 - 50	WM18716-ND♦	1.86	1.65	1.10	—	—	67265-2001	
6A	Type "Mini-B" OTG, Right Angle, PCB Mount	0 - 50	WM17115-ND	2.19	1.75	1.17	—	—	54819-0519	
6B	Type "Mini-AB" OTG, Right Angle, 5-Position, PCB Mount	0 - 50	WM17121-ND♦	3.79	3.35	2.23	—	—	56579-0519	
7	Type "A" Single, Right Angle, PCB Mount	-20 - 85	WM17117-ND♦	1.93	1.71	1.14	—	—	48037-0001	
8	Type "A" Single, Right Angle, SMD	-20 - 85	WM17118-ND♦	1.93	1.71	1.14	—	—	48037-1000	
9	Type "A" Single, Upright Right Angle, PCB Mount	-55 - 85	WM17136-ND♦	2.04	1.81	1.21	—	—	47500-0000	
10	Type "Mini-B" USB OTG, Vertical, 5-Position, PCB Mount	0 - 50	WM17120-ND♦	7.23	6.38	4.26	—	—	500075-0517	
	Type "Mini-B" USB OTG, Vertical, 5-Position, PCB Mount	0 - 50	WM2072-ND♦	7.23	6.39	4.26	—	—	500075-1517	
11A	Type "Mini-B" USB OTG, Right Angle, 5-Position, SMD	0 - 50	WM17116CT-ND†	1.76	1.41	.94	WM17116TR-ND	800	563.20	54819-0572
	Type "Mini-B" USB OTG, Right Angle, 5-Position, SMD, SMD Shield	0 - 50	WM5461CT-ND†	1.30	1.04	.87	WM5461TR-ND♦	500	291.50	67503-1020
	Type "Mini-B" USB OTG, Right Angle, 5-Position, SMD, Through Hole Shield, Short Body	0 - 50	WM5462CT-ND†♦	1.94	1.56	1.30	WM5462TR-ND♦	1,000	778.00	51387-0578
	Type "Mini-B" USB OTG, Right Angle, 5-Position, SMD, Through Hole Shield	-20 - 85	WM17139CT-ND†♦ NEW!	1.05	.97	.79	WM17139TR-ND♦ NEW!	800	307.00	47153-1002
11B	Type "Mini-AB" USB OTG, Right Angle, SMD, with Cover Tape	-40 - 85	WM17122CT-ND†♦	3.22	2.58	2.15	WM17122TR-ND♦	500	1030.40	56579-0576
12	Type "Mini-B" USB OTG, Right Angle, 5-Position, SMD, Sink Type	-20 - 85	WM17140CT-ND†♦ NEW!	.81	.75	.62	WM17140TR-ND♦ NEW!	700	332.50	48242-0001
13	Type "Micro-B" USB, SMD, Bottom Mount	-20 - 85	WM17141CT-ND†♦ NEW!	1.14	1.05	.86	WM17141TR-ND♦ NEW!	2,000	668.00/M	47346-0001
14	Type "Micro-B" USB, SMD, Mid Mount	-20 - 85	WM17142CT-ND†♦ NEW!	1.29	1.19	.97	WM17142TR-ND♦ NEW!	1,200	754.00/M	47491-0001
15	Type "Micro-AB" USB, SMD, Bottom Mount	-20 - 85	WM17143CT-ND†♦ NEW!	.88	.81	.67	WM17143TR-ND♦ NEW!	1,500	514.00/M	47589-0001
16	Type "Micro-AB" USB, SMD, Top Mount	-20 - 85	WM17144CT-ND†♦ NEW!	.88	.81	.67	WM17144TR-ND♦ NEW!	1,500	514.00/M	47590-0001

† Cut Tape ♦ RoHS Compliant

Firewire 1394 I/O Connectors

Specifications: Headers are offered in high temperature plastic for true SMT processing. Full metal shielding design supports ESD protection. Rugged gold plated leaf contacts withstands up to 1500 cycles.

Fig.	Digi-Key Part No.	Price Each			Molex Part No.
		1	10	100	
1	WM17302-ND	4.48	3.95	2.64	53462-0629
2	WM17303-ND	4.48	3.95	2.64	53460-0629



Fig. 1 - Right Angle Flat Header




Fig. 2 - Right Angle Upright Header



Digi-Reel Most SMT cutdown parts are available on a Digi-Reel®. For Digi-Reel part number, change 1-ND to 6-ND or CT-ND to DKR-ND. See Digi-Key® Services on page 2 for additional information.

More Product Available Online: www.digkey.com