



100" (2.54mm) Flat Flex Cable Assemblies (Cont.)

Receptacle Housing to Receptacle Housing

Mates with single row .025 (.64mm) square pin, .100 (2.54mm) headers.



Plain Style Housing — Material: Black thermoplastic, flame retardant, 94V-0 rated. Duplex plated contacts.

Table with columns: No. of Contacts, Length In. (mm), Digi-Key Part No., Pricing 1, 100. Lists various part numbers like A9BBG-0202F-ND and their prices.

A9BBG-□□□□F-ND = 15µ gold; A9BBA-□□□□F-ND = 30µ gold. Call for complete part number and pricing.

Receptacle Housing with Latch to Solder Tab



Latch Style Housing — Material: Black thermoplastic, flame retardant, 94V-0 rated. Duplex plated contacts.

Table with columns: No. of Contacts, Length In. (mm), Digi-Key Part No., Pricing 1, 100. Lists various part numbers like A9CAG-0202F-ND and their prices.

A9CAG-□□□□F-ND = 15µ gold; A9CAA-□□□□F-ND = 30µ gold. Call for complete part number and pricing.

Receptacle Housing with Latch to Receptacle Housing with Latch



Latch Style Housing — Material: Black thermoplastic, flame retardant, 94V-0 rated. Duplex plated contacts.

Table with columns: No. of Contacts, Length In. (mm), Digi-Key Part No., Pricing 1, 100. Lists various part numbers like A9CCG-0202F-ND and their prices.

A9CCG-□□□□F-ND = 15µ gold; A9CCA-□□□□F-ND = 30µ gold. Call for complete part number and pricing.

