


## 3M .100" x .100" (2.54mm x 2.54mm) Socket Connectors



Wire Accommodation: 26, 28, 30AWG solid or stranded.

**Physical Specifications:** • Insulation Material: Glass reinforced polyester • Flammability Rating: UL94V-0 • Color: Gray • Contact Material: Beryllium copper • Plating: 30µ" gold

• Wire Accommodation: 26 and 28AWG solid or stranded, 30AWG solid • Marking: 3M logo, part identification number and orientation triangle **Electrical Specifications:** • Current Rating: 1A • Insulation Resistance: >1x10<sup>10</sup>Ω @ 500VDC • Withstanding Voltage: 1000VRMS @ sea level **Environmental Specifications:** • Temperature Rating: -55°C ~ 105°C • UL File No.: E68080; CSA File No.: LR-40971



No. of Contacts	Dim. A Inch (mm)	Digi-Key Part No.	Pricing 1 10	3M Part No.
<b>Polarizing Slots (Open End)</b>				
10	.68 (17.27)	MSC10K-ND	2.00 16.80	3473-6000
14	.88 (22.35)	MSC14K-ND	2.41 20.30	3385-6000
16	.98 (24.89)	MSC16K-ND	2.64 22.23	3452-6000
20	1.18 (29.97)	MSC20K-ND	2.91 24.50	3421-6000
24	1.38 (35.05)	MSC24K-ND	3.49 29.40	3626-6000
26	1.48 (37.59)	MSC26K-ND	3.76 31.68	3399-6000
30	1.68 (42.67)	MSC30K-ND	4.33 36.40	3419-6000
34	1.88 (47.75)	MSC34K-ND	4.91 41.30	3414-6000
40	2.18 (55.37)	MSC40K-ND	5.76 48.48	3417-6000
50	2.68 (68.07)	MSC50K-ND	7.20 60.55	3425-6000
60	3.18 (80.77)	MSC60K-ND	8.92 75.08	3334-6000

No. of Contacts	Dim. A Inch (mm)	Digi-Key Part No.	Pricing 1 10	3M Part No.
<b>Center-Bumped Polarizing (Open End)</b>				
10	.68 (17.27)	MKC10K-ND	2.00 16.80	3473-6600
14	.88 (22.35)	MKC14K-ND	2.41 20.30	3385-6600
16	.98 (24.89)	MKC16K-ND	2.64 22.23	3452-6600
20	1.18 (29.97)	MKC20K-ND	2.91 24.50	3421-6600
24	1.38 (35.05)	MKC24K-ND	3.49 29.40	3626-6600
26	1.48 (37.59)	MKC26K-ND	3.76 31.68	3399-6600
30	1.68 (42.67)	MKC30K-ND	4.33 36.40	3419-6600
34	1.88 (47.75)	MKC34K-ND	4.91 41.30	3414-6600
40	2.18 (55.37)	MKC40K-ND	5.76 48.48	3417-6600
50	2.68 (68.07)	MKC50K-ND	7.20 60.55	3425-6600
60	3.18 (80.77)	MKC60K-ND	8.92 75.08	3334-6600

No. of Contacts	Dim. A Inch (mm)	Digi-Key Part No.	Pricing 1 10	3M Part No.
<b>Center-Bumped Polarizing (Closed End)</b>				
10	.68 (17.27)	MSD10K-ND	2.12 17.85	3473-7600
14	.88 (22.35)	MSD14K-ND	2.66 22.40	3385-7600
16	.98 (24.89)	MSD16K-ND	2.79 23.45	3452-7600
20	1.18 (29.97)	MSD20K-ND	3.06 25.73	3421-7600
24	1.38 (35.05)	MSD24K-ND	3.66 30.80	3626-7600
26	1.48 (37.59)	MSD26K-ND	3.97 33.43	3399-7600
30	1.68 (42.67)	MSD30K-ND	4.56 38.33	3419-7600
34	1.88 (47.75)	MSD34K-ND	5.12 43.05	3414-7600
40	2.18 (55.37)	MSD40K-ND	6.01 50.58	3417-7600
50	2.68 (68.07)	MSD50K-ND	7.49 63.00	3425-7600
60	3.18 (80.77)	MSD60K-ND	9.26 77.88	3334-7600

No. of Contacts	Dim. A Inch (mm)	Digi-Key Part No.	Pricing 1 10	3M Part No.
<b>Cable Strain Relief/Stabilizer</b>				
10	—	MSSR10-ND	25 2.10	3448-3010
14	—	MSSR14-ND	25 2.10	3448-3014
16	—	MSSR16-ND	25 2.10	3448-3016
20	—	MSSR20-ND	25 2.10	3448-3020
24	—	MSSR24-ND	33 2.80	3448-3024
26	—	MSSR26-ND	25 2.10	3448-3026
30	—	MSSR30-ND	46 3.85	3448-3030
34	—	MSSR34-ND	25 2.10	3448-3034
40	—	MSSR40-ND	25 2.10	3448-3040
50	—	MSSR50-ND	25 2.10	3448-3050
60	—	MSSR60-ND	27 2.28	3448-3060

## 3M 891 Series and D89 Series .100" x .100" (2.54mm x 2.54mm) Socket Connectors



These high-quality, standard-performance IDC sockets minimize applied assembly costs without sacrificing reliability. These interconnects also offer the quality and reliability you'd expect from 3M. They have been engineered with a "systems" approach that has a positive impact on your process and product costs. **Physical Specifications:** • Insulation Material: Glass reinforced polyester (PBT) • Flammability Rating: UL94V-0 • Marking: Molded Figures: 3M logo and orientation triangle • Pins: Phosphor bronze • Wire Accommodation: 26AWG solid or stranded, 30AWG stranded **891 Series** • Color: Gray • Contact Plating: Wipe Area: 30µ" gold • Underplate: 50µ" nickel, QQ-N-290, Class 2 **D89 Series** • Color: Black • Contact Plating: Wipe area: 10µ" gold • Underplate: 50µ" nickel **Electrical Specifications:** • Current Rating: 1A • Insulation Resistance: >1x10<sup>10</sup>Ω @ 500VDC • Withstanding Voltage: 1000VRMS @ Sea Level **Environmental Specifications:** • Operating Temperature: -55°C ~ 105°C • UL File No.: E68080

No. of Contacts	Dim. A Inch (mm)	Digi-Key Part No.	Pricing 1 10	3M Part No.
<b>891 Series, without Center Bump - 30µ" Gold</b>				
10	.68 (17.3)	MSC10A-ND	1.09 8.84	89110-0001
14	.88 (22.4)	MSC14A-ND	1.12 9.12	89114-0001
16	.98 (24.9)	MSC16A-ND	1.16 9.41	89116-0001
20	1.18 (30.0)	MSC20A-ND	1.26 10.26	89120-0001
24	1.38 (35.1)	MSC24A-ND	1.65 13.40	89124-0001
26	1.48 (37.6)	MSC26A-ND	1.44 11.69	89126-0001
30	1.68 (42.7)	MSC30A-ND	1.61 13.11	89130-0001
34	1.88 (47.8)	MSC34A-ND	1.61 13.11	89134-0001
40	2.18 (55.4)	MSC40A-ND	2.17 17.67	89140-0001
50	2.68 (68.1)	MSC50A-ND	2.35 19.10	89150-0001
60	3.18 (80.8)	MSC60A-ND	2.42 19.67	89160-0001

No. of Contacts	Dim. A Inch (mm)	Digi-Key Part No.	Pricing 1 10	3M Part No.
<b>891 Series, without Center Bump - 30µ" Gold</b>				
10	.68 (17.3)	MSC10A-ND	1.09 8.84	89110-0001
14	.88 (22.4)	MSC14A-ND	1.12 9.12	89114-0001
16	.98 (24.9)	MSC16A-ND	1.16 9.41	89116-0001
20	1.18 (30.0)	MSC20A-ND	1.26 10.26	89120-0001
24	1.38 (35.1)	MSC24A-ND	1.65 13.40	89124-0001
26	1.48 (37.6)	MSC26A-ND	1.44 11.69	89126-0001
30	1.68 (42.7)	MSC30A-ND	1.61 13.11	89130-0001
34	1.88 (47.8)	MSC34A-ND	1.61 13.11	89134-0001
40	2.18 (55.4)	MSC40A-ND	2.17 17.67	89140-0001
50	2.68 (68.1)	MSC50A-ND	2.35 19.10	89150-0001
60	3.18 (80.8)	MSC60A-ND	2.42 19.67	89160-0001

No. of Contacts	Dim. A Inch (mm)	Digi-Key Part No.	Pricing 1 10	3M Part No.
<b>891 Series, with Center Bump - 30µ" Gold</b>				
10	.68 (17.3)	MKC10A-ND	1.09 8.84	89110-0101
14	.88 (22.4)	MKC14A-ND	1.12 9.12	89114-0101
16	.98 (24.9)	MKC16A-ND	1.16 9.41	89116-0101
20	1.18 (30.0)	MKC20A-ND	1.26 10.26	89120-0101
24	1.38 (35.1)	MKC24A-ND	1.65 13.40	89124-0101
26	1.48 (37.6)	MKC26A-ND	1.44 11.69	89126-0101
30	1.68 (42.7)	MKC30A-ND	1.61 13.11	89130-0101
34	1.88 (47.8)	MKC34A-ND	1.61 13.11	89134-0101
40	2.18 (55.4)	MKC40A-ND	2.17 17.67	89140-0101
50	2.68 (68.1)	MKC50A-ND	2.35 19.10	89150-0101
60	3.18 (80.8)	MKC60A-ND	2.42 19.67	89160-0101


No. of Contacts	Dim. A Inch (mm)	Digi-Key Part No.	Pricing 1 10	3M Part No.
<b>891 Series Strain Reliefs</b>				
10	—	MKSR10-ND	32 2.57	3448-89110
14	—	MKSR14-ND	32 2.57	3448-89114
16	—	MKSR16-ND	32 2.57	3448-89116
20	—	MKSR20-ND	32 2.57	3448-89120
24	—	MKSR24-ND	49 3.99	3448-89124
26	—	MKSR26-ND	32 2.57	3448-89126
30	—	MKSR30-ND	49 3.99	3448-89130
34	—	MKSR34-ND	32 2.57	3448-89134
40	—	MKSR40-ND	32 2.57	3448-89140
50	—	MKSR50-ND	32 2.57	3448-89150
60	—	MKSR60-ND	46 3.71	3448-89160

No. of Contacts	Dim. A Inch (mm)	Digi-Key Part No.	Pricing 1 10	3M Part No.
<b>NEW! D89 Series, without Center Bump - 10µ" Gold - RoHS Compliant NEW!</b>				
10	.68 (17.3)	MSC10E-ND	40 3.33	D89110-0031HK
14	.88 (22.4)	MSC14E-ND	56 4.73	D89114-0031HK
16	.98 (24.9)	MSC16E-ND	54 4.55	D89116-0031HK
20	1.18 (30.0)	MSC20E-ND	56 4.73	D89120-0031HK
24	1.38 (35.1)	MSC24E-ND	58 4.90	D89124-0031HK
26	1.48 (37.6)	MSC26E-ND	58 4.90	D89126-0031HK
30	1.68 (42.7)	MSC30E-ND	64 5.43	D89130-0031HK
34	1.88 (47.8)	MSC34E-ND	73 6.13	D89134-0031HK
40	2.18 (55.4)	MSC40E-ND	85 7.18	D89140-0031HK
50	2.68 (68.1)	MSC50E-ND	1.06 8.93	D89150-0031HK

No. of Contacts	Dim. A Inch (mm)	Digi-Key Part No.	Pricing 1 10	3M Part No.
<b>NEW! D89 Series, with Center Bump - 10µ" Gold - RoHS Compliant NEW!</b>				
10	.68 (17.3)	MKC10E-ND	40 3.33	D89110-0131HK
14	.88 (22.4)	MKC14E-ND	56 4.73	D89114-0131HK
16	.98 (24.9)	MKC16E-ND	54 4.55	D89116-0131HK
20	1.18 (30.0)	MKC20E-ND	56 4.73	D89120-0131HK
24	1.38 (35.1)	MKC24E-ND	58 4.90	D89124-0131HK
26	1.48 (37.6)	MKC26E-ND	58 4.90	D89126-0131HK
30	1.68 (42.7)	MKC30E-ND	64 5.43	D89130-0131HK
34	1.88 (47.8)	MKC34E-ND	73 6.13	D89134-0131HK
40	2.18 (55.4)	MKC40E-ND	85 7.18	D89140-0131HK
50	2.68 (68.1)	MKC50E-ND	1.06 8.93	D89150-0131HK

No. of Contacts	Dim. A Inch (mm)	Digi-Key Part No.	Pricing 1 10	3M Part No.
<b>NEW! D89 Series Strain Reliefs NEW!</b>				
10	—	MESR10-ND	19 1.58	D3448-89110
14	—	MESR14-ND	19 1.58	D3448-89114
16	—	MESR16-ND	19 1.58	D3448-89116
20	—	MESR20-ND	19 1.58	D3448-89120
24	—	MESR24-ND	19 1.58	D3448-89124
26	—	MESR26-ND	19 1.58	D3448-89126
30	—	MESR30-ND	19 1.58	D3448-89130
34	—	MESR34-ND	19 1.58	D3448-89134
40	—	MESR40-ND	19 1.58	D3448-89140
50	—	MESR50-ND	19 1.58	D3448-89150

## 3M .100" x .100" (2.54mm x 2.54mm) Plug Connectors



**Physical Specifications:** • Insulation Material: Glass reinforced polyester (PBT) • Flammability Rating: UL94V-0 • Color: Gray • Contact Material: Flat Cable Connectors: Beryllium copper • Latch Eject Headers: Copper alloy • Plating: 30µ" gold • Wire Accommodation: 26 and 28AWG solid or stranded, 30AWG solid **Electrical Specifications:** • Current Rating: 1A • Insulation Resistance: >1x10<sup>10</sup>Ω @ 500VDC • Withstanding Voltage: 1000VRMS @ sea level **Environmental Specifications:** • Temperature Rating: -55°C ~ 105°C • UL File No.: E68080; CSA File No.: LR-40971

No. of Cont.	Dimension - Inch (mm)	Digi-Key Part No.	Pricing 1 10	3M Part No.
<b>With Slotted Mounting Flanges</b>				
10	1.20 (30.48)	.90 (22.86)	MPL10K-ND	2.95 24.85 4610-6050
14	1.40 (35.56)	1.10 (27.94)	MPL14K-ND	4.10 34.48 4614-6000
16	1.50 (38.10)	1.20 (30.48)	MPL16K-ND	4.64 39.03 4616-6000
20	1.70 (43.18)	1.40 (35.56)	MPL20K-ND	5.41 45.50 4620-6000
24	1.90 (48.26)	1.60 (40.64)	MPL24K-ND	5.95 50.05 4624-6000
26	2.00 (50.80)	1.70 (43.18)	MPL26K-ND	6.16 51.80 4626-6000
30	2.20 (55.88)	1.90 (48.26)	MPL30K-ND	6.76 56.88 4630-6000
34	2.40 (60.96)	2.10 (53.34)	MPL34K-ND	7.63 64.23 4634-6000
36	2.50 (63.50)	2.20 (55.88)	MPL36K-ND	8.07 67.90 4636-6000
40	2.70 (68.58)	2.40 (60.96)	MPL40K-ND	8.47 71.23 4640-6000
50	3.20 (81.28)	2.90 (73.66)	MPL50K-ND	9.17 77.18 4650-6000
60	3.70 (93.98)	3.40 (86.36)	MPL60K-ND	