


I/O INTERCONNECT Modular Cable

Flat modular line cord is available in either straight or coiled.

Straight: H004R is sold in hanks of 100, 500 and 1,000 feet, spools of 2,000 feet; H006R, H008R H010 and H010R are sold in hanks of 100 and 500 feet, spools of 1,000 feet.

Coiled: Hxx4□C, Hxx4□RC, Hxx6□C, Hxx6□RC, Hxx8□C, Hxx8□RC, Hxx10□C and Hxx10□RC are sold in 5, 7, 10 and 14 feet approximate optimum in three colors—white (designated by 1 for □ in part number), black (designated by 2 for □ in part number) and silver satin (designated by 3 for □ in part number).



Number of Conductors	Length Feet (Meter)	Digi-Key Part No.†	Price Each
		1	10
Coiled Line Cord - 5 ft. (1.52 meter), 7 ft. (2.13 meter), 10 ft. (3.05 meter) and 14 ft. (4.27 meter) approximate extended lengths - 26 AWG			
4	5 (1.52)	H054□C-ND	2.64
	7 (2.13)	H0741C-ND	2.79
	10 (3.05)	H1042C-ND	4.11
	10 (3.05)	H1043C-ND◆	3.42
6	5 (1.52)	H0563C-ND	2.79
	7 (2.13)	H076□C-ND	2.88
	10 (3.05)	H1061C-ND◆	5.16
	10 (3.05)	H1062C-ND◆	5.16
8	5 (1.52)	H0583C-ND	6.12
	7 (2.13)	H078□C-ND	4.86
	10 (3.05)	H108□C-ND	7.20
	14 (4.27)	H1481C-ND	8.16
10	5 (1.52)	H0510□C-ND◆	5.37
	7 (2.13)	H0710□C-ND◆	5.58
	10 (3.05)	H1010□C-ND◆	7.14
	14 (4.27)	H1410□C-ND◆	7.95

Number of Conductors	Length Feet (Meter)	Digi-Key Part No.†	Price Each
		1	10
Coiled Line Cord - 5 ft. (1.52 meter), 7 ft. (2.13 meter), 10 ft. (3.05 meter) and 14 ft. (4.27 meter) approximate extended lengths - 26 AWG - RoHS Compliant			
4	5 (1.52)	H0541RC-ND	4.68
		H0542RC-ND	4.05
		H0543RC-ND	3.96
	7 (2.13)	H0741RC-ND	5.10
		H0742RC-ND	5.10
		H0743RC-ND	4.74
	10 (3.05)	H1041RC-ND	7.44
		H1042RC-ND	7.11
		H1043RC-ND	6.06
	14 (4.27)	H1441RC-ND	8.61
		H1442RC-ND	7.65
		H1443RC-ND	8.16
6	5 (1.52)	H0561RC-ND	3.69
		H0562RC-ND	3.69
		H0563RC-ND	4.26
	7 (2.13)	H0761RC-ND	5.91
		H0762RC-ND	5.70
		H0763RC-ND	6.12
	10 (3.05)	H1061RC-ND	8.75
		H1062RC-ND	8.75
		H1063RC-ND	5.55
	14 (4.27)	H1461RC-ND	8.75
		H1462RC-ND	9.93
		H1463RC-ND	9.51
8	5 (1.52)	H0581RC-ND	6.75
		H0582RC-ND	6.12
		H0583RC-ND	7.20
	7 (2.13)	H0781RC-ND	6.93
		H0782RC-ND	6.42
		H0783RC-ND	6.55
	10 (3.05)	H1082RC-ND	10.26
		H1083RC-ND	9.76
		H1481RC-ND	11.91
	14 (4.27)	H1482RC-ND	11.55
		H1483RC-ND	10.98

Number of Conductors	Digi-Key Part No.††	Pricing			
		100 ft.	500 ft.	1,000 ft.	2,000 ft.
Straight Line Cord - 26 AWG - RoHS Compliant					
4	H0041R-X-ND	12.52	57.37	104.31	166.90
	H0042R-X-ND	12.52	57.37	104.31	166.90
	H0043R-X-ND	12.52	57.37	104.31	166.90
6	H0061R-X-ND	22.82	104.57	152.10	—
	H0062R-X-ND	22.82	104.57	152.10	—
	H0063R-X-ND	22.82	104.57	152.10	—
8	H0081R-X-ND	32.66	149.67	217.70	—
	H0082R-X-ND	32.66	149.67	217.70	—
	H0083R-X-ND	32.66	149.67	217.70	—
10	H0101R-X-ND	56.70	259.88	378.00	—
	H0102R-X-ND	56.70	259.88	378.00	—
	H0103R-X-ND	56.70	259.88	378.00	—

† 1 = White, 2 = Black, 3 = Silver Satin † "X" in the Digi-Key Part Number represents number of feet.
◆ RoHS Compliant

A

Paladin Tools® Tools




Tester Data/Link ID and Cable-Check™: Tests UTP, STP and flat satin cables with RJ45 terminations. Tests both data and phone connection schemes including patch cords and installed cables to identify: • Good connections • Opens • Shorts • Cross-connections. Identifies data and link transmission speeds with real time detection: 100 MB and 10 MB. Detect PC (NIC) and HUB data transmissions and PC (NIC) and HUB NLP or FLP link pulse.

SureStrip® 4.0: High quality wire stripping and cutting tool for 20-12 AWG (0.5 - 4.0 mm²) • Strips stranded and solid conductors with PVC insulation • Strips multiple conductors and thin, ribbon-cable conductors simultaneously • Built-in wire cutter • Precision self-adjusting blades prevent wire damage • Strips double-insulated cable in two work cycles • User-replaceable stripping blades • Adjustable wire stop to set strip lengths • Value stripper to prepare wire for wire and ferrule termination

Mini-Stripax® Plus: Universal wire stripper and cutter that uses changeable blades to strip PVC and Teflon® insulation. Strips PVC-insulated wire in the range of 28-18 AWG (0.80 - 1.0 mm²) and Teflon-insulated wire in the range of 32-18 AWG (.032 - 1.00 mm²) • Strips flexible and solid conductors with PVC, Teflon, silicone and other special insulations • Strips multiple conductors and thin ribbon-cable conductors simultaneously • Adjustable wire stop and built-in wire cutter • 28-18 AWG (0.80 - 1.00 mm²) PVC blade included

Stripax® Pro 6 Strippers: The new stripax performs powerful stripping of standard and industrial insulations including PVC, THHN, THHW, silicone and polyethylene. Stripping blades are composed of 68 individual spring-compression blades to adjust precisely to the insulation. Not for Teflon or Kapton hard insulations.



Description	Digi-Key Part No.	Price Each	Paladin Tools Part No.
Tester Data/Link ID and Cable-Check	1576-ND	69.99	1576
Sure Strip 4.0 (AWG 20-12)	PA904893-ND	72.99	904893
Mini-Stripax Plus (AWG 28-18)	PAL1115-ND	96.99	1115P
Replacement Blade for PAL1115-ND	PAL2108-ND	29.99	2108
Stripax Pro 6 (AWG 28-10)	PAL1113.1-ND	85.99	1113.1

Crimp Tools



- Fully ratcheting cycle
- Adjustable crimp tension
- Hardened dies for long life
- Crimp 4, 6, and 8 position
- Cuts and strips cable
- RJ45, RJ11




PAL1530R-ND Modular Crimp Tool..... \$129.99
PAL2530-ND Replacement Blade Set (for 1530R)..... \$9.99

Cable Tester



Features:

- Tests over 20 types of patch cables up to 1,000 feet in length (600 feet for 75Ω coax)
- LAN and telephone • Serial • Coax 50 and 75Ω • USB • VGA • Mini- SB • S-video
- FireWire • PS/2 keyboard • Parallel printer
- 9V battery included




PAL1577-ND Tool PC Cable Tester..... \$189.99

Data and Telephone Tool



Features:

- Crimping cavities for RJ45, RJ11/RJ12 and RJ22 handset modular plugs
- Cuts and strips round UTP/STP phone and data cable along with flat satin phone cable
- 22-28 AWG (.08 - .34mm²) flat or round; solid or stranded telephone and data cables



PAL1556-ND All-in-One Data and Telephone Tool..... \$46.99

More Product Available Online: www.digkey.com

Toll-Free: 1-800-344-4539 • Phone 218-681-6674 • Fax: 218-681-3380