

numonyx™		DigiReel®		NEW! StrataFlash® (Continued)		
Numonyx Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	10	100
JS28F128P33B85 888018	888018-ND	128Mb, 3V StrataFlash® Memory*.....56-TSOP	9.93	7.95	5.24	
JS28F128P33T85 888019	888019-ND	128Mb, 3V StrataFlash® Memory*.....56-TSOP	9.93	7.95	5.24	
RC28F128P33B85 888066	888066-ND	128Mb, 3V StrataFlash® Memory*.....64-EZBGA	10.51	8.41	5.54	
RC28F128P33T85 888067	888067-ND	128Mb, 3V StrataFlash® Memory*.....64-EZBGA	9.93	7.95	5.24	
PC28F128P33B85 888064	888064-ND	128Mb, 3V StrataFlash® Memory*.....64-EZBGA	9.93	7.95	5.24	
PC28F128P33B85 S LA37	888020-ND	128Mb, 3V StrataFlash® Memory*.....64-EZBGA	9.93	7.95	5.24	
PC28F128P33B85 S LA4N	888347CT-ND	128Mb, 3V StrataFlash® Memory*.....64-EZBGA	11.75	9.25	7.00	
PC28F128P33B85 S LA4N	888347TR-ND	128Mb, 3V StrataFlash® Memory*.....64-EZBGA		12750.00/2,000		
PC28F128P33T85 S LALN	892799CT-ND	128Mb, 3V StrataFlash® Memory*.....64-EZBGA	11.75	9.25	7.00	
PC28F128P33T85 S LALN	892799TR-ND	128Mb, 3V StrataFlash® Memory*.....64-EZBGA		12750.00/2,000		
PC28F128P33T85 888065	888065-ND	128Mb, 3V StrataFlash® Memory*.....64-EZBGA	11.75	9.25	7.00	
PC28F128P33T85 S LALM	892798-ND	128Mb, 3V StrataFlash® Memory*.....64-EZBGA	9.93	7.95	5.24	
TE28F256P33B95 884142	884142-ND	256Mb, 3V StrataFlash® Memory*.....56-TSOP	14.14	11.31	7.46	
TE28F256P33T95 883590	883590-ND	256Mb, 3V StrataFlash® Memory*.....56-TSOP	14.14	11.31	7.46	
JS28F256P33B95 884143	884143-ND	256Mb, 3V StrataFlash® Memory*.....56-TSOP	14.14	11.31	7.46	
JS28F256P33T95 883593	883593-ND	256Mb, 3V StrataFlash® Memory*.....56-TSOP	14.93	11.95	7.88	
RC28F256P33B85 884144	884144-ND	256Mb, 3V StrataFlash® Memory*.....64-EZBGA	14.93	11.95	7.88	
RC28F256P33T85 883591	883591-ND	256Mb, 3V StrataFlash® Memory*.....64-EZBGA	14.14	11.31	7.46	
PC28F256P33B85 884145	884145-ND	256Mb, 3V StrataFlash® Memory*.....64-EZBGA	14.14	11.31	7.46	
PC28F256P33B85 S L9R6	884123CT-ND	256Mb, 3V StrataFlash® Memory*.....64-EZBGA	16.45	12.95	9.80	
PC28F256P33B85 S L9R6	884123TR-ND	256Mb, 3V StrataFlash® Memory*.....64-EZBGA		17850.00/2,000		
PC28F256P33B85 S LA8F	889994-ND	256Mb, 3V StrataFlash® Memory*.....64-EZBGA	14.14	11.31	7.46	
PC28F256P33T85 883595	883595-ND	256Mb, 3V StrataFlash® Memory*.....64-EZBGA	14.14	11.31	7.46	
JS48F4400POTB00887798	887798-ND	512Mb, 3V StrataFlash® Memory*.....56-TSOP	21.15	16.65	12.60	
TE48F4400POTB00887797	887797-ND	512Mb, 3V StrataFlash® Memory*.....56-TSOP	21.15	16.65	12.60	
RC48F4400POTB00885960	885960-ND	512Mb, 3V StrataFlash® Memory*.....64-EZBGA	21.15	16.65	12.60	
PC48F4400POTB00885967	885967-ND	512Mb, 3V StrataFlash® Memory*.....64-EZBGA	21.15	16.65	12.60	
PC48F4400POTB00S LAFB	891111-ND	512Mb, 3V StrataFlash® Memory*.....64-EZBGA	21.15	16.65	12.60	
PF38F3050M0Y3DE 896724	896724-ND	128Mb, 1.8V NOR Flash*.....56-SCSP	13.45	10.76	7.10	
PF38F4050M0Y3CF 891082	891082-ND	256Mb, 1.8V NOR Flash*.....107-SCSP	17.66	14.13	9.31	
PF38F5060M0Y0BE 886439	886439-ND	512Mb, 1.8V NOR Flash*.....105-SCSP	21.18	16.94	11.17	

numonyx™		DigiReel®		NEW! MEMORY CARDS		
RoHS Compliant						
Numonyx Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	25	100
SMC064BF6E	SMC064BF6E-ND	64Mb CompactFlash Card.....	43.50	40.50	33.00	
SMC128BF06E	SMC128BF06E-ND	128Mb CompactFlash Card.....	52.20	48.00	39.60	
SMC256BFJ6E	SMC256BFJ6E-ND	256Mb CompactFlash Card.....	55.10	51.30	41.80	
SMC512BFK6E	SMC512BFK6E-ND	512Mb CompactFlash Card.....	54.00	50.00	40.00	
SMC01GBFK6E	SMC01GBFK6E-ND	1Gb CompactFlash Card.....	56.70	52.50	42.00	
SMC02GBFK6E	SMC02GBFK6E-ND	2Gb CompactFlash Card.....	103.50	94.50	81.00	
SMC04GBFK6E	SMC04GBFK6E-ND	4Gb CompactFlash Card.....	152.00	136.00	120.00	

numonyx™		DigiReel®		NEW! CODE STORAGE		
RoHS Compliant						
Numonyx Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	10	100
M25P Series						
M25P05-AVMB6TP	M25P05-AVMB6TPCT-ND	512Kb, Serial Flash, 50MHz SPI Bus Interface.....8-UDFPN	1.50	1.25	1.05	
M25P05-AVMB6TP	M25P05-AVMB6TPTR-ND	512Kb, Serial Flash, 50MHz SPI Bus Interface.....8-UDFPN		1625.00/2,500		
M25P05-AVMN6TP	M25P05-AVMN6TPCT-ND	512Kb, Serial Flash, 50MHz SPI Bus Interface.....SO-8	1.50	1.25	1.05	
M25P05-AVMN6TP	M25P05-AVMN6TPTR-ND	512Kb, Serial Flash, 50MHz SPI Bus Interface.....SO-8		1625.00/2,500		
M25P05-AVMP6TG	M25P05-AVMP6TGCT-ND	512Kb, Serial Flash, 50MHz SPI Bus Interface.....8-VDFPN	1.50	1.25	1.05	
M25P05-AVMP6TG	M25P05-AVMP6TGTR-ND	512Kb, Serial Flash, 50MHz SPI Bus Interface.....8-VDFPN		2600.00/4,000		

Numonyx Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	10	100
M25P10-AVMB6TG	M25P10-AVMB6TGCT-ND	1Mb, Serial Flash, 50MHz SPI Bus Interface.....8-UDFPN	1.80	1.50	1.26	
M25P10-AVMB6TG	M25P10-AVMB6TGTR-ND	1Mb, Serial Flash, 50MHz SPI Bus Interface.....8-UDFPN		1950.00/2,500		
M25P10-AVMN3P/X	M25P10-AVMN3P/X-ND	1Mb, Serial Flash, 50MHz SPI Bus Interface.....SO-8	1.80	1.50	1.26	
M25P10-AVMN3TP/X	M25P10-AVMN3TP/XCT-ND	1Mb, Serial Flash, 50MHz SPI Bus Interface.....SO-8	1.80	1.50	1.26	
M25P10-AVMN3TP/X	M25P10-AVMN3TP/XTR-ND	1Mb, Serial Flash, 50MHz SPI Bus Interface.....SO-8		1950.00/2,500		
M25P10-AVMN6TP	M25P10-AVMN6TPCT-ND	1Mb, Serial Flash, 50MHz SPI Bus Interface.....SO-8	1.65	1.38	1.16	
M25P10-AVMN6TP	M25P10-AVMN6TPTR-ND	1Mb, Serial Flash, 50MHz SPI Bus Interface.....SO-8		1787.50/2,500		
M25P10-AVMP6TG	M25P10-AVMP6TGCT-ND	1Mb, Serial Flash, 50MHz SPI Bus Interface.....8-VDFPN	1.80	1.50	1.26	
M25P10-AVMP6TG	M25P10-AVMP6TGTR-ND	1Mb, Serial Flash, 50MHz SPI Bus Interface.....8-VDFPN		3120.00/4,000		
M25P16-VME6G	M25P16-VME6G-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....8-VDFPN	2.70	2.35	1.75	
M25P16-VME6TG	M25P16-VME6TGCT-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....8-VDFPN	2.70	2.35	1.75	
M25P16-VME6TG	M25P16-VME6TGTR-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....8-VDFPN		5120.00/4,000		
M25P16-VMF6TP	M25P16-VMF6TPCT-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....SO-16	4.56	3.98	2.96	
M25P16-VMF6TP	M25P16-VMF6TPTR-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....SO-16		5619.25/2,500		
M25P16-VMN6P	M25P16-VMN6P-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....SO-8	2.70	2.35	1.75	
M25P16-VMN6P/ALT	M25P16-VMN6P/ALT-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....SO-8		2.70	2.35	1.75
M25P16-VMN6TP	M25P16-VMN6TPCT-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....SO-8	2.70	2.35	1.75	
M25P16-VMN6TP	M25P16-VMN6TPTR-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....SO-8		3200.00/2,500		
M25P16-VMP6G	M25P16-VMP6G-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....8-VDFPN	2.70	2.35	1.75	
M25P16-VMP6TG	M25P16-VMP6TGCT-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....8-VDFPN	2.70	2.35	1.75	
M25P16-VMP6TG	M25P16-VMP6TGTR-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....8-VDFPN		5120.00/4,000		
M25P16-VMW6TG	M25P16-VMW6TGCT-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....SO-8	2.70	2.35	1.75	
M25P16-VMW6TG	M25P16-VMW6TGTR-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....SO-8		5120.00/4,000		
M25P32-VME6G	M25P32-VME6G-ND	32Mb, LV, Serial Flash, 75MHz SPI Bus Interface.....8-VDFPN	2.97	2.59	1.93	
M25P32-VME6TG	M25P32-VME6TGCT-ND	32Mb, LV, Serial Flash, 75MHz SPI Bus Interface.....8-VDFPN	2.97	2.59	1.93	
M25P32-VME6TG	M25P32-VME6TGTR-ND	32Mb, LV, Serial Flash, 75MHz SPI Bus Interface.....8-VDFPN		5632.00/4,000		
M25P32-VMF6TP	M25P32-VMF6TPCT-ND	32Mb, LV, Serial Flash, 75MHz SPI Bus Interface.....SO-16	6.39	5.84	4.62	
M25P32-VMF6TP	M25P32-VMF6TPTR-ND	32Mb, LV, Serial Flash, 75MHz SPI Bus Interface.....SO-16		3544.50/1,000		
M25P32-VMP6G	M25P32-VMP6G-ND	32Mb, LV, Serial Flash, 75MHz SPI Bus Interface.....8-VDFPN	2.97	2.59	1.93	
M25P32-VMP6TG	M25P32-VMP6TGCT-ND	32Mb, LV, Serial Flash, 75MHz SPI Bus Interface.....8-VDFPN	2.97	2.59	1.93	
M25P32-VMP6TG	M25P32-VMP6TGTR-ND	32Mb, LV, Serial Flash, 75MHz SPI Bus Interface.....8-VDFPN		5632.00/4,000		
M25P32-VMW6G	M25P32-VMW6G-ND	32Mb, LV, Serial Flash, 75MHz SPI Bus Interface.....SO-8	5.67	4.94	3.68	
M25P32-VMW6TG	M25P32-VMW6TGCT-ND	32Mb, LV, Serial Flash, 75MHz SPI Bus Interface.....SO-8	2.97	2.59	1.93	
M25P32-VMW6TG	M25P32-VMW6TGTR-ND	32Mb, LV, Serial Flash, 75MHz SPI Bus Interface.....SO-8		2194.50/1,500		
M25P40-VMN3P/X	M25P40-VMN3P/X-ND	4Mb, LV, Serial Flash.....SO-8	2.40	2.00	1.68	
M25P40-VMN6TP	M25P40-VMN6TPCT-ND	4Mb, LV, Serial Flash.....SO-8	2.40	2.00	1.68	
M25P40-VMN6TP	M25P40-VMN6TPTR-ND	4Mb, LV, Serial Flash.....SO-8		2600.00/2,500		
M25P40-VMN3TP/X	M25P40-VMN3TP/XCT-ND	4Mb, LV, Serial Flash.....SO-8	2.40	2.00	1.68	
M25P40-VMN3TP/X	M25P40-VMN3TP/XTR-ND	4Mb, LV, Serial Flash.....SO-8		2600.00/2,500		
M25P40-VMN6TPMX	M25P40-VMN6TPMXCT-ND	4Mb, LV, Serial Flash.....SO-8	2.40	2.00	1.68	
M25P40-VMN6TPMX	M25P40-VMN6TPMXTR-ND	4Mb, LV, Serial Flash.....SO-8		2600.00/2,500		
M25P40-VMN6TPSO	M25P40-VMN6TPSOCT-ND	4Mb, LV, Serial Flash.....SO-8	2.40	2.00	1.68	
M25P40-VMN6TPSO	M25P40-VMN6TPSOCT-ND	4Mb, LV, Serial Flash.....SO-8		2600.00/2,500		
M25P40-VMP6G/TS	M25P40-VMP6G/TS-ND	4Mb, LV, Serial Flash.....8-VDFPN	2.40	2.00	1.68	
M25P40-VMP6G/TS	M25P40-VMP6G/TSCT-ND	4Mb, LV, Serial Flash.....8-VDFPN		2.40	2.00	1.68
M25P40-VMP6G/TS	M25P40-VMP6G/TS-ND	4Mb, LV, Serial Flash.....8-VDFPN		4160.00/4,000		
M25P80-VMN3TP/4	M25P80-VMN3TP/4CT-ND	8Mb, LV, Serial Flash.....SO-8	2.70	2.25	1.89	
M25P80-VMN3TP/4	M25P80-VMN3TP/4TR-ND	8Mb, LV, Serial Flash.....SO-8		2925.00/2,500		
M25P80-VMN6TP	M25P80-VMN6TPCT-ND	8Mb, LV, Serial Flash.....SO-8	2.70	2.25	1.89	
M25P80-VMN6TP	M25P80-VMN6TPTR-ND	8Mb, LV, Serial Flash.....SO-8		2925.00/2,500		
M25P80-VMP6TG	M25P80-VMP6TGCT-ND	8Mb, LV, Serial Flash.....8-VDFPN	2.70	2.25	1.89	
M25P80-VMP6TG	M25P80-VMP6TGTR-ND	8Mb, LV, Serial Flash.....8-VDFPN		4680.00/4,000		
M25P80-VMW6TG	M25P80-VMW6TGCT-ND	8Mb, LV, Serial Flash.....SO-8	2.70	2.25	1.89	
M25P80-VMW6TG	M25P80-VMW6TGTR-ND	8Mb, LV, Serial Flash.....SO-8		1822.50/1,500		
M25P64-VME6TG	M25P64-VME6TGCT-ND	64Mb, LV, Serial Flash.....8-VDFPN	6.90	6.30	4.98	
M25P64-VME6TG	M25P64-VME6TGTR-ND	64Mb, LV, Serial Flash.....8-VDFPN		15120.00/4,000		
M25P64-VMF6TP	M25P64-VMF6TPCT-ND	64Mb, LV, Serial Flash.....SO-16	11.27	10.29	8.14	
M25P64-VMF6TP	M25P64-VMF6TPTR-ND	64Mb, LV, Serial Flash.....SO-16		6247.50/1,000		
M25P128-VME6G	M25P128-VME6G-ND	128Mb, LV, Serial Flash.....8-VDFPN	9.89	9.03	7.14	
M25P128-VMF6P	M25P128-VMF6P-ND	128Mb, LV, Serial Flash.....SO-16	9.89	9.03	7.14	
M25P128-VMF6PALT	M25P128-VMF6PALT-ND	128Mb, LV, Serial Flash.....SO-16	10.00	9.25	7.00	
M25P128-VMF6TP	M25P128-VMF6TPCT-ND	128Mb, LV, Serial Flash.....SO-16	10.00	9.25	7.00	
M25P128-VMF6TP	M25P128-VMF6TPTR-ND	128Mb, LV, Serial Flash.....SO-16		6250.00/1,000		

*RoHS Compliant

★ CALL FOR LOWER PRICING ON LARGER QUANTITIES! ★

More Product Available Online: www.digikey.com
 Toll-Free: 1-800-344-4539 • Phone 218-681-6674 • Fax: 218-681-3380