

numonyx		Digi+Reel		NEW! PARAMETER AND DATA STORAGE — RoHS Compliant		
Numonyx Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	10	100
M25PE Series						
M25PE10-VMN6P	M25PE10-VMN6P-ND	1Mb, Page-Erasable Serial Flash.....SO-8	1.50	1.25	1.05	
M25PE10-VMN6TP	M25PE10-VMN6TPCT-ND	1Mb, Page-Erasable Serial Flash.....SO-8	1.80	1.50	1.26	
M25PE10-VMN6TP	M25PE10-VMN6TPTR-ND	1Mb, Page-Erasable Serial Flash.....SO-8		1950.00/2,500		
M25PE10-VMP6TG	M25PE10-VMP6TGCT-ND	1Mb, Page-Erasable Serial Flash.....8-VDFPN	1.80	1.50	1.26	
M25PE10-VMP6TG	M25PE10-VMP6TGTR-ND	1Mb, Page-Erasable Serial Flash.....8-VDFPN		3120.00/4,000		
M25PE20-VMN6P	M25PE20-VMN6P-ND	2Mb, Page-Erasable Serial Flash.....SO-8	2.10	1.75	1.47	
M25PE20-VMN6TP	M25PE20-VMN6TPCT-ND	2Mb, Page-Erasable Serial Flash.....SO-8	2.10	1.75	1.47	
M25PE20-VMN6TP	M25PE20-VMN6TPTR-ND	2Mb, Page-Erasable Serial Flash.....SO-8		2275.00/2,500		
M25PE20-VMP6G	M25PE20-VMP6G-ND	2Mb, Page-Erasable Serial Flash.....8-VDFPN	2.10	1.75	1.47	
M25PE40-VMN6TP	M25PE40-VMN6TPCT-ND	4Mb, Page-Erasable Serial Flash.....SO-8	2.40	2.00	1.68	
M25PE40-VMN6TP	M25PE40-VMN6TPTR-ND	4Mb, Page-Erasable Serial Flash.....SO-8		2600.00/2,500		
M25PE40-VMP6TG	M25PE40-VMP6TGCT-ND	4Mb, Page-Erasable Serial Flash.....8-VDFPN	2.12	1.77	1.49	
M25PE40-VMP6TG	M25PE40-VMP6TGTR-ND	4Mb, Page-Erasable Serial Flash.....8-VDFPN		3671.20/4,000		
M25PE40-VMW6G	M25PE40-VMW6G-ND	4Mb, Page-Erasable Serial Flash.....SO-8	2.40	2.00	1.68	
M25PE80-VMN6TP	M25PE80-VMN6TPCT-ND	8Mb, Page-Erasable Serial Flash.....SO-8	2.70	2.25	1.89	
M25PE80-VMN6TP	M25PE80-VMN6TPTR-ND	8Mb, Page-Erasable Serial Flash.....SO-8		2925.00/2,500		
M25PE80-VMP6TG	M25PE80-VMP6TGCT-ND	8Mb, Page-Erasable Serial Flash.....8-VDFPN	2.70	2.25	1.89	
M25PE80-VMP6TG	M25PE80-VMP6TGTR-ND	8Mb, Page-Erasable Serial Flash.....8-VDFPN		4680.00/4,000		
M25PE80-VMS6TG	M25PE80-VMS6TGCT-ND	8Mb, Page-Erasable Serial Flash.....8L-QFN	2.70	2.25	1.89	
M25PE80-VMS6TG	M25PE80-VMS6TGTR-ND	8Mb, Page-Erasable Serial Flash.....8L-QFN		4680.00/4,000		
M25PE80-VMW6TG	M25PE80-VMW6TGCT-ND	8Mb, Page-Erasable Serial Flash.....SO-8	3.51	3.06	2.28	
M25PE80-VMW6TG	M25PE80-VMW6TGTR-ND	8Mb, Page-Erasable Serial Flash.....SO-8		2593.50/1,500		
M25PE16-VMP6TG	M25PE16-VMP6TGCT-ND	16Mb, Page-Erasable Serial Flash.....8-VDFPN	2.70	2.35	1.75	
M25PE16-VMP6TG	M25PE16-VMP6TGTR-ND	16Mb, Page-Erasable Serial Flash.....8-VDFPN		5120.00/4,000		
M25PE16-VMW6TG	M25PE16-VMW6TGCT-ND	16Mb, Page-Erasable Serial Flash.....SO-8	2.81	2.45	1.82	
M25PE16-VMW6TG	M25PE16-VMW6TGTR-ND	16Mb, Page-Erasable Serial Flash.....SO-8		2074.80/1,500		

numonyx		Digi+Reel		NEW! CODE AND DATA STORAGE — RoHS Compliant		
Numonyx Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	10	100
M25PX Series						
M25PX80-VMW6G	M25PX80-VMW6G-ND	8Mb, Dual I/O, 4Kbyte Subsector Erase, Serial Flash.....SO-8	1.80	1.56	1.20	
M25PX32-VMF6F	M25PX32-VMF6FCT-ND	32Mb, Dual I/O, 4Kbyte Subsector Erase, Serial Flash.....SO-16	2.97	2.59	1.93	
M25PX32-VMF6F	M25PX32-VMF6FTR-ND	32Mb, Dual I/O, 4Kbyte Subsector Erase, Serial Flash.....SO-16		2194.50/1,500		
M25PX32-VMP6E	M25PX32-VMP6E-ND	32Mb, Dual I/O, 4Kbyte Subsector Erase, Serial Flash.....8-VDFPN	2.97	2.59	1.93	
M25PX64-VME6G	M25PX64-VME6G-ND	64Mb, Dual I/O, 4Kbyte Subsector Erase, Serial Flash.....8-VDFPN	6.90	6.30	4.98	
M25PX64-VMF6P	M25PX64-VMF6P-ND	64Mb, Dual I/O, 4Kbyte Subsector Erase, Serial Flash.....SO-16	5.43	4.73	3.52	
M25PX64-VMF6TP	M25PX64-VMF6TPCT-ND	64Mb, Dual I/O, 4Kbyte Subsector Erase, Serial Flash.....SO-16	6.90	6.30	4.98	
M25PX64-VMF6TP	M25PX64-VMF6TPTR-ND	64Mb, Dual I/O, 4Kbyte Subsector Erase, Serial Flash.....SO-16		3825.00/1,000		

numonyx		Digi+Reel		NEW! INDUSTRY STANDARD BOOT BLOCK — RoHS Compliant		
Numonyx Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	10	100
M28W Series						
M28W160CB70N6E	M28W160CB70N6E-ND	16Mb (1Mbx16, Boot Block) 3V Supply Flash.....48-TSOP	2.70	2.35	1.75	
M28W160CT70N6E	M28W160CT70N6E-ND	16Mb (1Mbx16, Boot Block) 3V Supply Flash.....48-TSOP	2.70	2.35	1.75	
M28W160ECB70ZB6E	M28W160ECB70ZB6E-ND	16Mb (1Mbx16, Boot Block) 3V Supply Flash.....46-TFBGA	2.70	2.35	1.75	
M28W160ECT70ZB6E	M28W160ECT70ZB6E-ND	16Mb (1Mbx16, Boot Block) 3V Supply Flash.....46-TFBGA	2.70	2.35	1.75	
M28W160ECT70ZB6U	M28W160ECT70ZB6UCT-ND	16Mb (1Mbx16, Boot Block) 3V Supply Flash.....46-TFBGA	2.70	2.35	1.75	
M28W160ECT70ZB6U	M28W160ECT70ZB6UTR-ND	16Mb (1Mbx16, Boot Block) 3V Supply Flash.....46-TFBGA		3200.00/2,500		

Numonyx Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	10	100
M28W320FCB70N6E	M28W320FCB70N6E-ND	32Mb (2Mbx16, Boot Block) 3V Supply Flash.....48-TSOP	2.97	2.59	1.93	
M28W320FCB70ZB6E	M28W320FCB70ZB6E-ND	32Mb (2Mbx16, Boot Block) 3V Supply Flash.....47-TFBGA	2.97	2.59	1.93	
M28W320FCT70N6E	M28W320FCT70N6E-ND	32Mb (2Mbx16, Boot Block) 3V Supply Flash.....48-TSOP	2.97	2.59	1.93	
M28W320FCT70ZB6E	M28W320FCT70ZB6E-ND	32Mb (2Mbx16, Boot Block) 3V Supply Flash.....47-TFBGA	2.97	2.59	1.93	
M28W640HCB70N6F	M28W640HCB70N6FCT-ND	64Mb (4Mbx16, Boot Block) 3V Supply Flash.....48-TSOP	6.90	6.30	4.98	
M28W640HCB70N6F	M28W640HCB70N6FTR-ND	64Mb (4Mbx16, Boot Block) 3V Supply Flash.....48-TSOP		5737.50/1,500		
M28W640HCB70ZB6F	M28W640HCB70ZB6FCT-ND	64Mb (4Mbx16, Boot Block) 3V Supply Flash.....48-TFBGA	6.90	6.30	4.98	
M28W640HCB70ZB6F	M28W640HCB70ZB6FTR-ND	64Mb (4Mbx16, Boot Block) 3V Supply Flash.....48-TFBGA		9450.00/2,500		
M28W640HCT70N6F	M28W640HCT70N6FCT-ND	64Mb (4Mbx16, Boot Block) 3V Supply Flash.....48-TSOP	6.90	6.30	4.98	
M28W640HCT70N6F	M28W640HCT70N6FTR-ND	64Mb (4Mbx16, Boot Block) 3V Supply Flash.....48-TSOP		5737.50/1,500		
M28W640HCT70ZB6F	M28W640HCT70ZB6FCT-ND	64Mb (4Mbx16, Boot Block) 3V Supply Flash.....48-TFBGA	6.90	6.30	4.98	
M28W640HCT70ZB6F	M28W640HCT70ZB6FTR-ND	64Mb (4Mbx16, Boot Block) 3V Supply Flash.....48-TFBGA		9450.00/2,500		

numonyx		Digi+Reel		NEW! AUTOMOTIVE STANDARD BOOT BLOCK		
Numonyx Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	10	100
M29W Series						
M29DW128G60ZAG6E	M29DW128G60ZAG6E-ND	128Mb (8Mbx16, Multiple Bank, Page, Dual Boot) 3V Supply Flash*.....64-TBGA	10.00	9.25	7.00	
M29DW128G70N6E	M29DW128G70N6E-ND	128Mb (8Mbx16, Multiple Bank, Page, Dual Boot) 3V Supply Flash*.....56-TSOP	10.00	9.25	7.00	
M29DW128G70ZAG6E	M29DW128G70ZAG6E-ND	128Mb (8Mbx16, Multiple Bank, Page, Dual Boot) 3V Supply Flash*.....64-TBGA	10.00	9.25	7.00	
M29DW323DB70N6E	M29DW323DB70N6E-ND	32Mb (4Mbx8 or 2Mbx16, Dual Bank 8:24, Boot Block) 3V Supply Flash*.....48-TSOP	9.09	8.30	6.56	
M29DW323DB70ZE6E	M29DW323DB70ZE6E-ND	32Mb (4Mbx8 or 2Mbx16, Dual Bank 8:24, Boot Block) 3V Supply Flash*.....48-TFBGA	9.09	8.30	6.56	
M29DW323DT70N6E	M29DW323DT70N6E-ND	32Mb (4Mbx8 or 2Mbx16, Dual Bank 8:24, Boot Block) 3V Supply Flash*.....48-TSOP	2.97	2.59	1.93	
M29DW323DT70ZE6E	M29DW323DT70ZE6E-ND	32Mb (4Mbx8 or 2Mbx16, Dual Bank 8:24, Boot Block) 3V Supply Flash*.....48-TFBGA	2.97	2.59	1.93	
M29W128GH70N6E	M29W128GH70N6E-ND	128Mb (16Mbx8 or 8Mbx16, Page, Uniform LBP) 3V Supply Flash*.....56-TSOP	6.67	6.09	4.82	
M29W128GH70ZAG6E	M29W128GH70ZAG6E-ND	128Mb (16Mbx8 or 8Mbx16, Page, Uniform LBP) 3V Supply Flash*.....64-TBGA	10.00	9.25	7.00	
M29W128GL70N6E	M29W128GL70N6E-ND	128Mb (16Mbx8 or 8Mbx16, Page, Uniform FB) 3V Supply Flash*.....56-TSOP	6.67	6.09	4.82	
M29W128GL70ZAG6E	M29W128GL70ZAG6E-ND	128Mb (16Mbx8 or 8Mbx16, Page, Uniform FB) 3V Supply Flash*.....64-TBGA	10.00	9.25	7.00	
M29W160EB70N6E	M29W160EB70N6E-ND	16Mb (2Mbx8 or 1Mbx16, Boot Block) 3V Supply Flash*.....48-TSOP	5.40	4.70	3.50	
M29W160EB70ZAG6E	M29W160EB70ZAG6E-ND	16Mb (2Mbx8 or 1Mbx16, Boot Block) 3V Supply Flash*.....48-TFBGA	2.70	2.35	1.75	
M29W160ET70N6E	M29W160ET70N6E-ND	16Mb (2Mbx8 or 1Mbx16, Boot Block) 3V Supply Flash*.....48-TSOP	5.40	4.70	3.50	
M29W160ET70N6F	M29W160ET70N6FCT-ND	16Mb (2Mbx8 or 1Mbx16, Boot Block) 3V Supply Flash*.....48-TSOP	2.70	2.35	1.75	
M29W160ET70N6F	M29W160ET70N6FTR-ND	16Mb (2Mbx8 or 1Mbx16, Boot Block) 3V Supply Flash*.....48-TSOP		1995.00/1,500		
M29W160ET70ZAG6E	M29W160ET70ZAG6E-ND	16Mb (2Mbx8 or 1Mbx16, Boot Block) 3V Supply Flash*.....48-TFBGA	2.70	2.35	1.75	
M29W160FB70N3E	M29W160FB70N3E-ND	16Mb (x8 or x16, Boot Block) 3V Supply Flash*.....48-TSOP	2.70	2.35	1.75	
M29W160FB70N3F	M29W160FB70N3FCT-ND	16Mb (x8 or x16, Boot Block) 3V Supply Flash*.....48-TSOP	2.70	2.35	1.75	
M29W160FB70N3F	M29W160FB70N3FTR-ND	16Mb (x8 or x16, Boot Block) 3V Supply Flash*.....48-TSOP		1995.00/1,500		
M29W160FB80ZA3E	M29W160FB80ZA3E-ND	16Mb (x8 or x16, Boot Block) 3V Supply Flash*.....48-TFBGA	2.70	2.35	1.75	
M29W160FT70N3E	M29W160FT70N3E-ND	16Mb (x8 or x16, Boot Block) 3V Supply Flash*.....48-TSOP	2.70	2.35	1.75	
M29W160FT70N3F	M29W160FT70N3FCT-ND	16Mb (x8 or x16, Boot Block) 3V Supply Flash*.....48-TSOP	2.70	2.35	1.75	
M29W160FT70N3F	M29W160FT70N3FTR-ND	16Mb (x8 or x16, Boot Block) 3V Supply Flash*.....48-TSOP		1995.00/1,500		
M29W320DB70N6E	M29W320DB70N6E-ND	32Mb (4Mbx8 or 2Mbx16, Non-Uniform Parameter Blocks, Boot Block)*.....48-TSOP	2.97	2.59	1.93	
M29W320DB70ZE6E	M29W320DB70ZE6E-ND	32Mb (4Mbx8 or 2Mbx16, Non-Uniform Parameter Blocks, Boot Block)*.....48-TFBGA	2.97	2.59	1.93	

*RoHS Compliant

(Continued)

★ CALL FOR LOWER PRICING ON LARGER QUANTITIES! ★

More Product Available Online: www.digikey.com

Toll-Free: 1-800-344-4539 • Phone 218-681-6674 • Fax: 218-681-3380