

<p>Fig. 38 — Emperor Wall Mount Cabinets NEW!</p> <ul style="list-style-type: none"> Fits 19" panel Mouse pad slides underneath right or left Takes up 2-U of panel space 	<p>Fig. 39 — Keyboard/Mouse Shelf</p> <ul style="list-style-type: none"> High quality Designed for long wear 	<p>Fig. 40 — Stationary Shelves</p> <ul style="list-style-type: none"> Fits 19" wide panel spaces Supports up to 200 pounds Requires two pairs of panel mounting rails per cabinet 	<p>Fig. 41 — External Mount Brackets NEW!</p>
<p>Fig. 42 — Equipment Shelves</p> <ul style="list-style-type: none"> Fits 19" panel spaces One piece construction Supports 150 pounds 	<p>Fig. 43 — Handles</p> <ul style="list-style-type: none"> High quality Designed for long wear 	<p>Fig. 44 — Panels</p>	<p>Fig. 45 — Slides</p> <ul style="list-style-type: none"> Telescoping Zinc-plated alloy steel with ball bearings
<p>Fig. 46 — Slide Mounting Brackets</p> <ul style="list-style-type: none"> Designed for mounting two and three piece slides Sold in pairs 	<p>Fig. 47 — Tem-Stat Temperature Control</p> <ul style="list-style-type: none"> Contacts open when there is a 10°F drop in temperature Prevents shut-downs caused by overheating 	<p>Fig. 48 — Fan Tray Assemblies</p> <ul style="list-style-type: none"> Standard EIA 19.00" x 1-U (1.75") panel mounting 115VAC 7" long, three prong, power cord 	<p>Fig. 49 — Keyboard / Mouse Shelf</p>

NEW! Emperor Wall Mount Cabinets

Dimensions - Inch (cm)			Digi-Key Part No.	Price Each		Bud Ind. Part No.
A	B	C		1	10	
Fig. 38 — Emperor Wall Mount						
23.62 (59.99)	15.75 (40.00)	25.00 (63.5)	377-1624-ND	428.00	356.67	WM-5601
23.62 (59.99)	15.75 (40.00)	51.34 (130.40)	377-1625-ND	656.30	546.92	WM-5606
23.62 (59.99)	21.65 (54.99)	25.00 (63.5)	377-1626-ND	485.10	404.26	WM-5611
23.62 (59.99)	21.65 (54.99)	51.34 (130.40)	377-1627-ND	713.30	594.42	WM-5616

Accessories

Color	Maximum Panel Keyboard Width - Inch (cm)	Digi-Key Part No.	Price Each		Bud Ind. Part No.
Fig. 39 — Keyboard / Mouse Shelf			1	10	
Black	19.0 x 16.5 (48.26 x 41.91)	377-1244-ND	198.00	165.33	KS-1785-BT

Color	Dimensions - Inch (cm)		Digi-Key Part No.	Price Each		Bud Ind. Part No.
	Width	Depth		1	3	
Fig. 40 — Stationary Shelves — Non-Ventilated						
Black	17.90 (45.47)	26.50 (67.31)	377-1306-ND	89.30	66.90	SH-2382
	17.90 (45.47)	19.25 (48.90)	377-1188-ND	79.40	59.50	60-2380
	17.90 (45.47)	22.75 (57.79)	377-1189-ND	83.40	62.50	60-2381
	17.00 (43.18)	17.75 (45.09)	377-1416-ND†	144.00	—	SH-2388

Color	Dimensions - Inch (cm)		Digi-Key Part No.	Price Each		Bud Ind. Part No.
	Width	Depth		1	3	
Fig. 40 — Stationary Shelves - Ventilated						
Black	17.90 (45.47)	17.75 (45.09)	377-1307-ND	83.20	62.35	SH-2384
	17.90 (45.47)	21.25 (53.98)	377-1308-ND	86.30	64.65	SH-2385
	17.90 (45.47)	26.50 (67.31)	377-1309-ND	93.50	70.05	SH-2386
	17.00 (43.18)	17.75 (45.09)	377-1415-ND†	146.40	—	SH-2392

Color	Dimensions - Inch (cm)		Digi-Key Part No.	Price Each		Bud Ind. Part No.
	Width	Depth		1	10	
NEW! Fig. 41 — External Mount Brackets						
Dk. Gray	—	—	377-1628-ND	2.00	1.67	MB-1390-DG
Lt. Gray	—	—	377-1629-ND	2.00	1.67	MB-1390-LG

† Sliding Shelf

Color	Dimensions - Inch (cm)		Digi-Key Part No.	Price Each		Bud Ind. Part No.
	A	B		1	10	
Fig. 42 — Equipment Shelves - Open Rack - Non-Ventilated						
Black	17.62 (44.75)	15.00 (38.10)	377-1291-ND	73.60	61.45	SA-1750-BT
	17.62 (44.75)	20.00 (50.80)	377-1293-ND	88.00	73.50	SA-1752-BT

Color	Dimensions - Inch (cm)		Digi-Key Part No.	Price Each		Bud Ind. Part No.
	A	B		1	10	
Fig. 42 — Equipment Shelves - Open Rack - Ventilated						
Black	17.62 (44.75)	15.00 (38.10)	377-1292-ND	80.40	67.15	SA-1751-BT
	17.62 (44.75)	20.00 (50.80)	377-1294-ND	95.40	79.65	SA-1753-BT

Hand Clearance	Dimensions - Inch (mm)		Digi-Key Part No.	Price Each		Bud Ind. Part No.
	Mounting Center	Diameter		1	10	
Fig. 43A — Chrome Plated Handles						
1.25 (31.75)	6.00 (152.4)	.37 (9.398)	377-1228-ND*	8.30	6.95	H-9110-B
.93 (23.62)	4.00 (101.6)	.37 (9.398)	377-1229-ND*	6.40	5.30	H-9111-B
.93 (23.62)	6.00 (152.4)	.37 (9.398)	377-1230-ND*	7.80	6.50	H-9112-B
.93 (23.62)	8.00 (203.2)	.37 (9.398)	377-1231-ND	10.60	8.85	H-9113-B
1.50 (38.1)	8.00 (203.2)	.50 (12.7)	377-1232-ND†	16.50	13.80	H-9114-B
1.68 (3.36)	3.50 (88.9)	.37 (9.398)	377-1233-ND†	12.40	10.35	H-9160-B
1.00 (25.4)	1.90 (48.26)	.25 (6.35)	377-1234-ND†	10.60	8.90	H-9161-B
1.00 (25.4)	3.00 (76.2)	.25 (6.35)	377-1235-ND§	6.00	5.00	H-9166-B
1.00 (25.4)	3.00 (76.2)	.25 (6.35)	377-1236-ND§	5.70	4.70	H-9168-B
Fig. 43B — Clear Anodized Aluminum Handle						
1.09 (27.69)	4.00 (101.6)	—	377-1237-ND‡	10.80	9.05	H-9174-B

* Includes 2 - #10-32 x .37" screws. † Includes 2 - #6-32 x .50" screws. § Includes 2 - 1/4"-28 Hex nuts
‡ Includes 2-8.32 x .37" screws

Dimension - Inch (mm)	Digi-Key Part No.	Price Each		Bud Ind. Part No.
		1	10	
Fig. 44 — 19" Aluminum Surface Shield Panels - .12" Thick				
1.75 (44.45)	377-1300-ND	9.50	7.95	SFA-1831
3.50 (88.9)	377-1301-ND	13.90	11.55	SFA-1832
5.25 (133.35)	377-1302-ND	17.80	14.90	SFA-1833
7.00 (177.8)	377-1303-ND	22.80	19.05	SFA-1834
8.75 (222.25)	377-1304-ND	25.00	20.85	SFA-1835
10.50 (266.7)	377-1305-ND	32.40	27.00	SFA-1836
Fig. 44 — 19" Aluminum Panels - .12" Thick (Gray)				
1.75 (44.45)	377-1247-ND	13.00	10.92	PA-1101-MG
3.50 (88.9)	377-1248-ND	18.20	15.17	PA-1102-MG
5.25 (133.35)	377-1249-ND	25.00	20.82	PA-1103-MG
7.00 (177.8)	377-1250-ND	31.10	26.03	PA-1104-MG
8.75 (222.25)	377-1251-ND	37.60	31.40	PA-1105-MG
10.50 (266.7)	377-1252-ND	47.70	39.86	PA-1106-MG
12.25 (311.15)	377-1253-ND	52.30	43.59	PA-1107-MG
14.00 (355.6)	377-1254-ND	67.00	55.89	PA-1108-MG

Slide Length	Dimensions - Inch (cm)		Load Rating (per pair)	Digi-Key Part No.	Price Each		Bud Ind. Part No.
	Travel	Travel			1	3	
Fig. 45 — Sliding Mechanisms - 2 Piece Slide							
12 (30.48)	8 (20.32)	140 lbs.	377-1199-ND	30.50	25.45	AS-5000-A	
16 (40.64)	12 (30.48)	120 lbs.	377-1200-ND	40.10	33.50	AS-5001-A	
20 (50.80)	15 (38.10)	92 lbs.	377-1201-ND	42.00	35.10	AS-5002-A	
26 (66.04)	19 (48.26)	70 lbs.	377-1202-ND	46.40	38.75	AS-5004-A	
20 (50.80)	20.875 (53.02)	91 lbs.	377-1203-ND*	91.00	76.00	AS-5042-A	

* 3 piece slide full extension

Description	Digi-Key Part No.	Price Each		Bud Ind. Part No.
		1	3	
Fig. 46 — Slide Mounting Brackets (Sold in Pairs)				
Universal Kit.....	377-1204-ND	30.20	25.05	BAS-5106

Description	Digi-Key Part No.	Price Each		Bud Ind. Part No.
		1	5	
Fig. 47 — Tem-Stat Temperature Control				
Normally Open; Closes on Temperature Rise...	377-1314-ND	34.80	—	TS-15

Description	Digi-Key Part No.	Price Each		Bud Ind. Part No.
		1	5	
Rack Mount Power Outlet Strip				
15 Amps.....	377-1414-ND	77.00	57.75	POS-194-S

Description	Digi-Key Part No.	Price Each		Bud Ind. Part No.
		1	5	
Fig. 48 — Fan Tray Assemblies				
Assembly with 3 Fans, Total CFM 315.....	377-1423-ND	215.10	155.95	FT-1973
Assembly with 6 Fans, Total CFM 630.....	377-1424-ND	330.90	239.92	FT-1976
Assembly with 9 Fans, Total CFM 945.....	377-1425-ND	434.00	314.66	FT-1979

More Product Available Online: www.digkey.com