



Description	Dimensions Width x Length	Digi-Key Part No.	Price Each		3M Part No.
			1	5	
3M Laminating Adhesives					
Adhesive Transfer Tape, 100MP Adhesive, Clear, .005", Dual-lined for Prototyping	8.5" x 8.5"	3M6446-ND	8.13	6.50	F9469PC
Adhesive Transfer Tape, 100MP Adhesive, Clear, .005"	3/8" x 60 yds.	3M9039-ND NEW!	23.25	18.60	F9469PC 3/8"X60YD
Adhesive Transfer Tape, 200MP Adhesive, Clear, .005", Dual-lined for Prototyping	8.5" x 8.5"	3M6447-ND	6.63	5.30	468MP
Adhesive Transfer Tape, 200MP Adhesive, Clear, .005"	3/4" x 60 yds.	3M9040-ND NEW!	21.65	17.32	468MP 3/4"X60YD
Adhesive Transfer Tape, 300LSE Adhesive, Clear, 5.0 mils	4" x 60 yds.	SCP284-ND NEW!	87.41	77.50	9472LE 4"X60YD
Double Coated Tape, 375 Adhesive, Translucent, 7.5 mils	19mm x 50M	3M9042-ND NEW!	17.68	14.14	9086 19MMX50M
Double Coated Tape, 375 Adhesive, White, 10.2 mils	19mm x 50M	3M9043-ND NEW!	21.20	16.96	9087 19MMX50M
Double Coated Tape, 375 Adhesive, Clear, 8.3 mils	19mm x 50M	3M9044-ND NEW!	19.05	15.24	9088 19MMX50M
Double Coated Tape, 200MP Adhesive, Clear, .0057", Dual-lined for Prototyping	8.5" x 8.5"	3M6448-ND	7.50	6.00	9495MP
Double Coated Tape, 300LSE Adhesive, Clear, .0067", Dual-lined for Prototyping	8.5" x 8.5"	3M6449-ND	7.75	6.20	9495LE
Double Coated Tape, 300LSE Adhesive, Clear, .0034"	3/4" x 60 yds.	3M9041-ND NEW!	33.28	26.62	9495LE 3/4"X60YD
Double Coated Tape, 300MP Adhesive, Tan, .0055", Dual-lined for Prototyping	8.5" x 8.5"	3M6450-ND	6.25	5.00	9786
Double Coated Tape, 300MP Adhesive, Clear, .0067", Dual-lined for Prototyping	8.5" x 8.5"	3M6451-ND	7.00	5.60	9490LE
Aluminum Foil Tape					
Aluminum Foil Tape, 2.8-mil, Acrylic Adhesive, Thermally Conductive, Heat & Light Reflective	1" x 60 yds.	3M5613-ND	22.87	19.61	425-1"X60YD-BULK
Aluminum Foil Tape, 2.8-mil, Acrylic Adhesive, Thermally Conductive, Heat & Light Reflective	3" x 60 yds.	3M5614-ND	68.60	58.80	425-3"X60YD-BULK
Aluminum Foil Tape, 2.8-mil, Acrylic Adhesive, Thermally Conductive, Heat & Light Reflective	2" x 60 yds.	3M5615-ND	69.63	59.69	427-2"X60YD
Aluminum Foil Tape, 2.0-mil, Silicone Adhesive, Thermally Conductive, Heat & Light Reflective	1" x 60 yds.	3M5617-ND	68.97	59.12	433-1"X60YD
Aluminum Foil Tape, 2.0-mil, Silicone Adhesive, Thermally Conductive, Heat & Light Reflective	2" x 60 yds.	3M5616-ND	137.95	118.25	433-2"X60YD
Aluminum Foil Tape, 2.0-mil, Silicone Adhesive, Thermally Conductive, Heat & Light Reflective, Lined	1" x 60 yds.	3M5632-ND	91.16	78.14	433L-1"X60YD
Aluminum Foil Tape, 2.0-mil, Silicone Adhesive, Thermally Conductive, Heat & Light Reflective, Lined	2" x 60 yds.	3M5631-ND	182.30	156.26	433L-2"X60YD
Aluminum Foil Tape, 5.0-mil, Acrylic Adhesive, Thermally Conductive, Heat and Light Reflective	2" x 60 yds.	3M5633-ND	83.18	71.30	438
Double Coated Foam Tape					
Attachment Tape, .045", Acrylic Plus Adhesive, High Performance, Black, Automotive Grade	1/4" x 20 yds.	3M6411-ND†	17.83	—	06386
Attachment Tape, .045", Acrylic Plus Adhesive, High Performance, Black, Automotive Grade	1/2" x 5 yds.	3M6410-ND	9.92	—	06384
Attachment Tape, .045", Acrylic Plus Adhesive, High Performance, Black, Automotive Grade	1/2" x 20 yds.	3M6408-ND	31.13	—	06382
Attachment Tape, .045", Acrylic Plus Adhesive, High Performance, Black, Automotive Grade	7/8" x 20 yds.	3M6409-ND	47.29	—	06383
Attachment Tape, .060", Acrylic Plus Adhesive, High Performance, Black, Automotive Grade	7/8" x 10 yds.	3M6412-ND	34.53	—	06395
Attachment Tape, .090", Acrylic Plus Adhesive, High Performance, Gray, Automotive Grade	1/2" x 10 yds.	3M6413-ND	22.84	—	06394
Double Coated Foam Tape, .125", Pressure Sensitive Acrylic Adhesive, Off-White Urethane Foam	1" x 36 yds.	3M4008-ND	61.61	—	4008 1"
Double Coated Foam Tape, .062", Pressure Sensitive Acrylic Adhesive, Off-White Urethane Foam	1" x 36 yds.	3M40161-ND	41.46	—	4016 1"
Double Coated Foam Tape, .062", Pressure Sensitive Acrylic Adhesive, Neutral Urethane Foam	1" x 36 yds.	3M4026-ND	35.63	—	4026 1"
Double Coated Foam Tape, .125", Pressure Sensitive Acrylic Adhesive, Black Vinyl Foam	1" x 36 yds.	3M44081-ND	85.57	—	4408 1"
Double Coated Foam Tape, .020", Pressure Sensitive Acrylic Adhesive, Black Vinyl Foam	1" x 36 yds.	3M44161B-ND	65.62	—	4416 1" BLACK
Double Coated Foam Tape, .062", Pressure Sensitive Acrylic Adhesive, White Vinyl Foam	1" x 36 yds.	3M44161W-ND	65.62	—	4416 1" WHITE
Double Coated Foam Tape, .045", Pressure Sensitive VHB™ Acrylic Adhesive, Dark Gray	1/2" x 36 yds.	3M6462-ND	33.06	28.34	4611 1/2" IN X 36 YD
Double Coated Foam Tape, .020", Pressure Sensitive VHB Acrylic Adhesive, Clear	1" x 72 yds.	3M6463-ND	146.04	125.18	4905-1"X72YD
Double Coated Foam Tape, .020", Pressure Sensitive VHB Acrylic Adhesive, Clear	1/2" x 72 yds.	3M6464-ND	78.23	67.05	4905-1/2"X72YD
Double Coated Foam Tape, .045", Pressure Sensitive VHB Acrylic Adhesive, Clear	3/4" x 72 yds.	3M6465-ND	104.30	89.40	4905-3/4"X72YD
Double Coated Foam Tape, .040", Pressure Sensitive VHB Acrylic Adhesive, Clear (small pack)	1/2" x 36 yds.	3M6466-ND	46.22	39.62	4910 -1/2"X36YD
Double Coated Foam Tape, .040", Pressure Sensitive VHB Acrylic Adhesive, Clear	1/2" x 36 yds.	3M6467-ND	37.42	32.07	4910-CLEAR-1/2"X36YD
Double Coated Foam Tape, .040", Pressure Sensitive VHB Acrylic Adhesive, Clear	3/4" x 15 yds.	3M5648-ND	30.59	26.22	4910 3/4"X15YD
Double Coated Foam Tape, .040", Pressure Sensitive VHB Acrylic Adhesive, Clear	1" x 36 yds.	3M5650-ND	62.37	53.46	4910-CLEAR-1"X36YD
Double Coated Foam Tape, .045", Pressure Sensitive VHB Acrylic Adhesive, White Acrylic Foam	1/2" x 36 yds.	3M5625-ND	60.15	51.56	4950-1/2"X36YD-SMPK
Double Coated Foam Tape, .045", Pressure Sensitive VHB Acrylic Adhesive, White Acrylic Foam	3/4" x 36 yds.	3M5626-ND	80.24	68.78	4950-3/4"X36YD-SMPK
Double Coated Foam Tape, .045", Pressure Sensitive VHB Acrylic Adhesive, White Acrylic Foam	1" x 36 yds.	3M5627-ND	100.24	85.92	4950-1"X36YD-SMPK
Double Coated Foam Tape, .045", Pressure Sensitive VHB Modified Acrylic Adhesive, Black	1/2" x 36 yds.	3M6468-ND	52.12	44.67	5952-1/2"X36YD
Double Coated Foam Tape, .045", Pressure Sensitive VHB Modified Acrylic Adhesive, Black	3/4" x 15 yds.	3M5647-ND	30.59	26.22	5952 3/4"X15YD
Double Coated Foam Tape, .045", Pressure Sensitive VHB Modified Acrylic Adhesive, Black	1" x 36 yds.	3M5649-ND	86.85	74.45	5952 1"X36YD
Duct Tape					
Duct Tape Clean Remove, 12.6-mil, Slate Blue Polyethylene Film, Synthetic Rubber Adhesive	1.88" x 60 yds.	3M5630-ND	13.46	11.54	8979-BLUE-48MMX54.8M
Duct Tape Industrial Grade, 10.7-mil, Black Polyethylene Film, Rubber Adhesive	1.88" x 60 yds.	3M69692B-ND	12.71	—	6969 2" BLACK
Duct Tape Industrial Grade, 10.7-mil, Silver Polyethylene Film, Rubber Adhesive	1.88" x 60 yds.	3M69692S-ND	11.52	—	6969 2" SILVER
Electrical Tape - Black					
Vinyl Mastic Pad, All-Weather Grade, 125-mil, Black Vinyl Film, Rubber Mastic	3-1/4" x 4-1/2"	3M11008-ND	4.00	—	2200 (3-1/4"X4-1/2")
Electrical Tape, General Purpose, 7-mil, Black PVC, Flame-Retardant	3/4" x 66'	3M1700-ND	1.20	—	1700 TEMFLEX
Electrical Tape, Premium Grade, All-Weather, 7-mil, Black PVC, Pressure-Sensitive Adhesive	3/4" x 66'	3M33+A-ND	6.06	—	33+ SUPER (3/4"X66')
Electrical Tape, Premium Grade, All-Weather, 8.5-mil, Black PVC, Pressure-Sensitive Adhesive	3/4" x 66'	3M88A-ND	6.80	—	88 SUPER (3/4"X66')
Electrical Color Coding Tape - Colored					
Electrical Color Coding Tape, Red PVC, 7-mil, Pressure-Sensitive Adhesive	3/4" x 66'	3M35-RD-ND	5.62	—	35 RED (3/4"X66')
Electrical Color Coding Tape, Orange PVC, 7-mil, Pressure-Sensitive Adhesive	3/4" x 66'	3M35-OR-ND	5.62	—	35 ORANGE (3/4"X66')
Electrical Color Coding Tape, Yellow PVC, 7-mil, Pressure-Sensitive Adhesive	3/4" x 66'	3M35-YL-ND	5.62	—	35 YELLOW (3/4"X66')
Electrical Color Coding Tape, Green PVC, 7-mil, Pressure-Sensitive Adhesive	3/4" x 66'	3M35-GN-ND	5.62	—	35 GREEN (3/4"X66')
Electrical Color Coding Tape, Blue PVC, 7-mil, Pressure-Sensitive Adhesive	3/4" x 66'	3M35-BL-ND	5.62	—	35 BLUE (3/4"X66')
Electrical Color Coding Tape, Violet PVC, 7-mil, Pressure-Sensitive Adhesive	3/4" x 66'	3M35-VL-ND	5.62	—	35 VIOLET (3/4"X66')
Electrical Color Coding Tape, Gray PVC, 7-mil, Pressure-Sensitive Adhesive	3/4" x 66'	3M35-GY-ND	5.62	—	35 GRAY (3/4"X66')
Electrical Color Coding Tape, White PVC, 7-mil, Pressure-Sensitive Adhesive	3/4" x 66'	3M35-WH-ND	5.62	—	35 WHITE (3/4"X66')
Glass and Aluminum/Glass Cloth Tape					
Glass Cloth Tape, White, 5.4-mil, Silicone Adhesive, High Tensil Strength, General Purpose	1" x 60 yds.	3M5609-ND	65.17	55.86	361-1"X60YD
Glass Cloth Tape, White, 5.4-mil, Silicone Adhesive, High Tensil Strength, General Purpose	2" x 60 yds.	3M5610-ND	130.32	111.71	361-2"X60YD
Aluminum/Glass Cloth Tape, 7.3-mil, Silicone Adhesive, Flame/Tear/Puncture-Resistant	1" x 36 yds.	3M5611-ND	108.43	92.94	363-1"X36YD
Aluminum/Glass Cloth Tape, 7.3-mil, Silicone Adhesive, Flame/Tear/Puncture-Resistant	2" x 36 yds.	3M5612-ND	216.84	185.87	363-2"X36YD
High Temperature Tape					
High Temperature Kapton Tape, 2.7-mil, Amber KAPTON Polyimide Film, Silicone Adhesive	1/2" x 36 yds.	3M541312-ND	25.84	—	5413 1/2"
High Temperature Kapton Tape, 2.7-mil, Amber KAPTON Polyimide Film, Silicone Adhesive	3/4" x 36 yds.	3M541334-ND	38.77	—	5413 3/4"
Wave Solder Tape, Low Static, 2.7-mil, Amber Polyimide Film, Silicone Adhesive	1/2" x 36 yds.	3M591912-ND	29.35	—	5419 1/2"
Wave Solder Tape, Low Static, 2.7-mil, Amber Polyimide Film, Silicone Adhesive	3/4" x 36 yds.	3M591934-ND	39.77	—	5419 3/4"
Wave Solder Tape, Water-Soluble, PVA Film Backing, Water-soluble Synthetic Adhesive	1/2" x 36 yds.	3M541412-ND	26.31	—	5414 1/2"
Wave Solder Tape, Water-Soluble, PVA Film Backing, Water-soluble Synthetic Adhesive	3/4" x 36 yds.	3M541434-ND	41.43	—	5414 3/4"

† Recommended for wheel flares or other less demanding applications due to a narrower width.

(Continued)

