

**Multimeters (Cont.)**

**Test Bench® Multimeters**


High quality, ruggedized, multi-function DMMs in a drop resistant case. Resistance and frequency measurement. Diode check. Auto power off. All current ranges fused. **Power Requirements:** Single 9V battery **Dimensions:** 7.8 x 3.5 x 1.5"

**Accessories Supplied:** 9V battery, test leads, instruction manual, rubber boot.

**3 Year Warranty**

**Model 388B:**

3-3/4 Digit LCD Display (4000 count). **DC Volts:** 400mV ~ 1000V **AC Volts:** 400mV ~ 750V **DC/AC Current:** 400µA ~ 10A **Resistance:** 400Ω ~ 40MΩ **Diode Test:** at 1mA, 3.2VDC max. type **Capacitance:** 4nF ~ 40µF **Frequency:** 4kHz ~ 4MHz. Logic level measure (TTL) Transistor gain (hFE) and peak hold.



**Model 390A:**

3-3/4 Digit LCD Display (4000 count). **Analog Bar Graph:** 41 Segments **DC Volts:** 400mV ~ 1000V **AC Volts:** 400mV ~ 750V **DC/AC Current:** 400µA ~ 10A **Resistance:** 400Ω ~ 40MΩ **Diode Test:** at 1.2mA, 3.0VDC max. type **Capacitance:** 4nF ~ 40mF **Frequency:** 4kHz ~ 40MHz **Temperature Range:** -50°C ~ 1300°C (1°C resolution). Auto/manual ranging. Relative mode. Minimum/Maximum hold. Data hold. Memory. RS-232. Audible continuity. Thermocouple Probe included.

**Model 389A:**

3-3/4 Digit LCD Display (4000 count). **Analog Bar Graph:** 41 Segments **DC Volts:** 400mV ~ 1000V **AC Volts:** 400mV ~ 750V **DC/AC Current:** 400µA ~ 10A **Resistance:** 400Ω ~ 40MΩ **Diode Test:** at 1.2mA, 3.0VDC max. type **Capacitance:** 4nF ~ 40mF **Frequency:** 4kHz ~ 40MHz. Auto/manual ranging. Relative mode. Min/max hold. Data hold. Memory. Audible continuity.

**Model 391A:**


4-1/2 Digit LCD Display (20,000 count). **DC Volts:** 200mV ~ 1000V **AC Volts:** 200mV ~ 750V **DC/AC Current:** 400µA ~ 10A True RMS reading **Resistance:** 200Ω ~ 20MΩ **Diode Test:** at 1mA, 3.2VDC max. type **Frequency:** 2kHz ~ 200kHz **Duty Cycle:** .0 ~ 90% (0.1% resolution). Data hold. Logic level measure (TTL).

BK388B-ND	.....	\$130.00
BK390A-ND	.....	\$170.00
BK389A-ND	.....	\$150.00
BK391A-ND	.....	\$190.00
LC-298-ND	Carrying Case (1 Year Warranty).....	\$19.71

**Accessories**

**DC/AC Current Clamp Adapter**

Measures current without disconnecting circuit under test. Measures to 400A DC or AC. Outputs 1 mV per Amp., operates on 2V range of any DMM.



**Power Requirements:** 9V battery  
**Operating Temp.:** 0°C ~ 50°C, <70% RH  
**Dimensions:** 7 x 2.8 x 1.3"

**Accessories Included:** Battery and instruction manual.

CP 3-ND	.....	\$95.03
---------	-------	---------


**Probes and Test Lead Sets**

TP-29-ND	Type K Bead Thermocouple Probe.....	\$10.34
BKTL-4-ND	Universal Test Lead Set.....	\$9.31
TL 2A-ND	Test Lead Set, Fully Shrouded SILIC, IEC61010-2-031 1,000V CATIII.....	\$22.10
TL-1-ND	Test Lead Set, Fully Shrouded.....	\$9.31
TL-3-ND	Test Lead Accessory Set for BKTL-4 and TL-2A.....	\$17.62

**High-Voltage Probes**

**Model PR-28A:**

Accessory for DMM's Multiplies instrument ranges by 1000 (40V becomes 40,000V). PR-28 for use with any high impedance (10MΩ or greater) voltmeter.



**Voltage Range:** 40kVDC and 20kVAC (60Hz)

**Frequency Range:** DC-8Hz 20kVAC max. 60Hz

**Impedance:** 600MΩ accuracy: ±3% plus instrument accuracy

**Calibration:** Internal; factory calibrated at 25kV

**Size:** 14" long; 2.25" diameter (max.); 48" cord

**Connector:** Dual banana


**Model HV 44A:**

Build in meter for stand-alone operation (No DMM required). Measures voltages up to 40,000VDC. Factory calibrated at 25kV (±2% accuracy); full scale ±3% accuracy. Conventional round needle type tip and flat spring type tip for easy access to CRT anode. **Size:** 16.5 x 2.1 x 2" **Color:** Black and Red **Positive Polarity Only - Not for microwave ovens.**

PR 28A-ND	.....	\$65.20
HV 44A-ND	.....	\$113.00

**Logic Probes**

**20MHz and 50MHz Logic Probes**



**Model DP-21:**


(20MHz Logic Probe): Tests TTL, DTL, RTL, HTL, CMOS and MOS. Displays pulse presence and logic states. Memory mode "freezes" pulse display. Catches pulses to 30ns or pulse trains to 20MHz. 1MΩ input impedance. **Operating Supply Voltage Range:** TTL-5V, CMOS 5-15V **Dimensions:** .7 x .7 x 8.2"

**Model DP-52**

(50 MHz Logic Probe): Tests TTL and CMOS. Displays DC to 50MHz. Detects 10ns pulse width. Overload protected. 120kΩ input impedance. **Operating Supply Voltage Range:** 4-18VDC **Dimensions:** .7 x .7 x 8.2"

DP-21-ND	.....	\$36.00
BKDP52-ND	.....	\$46.00

**Pulsar Probe**



For TTL and CMOS. Produces 10µs pulse signal at 100mA. External square wave terminal. **Output Current:** Pulsar mode-100mA sink/source square wave mode-5mA sink/source. **Operating Supply Voltage Range:** 5-15VDC **Sync Input Impedance:** 1MΩ **Dimensions:** .7 x .7 x 8.2"

DP 31A-ND	.....	\$36.00
-----------	-------	---------

**Component Testers**

**Dual-Display Auto Ranging LCR Meter**

Measures inductance, resistance and capacitance. 4 1/2 digit LCD display. Tests at 100Hz, 120Hz, 1kHz or 10kHz (120Hz or 1kHz for 878A only). Relative mode. Tolerance mode. Backlight (879 only).



**Accessories Included:** 9V battery, user manual and test alligator clips pair.

BK878A-ND	.....	\$249.00
BK879-ND	.....	\$299.00
LC-298-ND	Carrying Case (1 Year Warranty).....	\$19.71

**Bench LCR/ESR Meter with Component Tester**

Synthesized In-Circuit LCR/ESR Meter with Component Tester. Used for measuring inductors, capacitors and resistors with DC/AC Voltage measurements and Diode/Audible Continuity checks.



BK889A-ND	.....	\$1425.00
-----------	-------	-----------

**In-Circuit Testers**

**Model 885 — LCR/ESR Meter:**

**Specifications:** Measurement parameters: Z, L, C, DCR, ESR, D, Q, and 0 Test conditions: 100Hz, 120Hz, 1kHz, 10kHz, 1vrms, 0.25Vrms, 0.05Vrms **Features:** • 0.5% basic accuracy • Dual LCD display • SMD surface mount tweezer probe included • Fully auto/manual selection • DC resistance measurement • Rechargeable battery/AC powered

BK885-ND	.....	\$565.00
LC-298-ND	Carrying Case (1 Year Warranty).....	\$19.71

**LCR Meter**

**Model 875B:** Measures capacitance (200pF-20mF ±1%), resistance (2-20MΩ ±1%), and inductance (200µH-200mH ±1%). 3-1/2 digit LCD display. Low battery and overload indicator.



**Power:** Single standard 9V battery

**Dimensions:** 1.4 x 3.5 x 7.5"

**Accessories Included:** Test leads, battery, instruction manual.

BK875B-ND	.....	\$195.00
LC-298-ND	Carrying Case (1 Year Warranty).....	\$19.71

**Auto Ranging Capacitance Meter**

**Model 830B:** 4-1/2 digit LCD display. 11,000 counts resolution. Nine automatically selected ranges with full scale value from 1.0pF ~ 199.99mF. **Features:** • USB PC interface and data logging software included • Three year warranty **Specifications:** • Power Source: 9V battery • Dimensions: 7.24 x 3.42 x 1.61"



**Model 890B:** 4-1/2 LCD with dual display. 11,000 counts resolution. Nine automatically selected ranges with full scale value from 1.0pF ~ 50mF. **Features:** • Program unique values to sort for specific circuit applications • USB PC interface for data logging software available

BK830B-ND	.....	\$289.00
BK890B-ND	.....	\$134.00
LC-298-ND	Carrying Case (1 Year Warranty).....	\$19.71

**Capacitance Meter**

**Model 810C:** 3-1/2 digit LCD display. Nine ranges from 2000F to 20mF. Low battery and over-range indicator. **Power Source:** One 9V battery **Dimensions:** 5.7 x 3 x 1.6" **Accessories Included:** Test leads, battery, and manual.



BK810C-ND	.....	\$81.00
LC-298-ND	Carrying Case (1 Year Warranty).....	\$19.71

**IC Testers**

**Model 570A — Linear IC Tester:**

**Features:**

- Tests all common analog IC's • Auto identification of unmarked/house-coded devices listing possible replacements • Conditional/unconditional loop testing mode • Functional test emulates passive circuitry to implement a comprehensive test in a variety of configurations • Displays diagnostic information down to individual component pins • Rugged, hand-held, ergonomically designed case incorporates built-in membrane keypad, 2 x 16 dot matrix alpha numeric LCD and high quality 16 pin ZIF socket • Auto power off

BK570A-ND	.....	\$1399.00
-----------	-------	-----------

**Model 575A — Digital IC Tester:**

**Features:**

- 40 pin wide-entry ZIF sockets test a broad range of TTL, CMOS Memory, LSI, Interface and other devices (NAND gates to CPUs) • Identifies unmarked and house-coded devices • Detects intermittent and temperature related faults • Displays diagnostic information for individual pins

BK575A-ND	.....	\$1099.00
-----------	-------	-----------

**NTSC Generator**

**Model 1257:**

This portable, handheld NTSC Pattern Generator with S-Video, composite video and audio outputs is powered by a 9-volt battery or AC adapter. It provides NTSC color bars, crosshatch, dot, staircase, circle, center cross, windows, and a full range of color raster patterns. The outputs available are composite video and audio via two RCA connectors or an S-Video mini-DIN output. Signals can be produced as an interlaced or progressive scanning mode. No modulated RF signal is provided.

BK1257-ND	NTSC Generator.....	\$205.00
-----------	---------------------	----------

**Network and PC Cable Testers**

**Model 231A:**

Tests 10 BaseT, 100 Base2, RJ45, RJ11, 356A, TIA-568A, TIA-568B, and token ring cables. • Detects open, short, cross, and continuity • Tests Point-to-Point, rather than a Pair-to-Pair • Tests cables on wall plate or patch panel up to 1000 ft. away with the remote kit • Easy to read LED display

BK231A-ND	DLX Multi-Network Cable Tester.....	\$80.00
-----------	-------------------------------------	---------

**Deluxe EPROM Eraser**

**Model 851:**

Heavy duty EPROM eraser simultaneously erases up to 40 twenty-four pin EPROMs. Features a 60 minute timer.

BK851-ND	.....	\$179.00
----------	-------	----------


**3 1/2 Digit Hand-Held Parts Tester**

26 user ranges for versatile test selection. Tests capacitance from 0.1pF ~ 20mF. Tests resistance from 0.1Ω ~ 20MΩ. Tests transistors, SCRs, diodes and LEDs. Tests batteries under actual loaded conditions.

**Power:** One 9V transistor battery

**Dimensions:** 6.9 x 3.6 x 1.3"

**Accessories Included:** Test leads, spare fuse, battery, instruction manual.



BK815-ND	.....	\$102.00
LC-298-ND	Carrying Case (1 Year Warranty).....	\$19.71

**More Product Available Online: [www.digkey.com](http://www.digkey.com)**

**Toll-Free: 1-800-344-4539 • Phone 218-681-6674 • Fax: 218-681-3380**