

Items listed as digikey.com do not appear in the catalog, but appear on the Digi-Key Web Site.

A

Accelerometers2508-2511

Accessories/D-Sub See Hardware

AC Line Cords, Power Cords
..... 1546-1547

AC Receptacles1547-1548

Adapters
AC1548
Audio454
Auto Lighter Plug/Socket2347
D-Sub59-60
Fiber Optic313-314
Gender Changers60
Keyboard59
Memory Card491
Modular299, 303-304, 310
Mouse59
PLCC517
Programming/Prototyping583-584, 613,
628, 652, 679, 681, 755, 1387, 1389
QFP to PGA516
RF420-423, 427, 429, 433, 435-436,
439, 445-448, 550-551, 2321-2322
SCSI62
SOIC to DIP516
SOJ to DIP516
SSOP to DIP516
TO to DIP517
USB63

Adhesives
Clean Walk2264
Hot Melt2264
Scotch-Weld™2264
Tape2265

Alarms See Buzzers

Alligator Clips2325-2327

Altimeters1262, 1345

Antenna525, 527, 533-535,
551-554, 560, 569, 576, 579
Cellular/GPS552
Horn576
Hybrid Log576
Magnetic Mount552
Planar527, 553
RFid534-535
SMD525, 527, 552
UWB576
Whip525, 527, 553-554
Wireless569
Yagi552

Attenuators314, 1409, 1838, 1899

Audio Processors See digikey.com

Auto Accessories
Cigarette Lighter Plugs/Socket2347
Fuses and Fuseholders2022

B

Backlight, EL Element2535

Ballast, Lighting See digikey.com

Balun558, 1516, 1518

Batteries
Alkaline2343-2344
Camera2339, 2343
Carbon Zinc2343-2344
Chargers2331, 2335, 2345
Coin Cell2338-2343
Computer2339
Contact Cleaner2344
Holders/Clips2346-2349
Lead Acid2344-2345
Lithium2337-2343
Rechargeable2337, 2340-2341
Nickel-Cadmium2337
Nickel-Metal Hydride2335-2336
Packs2336

Bezels2540

Blowers/Fans See Fans/Blowers

Boards See PC Board Prototyping

Books1484

Boxes See Enclosures

Bumpers2264

Bushings
Shoulder2282
Strain Relief2268

Buzzers2234-2237, 2239-2242, 2244

C

Cabinets See Enclosures

Cable
Solar (Photovoltaic)209

Cable Assemblies
AC Line Cords2430
Audio460
BNC, Molded439
CAT 5 and CAT 5e Patch62-64, 310
CAT 6 Patch62-64, 310
Computer, Molded58-59, 62-64
DVI68, 210, 439
eco/mate™384
Fiber Optic315
Flat Flex Cable69-71
Flat Flex DF993
F Type (Television)439
HDMI68, 439
IDC28-36, 44, 48-53, 132
Card Edge35-36
DIP33-34, 44, 49, 53
D-Sub28, 32, 48
PCB34-36, 43-44
Pin/Plug31, 41-43, 51-53, 132
Socket30, 34-36, 41-43,
49-50, 52-53, 132
IEEE 128458
IEEE 139463, 68
Infiniband495
iPass™496
Modular293-294, 304
Molded386
Multi-Media61
Power460
Power Cord60-61, 1546-1547
RCA439
RF439, 445-447, 1409, 2324
SCSI62-63, 496
SDR55
Serial ATA210
Stereo Extension60-61
S Video61
Termination Jumpers28-29, 32-35, 39,
41, 44, 48-49, 52-53, 132
Twisted Pair41-43
USB62-63, 65-68
VGA59

Cable Clamps2268-2272, 2282

Cable/Cord Grips2219

Cable EMI Ferrite Cores1482,
1537-1539

Cable Splice Enclosures357

Cable Testers64, 295

Cable/Wire
Bus Bar2225
Coaxial2221, 2226
Fiber Optic313, 318
Fire Alarm2220
Flat Cable Jumpers73, 85, 87
Flat Flex Cable72-73, 85, 87
0.020" (0.5mm)73, 85
0.040" (1mm)73, 87
0.050" (1.27mm)72
0.100" (2.54mm)72
Hook-Up2217, 2224-2225

Instrumentation2220
Jumper Wires2284
Kits2224
LVDS2526
Microphone, Shielded2221
Modular295
Multiconductor2217-2220, 2222-2224
Shielded2218-2219, 2223-2224
Multi-Paired, Shielded2220, 2222-2223
Plenum2218-2219, 2221, 2226
Ribbon
0.040" (1mm)162
0.050" (1.27mm)45-47, 57
0.080" (2mm) See digikey.com
0.100" (2.54mm) Pre-cut Flat57
High Flex .050"46
Round Jacketed/Shielded47
Twisted Pair46
Sleeving2225
Speaker2217
Stripping Tools2217, 2221, 2293, 2298
Tinned Copper Flat Braid2225
Wire Wrap2286, 2293

Cable/Wire Ties ..2226, 2267-2272, 2277
Holders2267, 2270-2272
Spiral Wrap2226, 2271-2272
Tak Ties, Reusable2270-2272
Twist-Lok2268, 2270-2272
Wire Clamp2268, 2270-2272
Wire Tie Wrap2269, 2271-2272

Camera
Accessories576
Controller576

Camera Modules
CMOS Image Sensors733
Evaluation Boards733
Lens Kits733

Capacitor Arrays1750-1751, 1780,
1795, 1815, 1822-1823, 1900

Capacitor Networks1900

Capacitors
Aluminum Electrolytic1561-1580,
1585-1663, 1707
Axial1561-1564, 1707
Flatpack1580
Screw Terminal1585-1586
Snap-In1586-1595,
1632-1634, 1661-1663
Aluminum Organic1694
Automotive Multilayer Chip1774
Bi-Polar1565, 1600
Ceramic544-545, 1781-1783
Axial1735, 1738-1739, 1747
Chip1752, 1833, 1835
Disc1737, 1744-1746,
1748-1752, 1794, 1824-1826
Monolithic1738-1741,
1792-1793, 1795, 1806-1810
Multilayer1736, 1738-1741, 1743-1744,
1746-1748, 1795, 1827-1828
ArcGuard1827
Soft Termination1828
Multilayer Chip (MLCC)544-545,
1750-1751, 1754-1775,
1778-1791, 1795-1805, 1811-1823,
1826, 1828-1833
Flexisafe Capacitors1773
Low Profile1775
Safety1793
SMT1783
Soft Termination1773-1774
Tip and Ring1779
Trimmer1834-1837
CombiSuppressor1714
Computer Grade1585, 1596
Dry Film AC1735
Electric Double Layer (EDLC)1580,
1582-1584
EMI Suppression1713-1714, 1780
Feedthrough1523, 1529
Film1710, 1715-1717, 1720, 1722-1725,
1727-1729, 1732-1734, 1742, 1837
Gold1582-1583

Hardware1585
Interference Suppressor1732, 1742
Kits1814, 2332
Low Inductance1779-1780
Metalized Polyester1711-1712,
1714-1721, 1726, 1734, 1742
Metalized Polypropylene1712-1713,
1716, 1721, 1728-1733
MICA1833-1834
Microwave Chip1761, 1775-1778
Multilayer Chip (MLCC)546
Niobium Oxide1680
Polyester1709-1711
Polymer1618-1620, 1657-1660, 1664
RF Power1774
Supercapacitor Aerogel1581
Tantalum1664-1679, 1681-1707
Axial1682, 1700
Radial1667-1668, 1681, 1699
Thin Film RF1777-1778, 1834
Trimmer1834-1835, 1837
Ultracapacitors1580
Variable1834
Wet Tantalum1668, 1682, 1707-1708
X2Y®1781, 1832-1833

Card Racks2287
Backplanes2287

Cell Phone Chargers2343

Chokes See Coils/Inductors

Circuit Breakers
Accessories2034
DIN Rail2034
DIN Rail Mount2031, 2033-2034
Hydraulic-Magnetic2030, 2033
Switch1548, 2029, 2031, 2035-2036
Thermal2031-2032, 2035-2036
Thermal Links2029

Clean Room Products
Swabs and Applications2308

Clips
Alligator2325
Battery2348-2349
Fuse2014-2015, 2022-2023
Nano/Micro2320

Coils/Inductors .. 1424-1434, 1439-1444,
1446-1452, 1454-1482, 1488-1512,
1526-1527, 1530, 1533-1536
..... See also Transformers
Air Core1482
Axial1437
Bobbin1437-1438
Chip1439, 1463, 1499-1503,
1507-1509, 1533-1534
Kits1499-1500
Chokes1427, 1438, 1445, 1454-1462,
1467, 1472-1473, 1478-1481,
1512-1515, 1520-1521,
1526-1527, 1533-1536
CAN-BUS1535
Current Compensated1534-1535
Common Mode1427, 1432, 1438,
1481, 1503, 1512, 1520-1521,
1526-1527, 1533-1535, 2374
Arrays1534-1535
Conformal Coated1513, 1515
Drum Core1440, 1464
Film1441-1442
High Current1434-1435, 1439, 1462,
1466, 1468, 1475, 1478-1480,
1506, 1508, 1510-1515, 1533-1534
High Frequency1465-1466, 1474,
1488-1489, 1498,
1513-1515, 1534-1535, 2374
Kits1468, 1475-1477,
1482, 1535, 2334, 2374
Monolithic1441-1442, 1533-1534
Multilayer Chip1488-1489, 1499-1500
PAS1580
Power1424-1430, 1432-1433,
1436, 1439, 1454, 1458-1460,
1462, 1464-1466, 1468, 1474,
1478-1480, 1483-1487, 1490-1497,
1501-1502, 1507-1509, 1533-1535