

Items listed as digikey.com do not appear in the catalog, but appear on the Digi-Key Web Site.

Radial.....1437	Banana Plugs/Jacks.....405, 2323, 2325-2326	Hardware.....259, 261, 288	MetriMate.....216-217
Rod Core.....2374	Barrier Blocks.....343	HDI (High Density Interconnect).....257	Mezzanine.....198-199
Shielded.....1429-1432, 1434, 1439-1440, 1464, 1468, 1474-1480, 1488, 1492-1496, 1509	Battery.....485	HDMI.....210, 463, 482	MicroCross™ DVI.....210
Switchmode.....2374	Binding Posts.....405, 2284, 2323	Headers.....40, 120, 208, 504	Micro-D.....264
Thin Film.....1454	Blind Mate (BMI).....196, 198, 202	2mm.....106, 151-152, 155-157, 160-162, 510	Micro-Fit 3.0™.....195-198
Toroidal.....1432, 1438, 1464-1466, 1479, 1498, 1508, 1510-1512, 1520, 2369-2370, 2374	Board-to-Board.....45, 79, 88-97, 102, 104-105, 115, 118-132, 135, 137-138, 144-147, 151, 155-156, 160, 254-255, 257, 472, 480, 483, 2567	Latching.....57	Microphone.....399
Variable.....1505	Floating.....146	Shrouded.....57	Micro TCA.....274, 476, 481
Voltage Step-Up.....1455	In-Line.....2567	0.0197" (0.5mm).....118	Micror.....482
Wirewound.....1439, 1443-1452, 1463, 1468-1472, 1501-1502, 1504	Bus Bar.....472	0.031" (0.80mm).....118	Miniature Rectangular (MR).....233
CompactPCI® Products.....474-475, 2287-2288	Card Edge.....34, 40-41, 261, 461-467, 472, 480, 2287	0.040" (1.00mm).....118-119	Mini D Ribbon (MDR).....54-55
Computer Equipment	Centronics.....280, 288	0.050" (1.27mm).....119-120, 132, 510	Mini-Fit
Cable Assemblies.....58-64	C-Grid®.....182-186	0.0787" (2.00mm).....121, 132	BMI.....202
Keyboards.....2062-2063	Champ®.....252, 259-260	0.100" (2.54mm).....37-38, 44, 50-52, 124-132, 166, 170-179, 185-187, 189-190, 208, 238-241, 508-509, 512	HCS.....203
KVM Switches.....2330	Circular124-132, 166, 170-179, 185-187, 189-190, 208, 238-241, 508-509, 512	Jr.....200-201, 203
Trackballs.....2062	8D/D38999 Aluminum and Composite Series.....392	Female.....120	SMC.....203
Concentric Scale Dials.....1918	44 Series.....386	0.0197" (0.5mm).....118	Sr.....204
Connectorized	97 Series.....380-382	0.031" (0.80mm).....118	MiniSAS.....477, 493, 497
Amplifier.....1409	851 Series.....393	0.050" (1.27mm).....119-120	Modular.....63, 67, 292-293, 296-306, 308-312, 482
Regulator.....1409	Accessories.....381-382, 411-412, 416	0.0787" (2.00mm).....120-123, 132	70AA.....482
Connectors	Bayonet Lock.....396	0.100" (2.54mm).....123-128, 132, 166-170, 173, 177, 508-510, 512	70AD.....482
0.2mm.....75	C16.....384	IDC.....31, 40, 51-52, 57	Adapters, Filtered.....311-312
0.3mm.....75, 78, 81, 87	C091.....385	IDC Dip.....51-52	Adapters, IBM Equivalent.....299
0.4mm.....75, 88, 115, 199, 483	Coaxial.....415	Pin/Plug.....51-52	DSL Filter.....311
SlimStack™.....199	DIN.....415-416, 418-419	Protected.....51	Ethernet.....67, 292-293, 296-304, 311-312
0.5mm.....74-79, 81-82, 85-86, 89-90, 115-116, 135, 199	IP67.....383	Protected.....37-38, 45, 50, 132	RJ11.....301-302, 311
SlimStack™.....199	M8 and M12 Series.....417	Hoods, D-Sub.....269-270, 285-288	RJ45.....292-293, 296-300, 303-304, 311
0.6mm.....91	Medical.....409	HSSDC2.....495	Industrial.....67, 299, 306, 308-310
0.65mm.....91-92	Metal.....377-382, 394-401, 405, 416, 418	ICCON.....472	Modular Jacks, Filtered.....312
0.8mm.....82, 92, 116-117, 135, 144, 211, 256	MIL-C-5015.....380-381, 417	IDC Discrete	Power Over Ethernet (PoE).....304, 312
1.0mm.....74, 76-78, 82-84, 86-87, 93, 96, 135-136, 144-145, 148, 256, 261, 481, 483	MIL-C-26482.....377-379, 393	D-Sub.....266	Spring Loaded Contacts.....511
1.20mm.....136	MIL-C-38999.....392	Socket.....187-189, 191-193, 237-238	M-Series.....250-251
1.25mm.....97-98, 133, 136-137, 148-149	Miniature.....396-397, 399-401, 405, 407-409	Strip.....212	MT 100".....234-235
1.27mm.....158-159	Mini-DIN.....418-419	IDC Ribbon Cable.....39-41, 43	MTA 100" and 156".....187-194
1.5mm.....133, 137-138, 149	MS Series.....378, 382	2mm Socket.....155, 157, 163-164	MTE 100".....237-238, 242-243
Pico SPOX™.....149	Plastic.....384, 387, 396, 401-402, 410-412, 415, 417-419	Card Edge.....34, 40-41	MX150L.....388
2mm.....98-106, 134, 138-141, 150-153, 155-157, 160-165, 474-476, 478-479, 510	PT Series.....377-379	Delta.....43	Parallel Interface.....252-254, 259-260, 288
Hard Metric.....476, 478-479	Push-Pull Lock.....393, 395, 400-402	DIP.....29, 33, 48, 53	PCI Express.....466-467, 480, 490
Metral®.....479	RADSOK®.....376	D-Sub.....28, 32, 39, 48	PC Pins/Receptacles.....502, 513-514
Milli-Grid™.....151-152	Screw Lock.....384, 394-395, 397-401	Mini D (MDR).....54-55	Phono Jacks/Plugs.....453-455, 461
Millipacs®.....479	Sealed.....385-386, 410-411	PCB.....34, 43-44	Power.....147, 194, 204-206, 211, 213-214, 343, 455-460, 471-472, 1550
Mini-Clamp.....165	.125" Powerband Contact.....415	Pin/Plug.....31, 40, 51-52	Power Edge™.....463
Minitek™.....155-157	Wire Entry Seal Kits.....412	Socket.....30, 34, 49, 57	Power Supply.....110
Sherlock™.....150	Video.....396-397155, 157, 163-164	QSFP.....493
Socket.....510	Waterproof.....383, 403-404, 406-407	IEEE 1394 (Firewire).....63, 66, 302, 307	Rack and Panel.....215, 258
Z-Pack.....474-475	Compact Flash.....473	Waterproof.....307	RADSOK®.....376
2.5mm.....107-110, 141-142, 154, 257	CompactPCI®.....474-475	Industrial Ethernet.....67, 299, 343	RAPID LOCK.....472
SPOX™.....154	CROWN CLIP.....472	Interconnect Systems.....245-249, 495	Rectangular.....207-209
3.96mm.....154	CROWN EDGE.....472	Interface Modules.....351	Heavy Duty.....207-209
4.2mm.....216	Delta.....43	Intra-Connector™.....502	146E Series.....209
5.0mm.....111	DIN, Rectangular.....463, 468-471, 473, 481, 486, 502	I/O.....117, 211-214, 494, 496	IP65.....207-208
5.08mm.....203	DisplayPort®.....210	Jig Assemblies.....See digikey.com	Retention Modules.....261
6.2mm.....143	D-Sub.....28, 32, 39, 48, 262-292, 300, 332	Jones.....See digikey.com	Reverse Polarity SMA.....444, 550-551
7.5mm.....204	Accessories.....269-270, 272-274, 289	Jumpers	RF.....440
7.92mm.....111	Adapters.....285	Jumpers.....See Connectors - Shunts	Accessories.....433, 2321
0.050" (1.27mm).....56, 94-95, 145, 252-255, 509	Backshells.....274, 285-288, 290, 292	Juniper Wires.....112-113	Adapters.....427, 433, 435-436, 447-448, 2321
Picoflex™.....56	Combination.....274, 291	Socket.....40	AMC.....425
0.062".....205	Dual Port.....279	Termination Jumpers.....28-29, 32-35, 39, 41, 44, 48-49, 52-53	Audio/Video.....447
0.084".....205	Filtered.....289	LAN.....299, 312	BNC.....420, 426-427, 431-435, 447-449, 2321
0.093".....206	Gender Changers.....60, 285, 291	LED.....2567	Board-to-Board.....431
0.100" (2.54mm).....105, 165, 177, 181-190, 234-238, 240, 242-244	Hardware Kits.....268, 271-272, 274, 289	Light-N-Lok™.....2535	Coaxial.....431, 451-453
0.156" (3.96mm).....110, 143, 181, 191-194	High Density.....267, 274-277, 279, 289, 292, 300	LVDS.....96, 115	Decoupled.....435
AC.....1550	VGA.....274	Mate-N-Lok®.....218-231	F.....437
ATCA.....481	Interface Modules and Cables.....332	Memory	FL (Finger Lock).....451
Audio.....454-461	Press Fit.....279	CardBus.....492	H.FL.....451
Back Panel.....476	Water Resistant.....291, 300	Card Connectors.....463, 486, 488-492	MCM/MMCX Type.....422, 436, 438, 440-441, 444, 449
Backplane.....462, 472, 475	Dynamic.....245-249	Compact Flash.....485, 487, 489, 491	SMP.....425
Backshells.....45, 253, 269-270, 285-288, 290	Edgecard.....See Connectors - Card Edge	DDR.....487	N Type.....422, 427, 437, 448
Ballast.....2535	ELCON.....471	DIMM.....463, 490	QSL.....436
	Ethernet.....See Connectors - Modular	Memory Stick®.....489	SHV.....438
	Eurocard.....468-471, 473	MicroSD™/Transflash.....486, 489, 494	SMA/SMB.....420-421, 424-425, 428, 430, 438-440, 442-444
	ExpressCard™.....484, 490, 494	PCMCIA Memory Card.....485-486, 488-489, 492	FAKRA (SMA).....424-425
	FFC/FPC (Flat Flex).....72, 75-79, 81-87	SD™.....486	QMA (SMA).....425
	Fiber Optic.....313-315, 318	Secure Digital.....485, 487, 489, 491, 494	Waterproof.....438-439
	Flexi-Block.....343	SIM.....494	SKM.....444
	F Type.....440, 2321	SIMM.....490	Terminator Plugs.....435
	GBIC.....495	TransFlash.....491	TNC.....423, 427, 438, 448
	Hard Metric.....476, 478	MetPak™	Tools, Crimp.....423, 425, 438
		2-FB.....477	Twinaxial.....427
		CP2.....478	UHF.....429, 437, 448
		HSHM.....478	

More Product Available Online: www.digikey.com

Toll-Free: 1-800-344-4539 • Phone 218-681-6674 • Fax: 218-681-3380