

Items listed as digikey.com do not appear in the catalog, but appear on the Digi-Key Web Site.

UMC	447
UMCC	429
W,FL	451
Ribbon Shielded (SCR)	55
RITS	245
RJ45	See Connectors - Modular
Sabre™	204
SAS (Serial Attached SCSI)	480
SATA	55, 481
SCA2	484
Scotchlok™	356-357
SCSI	252-253, 477, 496
SCSI Terminator	62, 267
SDR	55
Serial ATA	210
SFP (Small Form Pluggable)	492-493, 496-497
Shunts/Jumpers	39, 41, 106, 155, 157, 160, 162, 166, 171, 176-177, 186, 194
SIM Card	483-484
Smart Card	484, 490, 498
SMP	443
Sockets, IC	See IC Sockets
Soft Shell .062" and .093"	231-232
Solar (Photovoltaic)	209
Spring Loaded Contacts	504
Switch	2136
System 50	255
Target Headers	504
Telecom	258
Television, "F" Type	448
Terminal Blocks	
Accessories	331-334, 336
Barrier Blocks	348-351
DIN Rail	332-333, 335-336, 2035
DIN Rail Mounted	329, 331-335
Eurostyle®	344-347, 350-351
PCB Mounted	319-329, 337-347, 350-351
Pluggable	328-329
Terminals/Splices	
Board-in-Crimp	143
Butt Splice	353-357, 362-364, 374
Closed End	357, 362
Crimp	179-180, 352-357, 359-375, 413-414
Disconnect	358
Faston	365-371, 375
Knife Disconnect	362
PC Quick-Fit	2278
Quick Connect	352-353, 355-357, 365, 375, 400-402, 405
Ring Tongue	353-360, 363-364, 372-375
See and Splice™	354
Snap Plug	355, 357, 375
Spade Lugs	353, 355-357, 361, 363-364, 374-375, 2278
Spade Plug	353
Spring Push	348
Test Points	2278, 2284
Wire Nut	355-356
Wire Pin	353
Wire Tap	354
Tip Jacks/Plugs	405
Toy Car Battery	182
Trim Trio	389-391
Accessories	391
Circular Harsh Environment Bayonet	389-390
Circular Quick Mate	390-391
Rectangular Panel/Cable	390-391
USB	62-63, 65-68, 292, 299-300, 302, 306, 312, 510
Bluetooth® Adapters	306
Waterproof	306-307
VHDCI	495
VITA 41/VITA 46	475
Water Resistant/Waterproof	139, 291-292, 388, 396-399
Weathertight	387-388
XFP	493, 495
Z-Pack	474-475
Contacts	See Connectors

Controllers	
Relays	2545
Temperature	2544-2545
Converters, AC-DC	See Power Supplies
Converters, DC-DC	See Power Supplies
Cordless Soldering Irons	2227
Cords	
Fan	2353
Power	1546-1547
Counters	2538-2539, 2544, 2547, 2551
Accessories	2544
Crystals	1363-1375, 1380, 1382-1386, 1395-1400, 1405-1409, 1412-1416, 2334
Cylinder Type	1385-1386, 1395-1396, 1405
Kits	2334
Microprocessor	1400
Oscillators	1408-1409
Tuning Fork	1405-1406
Current Indicators	2495

D

DC Block	1409
Delay Lines	1453
Detectors	
CO	See digikey.com
Combustible Gas Leak	See digikey.com
Refrigeration Leak	See digikey.com
Development Kits and Tools	
Accessories	679, 684, 686, 688-689
Adapters	583-584, 613, 628, 652, 679, 681, 755
BASIC Stamp Kits	630
Configuration Devices	597
Daughter Boards	526, 538, 652, 738
Debug Tools	651, 694, 720, 729, 732
Demo Kits	526-527, 598, 609, 683, 685, 689, 695, 717, 719, 729
Development/Starter Kits	526-529, 532, 534, 556, 558, 565, 569-570, 572, 577, 581, 587, 589, 598, 601, 605, 609-610, 613-619, 624, 626-627, 629, 667, 683, 685-686, 688, 707-710, 719, 727, 730-732, 2508
Emulators	610, 613, 652, 679, 681-682, 694, 707, 720, 738, 755
EPROM	652, 682
Flash	652
PIC	652
Evaluation Boards and Kits	522-523, 525-526, 538, 554-556, 561-563, 565-566, 569, 571-572, 575, 577, 580-581, 587, 589, 598, 604, 609-610, 613, 626-627, 683, 685, 688-689, 694-695, 702-703, 707-710, 712, 717, 719, 727, 729, 732, 736, 738-739, 755-757, 760-763, 1195-1196, 2491, 2507-2509, 2522
DSP	703, 736, 738
RF	522-523, 525-526, 538, 556, 561-563, 565, 569, 571, 577, 581
Sensors	2491, 2507, 2509, 2522
FPGA/CPLD Kits	589, 599-600
LED Discovery Kit	2574
Oscillator	1387, 1389
PCI	600
Programmable	538, 556, 572, 583-584, 587, 589, 598, 601, 605, 609-610, 613, 630, 652, 679, 681-682, 685-686, 688-689, 707, 709-710, 720, 727, 729, 736, 738, 755
Programming Cable	588, 598
Reference Design Kits	526, 625
Remote Control Design	682

Software	651, 702-703, 729, 732, 755-757
C-Compiler	651, 685, 732, 755
Library	See digikey.com
Module	See digikey.com
Speech Recognition Kit	628
Programmable Interactive Module	628
Voice Record/Playback	629
Web Server Kit	681
Diacs	1227, 1262, 1346, 1989
Dials, Concentric Scale	1939, 1944, 1947
DIN Rail	332-333, 335-336
Diodes/Rectifiers	1188-1189, 1200, 1210-1216, 1220-1227, 1242-1248, 1255-1260, 1267-1272, 1275-1276, 1282-1299, 1310-1312, 1318-1320, 1323-1330, 1332-1333, 1343-1344, 1346, 1349-1352
Arrays	1275, 1299, 1327, 1344
Bridge	1245, 1288-1289, 1312, 1328-1330, 1350-1352
ESD Protection	1223, 1985-1987
FREDs/HexFREDs	1246, 1320
Hyperabrupt Varactors	1188
Kits	1223, 2334
Modules	2213
I/O	2213
SCR	2213
PIN (RF)	1212, 1222-1223, 1333
Schottky	1188-1189, 1210-1211, 1221, 1242-1245, 1255-1257, 1270-1272, 1276, 1290-1293, 1295, 1298-1299, 1318-1320, 1343, 1349-1352
Super Barrier	1293
Switching	1189, 1212-1213, 1220, 1272, 1275, 1296-1297, 1318-1319, 1332, 1344, 1349
TVS	See Transient Voltage Suppressors
Varactors	1349
Variable Capacitance	539, 1200, 1222
Varistors	See Varistors
Zener	1189, 1213-1216, 1222, 1224-1225, 1267-1268, 1275-1276, 1282-1287, 1290, 1310-1312, 1330, 1333, 1344, 1349
PolyZen Micro Assembly	2002
Diplexers	Multilayer 1517
Displays	
Backlights	2530
Dot Matrix	2606
LCD	See LCDs
LED	See LEDs
Vacuum Fluorescent	2531, 2536
Duct Wiring	See digikey.com

E

EMI Suppression	
Absorber Pads	522
Arrays	1530, 1533-1535, 1540
Capacitors	1713
Common Mode Chokes	1533-1535
Ferrite Cable Cores	1482, 1538-1539
Ferrite Chips	1528-1533, 1545
Filter Capacitor Type	1531
Filters	1516, 1531, 1533-1536, 1538-1542, 1549, 1552, 1558-1560
High Current	1532-1535
LC Combined Chip	1531, 1540
Emulators	See Development Tools
Enclosures/Boxes/Racks	
Accessories and Hardware	2249-2251, 2253, 2255, 2258-2259, 2261-2262
Cabinets	2252, 2256-2258
Conductive	2252

Cases/Boxes	2249-2256, 2260-2263, 2321-2322
Aluminum	2249, 2254, 2256, 2260-2263, 2321-2322
E.M.I.	2250-2251
Plastic	2249-2253, 2255, 2260-2263, 2321-2322
Soft-Sided	2263
Nema	2253-2255
Racks	2257-2259
Watertight/Airtight Cases	2250-2252, 2263
Encoders	
Digital Contacting	2155
Magnetic	2138
Mechanical	2152, 2154
Modular	2152
Optical	2151-2152, 2155
Rotary	2151-2155
Square/Sealed	2155
Universal	2062
EPROM Eraser	2318
ESD Products	
Suppression	1276, 1541, 1960, 2002, 2007-2008, 2020
Arrays	1541, 2002, 2007
Multilayer Chip	1960
Surge Protectors	See digikey.com
TVS	See Transient Voltage Suppressors
Varistors/ZNRs	1956-1960, 1965

F

Fans/Blowers	
AC	2352, 2354, 2359, 2361-2362
Accessories	2352-2353
Blowers	2357, 2360-2364
Chip Cooler	2359
DC	2350-2351, 2354-2364
Axial	2355-2358, 2363
Brushless DC	2350-2351, 2358-2361
Hydro-wave Bearing (HWB)	2355-2357
Tachometer Output	2350-2351
Therma Pro-V	2352
Finger Guards	2350-2357, 2363-2364
Mini	2359
Fastening Systems	
Hook and Loop	2266
Velcro®	2267
Ferrites	
Bead Cores	1515, 1524, 1533-1534, 1539-1540, 1545
Chip Arrays	1524, 1530, 1533-1535
Chips	1522, 1528-1530, 1532-1534
Clamp-On	1521, 1537, 1539
Common Mode Chokes	1533-1535
Cylinder	1522, 1538-1539
Differential Mode	1533, 1535
EMI Discs and Plates	1536
Flat Core	1545
Flexible Ferrite Material	1482, 1523
High Current	1533
High Frequency Cores	1539
Kits	1536, 1539-1540
Low Frequency	1536
Ribbon Cable	1537
Ring Core	1538-1539, 1545
Split Cores	1537, 1539
Toroids	1519, 1536, 1538
Ferrules	
Crimp	268, 270
Fiber Optic	313
Split-Ring	270
Wire	330
Fiber Optic	
Accessories	313-315
Adapters	313-314, 316
Amplifiers	2506
Attenuators	314
Bare Cable	See digikey.com
Cable	313, 315, 318, 2506

More Product Available Online: www.digikey.com
 Toll-Free: 1-800-344-4539 • Phone 218-681-6674 • Fax: 218-681-3380