

Items listed as digikey.com do not appear in the catalog, but appear on the Digi-Key Web Site.

High Power 2596
 Holders/Mounts 2274, 2279, 2566
 Incandescent Replacement 2567, 2576, 2585
 Infrared 2449, 2463-2464, 2470, 2473, 2475-2476, 2481-2482, 2552
 Lenses/Caps 2599, 2606-2607, 2613
 Level Meters 2624
 Low Battery Indicators 2564
 Modular 2598
 Modules 2274
 Multi-Color 2578-2581, 2583, 2601
 Numeric Displays 2617, 2621
 Panel Mount 2565-2566
 RGB (Red/Green/Blue) 2557, 2563, 2574-2575, 2577, 2601, 2612
 Smart Displays 2617
 Spacers 2267, 2279
 Surface Mount 1167, 2571-2573, 2613
 Thermal Clad Boards 1167
 Through-Hole 2569-2570
 White 2556, 2576-2577, 2579, 2583-2584, 2590, 2594-2596, 2599, 2602-2603, 2611-2612, 2619-2621
 Wide Angle 2624

Lighting
 Connectors 2535, 2567

Light Pipes 2274, 2559, 2585, 2599

Lights
 Flashlights 2343
 Worklights 2329

Line Conditioners 2330

Lockouts See digikey.com

M

Magnetic Card Readers 2275

Magnets 2161-2162

Magnifiers 2328-2329, 2438

Memory
 Cards 795, 1164-1165
 Compact Flash 1164-1165
 Flash Disks 1164
 iDOC 1164
 PCMCIA 1165
 Secure Digital 1164-1165
 uDOC 1164
 DDR 1150-1151, 1165
 DDR2 1151, 1165
 DDR3 1151
 DiskOnChip 1161
 EEPROM 1022
 EEPROM, CMOS 813
 EEPROM, Parallel 1065, 1159
 EEPROM, Serial 1134-1135, 1152-1160
 Embedded 793-794
 EPROM 1021-1022, 1159
 FIFO 924-925, 1157
 Flash 792-793, 1022, 1151, 1159-1161
 iButton® 1148
 INAND 1161
 Magnetoresistive RAM 789
 Modules 1164-1165
 NVRAM 1022-1023, 1148
 PROM, Serial 589
 PSRAM 1151-1152
 SDRAM 1150, 1152, 1160, 1165
 Serial Dataflash 1160
 SRAM 813, 1000, 1005, 1152, 1156-1157, 1160-1161
 StrataFlash® 794-795

MESFETs 529, 570

Meters See Test Equipment

Microcontrollers
 See ICs - Microcontrollers

Microphones
 Cable 2221
 Electret Condenser 2245-2246
 Holders 2245-2246
 Magnetic 2247
 Silicon 2248

Microprocessors
 See ICs - Microprocessors

Microscopes 2328

MOSFET/MOSFET Drivers 562, 658-659, 994-995, 1189-1192, 1203-1205, 1219, 1230-1241, 1250-1252, 1263, 1277-1279, 1302-1308, 1313-1317, 1320-1322, 1326, 1332, 1334-1336, 1348, 1353-1359

Motor Control
 Modular Boards 667

Motors
 Geared 1166
 Stepper 1166

MOVs See Varistors

O

Optical Enhancement Films 2524

Optoelectronics
 Ambient Light Sensor 2466, 2477
 Evaluation Kits 2606
 Infrared Detectors 2464
 Infrared Emitters 2463, 2465, 2467-2468, 2470, 2473, 2475-2476, 2481, 2552
 Interrupter Modules 2464
 IrDA Transceiver Modules 2481, 2553
 Lenses, Spherical 2554
 Light Detectors 2463
 Logic Detectors 2464
 Optical Sensors 2466, 2471, 2473-2474, 2476, 2482, 2552
 Reflective 2476-2477, 2482
 Orientation Sensor 2470
 Photoconductive Cells 2467-2468
 Photo Detectors 2464-2465, 2467-2468, 2473, 2482
 Photo Diodes 2449, 2463, 2465, 2467-2469, 2475, 2481-2482
 Photo ICs 2469, 2482
 Photointerrupters 2462, 2476-2477, 2482
 Reflective 2462, 2482
 Photo Transistors 2449, 2463, 2469, 2473, 2475-2476, 2481
 Reflective Sensor 2470
 Remote Control Receivers 2553, 2587
 Touch Screens 2525-2526

Optoisolators/Photocouplers
 Digital 2453-2454, 2457, 2461
 High Speed Output 2442, 2452, 2460-2461
 IRED 2452
 Logic Output 2445, 2448, 2452, 2458-2461
 Magnetic 2457
 Optocouplers 2442-2444
 Photo-IC Output 2445
 Photo-Transistor Output 2441-2442, 2445-2448, 2450, 2452, 2455-2456, 2458
 Photovoltaic 1237, 2452
 SCR/Triac Output 2445, 2447-2448
 Thyristor Output 2451, 2454

Oscillators 1360-1363, 1369, 1375-1381, 1387-1395, 1400-1405, 1407, 1412-1415
 Clock 1360-1363, 1400-1402, 1414
 Crystal 1363-1372, 1381, 1391-1395, 1407, 1414
 Ovenized (OCXO) 1405, 1408
 Programmable 1387-1390
 Real Time Clock 1390
 SAW (Surface Acoustic Wave) 1408
 Silicon 1405
 Sockets 1394-1395, 1402
 Spread Spectrum 1412
 Synchronous Clock Generators 1404
 Temperature Compensated (TCXO), (TCVCXO) 1362, 1379, 1389, 1405, 1407-1408, 1413
 Voltage Controlled Saw (VCSO) 1408
 Voltage Controlled (VCO) 1409-1411
 Voltage Controlled (VCXO), (VCTCXO) 1362, 1377-1378, 1380, 1393, 1400, 1404, 1408

P

Panel Meters See Test Equipment

Paper
 Thermal Printer 2276
 Toner Transfer 2291

PC Board Prototyping
 Adapters, Application Specific 2292
 Backplanes 2287
 Etching Equipment 2290-2291
 Extender Cards 2286, 2288
 Prototyping Accessories 2264, 2279, 2285-2292, 2302, 2308, 2310
 Cleaners and Cloths 2264, 2302, 2308
 Etch Resist Pens 2291
 PCB Drill Bits 2291
 Swabs and Brushes 2290, 2308
 Wipes 2302, 2308
 Prototyping Boards 2279, 2285, 2287-2292
 Copper Clad Boards 2289-2291
 Solderless Breadboards 2284, 2288-2289
 Terminal/Distribution Strips 2289
 Toner Transfer Paper 2291

Photocouplers See Optoisolators

Photo Detectors See Optoelectronics

Photodiodes See Optoelectronics

Phototransistors See Optoelectronics

Potentiometers
 Angle Sensing/Positioning 1922, 1949
 Audio 1948
 Carbon 1927, 1931, 1934, 1943-1944, 1955
 Ceramic 1953-1954
 Cermet 1912-1917, 1923-1926, 1928-1939, 1942, 1949, 1955
 Conductive Plastic 1917, 1934, 1938-1940
 Digital 660-661
 Digital Readout Dial 1944
 Joystick Controller 1941
 Kits 1951, 1955, 2332
 Panel Control 1917, 1934, 1939
 Position Sensor 1950
 Rotary 1922, 1949
 Slide 1950
 Stock Pot™ 1942
 Thumbwheel 1949
 Trimmer 1912-1916, 1919-1928, 1930-1939, 1941-1942, 1949, 1951-1955
 Two-Axis Controller 1941
 Wirewound 1917-1918, 1931, 1936-1937, 1939, 1943-1944

Power Cords 60-61, 1546-1547
 EMI Filters 1538-1539

Power Dividers 1518, 1838

Power Entry Modules 1551-1554, 1558

Power Outlet 1548

Power Strips 2330-2331

Power Supplies
 AC Adapters 2428-2429, 2439-2440
 Accessories 2413-2414, 2427
 AC-DC Converters 2394-2395, 2401, 2410-2411, 2414, 2420-2424, 2426-2427, 2430-2433, 2438-2440
 Configurable 2396
 DC-DC Converters 2378-2393, 2402-2403, 2405-2408, 2415-2418, 2422, 2425, 2433-2437
 Adjustable Output 2415
 Point of Load (POL) 2392, 2415, 2433
 Programmable 2401, 2436-2437
 Desktop Switchers 2428-2430, 2438-2440
 DIN-Rail Mount 2422-2424

Dual Output 2392, 2402, 2416-2418, 2431-2436
 Energy Star 2409
 External 2316, 2331, 2410-2411, 2413-2414, 2428-2430, 2438-2440
 Filters 2391, 2404
 Hook-Up Cables 2316
 Linear 2412, 2419, 2427, 2438
 Medical Grade 2409-2411, 2439-2440
 Multiple Output 2394-2396, 2416-2418, 2431-2432, 2435, 2439-2440
 Power Modules 2396, 2416
 Power over Ethernet (POE) 2410
 Single Output 2390, 2392-2397, 2402, 2415-2418, 2431-2437
 Switching 2395, 2397-2401, 2409-2411, 2413-2414, 2420-2424, 2426-2436, 2438-2440
 Universal Input 2395, 2397, 2410-2412, 2414, 2426-2427, 2438-2440
 UPS Systems 2330
 Wall Transformers See Transformers

Printers
 Accessories 2277
 Labels 2277
 Thermal 2276-2277
 Thermal Paper 2277
 Wire Marker 2277

Privacy Filters 2524-2525

Probes
 Accessories 2318-2320, 2325
 Clips 2320, 2325
 Differential 2319
 Logic 2318
 Oscilloscope 2319, 2322
 Pulsar 2318
 Temperature 2515
 Thermocouple 2318, 2320

Programmable Tools See Development Tools

Prototyping See PC Board Prototyping

Protractors, Digital 2503

R

Raceway
 Wire Duct and Accessories 2273

Racks and Accessories
 See Enclosures

Rectifiers See Diodes/Rectifiers

Reference Books See digikey.com

Relays
 BGA 2159
 Control 2544, 2546
 Current Sensing 2496
 High Frequency 2159, 2167-2168, 2175
 I/O Modules 2198-2200, 2216
 Mechanical 2165-2197
 Power IC 2200
 Reed 2156-2160, 2163
 Safety 2198
 Sockets and Accessories 2170, 2172, 2174, 2181-2186, 2191, 2197
 Solid State 2198, 2201-2215
 Time Delay 2545, 2547

Resistor/Capacitor Networks 1900

Resistors
 Aluminum Housed 1876, 1894
 Anti-Sulfurated See digikey.com
 Arrays 1898, 1900-1906, 1908
 Audio 1866
 Capacitor Discharge 1879
 Capacitor Mount 1866
 Carbon Composition 1870, 1874
 Carbon Film 1859, 1861
 Carbon Film 1894
 Ceramic Composition 1875, 1877
 Chassis Mount 1864-1865, 1867
 Current Sense 1871-1872, 1886

More Product Available Online: www.digikey.com
 Toll-Free: 1-800-344-4539 • Phone 218-681-6674 • Fax: 218-681-3380