

Items listed as digikey.com do not appear in the catalog, but appear on the Digi-Key Web Site.

3M

- Adhesives
 - Clean-Walk 2264
 - Command™ 2264
 - Hot Melt 2264
 - Scotch-Weld™ 2264
- Breadboards 2284
- Bumpers 2264
- Cable
 - Clamps 46
 - Flat 47
 - High Flex 46
 - Ribbon 45-47, 54-55, 164
 - Round Jacketed/Shielded 47, 2219
 - Ties 2278
- Cable Assemblies 39-40, 43-44
- D-Sub 39
- PCB 43-44
- Plug and Socket 40, 43
- Termination Jumpers 44
- Cable Splice Enclosures 357
- Cleaning Cloth 2264
- Connector Hardware 261
- Connectors
 - 0.1" 44-45, 165
 - 2mm 163-165
 - Mini-Clamp 165
 - Card Edge 40-41
 - Delta 43
 - D-Sub 39
 - IDC 44, 54
 - Intra-Connector™ 502
 - Intra-Switch™ 502
- Memory
 - Compact Flash 487
 - DDR 487
 - microSD™ 486
 - SD™ 486
 - Secure Digital 487
 - MetPak™ 477
 - 2FP 477
 - CP2 478
 - HSHM 478
 - miniSAS 477
 - PCB 43-44
 - Plug and Socket 40-42
 - Ribbon
 - Mini D 54-55
 - Shielded 55
 - SATA 55
 - Scotchlok™ 356-357
 - SCSI 477
 - Termination Jumpers 41
- EMI Suppression
 - Absorber Pads 522
 - Headers 44-45, 163
 - Heat Shrink Tubing 2228
 - Hook and Loop Fasteners
 - Dual Lock™ 2267
 - Scotchmate™ 2267
- IC Sockets
 - DIP 520
 - PLCC Carrier 521
 - Type 'A' LCC 521
 - ZIF 487, 519-520
 - ZIP DIP 519-520
- IC Test Clips 521
- Jumper Wire 2284
- Kits
 - Heat Shrink Tubing 2228, 2334
 - Insulated Terminals 356
 - Optical Enhancement Films 2524
 - Optoelectronics 2525
 - Touch Screens 2525
 - Patch Cords 2324
 - Privacy Filters 2524-2525
 - Probe-It Clips 2325
 - Shorting Jumpers 166
 - Static Control Products 2299-2302
- Tape
 - Attachment 2265
 - Duct 2265
 - Electrical 522, 2265
 - Fabric 522
 - Foam 2265
 - Foil Shielding 522, 2265
 - Low Static 2265
 - Splicing 2266
 - Water Soluble 2265-2266

A

- Terminal Connectors 355-356
- Terminal Strips 2289
- Tools, Crimp 356
- Vacuum 2284
- Wire Marker Tape Dispensers 2266

Aavid Thermalloy

- Heat Sinks 1168-1170
- BGA 1170
- Thermal Compound 1168

Abrakon Corporation

- Crystals 1373-1375
- Filters, SAW 1417
- Oscillators 1375-1378, 1388
- Programmable 1388
- Resonators
 - Ceramic 1417
 - SAW 1417

ACL Staticide, Inc.

- Cleaning Wipes 2302
- Static Control Equipment
 - See digikey.com
- Static Control Products 2299, 2302
- Static Dissipative Soap 2302

ADI See Analog Devices, Inc.

Advanced Photonix, Inc.

- Photo Diodes/Emitters 2467-2468

Advanced Thermal Solutions, Inc.

- Heat Sinks
 - BGA 1173-1176
 - LED 1176
 - LGA 1176
 - Tools 1174
 - Thermal Management 1173
 - Kits 1173

Airpax See Sensata Technologies, Airpax

AlfaMag Electronics, LLC

- Inductors 1498

Allegro MicroSystems, Inc.

- Integrated Circuits
 - Hall Effect Sensors 1009-1011
 - Motor Drivers 1011
 - Power Management 1012

All Sensors Corporation

- Pressure Sensors 2493

Alpha & Omega Semiconductor, Inc.

- MOSFET/MOSFET Drivers 1358-1359
- Power Management 1126-1127
- Transient Voltage Suppressors (TVS) 1988

Alpha Wire Company

- Cable
 - Bus Bar 2225
 - Coaxial 2226
 - Ethernet 2226
 - Hook-Up 2224-2226
 - Multiconductor 2223-2224
 - Multi-paired 2222
 - Sleeving 2225
 - Spiral Wrap 2226
 - Test Lead 2225
 - Tinned Copper Flat Braid 2225
 - Heat Guns 2227
 - Tubing
 - Fabric 2227
 - Heat Shrink 2227
 - Teflon 2225

Altera

- Cables/Programming Hardware 597
- Development Kits and Tools 598-600
- Evaluation Kits 598
- Integrated Circuits/Semiconductors
 - CPLDs 595-597
 - FPGAs 591-595

Altium

- Development/Starter Kits 589
- Evaluation Boards and Kits 589
- FPGA/CPLD Kits 589

American Electrical, Inc.

- Cable Grips 2219
- Circuit Breakers, DIN Rail Mount 2033
- DIN Rail Mount 332
- Disconnect Switches 2110
- Accessories 2110
- Interface Modules and Cables 332
- Terminal Blocks
 - Accessories 331-332
 - DIN Rail Mount 331-332
- Tools, Crimp 330
- Wire Ferrules 330

Ametherm

- Inrush Current Limiters 1998
- Thermistors, NTC 2515

Amphenol Commercial Products

- Connectors
 - D-Sub 292-293
 - Backshells 293
 - High Density 293
 - Infinity 497
 - Modular, Ethernet 292-293
 - SAS 497
 - SFP 497
 - USB 292

Amphenol - Connex

- RF Adapters 420-423
- RF Connectors
 - BNC 420
 - MCX/MMCX 422
 - N Type 422
 - SMA/SMB 420-421
 - TNC 423
 - Tools, Crimp 423

Amphenol - Industrial

- Circular Connectors
 - 97 Series 380-382
 - Accessories 381-382
 - IP67 383
 - MS Series 378, 382
 - PT Series 377-379
 - RADSOK® 376
 - Waterproof 383
 - Cord Grips 2219

Amphenol - PCD

- Connectors 301-302
- IEEE 1394 302
- Modular, Ethernet (RJ11) 301-302
- Terminal Splices 328-329
- DIN Rail Mounted 329
- PCB Mounted 328-329
- Pluggable 328-329
- USB 302

Amphenol - RF Division

- Adapters, RF Coaxial 427, 429
- RF Connectors
 - AMC 425
 - BNC 426-427
 - N Type 427
 - SMA/SMB 424-425, 428
 - FAKRA (SMB) 424-425
 - QMA (SMA) 425
 - SMP 425
 - TNC 427
 - Twinaxial 427
 - UHF 429
 - Tools, Crimp 425, 429

Amphenol - Tuchel Electronics

- Cable Assemblies
 - eco/mate™ 384
- Connectors
 - Backshell Kit See digikey.com
 - Circular
 - 44 Series 386
 - C16 384
 - C091 385-386
 - eco/mate™ 384
 - Hand Tools 385-386
 - Rectangular, Heavy Duty 209
 - Smart Card 498

Amprobe

- Test Equipment
 - Accessories 2314-2315
 - Clamp Meters 2314-2315

- Data Logger 2314
- Hygrometer 2315
- Kits 2314-2315
- Megohmmeter 2315
- Multimeters 2314-2315
- Power Recorder 2315
- Psychrometer 2315
- Relay Switch 2315
- Resistivity Tester 2315
- Rotation 2315
- Test Leads 2314
- Voltage Detection 2315
- Wire Tracer 2315

AMP Tyco Electronics

- See Tyco Electronics AMP

Amulet Technologies LLC

- Graphic LCD Tool Kits 2529

Amveco Magnetics

- Transformers
 - Current Sense 2497
 - Medical Grade 2370
 - Power 2370
 - Toroidal 2369-2370

Analog Devices, Inc.

- DSP Emulators/Programmers 736-738
- Gyroscopes 2509
- ICs/Semiconductors 784
- Amplifiers 764-770
- Analog Computation Circuits 769
- Analog/Digital Audio 769-770
- ATE and Time Domain 770
- Audio/Video 770
- CCD 770
- Clock Generation and Distribution 770
- Data Communication 770
- Data Conversion 770-776
- Digital Potentiometers 776-777
- Display and Video Converters 777
- Evaluation Boards 778
- Fiber Optics and Networks 778
- Hardware Monitors and Thermal Management 778
- Interface 778-780
- Microcontrollers 738-739
- MicroConverter® 738-739
- Motion/Motor Control 780
- Power Management 780-783
- Sensor/Signal Conditioning 783-784
- Specialized IC 784
- Supervisory Circuits/Reset Generators 784
- Switches 785-786
- Waveform Generators 783
- Isolators, Digital 2453-2454
- RF/IF Products 522-525
- DDCs 524
- DDSs 525
- IF Receivers 524
- Sensors, Accelerometers 2509
- Evaluation Boards 2509

Antenna

- Antennas 525

APM Components, Inc.

- Security Guards 2071
- Switches
 - Emergency Stop 2102
 - Joysticks 2101
 - Keylock 2087, 2102
 - Pushbutton 2098, 2100-2102
 - Rocker 2087
 - Toggle 2077, 2087

API Delevan

- Bead Cores 1482
- Cable EMI Ferrite Cores 1482
- EMI Suppression Cable Cores 1482
- Ferrites, Flexible Material/Tubing 1482
- Inductors
 - Air Core 1482
 - Chip See digikey.com
 - Coils 1474
 - Common Mode Choke 1481-1482
 - Filter 1474
 - Fixed 1474-1482

More Product Available Online: www.digikey.com

Toll-Free: 1-800-344-4539 • Phone 218-681-6674 • Fax: 218-681-3380