




Termination Jumpers (Cont.)

Card Edge to Card Edge

* MC = Multi-Color
GR = Gray




Card Edge connector without strain relief shown.

No. of Cont.	Cont. Finish	Length In. (cm)	Ribbon Cable*	Digi-Key Part No.	Price Each 1 10
10	Gold	6(15.24)	MC	C3EEG-1006M-ND	5.73 4.35
	Tin	6(15.24)	MC	C3EEG-1006M-ND	4.93 3.74
	Gold	6(15.24)	GR	C3EEG-1006G-ND	5.46 4.14
	Tin	6(15.24)	GR	C3EEG-1006G-ND	4.65 3.53
	Gold	18(45.72)	MC	C3EEG-1018M-ND	6.54 4.96
	Tin	18(45.72)	MC	C3EEG-1018M-ND	5.73 4.35
	Gold	18(45.72)	GR	C3EEG-1018G-ND	5.71 4.33
	Tin	18(45.72)	GR	C3EEG-1018G-ND	4.90 3.72
	Gold	36(91.44)	MC	C3EEG-1036M-ND	7.74 5.87
	Tin	36(91.44)	MC	C3EEG-1036M-ND	6.93 5.26
20	Gold	6(15.24)	MC	C3EEG-2006M-ND	7.93 6.02
	Tin	6(15.24)	MC	C3EEG-2006M-ND	6.88 5.22
	Gold	6(15.24)	GR	C3EEG-2006G-ND	7.42 5.63
	Tin	6(15.24)	GR	C3EEG-2006G-ND	6.36 4.83
	Gold	18(45.72)	MC	C3EEG-2018M-ND	9.54 7.23
	Tin	18(45.72)	MC	C3EEG-2018M-ND	8.48 6.43
	Gold	18(45.72)	GR	C3EEG-2018G-ND	7.99 6.06
	Tin	18(45.72)	GR	C3EEG-2018G-ND	6.93 5.26
	Gold	36(91.44)	MC	C3EEG-2036M-ND	11.94 9.06
	Tin	36(91.44)	MC	C3EEG-2036M-ND	10.89 8.26
26	Gold	6(15.24)	MC	C3EEG-2606M-ND	8.85 6.71
	Tin	6(15.24)	MC	C3EEG-2606M-ND	8.23 6.25
	Gold	6(15.24)	GR	C3EEG-2606G-ND	8.85 6.71
	Tin	6(15.24)	GR	C3EEG-2606G-ND	7.54 5.72
	Gold	18(45.72)	MC	C3EEG-2618M-ND	11.62 8.81
	Tin	18(45.72)	MC	C3EEG-2618M-ND	10.32 7.83
	Gold	18(45.72)	GR	C3EEG-2618G-ND	9.55 7.25
	Tin	18(45.72)	GR	C3EEG-2618G-ND	8.25 6.26
	Gold	36(91.44)	MC	C3EEG-2636M-ND	14.75 11.19
	Tin	36(91.44)	MC	C3EEG-2636M-ND	13.45 10.20
34	Gold	6(15.24)	MC	C3EEG-3406M-ND	11.90 9.03
	Tin	6(15.24)	MC	C3EEG-3406M-ND	10.35 7.85
	Gold	6(15.24)	GR	C3EEG-3406G-ND	10.92 8.28
	Tin	6(15.24)	GR	C3EEG-3406G-ND	9.37 7.11
	Gold	18(45.72)	MC	C3EEG-3418M-ND	14.63 11.10
	Tin	18(45.72)	MC	C3EEG-3418M-ND	13.08 9.92
	Gold	18(45.72)	GR	C3EEG-3418G-ND	11.68 8.86
	Tin	18(45.72)	GR	C3EEG-3418G-ND	10.13 7.69
	Gold	36(91.44)	MC	C3EEG-3436M-ND	18.72 14.20
	Tin	36(91.44)	MC	C3EEG-3436M-ND	17.17 13.02
40	Gold	6(15.24)	MC	C3EEG-4006M-ND	13.94 10.57
	Tin	6(15.24)	MC	C3EEG-4006M-ND	12.08 9.16
	Gold	6(15.24)	GR	C3EEG-4006G-ND	12.87 9.76
	Tin	6(15.24)	GR	C3EEG-4006G-ND	11.01 8.35
	Gold	18(45.72)	MC	C3EEG-4018M-ND	17.15 13.01
	Tin	18(45.72)	MC	C3EEG-4018M-ND	15.29 11.60
	Gold	18(45.72)	GR	C3EEG-4018G-ND	13.94 10.57
	Tin	18(45.72)	GR	C3EEG-4018G-ND	12.08 9.16
	Gold	36(91.44)	MC	C3EEG-4036M-ND	21.96 16.65
	Tin	36(91.44)	MC	C3EEG-4036M-ND	20.10 15.24
50	Gold	6(15.24)	MC	C3EEG-5006M-ND	15.54 11.78
	Tin	6(15.24)	MC	C3EEG-5006M-ND	13.68 10.37
	Gold	6(15.24)	GR	C3EEG-5006G-ND	15.89 12.05
	Tin	6(15.24)	GR	C3EEG-5006G-ND	13.79 10.45
	Gold	18(45.72)	MC	C3EEG-5018M-ND	14.45 10.96
	Tin	18(45.72)	MC	C3EEG-5018M-ND	12.34 9.36
	Gold	18(45.72)	GR	C3EEG-5018G-ND	19.90 15.09
	Tin	18(45.72)	GR	C3EEG-5018G-ND	17.80 13.49
	Gold	36(91.44)	MC	C3EEG-5036M-ND	15.57 11.81
	Tin	36(91.44)	MC	C3EEG-5036M-ND	13.46 10.21

Socket Connector to PCB Connector

* MC = Multi-Color
GR = Gray



Socket connector and PCB connector without strain relief shown.


No. of Cont.	Cont. Finish	Length In. (cm)	Ribbon Cable*	Digi-Key Part No.	Price Each 1 10
10	Tin	6(15.24)	MC	C3APS-1006M-ND	2.82 2.14
	Tin	6(15.24)	GR	C3APS-1006G-ND	2.54 1.93
	Tin	18(45.72)	MC	C3APS-1018M-ND	3.62 2.75
	Tin	18(45.72)	GR	C3APS-1018G-ND	2.80 2.12
	Tin	36(91.44)	MC	C3APS-1036M-ND	4.82 3.66
	Tin	36(91.44)	GR	C3APS-1036G-ND	3.18 2.41

No. of Cont.	Cont. Finish	Length In. (cm)	Ribbon Cable*	Digi-Key Part No.	Price Each 1 10
20	Tin	6(15.24)	MC	C3APS-2006M-ND	4.18 3.17
	Tin	6(15.24)	GR	C3APS-2006G-ND	3.67 2.78
	Tin	18(45.72)	MC	C3APS-2018M-ND	5.79 4.39
	Tin	18(45.72)	GR	C3APS-2018G-ND	4.24 3.22
	Tin	36(91.44)	MC	C3APS-2036M-ND	8.19 6.21
	Tin	36(91.44)	GR	C3APS-2036G-ND	5.10 3.87
26	Tin	6(15.24)	MC	C3APS-2606M-ND	5.23 3.97
	Tin	6(15.24)	GR	C3APS-2606G-ND	4.54 3.44
	Tin	18(45.72)	MC	C3APS-2618M-ND	7.31 5.55
	Tin	18(45.72)	GR	C3APS-2618G-ND	5.24 3.98
	Tin	36(91.44)	MC	C3APS-2636M-ND	10.44 7.92
	Tin	36(91.44)	GR	C3APS-2636G-ND	6.30 4.78
34	Tin	6(15.24)	MC	C3APS-3406M-ND	6.51 4.94
	Tin	6(15.24)	GR	C3APS-3406G-ND	5.53 4.19
	Tin	18(45.72)	MC	C3APS-3418M-ND	9.24 7.01
	Tin	18(45.72)	GR	C3APS-3418G-ND	6.29 4.77
	Tin	36(91.44)	MC	C3APS-3436M-ND	13.33 10.11
	Tin	36(91.44)	GR	C3APS-3436G-ND	7.43 5.64
40	Tin	6(15.24)	MC	C3APS-4006M-ND	7.34 5.57
	Tin	6(15.24)	GR	C3APS-4006G-ND	6.27 4.76
	Tin	18(45.72)	MC	C3APS-4018M-ND	10.55 8.00
	Tin	18(45.72)	GR	C3APS-4018G-ND	7.33 5.56
	Tin	36(91.44)	MC	C3APS-4036M-ND	15.36 11.65
	Tin	36(91.44)	GR	C3APS-4036G-ND	8.93 6.78
50	Tin	6(15.24)	MC	C3APS-5006M-ND	9.04 6.86
	Tin	6(15.24)	GR	C3APS-5006G-ND	7.60 5.76
	Tin	18(45.72)	MC	C3APS-5018M-ND	13.05 9.90
	Tin	18(45.72)	GR	C3APS-5018G-ND	8.72 6.61
	Tin	36(91.44)	MC	C3APS-5036M-ND	19.07 14.46
	Tin	36(91.44)	GR	C3APS-5036G-ND	10.40 7.89
60	Tin	6(15.24)	MC	C3APS-6006M-ND	10.75 8.15
	Tin	6(15.24)	GR	C3APS-6006G-ND	9.10 6.90
	Tin	18(45.72)	MC	C3APS-6018M-ND	15.56 11.80
	Tin	18(45.72)	GR	C3APS-6018G-ND	10.62 8.05
	Tin	36(91.44)	MC	C3APS-6036M-ND	22.78 17.27
	Tin	36(91.44)	GR	C3APS-6036G-ND	12.89 9.78

Also available in the following versions:
 C3BP□-□□□□-ND - Socket Connector with Strain Relief.
 C3CP□-□□□□-ND - Socket Connector with Central Polarizing Key.
 C3DP□-□□□□-ND - Socket Connector with Strain Relief and Central Polarizing Key.
 Call for complete part number and pricing!

Socket Connector to Card Edge Connector

* MC = Multi-Color,
GR = Gray



Socket connector and Card Edge connectors without strain relief shown.


No. of Cont.	Cont. Finish	Length In. (cm)	Ribbon Cable*	Digi-Key Part No.	Price Each 1 10
10	Gold	6(15.24)	MC	C3AEG-1006M-ND	4.31 3.27
	Tin	6(15.24)	MC	C3AEG-1006M-ND	3.72 2.82
	Gold	6(15.24)	GR	C3AEG-1006G-ND	4.03 3.06
	Tin	6(15.24)	GR	C3AEG-1006G-ND	3.44 2.61
	Gold	18(45.72)	MC	C3AEG-1018M-ND	5.11 3.88
	Tin	18(45.72)	MC	C3AEG-1018M-ND	4.52 3.43
20	Gold	6(15.24)	MC	C3AEG-2006M-ND	6.48 4.91
	Tin	6(15.24)	MC	C3AEG-2006M-ND	5.64 4.28
	Gold	6(15.24)	GR	C3AEG-2006G-ND	5.96 4.52
	Tin	6(15.24)	GR	C3AEG-2006G-ND	5.12 3.89
	Gold	18(45.72)	MC	C3AEG-2018M-ND	8.08 6.13
	Tin	18(45.72)	MC	C3AEG-2018M-ND	7.24 5.49
26	Gold	6(15.24)	MC	C3AEG-2606M-ND	6.53 4.96
	Tin	6(15.24)	MC	C3AEG-2606M-ND	5.69 4.32
	Gold	6(15.24)	GR	C3AEG-2606G-ND	10.49 7.95
	Tin	6(15.24)	GR	C3AEG-2606G-ND	9.65 7.32
	Gold	18(45.72)	MC	C3AEG-2618M-ND	11.99 9.09
	Tin	18(45.72)	MC	C3AEG-2618M-ND	10.87 8.17
34	Gold	6(15.24)	MC	C3AEG-3406M-ND	7.85 5.96
	Tin	6(15.24)	MC	C3AEG-3406M-ND	7.85 5.96
	Gold	6(15.24)	GR	C3AEG-3406G-ND	9.73 7.38
	Tin	6(15.24)	GR	C3AEG-3406G-ND	8.49 6.44
	Gold	18(45.72)	MC	C3AEG-3418M-ND	8.75 6.64
	Tin	18(45.72)	MC	C3AEG-3418M-ND	7.51 5.70
40	Gold	6(15.24)	MC	C3AEG-4006M-ND	12.46 9.45
	Tin	6(15.24)	MC	C3AEG-4006M-ND	11.22 8.51
	Gold	6(15.24)	GR	C3AEG-4006G-ND	15.11 11.45
	Tin	6(15.24)	GR	C3AEG-4006G-ND	13.46 10.21
	Gold	18(45.72)	MC	C3AEG-4018M-ND	17.25 13.08
	Tin	18(45.72)	MC	C3AEG-4018M-ND	15.14 11.48

No. of Cont.	Cont. Finish	Length In. (cm)	Ribbon Cable*	Digi-Key Part No.	Price Each 1 10
34	Gold	18(45.72)	GR	C3AEG-3418G-ND	9.51 7.22
	Tin	18(45.72)	GR	C3AEG-3418G-ND	8.27 6.28
	Gold	36(91.44)	MC	C3AEG-3436M-ND	15.55 12.55
	Tin	36(91.44)	MC	C3AEG-3436M-ND	15.31 11.61
	Gold	36(91.44)	GR	C3AEG-3436G-ND	10.66 8.08
	Tin	36(91.44)	GR	C3AEG-3436G-ND	9.42 7.14
40	Gold	6(15.24)	MC	C3AEG-4006M-ND	11.18 8.48
	Tin	6(15.24)	MC	C3AEG-4006M-ND	9.73 7.38
	Gold	6(15.24)	GR	C3AEG-4006G-ND	10.11 7.67
	Tin	6(15.24)	GR	C3AEG-4006G-ND	8.65 6.57
	Gold	18(45.72)	MC	C3AEG-4018M-ND	14.39 10.91
	Tin	18(45.72)	MC	C3AEG-4018M-ND	12.93 9.81
50	Gold	6(15.24)	MC	C3AEG-5006M-ND	13.04 9.89
	Tin	6(15.24)	MC	C3AEG-5006M-ND	11.37 8.62
	Gold	6(15.24)	GR	C3AEG-5006G-ND	11.60 8.80
	Tin	6(15.24)	GR	C3AEG-5006G-ND	9.92 7.53
	Gold	18(45.72)	MC	C3AEG-5018M-ND	17.05 12.93
	Tin	18(45.72)	MC	C3AEG-5018M-ND	15.38 11.66
60	Gold	6(15.24)	MC	C3AEG-6006M-ND	12.72 9.65
	Tin	6(15.24)	MC	C3AEG-6006M-ND	11.04 8.38
	Gold	6(15.24)	GR	C3AEG-6006G-ND	23.07 17.49
	Tin	6(15.24)	GR	C3AEG-6006G-ND	21.39 16.22
	Gold	18(45.72)	MC	C3AEG-6018M-ND	14.40 10.92
	Tin	18(45.72)	MC	C3AEG-6018M-ND	12.72 9.65

Also available in the following versions:
 C3BE□-□□□□-ND - Socket Connector with Strain Relief.
 C3CE□-□□□□-ND - Socket Connector with Central Polarizing Key.
 C3DE□-□□□□-ND - Socket Connector with Strain Relief and Central Polarizing Key.
 Call for complete part number and pricing!

PCB Connector to Card Edge Connector

* MC = Multi-Color,
GR = Gray



PCB and Card Edge connectors are without strain relief.

No. of Cont.	Cont. Finish	Length In. (cm)	Ribbon Cable*	Digi-Key Part No.	Price Each 1 10
10	Tin	6(15.24)	MC	C3PES-1006M-ND	4.03 3.06
	Tin	6(15.24)	GR	C3PES-1006G-ND	3.75 2.85
	Tin	18(45.72)	MC	C3PES-1018M-ND	4.83 3.67
	Tin	18(45.72)	GR	C3PES-1018G-ND	4.01 3.04
	Tin	36(91.44)	MC	C3PES-1036M-ND	6.03 4.58
	Tin	36(91.44)	GR	C3PES-1036G-ND	4.38 3.33
20	Tin	6(15.24)	MC	C3PES-2006M-ND	5.42 4.11
	Tin	6(15.24)	GR	C3PES-2006G-ND	4.91 3.72
	Tin	18(45.72)	MC	C3PES-2018M-ND	7.03 5.33
	Tin	18(45.72)	GR	C3PES-2018G-ND	5.48 4.16
	Tin	36(91.44)	MC	C3PES-2036M-ND	9.43 7.15
	Tin	36(91.44)	GR	C3PES-2036G-ND	6.34 4.81
26	Tin	6(15.24)	MC	C3PES-2606M-ND	6.68 5.07
	Tin	6(15.24)	GR	C3PES-2606G-ND	5.99 4.55
	Tin	18(45.72)	MC	C3PES-2618M-ND</	