

3M Termination Jumpers Socket to Socket Connector (Cont.)



Table with columns: No. of Con-tacts, Conn. Finish, Length Inch (cm), Rib-bon Cable, Digi-Key Part No., Pricing 1 10. Rows include various configurations for 34, 40, 50, and 60 contacts.

Also available in the following configurations:

- M3BB-ND - Standard Open End with Strain Relief
M3CC-ND - Standard Open End with Polarizing Key
M3DD-ND - Standard Open End with Polarizing Key and Strain Relief
M3TTK-ND - Standard Closed End with Polarizing Key
M3UUK-ND - Standard Closed End with Polarizing Key and Strain Relief

Call for complete part number and pricing!

Socket to Socket Connector

\*Twisted Pair Cable Finished Length is Approximate.

Table with columns: No. of Con-tacts, Conn. Finish, Length Inch (cm), Rib-bon Cable, Digi-Key Part No., Pricing 1 10. Rows include various configurations for 10, 14, 16, 20, 26, and 34 contacts.


Table with columns: No. of Con-tacts, Conn. Finish, Length Inch (cm), Rib-bon Cable, Digi-Key Part No., Pricing 1 10. Rows include various configurations for 34, 40, 50, and 60 contacts.

Also available in the following configurations:

- M3BB-ND - Standard Open End with Strain Relief
M3CC-ND - Standard Open End with Polarizing Key
M3DD-ND - Standard Open End with Polarizing Key and Strain Relief
M3TTK-ND - Standard Closed End with Polarizing Key
M3UUK-ND - Std. Closed End with Polarizing Key and Strain Relief

Call for complete part number and pricing!

Plug Connector to Plug Connector



\*MC = 3M Multi-Color, GR = 3M Gray

Pin connector without flange, with polarizing key shown.

\*Twisted Pair Cable Finished Length is Approximate.

Table with columns: No. of Con-tacts, Conn. Finish, Length Inch (cm), Rib-bon Cable, Digi-Key Part No., Pricing 1 10. Rows include various configurations for 10, 14, 16, 20, 24, 26, 30, 34, and 40 contacts.

Table with columns: No. of Con-tacts, Conn. Finish, Length Inch (cm), Rib-bon Cable, Digi-Key Part No., Pricing 1 10. Rows include various configurations for 50, 60, 64, 10, 14, 16, 20, 34, 40, 50, 60, and 64 contacts.

Also available in the following configurations:

- M3RRK-ND - Pin Connector without Flange, with Polarizing Key and Strain Relief
M3WWK-ND - Pin Connector with Flange, with Polarizing Key
M3YYK-ND - Pin Connector with Flange, with Polarizing Key and Strain Relief

Call for complete part number and pricing!

Socket Connector to Plug Connector



Pin connector without flange, with polarizing key, and socket connector without strain relief shown.

\*MC = 3M Multi-Color, GR = 3M Gray

Table with columns: No. of Con-tacts, Conn. Finish, Length Inch (cm), Rib-bon Cable, Digi-Key Part No., Pricing 1 10. Rows include various configurations for 10, 16, 20, 24, 26, and 30 contacts.

(Continued)

More Product Available Online: www.digikey.com

Toll-Free: 1-800-344-4539 • Phone 218-681-6674 • Fax: 218-681-3380