



Socket Assemblies (Cont.)



No. of Con-tacts	Contact Finish	Length Inch (cm)	Rib-bon* Cable	Digi-Key Part No.	Price Each	
					1	10
20	Gold	36 (91.44)	MC	H1AXH-2036M-ND	6.05	4.59
	Tin	36 (91.44)	MC	H1AXS-2036M-ND	6.05	4.59
	Gold	36 (91.44)	GR	H1AXH-2036G-ND	2.96	2.25
	Tin	36 (91.44)	GR	H1AXS-2036G-ND	2.96	2.25
24	Gold	36 (91.44)	MC	H1AXH-2436M-ND	7.69	5.83
	Tin	36 (91.44)	MC	H1AXS-2436M-ND	7.69	5.83
	Gold	36 (91.44)	GR	H1AXH-2436G-ND	3.29	2.50
	Tin	36 (91.44)	GR	H1AXS-2436G-ND	3.29	2.50
26	Gold	36 (91.44)	MC	H1AXH-2636M-ND	7.50	5.69
	Tin	36 (91.44)	MC	H1AXS-2636M-ND	7.50	5.69
	Gold	36 (91.44)	GR	H1AXH-2636G-ND	3.36	2.55
	Tin	36 (91.44)	GR	H1AXS-2636G-ND	3.36	2.55
30	Gold	36 (91.44)	MC	H1AXH-3036M-ND	9.86	7.48
	Tin	36 (91.44)	MC	H1AXS-3036M-ND	9.86	7.48
	Gold	36 (91.44)	GR	H1AXH-3036G-ND	3.66	2.78
	Tin	36 (91.44)	GR	H1AXS-3036G-ND	3.66	2.78
34	Gold	36 (91.44)	MC	H1AXH-3436M-ND	9.42	7.15
	Tin	36 (91.44)	MC	H1AXS-3436M-ND	9.42	7.15
	Gold	36 (91.44)	GR	H1AXH-3436G-ND	3.53	2.68
	Tin	36 (91.44)	GR	H1AXS-3436G-ND	3.53	2.68
40	Gold	36 (91.44)	MC	H1AXH-4036M-ND	11.11	8.43
	Tin	36 (91.44)	MC	H1AXS-4036M-ND	11.11	8.43
	Gold	36 (91.44)	GR	H1AXH-4036G-ND	4.69	3.56
	Tin	36 (91.44)	GR	H1AXS-4036G-ND	4.69	3.56
50	Gold	36 (91.44)	MC	H1AXH-5036M-ND	13.89	10.54
	Tin	36 (91.44)	MC	H1AXS-5036M-ND	13.89	10.54
	Gold	36 (91.44)	GR	H1AXH-5036G-ND	5.22	3.96
	Tin	36 (91.44)	GR	H1AXS-5036G-ND	5.22	3.96
60	Gold	36 (91.44)	MC	H1AXH-6036M-ND	17.79	13.49
	Tin	36 (91.44)	MC	H1AXS-6036M-ND	17.79	13.49
	Gold	36 (91.44)	GR	H1AXH-6036G-ND	7.90	5.99
	Tin	36 (91.44)	GR	H1AXS-6036G-ND	7.90	5.99
64	Gold	36 (91.44)	MC	H1AXH-6436M-ND	21.23	16.10
	Tin	36 (91.44)	MC	H1AXS-6436M-ND	21.23	16.10
	Gold	36 (91.44)	GR	H1AXH-6436G-ND	10.13	7.69
	Tin	36 (91.44)	GR	H1AXS-6436G-ND	10.13	7.69

Also available in the following configuration:

H1BX□-□□□□-ND - Without polarizing key, With Strain Relief


H1CX□-□□□□-ND - With polarizing key, Without Strain Relief

H1DX□-□□□□-ND - With polarizing key, With Strain Relief

Call for complete part number and pricing

Double Ended Socket

- *MC=Multi-Color, GR=Gray



Without Polarizing Key without Strain Relief Shown

No. of Con-tacts	Contact Finish	Length Inch (cm)	Rib-bon* Cable	Digi-Key Part No.	Price Each	
					1	10
10	Gold	6 (15.24)	MC	H3AAH-1006M-ND	2.51	1.91
	Tin	6 (15.24)	MC	H3AAS-1006M-ND	2.51	1.91
	Gold	6 (15.24)	GR	H3AAH-1006G-ND	2.23	1.70
	Tin	6 (15.24)	GR	H3AAS-1006G-ND	2.23	1.70
	Gold	18 (45.72)	MC	H3AAH-1018M-ND	4.51	3.43
	Tin	18 (45.72)	MC	H3AAS-1018M-ND	4.51	3.43
	Gold	18 (45.72)	GR	H3AAH-1018G-ND	2.87	2.18
	Tin	18 (45.72)	GR	H3AAS-1018G-ND	2.87	2.18
	Gold	36 (91.44)	MC	H3AAH-1036M-ND	4.51	3.43
	Tin	36 (91.44)	MC	H3AAS-1036M-ND	4.51	3.43
	Gold	36 (91.44)	GR	H3AAH-1036G-ND	2.87	2.18
	Tin	36 (91.44)	GR	H3AAS-1036G-ND	2.87	2.18
14	Gold	6 (15.24)	MC	H3AAH-1406M-ND	3.08	2.34
	Tin	6 (15.24)	MC	H3AAS-1406M-ND	3.08	2.34
	Gold	6 (15.24)	GR	H3AAH-1406G-ND	2.66	2.02
	Tin	6 (15.24)	GR	H3AAS-1406G-ND	2.66	2.02
	Gold	18 (45.72)	MC	H3AAH-1418M-ND	6.09	4.62
	Tin	18 (45.72)	MC	H3AAS-1418M-ND	6.09	4.62
	Gold	18 (45.72)	GR	H3AAH-1418G-ND	3.54	2.69
	Tin	18 (45.72)	GR	H3AAS-1418G-ND	3.54	2.69
	Gold	36 (91.44)	MC	H3AAH-1436M-ND	6.09	4.62
	Tin	36 (91.44)	MC	H3AAS-1436M-ND	6.09	4.62
	Gold	36 (91.44)	GR	H3AAH-1436G-ND	3.54	2.69
	Tin	36 (91.44)	GR	H3AAS-1436G-ND	3.54	2.69
16	Gold	6 (15.24)	MC	H3AAH-1606M-ND	3.12	2.37
	Tin	6 (15.24)	MC	H3AAS-1606M-ND	3.12	2.37
	Gold	6 (15.24)	GR	H3AAH-1606G-ND	2.68	2.04
	Tin	6 (15.24)	GR	H3AAS-1606G-ND	2.68	2.04
	Gold	18 (45.72)	MC	H3AAH-1618M-ND	6.33	4.80
	Tin	18 (45.72)	MC	H3AAS-1618M-ND	6.33	4.80
	Gold	18 (45.72)	GR	H3AAH-1618G-ND	3.69	2.80
	Tin	18 (45.72)	GR	H3AAS-1618G-ND	3.69	2.80
	Gold	36 (91.44)	MC	H3AAH-1636M-ND	6.33	4.80
	Tin	36 (91.44)	MC	H3AAS-1636M-ND	6.33	4.80
	Gold	36 (91.44)	GR	H3AAH-1636G-ND	3.69	2.80
	Tin	36 (91.44)	GR	H3AAS-1636G-ND	3.69	2.80
20	Gold	6 (15.24)	MC	H3AAH-2006M-ND	3.28	2.49
	Tin	6 (15.24)	MC	H3AAS-2006M-ND	3.28	2.49
	Gold	6 (15.24)	GR	H3AAH-2006G-ND	2.77	2.10
	Tin	6 (15.24)	GR	H3AAS-2006G-ND	2.77	2.10
	Gold	18 (45.72)	MC	H3AAH-2018M-ND	7.29	5.53
	Tin	18 (45.72)	MC	H3AAS-2018M-ND	7.29	5.53
	Gold	18 (45.72)	GR	H3AAH-2018G-ND	4.20	3.19
	Tin	18 (45.72)	GR	H3AAS-2018G-ND	4.20	3.19

No. of Con-tacts	Contact Finish	Length Inch (cm)	Rib-bon* Cable	Digi-Key Part No.	Price Each	
					1	10
20	Gold	36 (91.44)	MC	H3AAH-2036M-ND	7.29	5.53
	Tin	36 (91.44)	MC	H3AAS-2036M-ND	7.29	5.53
	Gold	36 (91.44)	GR	H3AAH-2036G-ND	4.20	3.19
	Tin	36 (91.44)	GR	H3AAS-2036G-ND	4.20	3.19
24	Gold	6 (15.24)	MC	H3AAH-2406M-ND	4.35	3.30
	Tin	6 (15.24)	MC	H3AAS-2406M-ND	4.35	3.30
	Gold	6 (15.24)	GR	H3AAH-2406G-ND	3.62	2.75
	Tin	6 (15.24)	GR	H3AAS-2406G-ND	3.62	2.75
	Gold	18 (45.72)	MC	H3AAH-2418M-ND	9.36	7.10
	Tin	18 (45.72)	MC	H3AAS-2418M-ND	9.36	7.10
	Gold	18 (45.72)	GR	H3AAH-2418G-ND	4.96	3.77
	Tin	18 (45.72)	GR	H3AAS-2418G-ND	4.96	3.77
26	Gold	36 (91.44)	MC	H3AAH-2436M-ND	9.36	7.10
	Tin	36 (91.44)	MC	H3AAS-2436M-ND	9.36	7.10
	Gold	36 (91.44)	GR	H3AAH-2436G-ND	4.96	3.77
	Tin	36 (91.44)	GR	H3AAS-2436G-ND	4.96	3.77
30	Gold	6 (15.24)	MC	H3AAH-3006M-ND	3.52	2.67
	Tin	6 (15.24)	MC	H3AAS-3006M-ND	3.52	2.67
	Gold	6 (15.24)	GR	H3AAH-3006G-ND	2.83	2.15
	Tin	6 (15.24)	GR	H3AAS-3006G-ND	2.83	2.15
	Gold	18 (45.72)	MC	H3AAH-3018M-ND	8.74	6.63
	Tin	18 (45.72)	MC	H3AAS-3018M-ND	8.74	6.63
	Gold	18 (45.72)	GR	H3AAH-3018G-ND	4.60	3.49
	Tin	18 (45.72)	GR	H3AAS-3018G-ND	4.60	3.49
34	Gold	36 (91.44)	MC	H3AAH-3036M-ND	4.70	3.58
	Tin	36 (91.44)	MC	H3AAS-3036M-ND	4.70	3.58
	Gold	36 (91.44)	GR	H3AAH-3036G-ND	4.60	3.49
	Tin	36 (91.44)	GR	H3AAS-3036G-ND	4.60	3.49
40	Gold	6 (15.24)	MC	H3AAH-4006M-ND	4.58	3.48
	Tin	6 (15.24)	MC	H3AAS-4006M-ND	4.58	3.48
	Gold	6 (15.24)	GR	H3AAH-4006G-ND	3.51	2.66
	Tin	6 (15.24)	GR	H3AAS-4006G-ND	3.51	2.66
	Gold	18 (45.72)	MC	H3AAH-4018M-ND	12.60	9.56
	Tin	18 (45.72)	MC	H3AAS-4018M-ND	12.60	9.56
	Gold	18 (45.72)	GR	H3AAH-4018G-ND	6.17	4.68
	Tin	18 (45.72)	GR	H3AAS-4018G-ND	6.17	4.68
	Gold	36 (91.44)	MC	H3AAH-4036M-ND	12.60	9.56
	Tin	36 (91.44)	MC	H3AAS-4036M-ND	12.60	9.56
	Gold	36 (91.44)	GR	H3AAH-4036G-ND	6.17	4.68
	Tin	36 (91.44)	GR	H3AAS-4036G-ND	6.17	4.68
50	Gold	6 (15.24)	MC	H3AAH-5006M-ND	5.73	4.34
	Tin	6 (15.24)	MC	H3AAS-5006M-ND	5.73	4.34
	Gold	6 (15.24)	GR	H3AAH-5006G-ND	4.28	3.25
	Tin	6 (15.24)	GR	H3AAS-5006G-ND	4.28	3.25
	Gold	18 (45.72)	MC	H3AAH-5018M-ND	15.75	11.95
	Tin	18 (45.72)	MC	H3AAS-5018M-ND	15.75	11.95
	Gold	18 (45.72)	GR	H3AAH-5018G-ND	7.08	5.37
	Tin	18 (45.72)	GR	H3AAS-5018G-ND	7.08	5.37
	Gold	36 (91.44)	MC	H3AAH-5036M-ND	15.75	11.95
	Tin	36 (91.44)	MC	H3AAS-5036M-ND	15.75	11.95
	Gold	36 (91.44)	GR	H3AAH-5036G-ND	7.08	5.37
	Tin	36 (91.44)	GR	H3AAS-5036G-ND	7.08	5.37
60	Gold	6 (15.24)	MC	H3AAH-6006M-ND	9.10	6.90
	Tin	6 (15.24)	MC	H3AAS-6006M-ND	9.10	6.90
	Gold	6 (15.24)	GR	H3AAH-6006G-ND	7.45	5.66
	Tin	6 (15.24)	GR	H3AAS-6006G-ND	7.45	5.66
	Gold	18 (45.72)	MC	H3AAH-6018M-ND	21.13	16.03
	Tin	18 (45.72)	MC	H3AAS-6018M-ND	21.13	16.03
	Gold	18 (45.72)	GR	H3AAH-6018G-ND	11.25	8.53
	Tin	18 (45.72)	GR	H3AAS-6018G-ND	11.25	8.53
	Gold	36 (91.44)	MC	H3AAH-6036M-ND	21.13	16.03
	Tin	36 (91.44)	MC	H3AAS-6036M-ND	21.13	16.03
	Gold	36 (91.44)	GR	H3AAH-6036G-ND	11.25	8.53
	Tin	36 (91.44)	GR	H3AAS-6036G-ND	11.25	8.53
64	Gold	6 (15.24)	MC	H3AAH-6406M-ND	14.22	10.79
	Tin	6 (15.24)	MC	H3AAS-6406M-ND	14.22	10.79
	Gold	6 (15.24)	GR	H3AAH-6406G-ND	12.37	9.38
	Tin	6 (15.24)	GR	H3AAS-6406G-ND	12.37	9.38
	Gold	18 (45.72)	MC	H3AAH-6418M-ND	27.06	20.51
	Tin	18 (45.72)	MC	H3AAS-6418M-ND	27.06	20.51
	Gold	18 (45.72)	GR	H3AAH-6418G-ND	15.96	12.10
	Tin	18 (45.72)	GR	H3AAS-6418G-ND	15.96	12.10
	Gold	36 (91.44)	MC	H3AAH-6436M-ND		