

ASSMANN Computer Cable Assemblies

A




Fig.	Length Feet (Meters)	Lines	Description	Digi-Key Part No.	1	Price Each 10	25	Assmann Part No.
Molded Extension for 36-Pin Centronics Interfaces								
1	6.56 (2) 9.84 (3)	36	2x Centronics 36-Pin Male to Male	AE1362-ND◆	14.92	13.11	11.76	AK138-2-R
	AE1363-ND◆			20.36	17.90	16.05	AK426-3-R	
	6.56 (2) 9.84 (3)	36	2x Centronics 36-Pin Male to Female	AE1004-ND	11.55	10.15	9.10	AK140-2
	AE1364-ND◆			15.68	13.78	12.35	AK140-2-R	
AE1365-ND◆	17.99	15.81	14.17	AK430-3-R				
Parallel Printer Cable, IBM PC and Compatibles								
2	5.90 (1.8) 9.84 (3) 22.96 (7)	25	D-Sub 25-Pin Male to Centronics 36-Pin Male, Snap-Hoods	AE1366-ND◆	9.77	8.59	7.70	AK101-1.8-R
	AE1367-ND◆			12.41	10.91	9.78	AK102-3-R	
	AE9853-ND◆			16.17	14.21	12.74	AK104-7-R	
3	6.56 (2) 9.84 (3) 22.96 (7)	25	D-Sub 25-Pin Male to Centronics 36-Pin Male, Molded Hoods	AE9858-ND◆	9.34	8.21	7.36	AK108-2-R
	AE1368-ND◆			9.14	8.04	7.21	AK127-3-R	
	AE9859-ND◆			14.52	12.76	11.44	AK159-7-R	
4	6.56 (2)	25	D-Sub 25-Pin Male to Right Angle Centronics 36-Pin Male	AE9860-ND◆	10.92	9.60	8.61	AK525-2-R
	6.56 (2)	25	D-Sub 25-Pin Male to Left Angle Centronics 36-Pin Male	AE1369-ND◆	10.92	9.60	8.61	AK525-2L-R
Serial Printer Cable, IBM PC and Compatibles — RoHS Compliant								
5	9.84 (3)	8	D-Sub 9-Pin Female to D-Sub 25-Pin Male, Snap-Hoods	AE1370-ND	7.46	6.56	5.88	AK150-3-R
IEEE 1284 Bi-Directional Cable - Molded Hoods — RoHS Compliant								
6	5.90 (1.8) 9.84 (3) 16.40 (5)	25	D-Sub 25-Pin Male to Centronics 36-Pin Male, Printer	AE1371-ND	16.14	14.19	12.72	AK711-1.8-R
	AE1372-ND			22.61	19.87	17.81	AK712-3-R	
	AE1373-ND			31.61	27.79	24.91	AK713-5-R	
7	5.90 (1.8) 9.84 (3) 16.40 (5)	25	D-Sub 25-Pin Male to D-Sub 25-Pin Female, Connection	AE9861-ND	17.16	15.08	13.52	AK733-1.8-R
	AE1374-ND			24.16	21.23	19.04	AK734-3-R	
	AE1375-ND			31.61	27.79	24.91	AK735-5-R	
8	5.90 (1.8) 9.84 (3) 16.40 (5)	25	D-Sub 25-Pin Male to D-Sub 25-Pin Male, Extension	AE9862-ND	18.32	16.10	14.43	AK736-1.8-R
	AE1376-ND			24.16	21.23	19.04	AK737-3-R	
	AE1377-ND			31.61	27.79	24.91	AK738-5-R	
Snap-Hood Connection for 25-Pin Interface — RoHS Compliant								
9	6.56 (2)	25	D-Sub 25-Pin Male to D-Sub 25-Pin Male, Snap-Hoods	AE9863-ND	7.59	6.67	5.98	AK401-2-R
Molded Extension for 25-Pin Interfaces								
10	6.56 (2) 6.56 (2) 9.84 (3)	25	2x D-Sub 25-Pin Male to Male	AE1010-ND	6.93	6.09	5.46	AK137-2
	AE1378-ND◆			10.00	8.79	7.88	AK137-2-R	
	AE9864-ND◆			13.40	11.78	10.56	AK162-3-R	
	6.56 (2) 9.84 (3)	25	2x D-Sub 25-Pin Male to Female	AE9865-ND◆	11.45	10.07	9.03	AK135-2-R
	AE9866-ND◆			11.02	9.69	8.69	AK166-3-R	
	6.56 (2) 9.84 (3)			25	2x D-Sub 25-Pin Female to Female	AE9867-ND◆	9.64	8.47
AE9868-ND◆	12.94	11.37	10.20			AK170-3-R		
Molded Extension for 9-Pin Interfaces — RoHS Compliant								
11	6.56 (2) 9.84 (3)	9	2x D-Sub 9-Pin Male to Male	AE9869-ND	7.36	6.47	5.80	AK129-2-R
	AE9870-ND			8.15	7.17	6.43	AK174-3-R	

◆ RoHS Compliant

(Continued)

More Product Available Online: www.digikey.com

Toll-Free: 1-800-344-4539 • Phone 218-681-6674 • Fax: 218-681-3380