

TEXAS INSTRUMENTS		DigiKey®		POWER SUPPLY PRODUCTS (Continued)	
T. I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each	★ 100
TLVH431QDBVR	296-18050-2-ND	Low Volt. Adj. Prec. Shunt Reg. *	SOT-23-5	897.00/3,000	
TLVH431QDBZR	296-17975-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-23	92.69	52
TLVH431QDCBR	296-17975-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-23	897.00/3,000	
TLVH431QDCR	296-18051-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SGT0-6	.75	63 50
TLVH431QDCKR	296-18051-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SGT0-6	975.00/3,000	
TLVH431QLPR	296-21134-1-ND	Low Volt. Adj. Precision Shunt Reg. *	TO-92	92.69	52
TLVH431QLPR	296-21134-3-ND	Low Volt. Adj. Precision Shunt Reg. *	TO-92	612.00/2,000	
TLVH431QPKP	296-18627-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	.75	63 50
TLVH431QPKP	296-18627-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	333.00/1,000	
TLVH431QPKG3	296-19350-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	.75	63 50
TLVH431QPKG3	296-19350-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	333.00/1,000	
TLVH432ACDBZR	296-17976-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-23	.68	51 39
TLVH432ACDBZR	296-17976-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-23	663.00/3,000	
TLVH432ACPK	296-18628-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	.76	57 43
TLVH432ACPK	296-18628-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	253.00/1,000	
TLVH432ACPKG3	296-19351-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	.76	57 43
TLVH432ACPKG3	296-19351-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	253.00/1,000	
TLVH432AIDBZR	296-17977-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-23	.76	57 43
TLVH432AIDBZR	296-17977-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-23	741.00/3,000	
TLVH432AIPK	296-18629-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	.84	63 48
TLVH432AIPK	296-18629-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	279.00/1,000	
TLVH432AIPKG3	296-19352-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	.84	63 48
TLVH432AIPKG3	296-19352-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	279.00/1,000	
TLVH432AIDBZR	296-17978-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-23	.78	65 52
TLVH432AIDBZR	296-17978-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-23	1014.00/3,000	
TLVH432AIPK	296-18630-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	.84	70 56
TLVH432AIPK	296-18630-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	372.00/1,000	
TLVH432AIPKG3	296-19353-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	.84	70 56
TLVH432AIPKG3	296-19353-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	372.00/1,000	
TLVH432CDBZR	296-17979-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-23	.92	69 52
TLVH432CDBZR	296-17979-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-23	897.00/3,000	
TLVH432BPK	296-18631-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	.75	63 50
TLVH432BPK	296-18631-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	333.00/1,000	
TLVH432BPKG3	296-19354-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	.75	63 50
TLVH432BPKG3	296-19354-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	333.00/1,000	
TLVH432BIDBZR	296-17980-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-23	.75	63 50
TLVH432BIDBZR	296-17980-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-23	975.00/3,000	
TLVH432BIPK	296-18632-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	.81	68 54
TLVH432BIPK	296-18632-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	359.00/1,000	
TLVH432BIPKG3	296-19355-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	.81	68 54
TLVH432BIPKG3	296-19355-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	359.00/1,000	
TLVH432BODBZR	296-17981-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-23	1.05	88 70
TLVH432BODBZR	296-17981-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-23	1365.00/3,000	
TLVH432BOPK	296-18633-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	1.11	93 74
TLVH432BOPK	296-18633-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	492.00/1,000	
TLVH432BOPKG3	296-19356-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	1.11	93 74
TLVH432BOPKG3	296-19356-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	492.00/1,000	
TLVH432CDBZR	296-17982-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-23	.60	45 34
TLVH432CDBZR	296-17982-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-23	585.00/3,000	
TLVH432CCKP	296-18634-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	.68	51 39
TLVH432CCKP	296-18634-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	226.00/1,000	
TLVH432CCKG3	296-19357-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	.68	51 39
TLVH432CCKG3	296-19357-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	226.00/1,000	
TLVH432IDBZR	296-17983-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-23	.68	51 39
TLVH432IDBZR	296-17983-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-23	663.00/3,000	
TLVH432IPK	296-18635-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	.76	57 43
TLVH432IPK	296-18635-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	253.00/1,000	
TLVH432IPKG3	296-19358-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	.76	57 43
TLVH432IPKG3	296-19358-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	253.00/1,000	
TLVH432QDBZR	296-17984-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-23	.92	69 52
TLVH432QDBZR	296-17984-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-23	897.00/3,000	
TLVH432QPK	296-18636-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	.75	63 50
TLVH432QPK	296-18636-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	333.00/1,000	
TLVH432QPKG3	296-19359-1-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	.75	63 50
TLVH432QPKG3	296-19359-2-ND	Low Volt. Adj. Precision Shunt Reg. *	SOT-89	333.00/1,000	
UA78L02ACD	296-11116-5-ND	2.0V, 100mA Regulator *	8-SOP	.45	36 27
UA78L02ACP	296-11117-5-ND	2.0V, 100mA Regulator *	TO-226AA	.40	32 24
UA78L05ACD	296-1364-5-ND	5.0V, 100mA Regulator *	8-SOP	.48	37 28
UA78L05ACDR	296-1364-1-ND	5.0V, 100mA Regulator *	8-SOIC	.55	44 33
UA78L05ACDR	296-1364-2-ND	5.0V, 100mA Regulator *	8-SOIC	372.50/2,500	
UA78L05ACLPR	296-1365-ND	5.0V, 100mA Regulator *	TO-92	.48	37 28
UA78L05ACLPR	296-1365-1-ND	5.0V, 100mA Regulator *	TO-92	.55	44 33
UA78L05ACLPR	296-1365-2-ND	5.0V, 100mA Regulator *	TO-92	308.00/2,000	
UA78L05ACP	296-11118-1-ND	5.0V, 100mA Regulator *	SOT-89	.56	43 32
UA78L05ACP	296-11118-2-ND	5.0V, 100mA Regulator *	SOT-89	188.00/1,000	
UA78L05AIDR	296-16903-1-ND	5.0V, 100mA Regulator *	8-SOIC	.52	39 30
UA78L05AIDR	296-16903-2-ND	5.0V, 100mA Regulator *	8-SOIC	422.50/2,500	
UA78L05AIP	296-11119-5-ND	5.0V, 100mA Regulator *	TO-92	.56	43 32
UA78L05AIP	296-11119-1-ND	5.0V, 100mA Regulator *	SOT-89	.56	43 32
UA78L05AIP	296-11119-2-ND	5.0V, 100mA Regulator *	SOT-89	188.00/1,000	
UA78L05D	296-11120-5-ND	5.0V, 100mA Regulator *	8-SOP	.40	32 24
UA78L05D	296-11121-5-ND	5.0V, 100mA Regulator *	TO-226AA	.46	37 26
UA78L05D	296-13531-1-ND	5.0V, 100mA Regulator *	SOT-89	.40	32 24
UA78L05D	296-13531-2-ND	5.0V, 100mA Regulator *	SOT-89	112.00/1,000	
UA78L06ACLPR	296-11122-5-ND	6.0V, 100mA Regulator *	TO-226AA	.39	32 22
UA78L06ACP	296-15739-1-ND	6.0V, 100mA Regulator *	SOT-89	.40	32 24
UA78L06ACP	296-15739-2-ND	6.0V, 100mA Regulator *	SOT-89	112.00/1,000	
UA78L08ACD	296-11123-5-ND	8.0V, 100mA Regulator *	8-SOP	.40	32 24
UA78L08ACD	296-11124-5-ND	8.0V, 100mA Regulator *	TO-226AA	.40	32 24
UA78L08ACLPR	296-15052-1-ND	8.0V, 100mA Regulator *	TO-226	.40	32 24
UA78L08ACLPR	296-15052-2-ND	8.0V, 100mA Regulator *	TO-226	224.00/2,000	
UA78L08ACP	296-11125-1-ND	8.0V, 100mA Regulator *	SOT-89	.52	39 30
UA78L08ACP	296-11125-2-ND	8.0V, 100mA Regulator *	SOT-89	173.00/1,000	
UA78L09ACD	296-11126-5-ND	9.0V, 100mA Regulator *	8-SOP	.45	36 27
UA78L09ACD	296-15053-1-ND	9.0V, 100mA Regulator *	8-SOIC	.40	32 24
UA78L09ACDR	296-15053-2-ND	9.0V, 100mA Regulator *	8-SOIC	270.00/2,500	
UA78L09ACLPR	296-11127-5-ND	9.0V, 100mA Regulator *	TO-226AA	.40	32 24
UA78L09ACP	296-14331-1-ND	9.0V, 100mA Regulator *	SOT-89	.45	36 27
UA78L09ACP	296-14331-2-ND	9.0V, 100mA Regulator *	SOT-89	126.00/1,000	
UA78L10ACD	296-11129-5-ND	10.0V, 100mA Regulator *	8-SOP	.45	36 27
UA78L10ACLPR	296-1996-ND	10.0V, 100mA Regulator *	TO-92	.40	32 24
UA78L10ACP	296-15327-1-ND	10.0V, 100mA Regulator *	SOT-89	.45	36 27
UA78L10ACP	296-15327-2-ND	10.0V, 100mA Regulator *	SOT-89	126.00/1,000	
UA78L12ACD	296-11130-5-ND	12.0V, 100mA Regulator *	8-SOP	.45	36 27
UA78L12ACDR	296-15054-1-ND	12.0V, 100mA Regulator *	8-SOIC	.40	32 24

*RoHS Compliant

(Continued)

★ CALL FOR LOWER PRICING ON LARGER QUANTITIES! ★

All prices are in U.S. dollars (www.digikey.com). — Toll-Free: 00801-85-4023 Fax: (852) 3104 0686 — Taiwan dollar available by credit card at www.digikey.tw. (TW092-10) 911