

D

Fig.	Series	Frequency	Digi-Key Part No.	Cut Tape Price Each			Digi-Key Part No.	Tape and Reel		Epson Part No.		
				1	10	50		Qty.	Pricing			
1	MA-506	18.00000 MHz	SE2632CT-ND	1.12	.96	.80	SE2632TR-ND	1,000	448.00	MA-506 18.0000M-C0		
		18.43200 MHz	SE2633CT-ND	1.12	.96	.80	SE2633TR-ND	1,000	448.00	MA-506 18.4320M-C0		
		19.66080 MHz	SE2635CT-ND	1.12	.96	.80	SE2635TR-ND	1,000	448.00	MA-506 19.6608M-C0		
		20.00000 MHz	SE2609CT-ND	1.12	.96	.80	SE2609TR-ND	1,000	448.00	MA-506 20.0000M-C0		
		20.48000 MHz	SE2636CT-ND	1.12	.96	.80	SE2636TR-ND	1,000	448.00	MA-506 20.4800M-C0		
		22.11840 MHz	SE2637CT-ND	1.12	.96	.80	SE2637TR-ND	1,000	448.00	MA-506 22.1184M-C0		
		24.00000 MHz	SE2610CT-ND	1.12	.96	.80	SE2610TR-ND	1,000	448.00	MA-506 24.0000M-C0		
		24.57600 MHz	SE2638CT-ND	1.12	.96	.80	SE2638TR-ND	1,000	448.00	MA-506 24.5760M-C0		
		25.00000 MHz	SE2639CT-ND	1.12	.96	.80	SE2639TR-ND	1,000	448.00	MA-506 25.0000M-C0		
		27.00000 MHz	SE2641CT-ND	1.12	.96	.80	SE2641TR-ND	1,000	448.00	MA-506 27.0000M-C0:(FUND)		
		28.63600 MHz	SE2642CT-ND	1.12	.96	.80	SE2642TR-ND	1,000	448.00	MA-506 28.6360M-C0:(30T)		
		33.00000 MHz	SE2647CT-ND	1.12	.96	.80	SE2647TR-ND	1,000	448.00	MA-506 33.0000M-C0		
		40.00000 MHz	SE2615CT-ND	1.12	.96	.80	SE2615TR-ND	1,000	448.00	MA-506 40.0000M-C0		
		48.00000 MHz	SE2651CT-ND	1.12	.96	.80	SE2651TR-ND	1,000	448.00	MA-506 48.0000M-C0		
		50.00000 MHz	SE2616CT-ND	1.12	.96	.80	SE2616TR-ND	1,000	448.00	MA-506 50.0000M-C0		
		64.00000 MHz	SE2653CT-ND	1.23	1.05	.88	SE2653TR-ND	1,000	490.00	MA-506 64.0000M-C0		
		2	MC-146	32.76800 kHz	SE2416CT-ND	1.40	1.20	1.00	SE2416TR-ND	250	200.00	MC-146 32.768KA-AC3
		3	MC-156	32.76800 kHz	SE2412CT-ND	1.30	1.11	.93	SE2412TR-ND	1,000	518.00	MC-156 32.7680KA-A0
4	MC-306	32.76800 kHz	SE2407CT-ND	.95	.81	.68	SE2407TR-ND	1,000	378.00	MC-306 32.7680K-A0		
		32.76800 kHz	SE2417CT-ND	.95	.81	.68	SE2417TR-ND	250	135.00	MC-306 32.768K-E3		
5	MC-405	32.76800 kHz	SE2405CT-ND	.95	.81	.68	SE2405TR-ND	1,000	378.00	MC-405 32.7680K-A0		
6	MC-406	32.76800 kHz	SE2418CT-ND	.95	.81	.68	SE2418TR-ND	250	135.00	MC-406 32.768K-A3		
RoHS Compliant												
7	FC-135	32.76800 kHz	SE2413CT-ND	2.98	2.55	2.13	SE2413TR-ND	250	425.00	FC-135 32.7680KA-A3		
8	FC-255	32.76800 kHz	SE2415CT-ND	1.86	1.59	1.33	SE2415TR-ND	250	265.00	FC-255 32.7680K-A3		
9	MA-406	10.00000 MHz	SER3646CT-ND	1.12	.96	.80	SER3646TR-ND	250	160.00	MA-406 10.0000M-C3:ROHS		
		12.00000 MHz	SER3643CT-ND	1.12	.96	.80	SER3643TR-ND	250	160.00	MA-406 12.0000M-C3:ROHS		
		14.31818 MHz	SER3647CT-ND	1.12	.96	.80	SER3647TR-ND	250	160.00	MA-406 14.31818M-C3:ROHS		
		16.00000 MHz	SER3645CT-ND	1.12	.96	.80	SER3645TR-ND	250	160.00	MA-406 16.0000M-C3:ROHS		
		25.00000 MHz	SER3644CT-ND	1.12	.96	.80	SER3644TR-ND	250	160.00	MA-406 25.0000M-C3:ROHS		
		25.00000 MHz	SER3642CT-ND	1.12	.96	.80	SER3642TR-ND	250	160.00	MA-406 25.0000M-G3:ROHS		
1	MA-505	4.00000 MHz	SER2518CT-ND	2.80	2.40	2.00	SER2518TR-ND	1,000	1120.00	MA-505 4.0000M-C0:ROHS		
		4.09600 MHz	SER2519CT-ND	2.80	2.40	2.00	SER2519TR-ND	1,000	1120.00	MA-505 4.0960M-C0:ROHS		
		4.91520 MHz	SER2520CT-ND	2.80	2.40	2.00	SER2520TR-ND	1,000	1120.00	MA-505 4.9152M-C0:ROHS		
		6.00000 MHz	SER2501CT-ND	1.12	.96	.80	SER2501TR-ND	1,000	448.00	MA-505 6.0000M-C0:ROHS		
		7.37280 MHz	SER2503CT-ND	1.12	.96	.80	SER2503TR-ND	1,000	448.00	MA-505 7.3728M-C0:ROHS		
		8.00000 MHz	SER2504CT-ND	1.12	.96	.80	SER2504TR-ND	1,000	448.00	MA-505 8.0000M-C0:ROHS		
		9.83040 MHz	SER2524CT-ND	1.12	.96	.80	SER2524TR-ND	1,000	448.00	MA-505 9.8304M-C0:ROHS		
		10.00000 MHz	SER2505CT-ND	1.12	.96	.80	SER2505TR-ND	1,000	448.00	MA-505 10.0000M-C0:ROHS		
		11.05920 MHz	SER2506CT-ND	1.12	.96	.80	SER2506TR-ND	1,000	448.00	MA-505 11.0592M-C0:ROHS		
		12.00000 MHz	SER2507CT-ND	1.12	.96	.80	SER2507TR-ND	1,000	448.00	MA-505 12.0000M-C0:ROHS		
		14.31800 MHz	SER2528CT-ND	1.12	.96	.80	SER2528TR-ND	1,000	448.00	MA-505 14.3180M-C0:ROHS		
		14.74560 MHz	SER2529CT-ND	1.12	.96	.80	SER2529TR-ND	1,000	448.00	MA-505 14.7456M-C0:ROHS		
		16.00000 MHz	SER2508CT-ND	1.12	.96	.80	SER2508TR-ND	1,000	448.00	MA-505 16.0000M-C0:ROHS		
		18.43200 MHz	SER2533CT-ND	1.12	.96	.80	SER2533TR-ND	1,000	448.00	MA-505 18.4320M-C0:ROHS		
		19.66000 MHz	SER2535CT-ND	1.12	.96	.80	SER2535TR-ND	1,000	448.00	MA-505 19.6600M-C0:ROHS		
		20.00000 MHz	SER2509CT-ND	1.12	.96	.80	SER2509TR-ND	1,000	448.00	MA-505 20.0000M-C0:ROHS		
		24.00000 MHz	SER2510CT-ND	1.12	.96	.80	SER2510TR-ND	1,000	448.00	MA-505 24.0000M-C0:ROHS		
		24.57600 MHz	SER2538CT-ND	1.12	.96	.80	SER2538TR-ND	1,000	448.00	MA-505 24.5760M-C0:ROHS		
		25.00000 MHz	SER2539CT-ND	1.12	.96	.80	SER2539TR-ND	1,000	448.00	MA-505 25.0000M-C0:ROHS		
		29.49120 MHz	SER2543CT-ND	1.12	.96	.80	SER2543TR-ND	1,000	448.00	MA-505 29.4912M-C0:(30T):ROHS		
		30.00000 MHz	SER2544CT-ND	1.12	.96	.80	SER2544TR-ND	1,000	448.00	MA-505 30.0000M-C0:ROHS		
		40.00000 MHz	SER2515CT-ND	1.12	.96	.80	SER2515TR-ND	1,000	448.00	MA-505 40.0000M-C0:ROHS		
		1	MA-506	4.00000 MHz	SER2618CT-ND	2.80	2.40	2.00	SER2618TR-ND	1,000	1120.00	MA-506 4.0000M-C0:ROHS
				4.09600 MHz	SER2619CT-ND	2.80	2.40	2.00	SER2619TR-ND	1,000	1120.00	MA-506 4.0960M-C0:ROHS
4.91520 MHz	SER2620CT-ND			2.80	2.40	2.00	SER2620TR-ND	1,000	1120.00	MA-506 4.9152M-C0:ROHS		
6.00000 MHz	SER2601CT-ND			1.12	.96	.80	SER2601TR-ND	1,000	448.00	MA-506 6.0000M-C0:ROHS		
6.14400 MHz	SER2602CT-ND			1.12	.96	.80	SER2602TR-ND	1,000	448.00	MA-506 6.1440M-C0:ROHS		
7.37280 MHz	SER2603CT-ND			1.12	.96	.80	SER2603TR-ND	1,000	448.00	MA-506 7.3728M-C0:ROHS		
8.00000 MHz	SER2604CT-ND			1.12	.96	.80	SER2604TR-ND	1,000	448.00	MA-506 8.0000M-C0:ROHS		
9.83000 MHz	SER2624CT-ND			1.12	.96	.80	SER2624TR-ND	1,000	448.00	MA-506 9.8300M-C0:ROHS		
10.00000 MHz	SER2605CT-ND			1.12	.96	.80	SER2605TR-ND	1,000	448.00	MA-506 10.0000M-C0:ROHS		
11.05920 MHz	SER2606CT-ND			1.12	.96	.80	SER2606TR-ND	1,000	448.00	MA-506 11.0592M-C0:ROHS		
12.00000 MHz	SER2607CT-ND			1.12	.96	.80	SER2607TR-ND	1,000	448.00	MA-506 12.0000M-C0:ROHS		
12.28800 MHz	SER2627CT-ND			1.12	.96	.80	SER2627TR-ND	1,000	448.00	MA-506 12.2880M-C0:ROHS		
14.31818 MHz	SER2628CT-ND	1.12	.96	.80	SER2628TR-ND	1,000	448.00	MA-506 14.31818M-C0:ROHS				
14.74560 MHz	SER2629CT-ND	1.12	.96	.80	SER2629TR-ND	1,000	448.00	MA-506 14.7456M-C0:ROHS				
16.00000 MHz	SER2608CT-ND	1.12	.96	.80	SER2608TR-ND	1,000	448.00	MA-506 16.0000M-C0:ROHS				
1	MA-506	18.00000 MHz	SER2632CT-ND	1.12	.96	.80	SER2632TR-ND	1,000	448.00	MA-506 18.0000M-C0:ROHS		
		18.43200 MHz	SER2633CT-ND	1.12	.96	.80	SER2633TR-ND	1,000	448.00	MA-506 18.4320M-C0:ROHS		
		20.00000 MHz	SER2609CT-ND	1.12	.96	.80	SER2609TR-ND	1,000	448.00	MA-506 20.0000M-C0:ROHS		
		22.11840 MHz	SER2637CT-ND	1.12	.96	.80	SER2637TR-ND	1,000	448.00	MA-506 22.1184M-C0:ROHS		
		24.00000 MHz	SER2610CT-ND	1.12	.96	.80	SER2610TR-ND	1,000	448.00	MA-506 24.0000M-C0:ROHS		
		24.57600 MHz	SER2638CT-ND	1.12	.96	.80	SER2638TR-ND	1,000	448.00	MA-506 24.5760M-C0:ROHS		
		25.00000 MHz	SER2639CT-ND	1.12	.96	.80	SER2639TR-ND	1,000	448.00	MA-506 25.0000M-C0:ROHS		
		27.00000 MHz	SER2641CT-ND	1.12	.96	.80	SER2641TR-ND	1,000	448.00	MA-506 27.0000M-C0:(FUND):ROHS		
		28.63600 MHz	SER2642CT-ND	1.12	.96	.80	SER2642TR-ND	1,000	448.00	MA-506 28.6360M-C0:(30T):ROHS		
		32.76800 MHz	SER2646CT-ND	1.12	.96	.80	SER2646TR-ND	1,000	448.00	MA-506 32.7680M-C0:ROHS		
		48.00000 MHz	SER2651CT-ND	1.12	.96	.80	SER2651TR-ND	1,000	448.00	MA-506 48.0000M-C0:ROHS		
		64.00000 MHz	SER2653CT-ND	1.23	1.05	.88	SER2653TR-ND	1,000	490.00	MA-506 64.0000M-C0:ROHS		
		2	MC-146	32.76800 kHz	SER2416CT-ND	1.40	1.20	1.00	SER2416TR-ND	250	200.00	MC-146 32.768KA-AC3:ROHS
		3	MC-156	32.76800 kHz	SER2412CT-ND	1.30	1.11	.93	SER2412TR-ND	1,000	518.00	MC-156 32.7680KA-A0:ROHS
		4	MC-306	32.76800 kHz	SER2407CT-ND	.95	.81	.68	SER2407TR-ND	1,000	378.00	MC-306 32.7680K-A0:ROHS
				32.76800 kHz	SER2417CT-ND	.95	.81	.68	SER2417TR-ND	250	135.00	MC-306 32.768K-E3:ROHS
		6	MC-406	32.76800 kHz	SER2405CT-ND	.95	.81	.68	SER2405TR-ND	1,000	378.00	MC-406 32.7680K-A0:ROHS
				32.76800 kHz	SER2418CT-ND	.95	.81	.68	SER2418TR-ND	250	135.00	MC-406 32.768K-A3:ROHS

Digi-Reel® Most SMT cutdown parts are available on a Digi-Reel®. For Digi-Reel part number, change 1-ND to 6-ND or CT-ND to DKR-ND. See Digi-Key® Services on page 2 for additional information.

All prices are in U.S. dollars (www.digikey.com). — Toll-Free: 00801-85-4023

1334 (TW092-10) Fax: (852) 3104 0686 — Taiwan dollar available by credit card at www.digikey.tw.