

More Product Available at uk.digikey.com

A

Accelerometers2266-2269

Accessories/D-Sub See Hardware

Adapters

 Audio436

 D-Sub55-56

 Fiber Optic296-297

 Gender Changers56

 Keyboard55

 Memory Card473

 Modular282, 286-287, 293

 Mouse55

 PLCC499

 Programming/Prototyping551-552, 579,

 593, 617, 644, 646, 1327, 1329

 QFP to PGA498

 RF402-405, 409, 411, 415,

 417-418, 421, 427-430, 523-524

 SCSI58

 SOIC to DIP498

 SOJ to DIP498

 SSOP to DIP498

 TO to DIP499

 USB59

Alarms See Buzzers

Alternistors1203, 1285

Antenna507, 509, 511,

 524-527, 532, 540, 544, 547

 Cellular/GPS525

 Horn544

 Hybrid Log544

 Magnetic Mount525

 Planar509, 526

 SMD507, 509, 525

 UWB544

 Whip507, 509, 526-527

 Wireless540

 Yagi525

Attenuators297, 1349, 1774, 1835

Auto Accessories

 Fuses and Fuseholders1958

B

Backlight, EL Element2292

Balun531, 1452, 1454

Bezels2296

Blowers/Fans See Fans/Blowers

Books1423

Buzzers2144-2147, 2149-2152, 2154

C

Cable

 Solar (Photovoltaic)197

Cable Assemblies

 Audio442

 BNC, Molded421

 CAT 5 and CAT 5e Patch58-60, 293

 CAT 6 Patch58-60, 293

 Computer, Molded54-55, 58-60

 DVI64, 198, 421

 eco/mate™366

 Fiber Optic298

 Flat Flex DF984

 F Type (Television)421

 HDMI64, 421

 IDC26-34, 42, 44-49, 120

 Card Edge33-34

 DIP31-32, 42, 45, 49

 D-Sub26, 30, 44

 PCB32-34, 41-42

 Pin/Plug29, 39-41, 47-49, 120

 Socket28, 32-34, 39-41, 45-46, 48-49, 120

 IEEE 128454

IEEE 139459, 64

Infiniband477

iPass™478

Modular278, 287

Molded368

Multi-Media57

Power42

Power Cord56-57

RCA421

RF421, 427-429, 1349

SCSI58-59, 478

SDR51

Serial ATA198

Stereo Extension56-57

S Video57

Termination Jumpers26-27, 30-33, 37,

 39, 42, 44-45, 48-49, 120

Twisted Pair39-41

USB58-59, 61-64

VGA55

Cable EMI Ferrite Cores1421, 1472-1474

Cable Splice Enclosures339

Cable Testers60

Cable/Wire

 Fiber Optic296, 300

 Flat Cable Jumpers76, 78

 Flat Flex Cable65, 76, 78

 0.020" (0.5mm)76

 0.040" (1mm)78

 0.050" (1.27mm)65

 0.100" (2.54mm)65

 LVDS2284

 Ribbon

 0.040" (1mm)150

 0.050" (1.27mm)43, 53

 0.100" (2.54mm) Pre-cut Flat53

Camera

 Accessories544

 Controller544

Camera Modules

 CMOS Image Sensors695

 Evaluation Boards695

 Lens Kits695

Capacitor Arrays1682-1683, 1711,

 1728, 1750, 1758-1759, 1836

Capacitor Networks1836

Capacitors

 Aluminum Electrolytic1493-1512,

 1517-1595, 1639

 Axial1493-1496, 1639

 Flatpack1512

 Screw Terminal1517-1518

 Snap-In1518-1527, 1564-1566, 1593-1595

 Aluminum Organic1626

 Automotive Multilayer Chip1705

 Bi-Polar1497, 1532

 Ceramic517-518, 1712-1714

 Axial1667, 1670-1671, 1679

 Chip1684, 1769, 1771

 Disc1669, 1676-1678,

 1680-1684, 1727, 1760-1762

 Monolithic1670-1673,

 1725-1726, 1728, 1741-1745

 Multilayer1668, 1670-1673, 1675-1676,

 1678-1680, 1728, 1763-1764

 ArcGuard1763

 Soft Termination1764

 Multilayer Chip

 Flexisafe Capacitors1704

 Multilayer Chip (MLCC)517-518, 1682-1683,

 1685-1706, 1709-1724,

 1728-1740, 1746-1759, 1762, 1764-1769

 Low Profile1706

 Safety1714, 1726

 SMT1714

 Soft Termination1704-1705

 Tip and Ring1710

 Trimmer1770-1773

 CombiSuppressor1646

 Computer Grade1517, 1528

 Dry Film AC1667

 Electric Double Layer (EDLC)1512, 1514-1516

 EMI Suppression1645-1646, 1711

Feedthrough1458, 1464

Film1642, 1647-1649, 1652, 1654-1657,

 1659-1661, 1664-1666, 1674, 1773

Gold1514-1515

Hardware1517

Interference Suppressor1664, 1674

Kits1749, 2139

Low Inductance1710-1711

Metallized Polyester1643-1644,

 1646-1653, 1658, 1666, 1674

Metallized Polypropylene1644-1645,

 1648, 1653, 1660-1665

MICA1769-1770

Microwave Chip1692, 1706-1709

Multilayer Chip (MLCC)519

Niobium Oxide1612

Polyester1641-1643

Polymer1550-1552, 1589-1592, 1596

RF Power1705

Supercapacitor Aerogel1513

Tantalum1596-1611, 1613-1639

 Axial1614, 1632

 Radial1599-1600, 1613, 1631

 Thin Film RF1708-1709, 1770

 Trimmer1770-1771, 1773

 Ultracapacitors1512

 Variable1770

 Wet Tantalum1600, 1614, 1639-1640

X2Y®1712, 1768-1769

Chokes See Coils/Inductors

Circuit Breakers

 Accessories1970

 DIN Rail1970

 DIN Rail Mount1967, 1969-1970

 Hydraulic-Magnetic1966, 1969

 Switch1965, 1967, 1971-1972

 Thermal1967-1968, 1971-1972

 Thermal Links1965

Clips

 Fuse1950-1951, 1958-1959

Coils/Inductors1364-1374, 1379-1384, 1386-1392,

 1394-1421, 1427-1448, 1461-1462, 1465, 1468-1471

 See also Transformers

 Air Core1421

 Axial1377

 Bobbin1377-1378

 Chip1379, 1403, 1438-1441,

 1443-1445, 1468-1469

 Kits1438-1439

 Chokes1367, 1378, 1385, 1394-1402, 1407,

 1411-1412, 1417-1420, 1448-1451,

 1455-1456, 1461-1462, 1468-1471

 CAN-BUS1470

 Current Compensated1469-1470

 Common Mode1367, 1372, 1378, 1420, 1448,

 1455-1456, 1461-1462, 1468-1470, 2173

 Arrays1469-1470

 Conformal Coated1449, 1451

 Drum Core1380, 1404

 Film1381-1382

 High Current1374-1375, 1379, 1402,

 1406, 1414, 1417-1419, 1442,

 1444, 1446-1451, 1468-1469

 High Frequency1405-1406, 1413, 1427-1428,

 1437, 1449-1451, 1469-1470, 2173

 Kits1414-1416, 1421, 1470, 2141, 2173

 Monolithic1381-1382, 1468-1469

 Multilayer Chip1427-1428, 1438-1439

 PAS1512

 Power1364-1370, 1372-1373, 1376,

 1379, 1394, 1398-1400, 1402,

 1404-1406, 1413, 1417-1419, 1422-1426,

 1429-1436, 1440-1441, 1443-1445, 1468-1470

 Radial1377

 Rod Core2173

 Shielded1369-1372, 1374, 1379-1380,

 1404, 1413-1419, 1427, 1431-1435, 1445

 Switchmode2173

 Thin Film1394

 Toroidal1372, 1378, 1404-1406, 1418,

 1437, 1444, 1446-1448, 1455, 2171, 2173

 Voltage Step-Up1395

 Wirewound1379, 1383-1392, 1403,

 1408-1411, 1440-1441

CompactPCI® Products456-457

Free shipping on orders over £50! All prices are in British pound sterling and include duties.

uk.digikey.com — FREEPHONE: 0-800-587-0991 • 0-800-904-7786 — FREEFAX: 0-800-587-0992 • 0-800-904-7783