

More Product Available at uk.digikey.com

Computer Equipment		Medical.....	391	IDC Ribbon Cable.....	37-39, 41
Cable Assemblies.....	54-60	Metal.....	359-364, 376-383, 387, 398, 400	2mm Socket.....	143, 145, 151-152
Concentric Scale Dials	1854	MIL-C-5015.....	362-363, 399	Card Edge.....	32, 38-39
Connectorized		MIL-C-26482.....	359-361, 375	Delta.....	41
Amplifier.....	1349	MIL-C-38999.....	374	DIP.....	27, 31, 44, 49
Regulator.....	1349	Miniature.....	378-379, 381-383, 387, 389-391	D-Sub.....	26, 30, 37, 44
Connectors		Mini-DIN.....	400-401	Mini D (MDR).....	50-51
0.2mm.....	67	MS Series.....	360, 364	PCB.....	32, 41-42
0.3mm.....	67, 70, 72, 78	Plastic.....	366, 369, 378, 383-384,	Pin/Plug.....	29, 38, 47-48
0.4mm.....	67, 79, 103, 187, 465	PT Series.....	392-394, 397, 399-401	Socket.....	28, 32, 45, 53, 143, 145, 151-152
SlimStack™.....	187	Push-Pull Lock.....	375, 377, 382-384	IEEE 1394 (Firewire).....	59, 62, 285, 290
0.5mm.....	66-73, 76-77, 80-81, 103-104, 123, 187	RADSOK®.....	358	Waterproof.....	290
SlimStack™.....	187	Screw Lock.....	366, 376-377, 379-383	Industrial Ethernet.....	63, 282, 325
0.6mm.....	82	Sealed.....	367-368, 392-393	Interconnect Systems.....	233-237, 477
0.65mm.....	82-83	.125" Powerband Contact.....	397	Interface Modules.....	333
0.8mm.....	73, 83, 104-105, 123, 132, 199, 244	Wire Entry Seal Kits.....	394	Intra-Connector™.....	484
1.0mm.....	66, 68-70, 73-75, 77-78, 84, 87,	Video.....	378-379	I/O.....	105, 199-202, 476, 478
.....	123-124, 132-133, 136, 244, 249, 463, 465	Waterproof.....	365, 385-386, 388-389	Jumpers	
1.20mm.....	124	Compact Flash.....	455	Jumpers.....	See Connectors - Shunts
1.25mm.....	88-89, 121, 124-125, 136-137	CompactPCI®.....	456-457	Socket.....	38
1.27mm.....	146-147	CROWN CLIP.....	454	Termination Jumpers.....	26-27, 30-33, 37,
1.5mm.....	121, 125-126, 137	CROWN EDGE.....	454	39, 42, 44-45, 48-49
Pico SPOX™.....	137	Delta.....	41	LAN.....	282, 295
2mm.....	89-97, 122, 126-129, 138-141,	DIN, Rectangular.....	445, 450-453,	LED.....	2323
.....	143-145, 148-153, 456-458, 460-461, 492	DisplayPort®.....	455, 463, 468, 484	Light-N-Lok™.....	2292
Hard Metric.....	458, 460-461	D-Sub.....	26, 30, 37, 44, 250-277, 283, 314	LVDS.....	87, 103
Metral®.....	461	Accessories.....	256-257, 259-260, 274	Mate-N-Lok®.....	206-219
Milli-Grid™.....	139-140	Adapters.....	271	Memory	
Millipacs®.....	461	Backshells.....	260, 271-273, 275, 277	CardBus.....	474
Mini-Clamp.....	153	Combination.....	260, 276	Card Connectors.....	445, 468, 470-474
Minitek™.....	143-145	Dual Port.....	265	Compact Flash.....	467, 469, 471, 473
Sherlock™.....	138	Filtered.....	274	DDR.....	469
Socket.....	492	Gender Changers.....	56, 271, 276	DIMM.....	445, 472
Z-Pack.....	456-457	Hardware Kits.....	258, 260, 274	Memory Stick®.....	471
2.5mm.....	98-101, 129-130, 142, 245	High Density.....	255, 260-263, 265, 274, 277, 283	MicroSD™/Transflash.....	468, 471, 476
SPOX™.....	142	VGA.....	260	PCMCIA Memory Card.....	467-468, 470-471, 474
3.96mm.....	142	Interface Modules and Cables.....	314	SD™.....	468
4.2mm.....	204	Press Fit.....	265	Secure Digital.....	467, 469, 471, 473, 476
5.0mm.....	102	Water Resistant.....	276, 283	SIM.....	476
5.08mm.....	191	Dynamic.....	233-237	SIMM.....	472
6.2mm.....	131	Edgecard.....	See Connectors - Card Edge	TransFlash.....	473
7.5mm.....	192	ELCON.....	453	MetPak™.....	
7.92mm.....	102	Ethernet.....	See Connectors - Modular	2-FB.....	459
0.050" (1.27mm).....	52, 85-86, 133, 240-243, 491	Eurocard.....	450-453, 455	CP2.....	460
Picoflex™.....	52	ExpressCard™.....	466, 472, 476	HSHM.....	460
0.062".....	193	FFC/FPC (Flat Flex).....	65, 67-78	Metrimate.....	204-205
0.084".....	193	Fiber Optic.....	296-298, 300	Mezzanine.....	186-187
0.093".....	194	Flexi-Block.....	325	MicroCross™ DVI.....	198
0.100" (2.54mm).....	96, 153, 165, 169-178,	F Type.....	422	Micro-D.....	252
.....	222-226, 228, 230-232	GBIC.....	477	Micro-Fit 3.0™.....	183-186
0.156" (3.96mm).....	101, 131, 169, 179-182	Hard Metric.....	458, 460	Microphone.....	381
AC.....	1482	Hardware.....	247, 249	Micro TCA.....	260, 458, 463
ATCA.....	463	HDI (High Density Interconnect).....	245	Mictor.....	464
Audio.....	436-443	HDMI.....	198, 445, 464	Miniature Rectangular (MR).....	221
Back Panel.....	458	Headers.....	38, 108, 196, 486	Mini D Ribbon (MDR).....	50-51
Backplane.....	444, 454, 457	2mm.....	97, 139-140, 143-145, 148-150, 492	Mini-Fit.....	
Backshells.....	43, 241, 256-257, 271-273, 275	Latching.....	53	BML.....	190
Ballast.....	2292	Shrouded.....	53	HCS.....	191
Banana Plugs/Jacks.....	387	0.0197" (0.5mm).....	106	Jr.....	188-189, 191
Barrier Blocks.....	325	0.031" (0.80mm).....	106	SMC.....	191
Battery.....	467	0.040" (1.00mm).....	106-107	Sr.....	192
Binding Posts.....	387	0.050" (1.27mm).....	107-108, 120, 492	MiniSAS.....	459, 475, 479
Blind Mate (BML).....	184, 186, 190	0.0787" (2.00mm).....	109, 120	Modular.....	59, 63, 277-289, 291-295, 464
Board-to-Board.....	43, 71, 79-88, 93, 95-96, 103,	0.100" (2.54mm).....	35-36, 42, 46-48,	70AA.....	464
.....	106-120, 123, 125-126, 132-135, 139,	0.100" (2.54mm).....	112-120, 154, 158-167, 173-175,	70AD.....	464
.....	143-144, 148, 242-243, 245, 454, 462, 465, 2323	0.156" (3.96mm).....	177-178, 196, 226-229, 490-491, 494	Adapters, Filtered.....	294-295
Floating.....	134	Female.....	167-168, 179, 182	Adapters, IBM Equivalent.....	282
In-Line.....	2323	0.0197" (0.5mm).....	106	DSL Filter.....	294
Bus Bar.....	454	0.031" (0.80mm).....	106	Ethernet.....	63, 277-287, 294-295
Card Edge.....	32, 38-39, 249, 443-449, 454, 462	0.050" (1.27mm).....	107-108	RJ11.....	284-285, 294
Centronics.....	266	0.0787" (2.00mm).....	108-111, 120	RJ45.....	277-283, 286-287, 294
C-Grid®.....	170-174	0.100" (2.54mm).....	111-116, 120,	Industrial.....	63, 282, 289, 291-293
Champ®.....	240, 247-248	154-158, 161, 165, 490-492, 494	Modular Jacks, Filtered.....	295
Circular.....		IDC.....	29, 38, 47-48, 53	Power Over Ethernet (PoE).....	287, 295
8D/D38999 Aluminum and Composite Series.....	374	IDC Dip.....	47-48	Spring Loaded Contacts.....	493
44 Series.....	368	Pin/Plug.....	47-48	M-Series.....	238-239
97 Series.....	362-364	Protected.....	47	MT .100".....	222-223
851 Series.....	375	Protected.....	35-36, 43, 46, 120	MTA .100" and .156".....	175-182
Accessories.....	363-364, 393-394, 398	Hoods, D-Sub.....	256-257, 271-273	MTE .100".....	225-226, 230-231
Bayonet Lock.....	378	HSSDC2.....	477	MX150L.....	370
C16.....	366	ICCON.....	454	Parallel Interface.....	240-242, 247-248
C091.....	367	IDC Discrete.....		PCI Express.....	448-449, 462, 472
Coaxial.....	397	D-Sub.....	254	PC Pins/Receptacles.....	484, 495-496
DIN.....	397-398, 400-401	Socket.....	175-177, 179-181, 225-226	Phono Jacks/Plugs.....	435-437, 443
IP67.....	365	Strip.....	200	Power.....	135, 182, 192-194, 199,
M8 and M12 Series.....	399			201-202, 325, 437-442, 453-454, 1482

Free shipping on orders over £50! All prices are in British pound sterling and include duties.

4 (UK091) uk.digikey.com — FREEPHONE: 0-800-587-0991 • 0-800-904-7786 — FREEFAX: 0-800-587-0992 • 0-800-904-7783