

More Product Available at [uk.digikey.com](http://uk.digikey.com)

**K**

**Kits**

- Adapters
- RF.....421
- BASIC Stamp Kits .....595
- Bead Cores.....1475
- Buzzers.....2147
- Capacitors
- Aluminum Electrolytic .....1500, 1502, 1511, 1552, 2139
- Ceramic .....1673, 1692, 1724, 2139
- Film .....1642, 1658-1659, 1674, 2139, 2141
- Polyester.....1641, 1643, 2139
- RF/Microwave.....1707
- CeraDiodes.....1899
- Chokes.....1470
- Connector.....170, 193-194, 248, 338
- Crimp Wire Ferrules.....312
- Crystal .....2141
- Diodes.....1226-1227, 2141
- Zener.....1226-1227, 2141
- EEPROM Kits .....2139
- EMI Components.....1471-1474
- ESD .....2141
- Ferrite Cable Cores.....1473-1474
- Ferrite Chips Beads.....1468
- Fiber Optic.....298
- Fuses.....1945-1949, 1953-1955, 2139
- Hardware.....2141
- Heat Shrink Tubing .....2135-2138, 2141
- Inductors.....1414-1416, 1421, 2139, 2141, 2173
- Integrated Circuits.....2141
- LEDs.....2141, 2368
- Potentiometers.....1887, 1891, 2139
- Resistors.....1774-1778, 1789-1793, 1797-1798, 1832, 2140-2141
- Switches .....1985, 2047, 2094, 2141
- Terminals, Insulated.....338-339
- Thermistors.....1930, 2141, 2278

**Knobs** .....1881-1883, 2072

**L**

**Labels**

- Solar (Photovoltaic) .....197

**Lamps**

- Assemblies.....2292
- CCFL.....2292
- UV.....2292

**Laser**

- Diodes Modules
- Adjustable Focus .....2310
- Infrared .....2310
- Laser Line Generator.....2310

**LCDs**

- 7-Segment Displays .....2287, 2293, 2311
- Character Display Modules .....2286-2289
- Controller Boards and Accessories.....2284
- Dot Matrix Modules .....2293
- Graphic Display Modules.....2285-2286, 2288-2289, 2293
- Organic (OLED) Displays .....2283
- TFT Displays .....2284-2286, 2289, 2293
- Development Kits .....2285-2286

**LEDs**.....1108, 2224-2225, 2230-2232, 2235-2236, 2241-2242, 2308, 2311-2323, 2330-2340, 2344-2376

- 7-Segment Displays .....2311, 2324, 2344, 2348, 2373
- Accessories .....2338
- Alphanumeric Displays .....2348
- Arrays/Light Bars .....2320, 2322, 2330-2331, 2338, 2344, 2368-2369
- Arrays/Light Engine .....2330-2331
- Assemblies .....2354, 2357
- Bar Graph Array.....2324, 2347, 2376
- Based .....2323, 2332
- Bi-Color.....2313-2317, 2320, 2333-2337, 2339-2340, 2345-2347, 2349-2353, 2356-2357, 2372-2373, 2376
- Blue .....2312, 2316-2319, 2330-2337, 2339-2340, 2345-2346, 2349-2350, 2352, 2358-2359, 2367-2368, 2370-2373

- Circuit Board Indicators .....2355
- Cluster .....2320, 2323
- Connectors .....2323
- Design Kits .....2368
- Dot Matrix Display .....2347
- Driver .....2339
- DSP .....2312
- Fiber Optic.....300
- Flashing/Blinking .....2314, 2320, 2354
- Heat Sinks .....2330
- High Brightness.....2312, 2320, 2339, 2342-2343, 2349-2350, 2352, 2355, 2367-2368, 2370-2373, 2376
- High Power.....2352
- Holders/Mounts .....2322
- Incandescent Replacement.....2323, 2332, 2341
- Infrared .....2214, 2224-2225, 2230, 2233, 2235-2236, 2241-2242, 2308
- Lenses/Caps.....2355, 2362-2363, 2369
- Level Meters .....2376
- Low Battery Indicators .....2320
- Modular .....2354
- Multi-Color .....2334-2337, 2339, 2357
- Numeric Displays.....2373
- Panel Mount .....2321-2322
- RGB (Red/Green/Blue).....2313, 2319, 2330-2331, 2333, 2357, 2368
- Surface Mount .....1108, 2327-2329, 2369
- Thermal Clad Boards .....1108
- Through-Hole .....2325-2326
- White .....2312, 2332-2333, 2335, 2339-2340, 2346, 2350-2352, 2355, 2358-2359, 2367-2368, 2371-2373
- Wide Angle .....2376

**Lighting**

- Connectors .....2292, 2323

**Light Pipes** .....2315, 2341, 2355

**M**

**Magnets**.....2093

**Memory**

- Cards .....739, 1106-1107
- Compact Flash .....1106-1107
- Flash Disks .....1106
- iDOC .....1106
- PCMCIA .....1107
- Secure Digital .....1106-1107
- uDOC .....1106
- DDR.....1093-1094, 1107
- DDR2 .....1094, 1107
- DDR3.....1094
- DiskOnChip .....1104
- EEPROM .....966
- EEPROM, CMOS .....757
- EEPROM, Parallel .....1009, 1102
- EEPROM, Serial .....1077-1078, 1095-1103
- Embedded .....737-738
- EPROM .....965-966, 1102
- FIFO .....868-869, 1100
- Flash .....736-737, 966, 1094, 1102-1104
- iButton® .....1091
- INAND .....1104
- Magnetoresistive RAM.....733
- Modules .....1106-1107
- NVRAM .....966-967, 1091
- PROM, Serial.....556
- PSRAM .....1094-1095
- SDRAM.....1093, 1095, 1103, 1107
- Serial Dataflash .....1103
- SRAM .....757, 944, 949, 1095, 1099-1100, 1103-1104
- StrataFlash® .....738-739

**MESFETs**.....510

**Meters**.....See Test Equipment

**Microcontrollers** .....See ICs - Microcontrollers

**Microphones**

- Electret Condenser.....2155-2156
- Holders .....2155-2156
- Magnetic.....2157
- Silicon .....2158

**Microprocessors** .....See ICs - Microprocessors

**MOSFET/MOSFET Drivers** .....534, 623-624, 938-939, 1130-1133, 1144-1146, 1160, 1171-1182, 1191-1193, 1204, 1218-1220, 1243-1249, 1254-1258, 1261-1263, 1267, 1273, 1275-1276, 1288, 1293-1299

**Motor Control**

- Modular Boards .....632

**MOVs** .....See Varistors

**O**

**Optical Enhancement Films** .....2282

**Optoelectronics**

- Ambient Light Sensor .....2226, 2237
- Evaluation Kits .....2362
- Infrared Detectors .....2225
- Infrared Emitters .....2224, 2227-2228, 2230, 2233, 2235-2236, 2241, 2308
- Interrupter Modules .....2225
- IrDA Transceiver Modules .....2241, 2309
- Lenses, Aspherical .....2310
- Light Detectors.....2224
- Logic Detectors.....2225
- Optical Sensors .....2226, 2231, 2233-2234, 2236, 2242, 2308
- Reflective.....2236-2237, 2242
- Orientation Sensor.....2230
- Photoconductive Cells .....2227-2228
- Photo Detectors .....2225, 2227-2228, 2233, 2242
- Photo Diodes .....2214, 2224, 2227-2229, 2235, 2241-2242
- Photo ICs .....2229, 2242
- Photointerrupters .....2223, 2236-2237, 2242
- Reflective.....2223, 2242
- Photo Transistors .....2214, 2224, 2229, 2233, 2235-2236, 2241
- Reflective Sensor.....2230
- Remote Control Receivers.....2309, 2343
- Touch Screens .....2283-2284

**Optoisolators/Photocouplers**

- Digital.....2218-2219, 2222
- High Speed Output .....2207, 2217
- IREC .....2217
- Logic Output .....2210, 2213, 2217
- Magnetic.....2222
- Optocouplers .....2207-2209
- Photo-IC Output.....2210
- Photo-Transistor Output.....2206-2207, 2210-2213, 2215, 2217, 2220-2221
- Photovoltaic .....1178, 2217
- SCR/Triac Output .....2210, 2212-2213
- Thyristor Output.....2216, 2219

**Oscillators** .....1300-1303, 1309, 1315-1321, 1327-1335, 1340-1345, 1347, 1352-1355

- Clock.....1300-1303, 1340-1342, 1354
- Crystal .....1303-1312, 1321, 1331-1335, 1347, 1354
- Ovenized (OCXO).....1345, 1348
- Programmable .....1327-1330
- Real Time Clock.....1330
- SAW (Surface Acoustic Wave).....1348
- Silicon.....1345
- Sockets.....1334-1335, 1342
- Spread Spectrum .....1352
- Synchronous Clock Generators .....1344
- Temperature Compensated (TCXO), (TCVCXO) .....1302, 1319, 1329, 1345, 1347-1348, 1353
- Voltage Controlled Saw (VCSO) .....1348
- Voltage Controlled (VCO) .....1349-1351
- Voltage Controlled (VCXO), (VCTCXO) .....1302, 1317-1318, 1320, 1333, 1340, 1344, 1348

**P**

**Panel Meters** .....See Test Equipment

**Photocouplers** .....See Optoisolators

**Photo Detectors** .....See Optoelectronics

**Photodiodes** .....See Optoelectronics

**Phototransistors** .....See Optoelectronics

**Potentiometers**

- Angle Sensing/Positioning .....1858, 1885

Free shipping on orders over £50! All prices are in British pound sterling and include duties.

8 (UK091) [uk.digikey.com](http://uk.digikey.com) — FREEPHONE: 0-800-587-0991 • 0-800-904-7786 — FREEFAX: 0-800-587-0992 • 0-800-904-7783