

More Product Available at uk.digikey.com

Symbols

3M

- Adhesives
 - Tape See Tape
- Cable
 - Ribbon 43, 50-51, 152
- Cable Assemblies 37-38, 41-42
- D-Sub 37
- PCB 41-42
- Plug and Socket 38, 41
- Termination Jumpers 42
- Cable Splice Enclosures 339
- Connector Hardware 249
- Connectors
 - 0.1" 42-43, 153
 - 2mm 151-153
 - Mini-Clamp 153
 - Card Edge 38-39
 - Delta 41
 - D-Sub 37
 - IDC 42, 50
 - Intra-Connector™ 484
 - Intra-Switch™ 484
 - Memory
 - Compact Flash 469
 - DDR 469
 - microSD™ 468
 - SD™ 468
 - Secure Digital 469
 - MetPak™
 - 2FP 459
 - CP2 460
 - HSHM 460
 - miniSAS 459
 - PCB 41-42
 - Plug and Socket 38-40
 - Ribbon
 - Mini D 50-51
 - Shielded 51
 - SATA 51
 - Scotchlok™ 338-339
 - SCSI 459
 - Termination Jumpers 39
 - EMI Suppression
 - Absorber Pads 504
 - Headers 42-43, 151
 - Heat Shrink Tubing 2135
 - IC Sockets
 - DIP 502
 - PLCC Carrier 503
 - Type "A" LCC 503
 - ZIF 469, 501-502
 - ZIP DIP 501-502
 - IC Test Clips 503
 - Kits
 - Heat Shrink Tubing 2135, 2141
 - Insulated Terminals 338
 - Optical Enhancement Films 2282
 - Optoelectronics 2283
 - Touch Screens 2283
 - Privacy Filters 2282-2283
 - Shorting Jumpers 154
 - Tape
 - Electrical 504
 - Fabric 504
 - Foil Shielding 504
 - Terminal Connectors 337-338
 - Tools, Crimp 338

A

- Aavid Thermalloy**
 - Heat Sinks 1109-1111
 - BGA 1111
 - Thermal Compound 1109
- Abracon Corporation**
 - Crystals 1313-1315
 - Filters, SAW 1357
 - Oscillators 1315-1318, 1328
 - Programmable 1328
 - Resonators
 - Ceramic 1357
 - SAW 1357
- ADI** See Analog Devices, Inc.
- Advanced Photonix, Inc.**
 - Photo Diodes/Emitters 2227-2228
- Advanced Thermal Solutions, Inc.**
 - Heat Sinks
 - BGA 1114-1117
 - LED 1117
 - LGA 1117
 - Tools 1115
 - Thermal Management 1114
 - Kits 1114
- Airpax** See Sensata Technologies, Airpax

- AlfaMag Electronics, LLC**
 - Inductors 1437
- Allegro MicroSystems, Inc.**
 - Integrated Circuits
 - Hall Effect Sensors 953-955
 - Motor Drivers 955
 - Power Management 956
- All Sensors Corporation**
 - Pressure Sensors 2253
- Alpha & Omega Semiconductor, Inc.**
 - MOSFET/MOSFET Drivers 1298-1299
 - Power Management 1069-1070
 - Transient Voltage Suppressors (TVS) 1924
- Alpha Wire Company**
 - Tubing
 - Fabric 2134
 - Heat Shrink 2134
- Altera**
 - Cables/Programming Hardware 563
 - Development Kits and Tools 564-566
 - Evaluation Kits 564
 - Integrated Circuits/Semiconductors
 - CPLDs 561-563
 - FPGAs 557-561
- Altium**
 - Development/Starter Kits 556
 - Evaluation Boards and Kits 556
 - FPGA/CPLD Kits 556
- American Electrical, Inc.**
 - Circuit Breakers, DIN Rail Mount 1969
 - DIN Rail Mount 314
 - Disconnect Switches 2043
 - Accessories 2043
 - Interface Modules and Cables 314
 - Terminal Blocks
 - Accessories 313-314
 - DIN Rail Mount 313-314
 - Tools, Crimp 312
 - Wire Ferrules 312
- Ametherm**
 - Inrush Current Limiters 1934
 - Thermistors, NTC 2273
- Amphenol Commercial Products**
 - Connectors
 - D-Sub 277-278
 - Backshells 278
 - High Density 278
 - Infinity 479
 - Modular, Ethernet 277-278
 - SAS 479
 - SFP 479
 - USB 277
- Amphenol - Connex**
 - RF Adapters 402-405
 - RF Connectors
 - BNC 402
 - MCX/MMCX 404
 - N Type 404
 - SMA/SMB 402-403
 - TNC 405
 - Tools, Crimp 405
- Amphenol - Industrial**
 - Circular Connectors
 - 97 Series 362-364
 - Accessories 363-364
 - IP67 365
 - MS Series 360, 364
 - PT Series 359-361
 - RADSOK® 358
 - Waterproof 365
- Amphenol - PCD**
 - Connectors 284-285
 - IEEE 1394 285
 - Modular, Ethernet (RJ11) 284-285
 - Terminal Splices
 - DIN Rail Mounted 310-311
 - PCB Mounted 310-311
 - Pluggable 310-311
 - USB 285
- Amphenol - RF Division**
 - Adapters, RF Coaxial 409, 411
 - RF Connectors
 - AMC 407
 - BNC 408-409
 - N Type 409
 - SMA/SMB 406-407, 410
 - FAKRA (SMB) 406-407
 - QMA (SMA) 407
 - SMP 407
 - TNC 409
 - Twinaxial 409
 - UHF 411
 - Tools, Crimp 407, 411

- Amphenol - Tuchel Electronics**
 - Cable Assemblies
 - eco/mate™ 366
 - Connectors
 - Circular
 - 44 Series 368
 - C16 366
 - C091 367-368
 - eco/mate™ 366
 - Hand Tools 367-368
 - Rectangular, Heavy Duty 197
 - Smart Card 480
- AMP Tyco Electronics** See Tyco Electronics AMP
- Amulet Technologies LLC**
 - Graphic LCD Tool Kits 2286
- Amveco Magnetics**
 - Transformers
 - Current Sense 2257
 - Toroidal 2171
- Analog Devices, Inc.**
 - DSP Emulators/Programmers 696-698
 - ICs/Semiconductors 728
 - Amplifiers 708-714
 - Analog Computation Circuits 713
 - Analog/Digital Audio 713-714
 - ATE and Time Domain 714
 - Audio/Video 714
 - CCD 714
 - Clock Generation and Distribution 714
 - Data Communication 714
 - Data Conversion 714-720
 - Digital Potentiometers 720-721
 - Display and Video Converters 721
 - Evaluation Boards 722
 - Fiber Optics and Networks 722
 - Hardware Monitors and Thermal Management 722
 - Interface 722-724
 - Microcontrollers 698-699
 - MicroConverter® 698-699
 - Motion/Motor Control 724
 - Power Management 724-727
 - Sensor/Signal Conditioning 727-728
 - Specialized IC 728
 - Supervisory Circuits/Reset Generators 728
 - Switches 729-730
 - Waveform Generators 727
 - Isolators, Digital 2218-2219
 - RF/IF Products 504-507
 - DDCs 506
 - DDS 507
 - IF Receivers 506
 - Sensors, Accelerometers 2267
 - Evaluation Boards 2267
- Antenna**
 - Antennas 507
- APEM Components, Inc.**
 - Security Guards 2004
 - Switches
 - Emergency Stop 2035
 - Joysticks 2034
 - Keylock 2020, 2035
 - Pushbutton 2031, 2033-2035
 - Rocker 2020
 - Toggle 2010, 2020
- API Delevan**
 - Bead Cores 1421
 - Cable EMI Ferrite Cores 1421
 - EMI Suppression Cable Cores 1421
 - Ferrites, Flexible Material/Tubing 1421
 - Inductors
 - Air Core 1421
 - Coils 1413
 - Common Mode Choke 1420-1421
 - Filter 1413
 - Fixed 1413-1421
 - High Current 1413, 1416-1419
 - Kits 1414-1416, 1421
 - Power Choke 1417-1419
 - Shielded 1413-1419
- APM Hexseal**
 - Switch Seals 1998
- Aries Electronics, Inc.**
 - Adapters
 - DIP 498-499
 - IC Socket 498-499
 - Headers
 - Covers 497
 - DIP 497
 - IC Sockets
 - Adapter 498-499
 - Collet 497
 - Horizontal 497
 - Lock Eject DIP 498
 - Open Frame 497
 - PGA 498-499
 - Pin Line 498
 - PLCC 499
 - QFP 498

SUPPLIER INDEX

Free shipping on orders over £50! All prices are in British pound sterling and include duties.

uk.digikey.com — FREEPHONE: 0-800-587-0991 • 0-800-904-7786 — FREEFAX: 0-800-587-0992 • 0-800-904-7783

(UK091) 11