

More Product Available at [uk.digikey.com](http://uk.digikey.com)

Connectors

Beau

Barrier Blocks ..... 331

Terminal Blocks ..... 331

Blind Mate (BML) ..... 183-186

Board-to-Board ..... 186-187

Mezzanine ..... 186

SlimStack™ ..... 187

C-Grid® ..... 170-172

C-Grid III™ ..... 172-174

Crimp Terminals ..... 167-168, 170, 172, 334-336

Disk Drive ..... 191

DisplayPort® ..... 198

ETC

Crimp Terminals ..... 334-336

Wire Tap ..... 336

FFC/FPC ..... 76-78

GBIC ..... 477

HandyLink™ ..... 199

HDMI ..... 198

HSSDC2 ..... 477

IEEE 1386 (Mezzanine) ..... 187

IEEE 1394 (Firewire) ..... 62

Industrial Ethernet ..... 63

Infiniband™ ..... 477

iPass™ ..... 478

Memory

Compact Flash ..... 473

DDR DIMM ..... 472

DIMM ..... 472

ExpressCard™ ..... 472

Secure Digital ..... 473

SIMM ..... 472

SO DIMM ..... 472

TransFlash ..... 473

Metric

0.3mm ..... 76

0.4mm ..... 187

0.5mm ..... 76-77, 187

1.00mm ..... 77

1.25mm ..... 136-137

1.50mm Pico SPOX™ ..... 137

2.0mm Cable-to-Board ..... 150

2.0mm iGrid™ ..... 141

2.0mm MicroBlade™ ..... 141

2.0mm Milli-Grid™ ..... 139-140

2.0mm Sherlock™ ..... 138

2.5mm SPOX™ ..... 142

3.96mm SPOX™ ..... 142

MicroCross™ DVI ..... 198

Micro-Fit 3.0™ ..... 183-186

Mi II™ ..... 138

Mini-Fit BML™ ..... 190

Mini-Fit HCS™ ..... 191

Mini-Fit Jr.™ ..... 188-189, 191

Mini-Fit SMC™ ..... 191

Mini-Fit Sr.™ ..... 192

Modular ..... 288

MX150L ..... 370

PanelMate™ ..... 137

PCI Express ..... 472

Pico Clasp™ ..... 136

Power ..... 192-194, 199

.062" ..... 193

.084" ..... 193

.093" ..... 194

Power Edge™ ..... 445

RF

BNC ..... 431

MCX ..... 431

MMCX ..... 431

SMA ..... 431

Sabre™ ..... 192

SAE

0.050" Picoflex™ ..... 52

0.100" ..... 165, 169-174

0.156" ..... 169

SCSI ..... 477

See and Splice™ ..... 336

Serial ATA ..... 198

SFP (Small Frame Pluggable) ..... 478

SlimStack™ ..... 187

Switch Connection ..... 2068

Terminal Blocks ..... 332-333

Barrier Blocks ..... 332-333

Toy Car Battery ..... 170

USB ..... 62

VHDCI ..... 477

Waterproof ..... 335, 370

MX150L ..... 370

Perma-Seal ..... 335

XFP ..... 477

Flat Cable Jumpers ..... 53, 76, 78

Headers

0.100" (2.54mm) ..... 166

0.156" (3.96mm) ..... 167-168

C-Grid® ..... 164-165, 173-174

KK® Series ..... 164-165

Interface Modules ..... 333

Shunts/Jumpers ..... 142, 164-165

Tools

Crimp ..... 52, 137-138, 142, 167-168, 170, 172, 185-186, 190-194, 336

Insertion/Extraction ..... 52, 137, 167-168, 172, 185-186, 191-194

Transistor Sockets ..... 1119

**Multi-Tech Systems, Inc.**

Socket Modems ..... 530-531

**Murata Electronics**

Buzzers ..... 2154

Capacitors

Arrays ..... 1728

Ceramic, Trimmer ..... 1772-1773

High Voltage ..... 1727

Monolithic Ceramic Chip ..... 1725-1726, 1728, 1741-1745

Multilayer Ceramic Chip (MLCC) ..... 1728-1740

Safety ..... 1726

Tuning Tools ..... 1772-1773

Chokes

Wirewound ..... 1385

Coils/Inductors ..... 1381-1384

Film ..... 1381-1382

Monolithic ..... 1381-1382

Wirewound ..... 1383-1384

Connectors

Coaxial ..... 435

DC-DC Converters ..... 2193-2196

EMI Suppression

Arrays ..... 1465-1466

Ferrite Chips ..... 1465-1466

Filter Capacitor Type ..... 1466

Filters ..... 1466

LC Combined Chip ..... 1466

Filters

Bandpass ..... 531

Ceramic ..... 1361

Discriminator ..... 1361

SAW ..... 531

Potentiometers ..... 1855-1858

Angle Sensing/Positioning ..... 1858

Resonators, Ceramic ..... 1360

Sensors/Controllers

Position/Proximity ..... 1858

Thermistors ..... 1928-1929, 2271

Inrush Current Limiters ..... 1928

NTC ..... 1928

PTC ..... 1928-1929

Transformers, Balun ..... 531

**Murata Power Solutions, Inc.**

DC-DC Converters ..... 2183-2185

Inductors

Axial ..... 1377

Bobbin ..... 1377-1378

Chokes ..... 1378

Common Mode ..... 1378

Power ..... 1376

Radial ..... 1377

Toroidal ..... 1378

Panel Meters ..... 2297-2298

Digital ..... 2297-2298

**N**

**National Semiconductor**

A/D and D/A Converters ..... 1012

ICs/Semiconductors

A/D and D/A Converters ..... 1013

Data Communication ..... 1013

Interface Chips ..... 1013-1015

Linear ..... 1015-1043

PLL/Frequency Synthesizers ..... 512, 532

Telecommunications ..... 1043

UARTs ..... 1043

**NDK**

Crystals ..... 1352-1353

Oscillators ..... 1353

TCXO ..... 1353

**Ne arson, Inc.**

Antennas ..... 532

**NEC** ..... See CEL California Eastern Laboratories

**Nesscap**

Pseudocapacitor ..... 1512

Ultracapacitor ..... 1512

**NetBurner, Inc.**

Development Kits ..... 551

Microprocessor Modules ..... 551

**Newhaven Displays International, LLC**

Character Display Modules ..... 2289

Displays, Vacuum Fluorescent ..... 2288

Graphic Display Modules ..... 2289

TFT Displays ..... 2289

**Nichicon**

Capacitors

Aluminum Electrolytic ..... 1553-1572

Polymer ..... 1596

Tantalum Electrolytic ..... 1596-1598

**NJR Corporation**

Integrated Circuits

Amplifiers ..... 1071-1072

Drivers ..... 1072

Multiplexers ..... 1072

Power Management ..... 1072-1073

Specialized ..... 1073

Switches ..... 1073

**NKK Switches**

Keypads ..... 1997

Switches

Accessories ..... 2008-2009, 2011, 2045-2046

Splashproof Boots ..... 2008, 2011

DIP ..... 2075

Illuminated ..... 2009, 2044-2046

Keylock ..... 2053

Pushbutton ..... 2011, 2031, 2044-2046

Rocker ..... 2013-2014

Sealed ..... 2006, 2009

Slide ..... 2011

Tact ..... 2044

Tilt ..... 2223

Toggle ..... 2006-2009

Kit ..... 2007-2008

**NMB Technologies Corp.**

Fans/Blowers ..... 2163-2166

**NorComp**

Backshells, D-Sub ..... 271-273

Connectors

2mm ..... 97

DIN Rectangular ..... 484

D-Sub ..... 261-273

Adapters ..... 271

Gender Changers ..... 271

Shunts ..... 97

Tools

Crimp ..... 261, 266

Insertion/Extraction ..... 261, 266

**Numonyx**

Integrated Circuits/Semiconductors

Automotive Burst Mode ..... 742

Automotive Standard Boot Block ..... 740-742

Code and Data Storage ..... 740

Code Storage ..... 739

Industry Standard Boot Block ..... 740

Parameter and Data Storage ..... 740

Memory

Cards ..... 739

Embedded Flash ..... 737-738

Flash ..... 737

StrataFlash® ..... 738-739

**NVE Corporation**

GMR Sensor Evaluation Kit ..... 2280

Isolators, Digital and Analog ..... 2222

Sensors

Gear Tooth and Encoder ..... 2280

Magnetic ..... 2280

**NXP Semiconductors**

Development Tools and Kits ..... 537, 657

Emulators ..... 657

Evaluation Boards/Kits ..... 537, 657

Reader Modules ..... 537

Diacs ..... 1168

Diodes/Rectifiers ..... 1161-1166, 2141

ESD Protection ..... 1164

Kits ..... 1164, 2141

PIN (RF) ..... 1163-1164

Schottky ..... 1162-1163

Variable ..... 1163

Zener ..... 1165-1166

ICs/Semiconductors

Amplifiers ..... 538, 744

Clock Management ..... 744

Data Communication ..... 744-745

Data Conversion ..... 745

Data Transmission ..... 745-748

Digital Logic

74ABT ..... 748

74AHC ..... 748

74AHT ..... 748

74ALVC ..... 748

74ALVT ..... 748

74AUP ..... 749

74AVCH ..... 749

74AVCM ..... 749

74CBT ..... 749

74F ..... 755-756

74HC/HCT/HCU ..... 749-753

74LV/LVC ..... 753-755

74LVT ..... 755

4000 ..... 756

I/O Expanders ..... 756-757

Logic Translation ..... 757

Memory ..... 757

Free shipping on orders over £50! All prices are in British pound sterling and include duties.

18 (UK091) [uk.digikey.com](http://uk.digikey.com) — FREEPHONE: 0-800-587-0991 • 0-800-904-7786 — FREEFAX: 0-800-587-0992 • 0-800-904-7783