

More Product Available at uk.digikey.com

74S 867	TriQuint Semiconductor, Inc.	Tools 356
74SSQE 867	RF 549-550	Crimp 178-179, 182, 204-205, 207, 210, 212, 215-216, 219-221, 223-224, 226, 239, 247, 253-255, 258, 281, 342-344, 346-347, 353-356, 391, 397-398, 412
74SST 867-868	Amplifiers 549-550	Fiber Optic 298
4000 814-815	Filters 549-550	Insertion/Extraction 205, 207, 212, 215-216, 219-221, 224, 239, 247, 253-255, 258, 391, 397
Bus Switch 868	TT Electronics/Optek Technology	Modular Crimp 281
Bus Switch Products 837-842	LEDs	Tubing, Corrugated 394
Microgate Family 826-827	Arrays 2368-2369	Cable
TTL 868	Design Kit 2368	Solar (Photovoltaic) 197
TVC 868	High Brightness 2367, 2369	Connectors/Contacts
VMEH 868	InGaN 2368	0.8mm 244
Digital Radio 868	Lenses 2369	1.0mm 244
Digital Signal Processors 661-665	RGB (Red/Green/Blue) 2368	1.5mm 121
Evaluation Boards 919	Surface Mount 2368-2369	1.25mm 121
FIFO Memory 868-869	Optoisolators/Photocouplers 2209	2mm 122
Filters 869	Optocouplers 2209	2.5mm 245
Integrators 869	Photodiodes 299, 2235	Back Plane 457
Interface 869	Relays	Ballast 2292
I/O Expanders 869-871	Solid State 2123	Barrier Blocks 325
Linear Peripheral Drivers 871	Sensors	Board-to-Board 245
Microcontrollers 658-662	Fluid 2234	Circular 399
Multiplexers 872	Hall Effect 2238	Dynamic 234-237
Optical Sensors 872	Optical 2234	HDMI™ 464
Power Control Management Products 872-873	Tyco Electronics	Industrial Ethernet 282
Power Supply Products 873-917	Adapters	Interconnect Systems 233-237
Precision Ground Reference 917	Modular 282	LAN 282
Programmable Gate Arrays 917	RF 415	Light-N-Lok™ 2292
Real Time Clocks 917	AMP	MetPak™ 2-FB 456
RF Products 545	Cable	MiniSAS 475
Transceivers/Transmitters 545	Fiber Optic 296	Modular 282
Signal Controllers 917-918	Cable Assemblies	PCI 457
Specialized ICs 873	DIP 26	PCI Express 457
Temperature Sensors 918-919	D-Sub 27	QSFP 475
Timers 919	Pin and Socket 28-29	RF 413, 416
Texas Instruments/Plug-In Power Solutions	Connectors/Contacts 220, 230-231	Accessories 415
Integrated Circuits	0.050" (1.27mm) 240-243	Adapters 418
DC-DC Converters 2174-2182	0.100" (2.54mm) 222-226, 228, 230, 232	BNC 414-417
TI-RFid Systems	1mm 249	Decoupled 417
Antennas 547	2mm Ribbon 150	F 419
RFid	4.2mm 204	MCMX 418
Evaluation Kits 548	Backshells, D-Sub 241, 256-257	N Type 419
Modules 547	Board-to-Board, In-Line 2323	QSL 418
Readers 547-548	Card Edge 249, 449	SHV 420
Transponders 546-547	Champ® 240, 247-248	TNC 420
Toshiba America Electronic Components	Circular 387, 389-394, 397-399	UHF 419
Development Tools	Crimp Terminals 343-357, 395-397	RITS 233
Evaluation and Starter Kits 652	D-Sub 26-27, 250-258	SFP 474-475
RF 549	Eurocard 451-453, 455	Solar (Photovoltaic) 197
Fiber Optic	Fastons 347-353	Switch 2068
Transmitting/Receiving Modules 300	Fiber Optic 296-298	Terminal Blocks 326-329
Integrated Circuits	Flexi-Block 325	Eurostyle® 326-329
Darlington Sink Drivers 998-999	Hardware 247-248, 257, 397	PCB Mounted 326-329
Digital Logic 995-998	Hoods, D-Sub 256-257	USB 282
74AC/ACT 995-996	IDC 27-29, 175-178, 180-181, 225-226, 254	VITA 41/VITA 46 457
74HC 996	LEDs 2323	XFP 475
74LCX 996	Mate-N-Lok® 206-219	Z-pack, 2mm 456-457
74LVX 996-997	Medical 391	Corcom
74VHC 997	Metricite 204-205	Capacitors, Feed Through 1458
LMOS 997-998	Micro-D 252	Filters, Feed Through 1458
TC7W 998	Micror 464	Modular Jacks, Filtered 294
LED Drivers/DC-to-DC Converters 999	Miniature Rectangle (MR) 221	Power Entry Modules 1485-1486
Linear 999-1000	Modular 279-281	RF Line Filters 1486-1491
Motor Drivers/Controllers 999	M-Series 238-239	ELCON
LCDs, TFT Displays 2284	MT (.100") 222-223	Connectors/Contacts
Memory ICs	MTA (.100" and .156") 175-182	Backplane 454
Floppy Disk Cards 1107	MTE (.100") 225-226, 230-231	Board-to-Board 454
SRAM 1095	Parallel Interface 240-242, 247-248	Bus Bar 454
Microcontroller, Flash 652	Power 182	Card Edge 454
MOSFETs 1288	Rectangular DIN 451-453, 455	CROWN CLIP 454
Optoisolators 2215-2217	Retention Modules 249	CROWN EDGE 454
IREC 2217	RF 412	ICCON 454
Photovoltaic Coupler 2217	SCSI 240-241	Power 454
Rectifiers	Sealed 392-393	Rapid Lock 454
Schottky 1289	Softshell (.062" and .093") 219-220	Power 453
Switching 1289	Fiber Optic	Inductors, Drum Core 1380
Varactors 1289	Adapters 297	Knobs 1881
Relays, Solid State 2123	Attenuators 297	Labels
RF Transceivers/Receivers 549	Cable Assemblies 298	Solar (Photovoltaic) 197
Sensors, Illumination 2223	Connectors 297	Lighting, Connectors 2292
Transistors 1289	Tools 298	P&B
TPi (Test Products International)	Headers 35-36, 175-179, 181-182, 226-230	Circuit Breakers 1965-1968
Adapters, RF	Protected 35-36	Raychem
Kits 421	IC Sockets	ESD Products 1938
BNC Cables 421	BGA 483	Suppression, Arrays 1938
Coax Adapter Connector Kit 421	DIP 482	Fuses 1938-1939
DVI/HDMI Cables 421	Miniature Spring 481	Resettable 1936-1939
F (Television) Cables 421	PLCC 482	SMD 1936-1937, 1939
RF/IF 421	PQFP 483	Heat Shrink
Attenuators 421	SIP 483	Kits 2137
Triad Magnetics	Test 483	Terminals and Splices 2136
Inductors	LED, Connectors 2323	Tubing 2136-2137
Common Mode 2173	Lighting, Connectors 2323	Wraparound Repair Sleeves 2137
High Frequency 2173	Pin and Socket 29	PolyZen 1938
Rod Core 2173	Shunt 182	Power Distribution Switches 1935-1937
Switchmode 2173	Socket Assemblies, Mod. II and IV 232	Relays
Toroidal 2173	Terminal Blocks 325	Timer Delay 2301
Transformers 2172-2173	Terminals - Splices 341-357	Resettable Devices 1935-1937
Audio 2172	Terminators, SCSI 255	Surge Protectors, SiBar Thyristor 1937-1939
Current Sense 2173		Varistors 1938
Power 2172		2 Pro Overcurrent/Overvoltage Devices 1938
Switchmode 2173		

Free shipping on orders over £50! All prices are in British pound sterling and include duties.

22 (UK091) uk.digikey.com — FREEPHONE: 0-800-587-0991 • 0-800-904-7786 — FREEFAX: 0-800-587-0992 • 0-800-904-7783