



Socket Assemblies (Cont.)



No. of Con-tacts	Contact Finish	Length Inch (cm)	Rib-bon+ Cable	Digi-Key Part No.	Price Each	
					1	10
20	Gold	36 (91.44)	MC	H1AXH-2036M-ND	4.41	3.34
	Tin	36 (91.44)	MC	H1AXS-2036M-ND	4.41	3.34
	Gold	36 (91.44)	GR	H1AXH-2036G-ND	2.16	1.64
	Tin	36 (91.44)	GR	H1AXS-2036G-ND	2.16	1.64
24	Gold	36 (91.44)	MC	H1AXH-2436M-ND	5.58	4.24
	Tin	36 (91.44)	MC	H1AXS-2436M-ND	5.58	4.24
	Gold	36 (91.44)	GR	H1AXH-2436G-ND	2.39	1.81
	Tin	36 (91.44)	GR	H1AXS-2436G-ND	2.39	1.81
26	Gold	36 (91.44)	MC	H1AXH-2636M-ND	5.45	4.14
	Tin	36 (91.44)	MC	H1AXS-2636M-ND	5.45	4.14
	Gold	36 (91.44)	GR	H1AXH-2636G-ND	2.45	1.86
	Tin	36 (91.44)	GR	H1AXS-2636G-ND	2.45	1.86
30	Gold	36 (91.44)	MC	H1AXH-3036M-ND	7.16	5.43
	Tin	36 (91.44)	MC	H1AXS-3036M-ND	7.16	5.43
	Gold	36 (91.44)	GR	H1AXH-3036G-ND	3.09	2.35
	Tin	36 (91.44)	GR	H1AXS-3036G-ND	3.09	2.35
34	Gold	36 (91.44)	MC	H1AXH-3436M-ND	6.85	5.20
	Tin	36 (91.44)	MC	H1AXS-3436M-ND	6.85	5.20
	Gold	36 (91.44)	GR	H1AXH-3436G-ND	2.57	1.95
	Tin	36 (91.44)	GR	H1AXS-3436G-ND	2.57	1.95
40	Gold	36 (91.44)	MC	H1AXH-4036M-ND	8.05	6.11
	Tin	36 (91.44)	MC	H1AXS-4036M-ND	8.05	6.11
	Gold	36 (91.44)	GR	H1AXH-4036G-ND	3.38	2.57
	Tin	36 (91.44)	GR	H1AXS-4036G-ND	3.38	2.57
50	Gold	36 (91.44)	MC	H1AXH-5036M-ND	10.10	7.66
	Tin	36 (91.44)	MC	H1AXS-5036M-ND	10.10	7.66
	Gold	36 (91.44)	GR	H1AXH-5036G-ND	3.80	2.89
	Tin	36 (91.44)	GR	H1AXS-5036G-ND	3.80	2.89
60	Gold	36 (91.44)	MC	H1AXH-6036M-ND	12.91	9.79
	Tin	36 (91.44)	MC	H1AXS-6036M-ND	12.91	9.79
	Gold	36 (91.44)	GR	H1AXH-6036G-ND	5.73	4.35
	Tin	36 (91.44)	GR	H1AXS-6036G-ND	5.73	4.35
64	Gold	36 (91.44)	MC	H1AXH-6436M-ND	15.43	11.70
	Tin	36 (91.44)	MC	H1AXS-6436M-ND	15.43	11.70
	Gold	36 (91.44)	GR	H1AXH-6436G-ND	7.38	5.60
	Tin	36 (91.44)	GR	H1AXS-6436G-ND	7.38	5.60

Also available in the following configuration:
 H1BX□-□□□□-ND - Without polarizing key, With Strain Relief
 H1CX□-□□□□-ND - With polarizing key, Without Strain Relief
 H1DX□-□□□□-ND - With polarizing key, With Strain Relief
 Call for complete part number and pricing

Double Ended Socket

•MC=Multi-Color, GR=Gray



Without Polarizing Key without Strain Relief Shown

No. of Con-tacts	Contact Finish	Length Inch (cm)	Rib-bon+ Cable	Digi-Key Part No.	Price Each	
					1	10
10	Gold	6 (15.24)	MC	H3AAH-1006M-ND	1.82	1.38
	Tin	6 (15.24)	MC	H3AAS-1006M-ND	1.82	1.38
	Gold	6 (15.24)	GR	H3AAH-1006G-ND	1.61	1.23
	Tin	6 (15.24)	GR	H3AAS-1006G-ND	1.61	1.23
	Gold	18 (45.72)	MC	H3AAH-1018M-ND	3.27	2.48
	Tin	18 (45.72)	MC	H3AAS-1018M-ND	3.27	2.48
	Gold	18 (45.72)	GR	H3AAH-1018G-ND	2.07	1.57
	Tin	18 (45.72)	GR	H3AAS-1018G-ND	2.07	1.57
	Gold	36 (91.44)	MC	H3AAH-1036M-ND	3.27	2.48
	Tin	36 (91.44)	MC	H3AAS-1036M-ND	3.27	2.48
	Gold	36 (91.44)	GR	H3AAH-1036G-ND	2.07	1.57
	Tin	36 (91.44)	GR	H3AAS-1036G-ND	2.07	1.57
14	Gold	6 (15.24)	MC	H3AAH-1406M-ND	2.26	1.71
	Tin	6 (15.24)	MC	H3AAS-1406M-ND	2.26	1.71
	Gold	6 (15.24)	GR	H3AAH-1406G-ND	1.95	1.48
	Tin	6 (15.24)	GR	H3AAS-1406G-ND	1.95	1.48
	Gold	18 (45.72)	MC	H3AAH-1418M-ND	4.44	3.37
	Tin	18 (45.72)	MC	H3AAS-1418M-ND	4.44	3.37
	Gold	18 (45.72)	GR	H3AAH-1418G-ND	2.59	1.97
	Tin	18 (45.72)	GR	H3AAS-1418G-ND	2.59	1.97
	Gold	36 (91.44)	MC	H3AAH-1436M-ND	4.44	3.37
	Tin	36 (91.44)	MC	H3AAS-1436M-ND	4.44	3.37
	Gold	36 (91.44)	GR	H3AAH-1436G-ND	2.59	1.97
	Tin	36 (91.44)	GR	H3AAS-1436G-ND	2.59	1.97
16	Gold	6 (15.24)	MC	H3AAH-1606M-ND	2.29	1.74
	Tin	6 (15.24)	MC	H3AAS-1606M-ND	2.29	1.74
	Gold	6 (15.24)	GR	H3AAH-1606G-ND	1.97	1.49
	Tin	6 (15.24)	GR	H3AAS-1606G-ND	1.97	1.49
	Gold	18 (45.72)	MC	H3AAH-1618M-ND	4.61	3.50
	Tin	18 (45.72)	MC	H3AAS-1618M-ND	4.61	3.50
	Gold	18 (45.72)	GR	H3AAH-1618G-ND	2.70	2.05
	Tin	18 (45.72)	GR	H3AAS-1618G-ND	2.70	2.05
	Gold	36 (91.44)	MC	H3AAH-1636M-ND	4.61	3.50
	Tin	36 (91.44)	MC	H3AAS-1636M-ND	4.61	3.50
	Gold	36 (91.44)	GR	H3AAH-1636G-ND	2.70	2.05
	Tin	36 (91.44)	GR	H3AAS-1636G-ND	2.70	2.05
20	Gold	6 (15.24)	MC	H3AAH-2006M-ND	2.40	1.82
	Tin	6 (15.24)	MC	H3AAS-2006M-ND	2.40	1.82
	Gold	6 (15.24)	GR	H3AAH-2006G-ND	2.03	1.54
	Tin	6 (15.24)	GR	H3AAS-2006G-ND	2.03	1.54
	Gold	18 (45.72)	MC	H3AAH-2018M-ND	5.31	4.03
	Tin	18 (45.72)	MC	H3AAS-2018M-ND	5.31	4.03
	Gold	18 (45.72)	GR	H3AAH-2018G-ND	3.06	2.33
	Tin	18 (45.72)	GR	H3AAS-2018G-ND	3.06	2.33

No. of Con-tacts	Contact Finish	Length Inch (cm)	Rib-bon+ Cable	Digi-Key Part No.	Price Each	
					1	10
20	Gold	36 (91.44)	MC	H3AAH-2036M-ND	5.31	4.03
	Tin	36 (91.44)	MC	H3AAS-2036M-ND	5.31	4.03
	Gold	36 (91.44)	GR	H3AAH-2036G-ND	3.06	2.33
	Tin	36 (91.44)	GR	H3AAS-2036G-ND	3.06	2.33
24	Gold	6 (15.24)	MC	H3AAH-2406M-ND	3.16	2.40
	Tin	6 (15.24)	MC	H3AAS-2406M-ND	3.16	2.40
	Gold	6 (15.24)	GR	H3AAH-2406G-ND	2.63	2.00
	Tin	6 (15.24)	GR	H3AAS-2406G-ND	2.63	2.00
	Gold	18 (45.72)	MC	H3AAH-2418M-ND	6.80	5.16
	Tin	18 (45.72)	MC	H3AAS-2418M-ND	6.80	5.16
	Gold	18 (45.72)	GR	H3AAH-2418G-ND	3.60	2.74
	Tin	18 (45.72)	GR	H3AAS-2418G-ND	3.60	2.74
26	Gold	36 (91.44)	MC	H3AAH-2436M-ND	6.80	5.16
	Tin	36 (91.44)	MC	H3AAS-2436M-ND	6.80	5.16
	Gold	36 (91.44)	GR	H3AAH-2436G-ND	3.60	2.74
	Tin	36 (91.44)	GR	H3AAS-2436G-ND	3.60	2.74
26	Gold	6 (15.24)	MC	H3AAH-2606M-ND	2.58	1.96
	Tin	6 (15.24)	MC	H3AAS-2606M-ND	2.58	1.96
	Gold	6 (15.24)	GR	H3AAH-2606G-ND	2.08	1.58
	Tin	6 (15.24)	GR	H3AAS-2606G-ND	2.08	1.58
26	Gold	18 (45.72)	MC	H3AAH-2618M-ND	6.36	4.83
	Tin	18 (45.72)	MC	H3AAS-2618M-ND	6.36	4.83
	Gold	18 (45.72)	GR	H3AAH-2618G-ND	3.35	2.55
	Tin	18 (45.72)	GR	H3AAS-2618G-ND	3.35	2.55
26	Gold	36 (91.44)	MC	H3AAH-2636M-ND	6.36	4.83
	Tin	36 (91.44)	MC	H3AAS-2636M-ND	6.36	4.83
	Gold	36 (91.44)	GR	H3AAH-2636G-ND	3.35	2.55
	Tin	36 (91.44)	GR	H3AAS-2636G-ND	3.35	2.55
30	Gold	6 (15.24)	MC	H3AAH-3006M-ND	3.42	2.60
	Tin	6 (15.24)	MC	H3AAS-3006M-ND	3.42	2.60
	Gold	6 (15.24)	GR	H3AAH-3006G-ND	2.74	2.08
	Tin	6 (15.24)	GR	H3AAS-3006G-ND	2.74	2.08
	Gold	18 (45.72)	MC	H3AAH-3018M-ND	8.37	6.35
	Tin	18 (45.72)	MC	H3AAS-3018M-ND	8.37	6.35
	Gold	18 (45.72)	GR	H3AAH-3018G-ND	4.31	3.27
	Tin	18 (45.72)	GR	H3AAS-3018G-ND	4.31	3.27
	Gold	36 (91.44)	MC	H3AAH-3036M-ND	8.37	6.35
	Tin	36 (91.44)	MC	H3AAS-3036M-ND	8.37	6.35
	Gold	36 (91.44)	GR	H3AAH-3036G-ND	4.31	3.27
	Tin	36 (91.44)	GR	H3AAS-3036G-ND	4.31	3.27
34	Gold	6 (15.24)	MC	H3AAH-3406M-ND	2.81	2.13
	Tin	6 (15.24)	MC	H3AAS-3406M-ND	2.81	2.13
	Gold	6 (15.24)	GR	H3AAH-3406G-ND	2.10	1.59
	Tin	6 (15.24)	GR	H3AAS-3406G-ND	2.10	1.59
	Gold	18 (45.72)	MC	H3AAH-3418M-ND	7.76	5.89
	Tin	18 (45.72)	MC	H3AAS-3418M-ND	7.76	5.89
	Gold	18 (45.72)	GR	H3AAH-3418G-ND	3.48	2.64
	Tin	18 (45.72)	GR	H3AAS-3418G-ND	3.48	2.64
	Gold	36 (91.44)	MC	H3AAH-3436M-ND	7.76	5.89
	Tin	36 (91.44)	MC	H3AAS-3436M-ND	7.76	5.89
	Gold	36 (91.44)	GR	H3AAH-3436G-ND	3.48	2.64
	Tin	36 (91.44)	GR	H3AAS-3436G-ND	3.48	2.64
40	Gold	6 (15.24)	MC	H3AAH-4006M-ND	3.29	2.50
	Tin	6 (15.24)	MC	H3AAS-4006M-ND	3.29	2.50
	Gold	6 (15.24)	GR	H3AAH-4006G-ND	2.51	1.91
	Tin	6 (15.24)	GR	H3AAS-4006G-ND	2.51	1.91
	Gold	18 (45.72)	MC	H3AAH-4018M-ND	9.11	6.91
	Tin	18 (45.72)	MC	H3AAS-4018M-ND	9.11	6.91
	Gold	18 (45.72)	GR	H3AAH-4018G-ND	4.44	3.37
	Tin	18 (45.72)	GR	H3AAS-4018G-ND	4.44	3.37
	Gold	36 (91.44)	MC	H3AAH-4036M-ND	9.11	6.91
	Tin	36 (91.44)	MC	H3AAS-4036M-ND	9.11	6.91
	Gold	36 (91.44)	GR	H3AAH-4036G-ND	4.44	3.37
	Tin	36 (91.44)	GR	H3AAS-4036G-ND	4.44	3.37
50	Gold	6 (15.24)	MC	H3AAH-5006M-ND	4.18	3.18
	Tin	6 (15.24)	MC	H3AAS-5006M-ND	4.18	3.18
	Gold	6 (15.24)	GR	H3AAH-5006G-ND	3.14	2.38
	Tin	6 (15.24)	GR	H3AAS-5006G-ND	3.14	2.38
	Gold	18 (45.72)	MC	H3AAH-5018M-ND	11.46	8.69
	Tin	18 (45.72)	MC	H3AAS-5018M-ND	11.46	8.69
	Gold	18 (45.72)	GR	H3AAH-5018G-ND	5.17	3.92
	Tin	18 (45.72)	GR	H3AAS-5018G-ND	5.17	3.92
	Gold	36 (91.44)	MC	H3AAH-5036M-ND	11.46	8.69
	Tin	36 (91.44)	MC	H3AAS-5036M-ND	11.46	8.69
	Gold	36 (91.44)	GR	H3AAH-5036G-ND	5.17	3.92