

ASSMANN Computer Cable Assemblies

A





















 <p>Fig. 1 — Parallel Extension</p>	 <p>Fig. 2 — Parallel Printer (Snap Hood)</p>	 <p>Fig. 3 — Parallel Printer (Molded Hood)</p>	 <p>Fig. 4 — Right Angle Parallel Printer</p>
 <p>Fig. 5 — Serial Printer (Snap Hoods)</p>	 <p>Fig. 6 — IEEE 1284 Bi-Directional Printer</p>	 <p>Fig. 7 — IEEE 1284 Bi-Directional Connection</p>	 <p>Fig. 8 — IEEE 1284 Bi-Directional Extension</p>
 <p>Fig. 9 — Connection Cable, 25-Pin Interface Serial/Parallel</p>	 <p>Fig. 10 — 25-Pin Interface Extension</p>	 <p>Fig. 11 — 9-Pin Interface Extension</p>	 <p>Fig. 12 — VGA Monitor Extension</p>
 <p>Fig. 13 — Premium VGA Monitor Extension</p>	 <p>Fig. 14 — PC/XT/AT Keyboard Extension</p>	 <p>Fig. 15 — PS/2 Keyboard Extension - Spiral</p>	 <p>Fig. 16 — PS/2 Keyboard Extension - Straight</p>
 <p>Fig. 17 — PS/2 Keyboard Cable - Straight</p>	 <p>Fig. 18 — IBM Modem/Adapter</p> <p>AE1382-ND & AE9877-ND : 1-8, 2-3, 3-2, 4-20, 5-7, 6-6, 7-4, 8-5, 9-22, shell-shell AE9878-ND & AE1383-ND: 1-8, 2-2, 3-3, 4-6, 5-7, 6-20, 7-5, 8-4, 9-22, shell-shell</p>	 <p>Fig. 19 — Null Modem Cross-Over Cable</p> <p>AE9879-ND & AE9880-ND: 1-4, 2-3, 3-2, 4-1, 5-5, 7-8, 8-7, 9-9, shell-shell</p>	 <p>Fig. 20 — Null Modem Serial Cable</p> <p>AE1035-ND & AE1384-ND: 1-1; 2-3; 3-2; 4-5; 5-4; 7-7; 8-20; 15, 17-8, 24-15 AE1385-ND: 2-15, 3-13, 4-12, 5-10, 6-11, 10-5, 11-6, 12-4, 13-3, 15-2, 25-25 AE1386-ND: 1-1; 2-3, 3-2, 4-5, 5-4, (6+8)-20, 7-7, 20-(6+8).</p>

Fig.	Length Feet (Meters)	Lines	Description	Digi-Key Part No.	1	Price Each 10	25	Assmann Part No.
Molded Extension for 36-Pin Centronics Interfaces								
1	6.56 (2) 9.84 (3)	36	2x Centronics 36-Pin Male to Male	AE1362-ND◆	10.83	9.53	8.54	AK138-2-R
				AE1363-ND◆	14.78	12.99	11.65	AK426-3-R
	6.56 (2) 9.84 (3)	36	2x Centronics 36-Pin Male to Female	AE1004-ND	8.39	7.37	6.61	AK140-2
				AE1364-ND◆	11.38	10.01	8.97	AK140-2-R
				AE1365-ND◆	13.06	11.48	10.29	AK430-3-R
Parallel Printer Cable, IBM PC and Compatibles								
2	5.90 (1.8) 9.84 (3) 22.96 (7)	25	D-Sub 25-Pin Male to Centronics 36-Pin Male, Snap-Hoods	AE1366-ND◆	7.10	6.24	5.60	AK101-1.8-R
				AE1367-ND◆	9.02	7.93	7.11	AK102-3-R
				AE9853-ND◆	11.75	10.33	9.26	AK104-7-R
3	6.56 (2) 9.84 (3) 22.96 (7)	25	D-Sub 25-Pin Male to Centronics 36-Pin Male, Molded Hoods	AE9858-ND◆	6.78	5.96	5.35	AK108-2-R
				AE1368-ND◆	6.64	5.84	5.24	AK127-3-R
				AE9859-ND◆	10.54	9.27	8.31	AK159-7-R
4	6.56 (2)	25	D-Sub 25-Pin Male to Right Angle Centronics 36-Pin Male	AE9860-ND◆	7.94	6.98	6.26	AK525-2-R
	6.56 (2)	25	D-Sub 25-Pin Male to Left Angle Centronics 36-Pin Male	AE1369-ND◆	7.93	6.97	6.25	AK525-2L-R
Serial Printer Cable, IBM PC and Compatibles — RoHS Compliant								
5	9.84 (3)	8	D-Sub 9-Pin Female to D-Sub 25-Pin Male, Snap-Hoods	AE1370-ND	5.42	4.76	4.27	AK150-3-R
IEEE 1284 Bi-Directional Cable - Molded Hoods — RoHS Compliant								
6	5.90 (1.8) 9.84 (3) 16.40 (5)	25	D-Sub 25-Pin Male to Centronics 36-Pin Male, Printer	AE1371-ND	11.72	10.30	9.24	AK711-1.8-R
				AE1372-ND	16.41	14.43	12.93	AK712-3-R
				AE1373-ND	22.95	20.17	18.09	AK713-5-R
7	5.90 (1.8) 9.84 (3) 16.40 (5)	25	D-Sub 25-Pin Male to D-Sub 25-Pin Female, Connection	AE9861-ND	12.47	10.96	9.82	AK733-1.8-R
				AE1374-ND	17.54	15.42	13.82	AK734-3-R
				AE1375-ND	22.95	20.17	18.09	AK735-5-R
8	5.90 (1.8) 9.84 (3) 16.40 (5)	25	D-Sub 25-Pin Male to D-Sub 25-Pin Male, Extension	AE9862-ND	13.30	11.69	10.48	AK736-1.8-R
				AE1376-ND	17.54	15.42	13.82	AK737-3-R
				AE1377-ND	22.95	20.17	18.09	AK738-5-R
Snap-Hood Connection for 25-Pin Interface — RoHS Compliant								
9	6.56 (2)	25	D-Sub 25-Pin Male to D-Sub 25-Pin Male, Snap-Hoods	AE9863-ND	5.52	4.85	4.35	AK401-2-R
Molded Extension for 25-Pin Interfaces								
10	6.56 (2) 6.56 (2) 9.84 (3)	25	2x D-Sub 25-Pin Male to Male	AE1010-ND	5.03	4.43	3.97	AK137-2
				AE1378-ND◆	7.27	6.39	5.73	AK137-2-R
				AE9864-ND◆	9.73	8.55	7.67	AK162-3-R
	6.56 (2) 9.84 (3)	25	2x D-Sub 25-Pin Male to Female	AE9865-ND◆	8.31	7.31	6.55	AK135-2-R
				AE9866-ND◆	8.01	7.04	6.32	AK166-3-R
	6.56 (2) 9.84 (3)	25	2x D-Sub 25-Pin Female to Female	AE9867-ND◆	7.00	6.15	5.52	AK133-2-R
				AE9868-ND◆	9.39	8.26	7.40	AK170-3-R
Molded Extension for 9-Pin Interfaces — RoHS Compliant								
11	6.56 (2) 9.84 (3)	9	2x D-Sub 9-Pin Male to Male	AE9869-ND	5.35	4.71	4.22	AK129-2-R
				AE9870-ND	5.92	5.20	4.67	AK174-3-R

◆ RoHS Compliant

(Continued)

Free shipping on orders over £50! All prices are in British pound sterling and include duties.

54 (UK091)

uk.digikey.com — FREEPHONE: 0-800-587-0991 • 0-800-904-7786 — FREEFAX: 0-800-587-0992 • 0-800-904-7783