

**FCI** 1.00 mm (0.039") FFC-FPC Connectors (Cont.)



**A**

Fig.	No. of Positions	Dimension - Inch (mm)		Digi-Key Part No.	Cut Tape Pricing			Digi-Key Part No.	Tape and Reel		FCI Part No.	
		A	B		1	25	100		Qty.	Pricing		
1	20	1.031 (26.20)	0.835 (21.20)	609-1949-ND†	.74	9.71	32.80	—	—	—	SLW20S-1C7LF	
	22	1.110 (28.20)	0.913 (23.20)	609-1951-ND†	.57	7.10	23.08	—	—	—	SLW22S-1C7LF	
	24	1.189 (30.20)	0.992 (25.20)	609-1953-ND†	1.57	15.67	53.71	—	—	—	SLW24S-1C7LF	
	26	1.268 (32.20)	1.071 (27.20)	609-1955-ND†	.63	7.41	24.10	—	—	—	SLW26S-1C7LF	
	28	1.346 (34.20)	1.150 (29.20)	609-1957-ND†	.46	5.79	18.51	—	—	—	SLW28S-1C7LF	
	30	1.425 (36.20)	1.228 (31.20)	609-1959-ND†	.80	11.01	37.03	—	—	—	SLW30S-1C7LF	
<b>HLW Series — Top Entry PC Mount LIF</b>												
2	4	0.260 (6.60)	0.118 (3.00)	609-1815-ND†	.17	1.84	5.68	—	—	—	HLW4S-2C7LF	
	5	0.300 (7.60)	0.157 (4.00)	609-1817-ND†	.18	1.97	6.10	—	—	—	HLW5S-2C7LF	
	6	0.339 (8.60)	0.197 (5.00)	609-1819-ND†	.19	2.04	6.32	—	—	—	HLW6S-2C7LF	
	8	0.417 (10.60)	0.276 (7.00)	609-1821-ND†	.22	2.39	7.31	—	—	—	HLW8S-2C7LF	
	10	0.496 (12.60)	0.354 (9.00)	609-1823-ND†	.20	2.11	6.53	—	—	—	HLW10S-2C7LF	
	12	0.575 (14.60)	0.433 (11.00)	609-1825-ND†	.33	3.99	12.99	—	—	—	HLW12S-2C7LF	
	14	0.654 (16.60)	0.512 (13.00)	609-1827-ND†	.21	2.45	7.51	—	—	—	HLW14S-2C7LF	
	15	0.693 (17.60)	0.551 (14.00)	609-1829-ND†	.25	2.86	9.20	—	—	—	HLW15S-2C7LF	
	16	0.732 (18.60)	0.591 (15.00)	609-1831-ND†	.25	2.93	9.39	—	—	—	HLW16S-2C7LF	
	18	0.811 (20.60)	0.670 (17.00)	609-1833-ND†	.27	3.11	9.79	—	—	—	HLW18S-2C7LF	
	20	0.890 (22.60)	0.748 (19.00)	609-1835-ND†	.28	3.18	9.98	—	—	—	HLW20S-2C7LF	
	22	0.969 (24.60)	0.827 (21.00)	609-1837-ND†	.28	3.30	10.38	—	—	—	HLW22S-2C7LF	
	24	1.047 (26.60)	0.906 (23.00)	609-1839-ND†	.28	3.37	10.59	—	—	—	HLW24S-2C7LF	
	26	1.126 (28.60)	0.984 (25.00)	609-1841-ND†	.30	3.56	11.39	—	—	—	HLW26S-2C7LF	
	28	1.205 (30.60)	1.063 (27.00)	609-1843-ND†	.30	3.68	11.79	—	—	—	HLW28S-2C7LF	
	30	1.283 (32.60)	1.142 (29.00)	609-1845-ND†	.30	3.68	11.79	—	—	—	HLW30S-2C7LF	
	<b>SLW Series — Side Entry PC Mount ZIF</b>											
	3	4	0.402 (10.20)	0.205 (5.20)	609-1928-ND†	.38	4.43	14.30	—	—	—	SLW4R-1C7LF
5		0.441 (11.20)	0.244 (6.20)	609-1930-ND†	.30	3.56	11.39	—	—	—	SLW5R-1C7LF	
6		0.480 (12.20)	0.283 (7.20)	609-1932-ND†	.30	3.56	11.39	—	—	—	SLW6R-1C7LF	
8		0.559 (14.20)	0.362 (9.20)	609-1934-ND†	.40	4.88	15.61	—	—	—	SLW8R-1C7LF	
10		0.638 (16.20)	0.441 (11.20)	609-1936-ND†	.44	5.41	17.31	—	—	—	SLW10R-1C7LF	
12		0.717 (18.20)	0.520 (13.20)	609-1938-ND†	.87	11.95	40.18	—	—	—	SLW12R-1C7LF	
14		0.795 (20.20)	0.598 (15.20)	609-1940-ND†	.60	7.31	24.80	—	—	—	SLW14R-1C7LF	
15		0.835 (21.20)	0.638 (16.20)	609-1942-ND†	.52	6.19	20.62	—	—	—	SLW15R-1C7LF	
16		0.874 (22.20)	0.677 (17.20)	609-1944-ND†	.54	6.55	21.82	—	—	—	SLW16R-1C7LF	
18		0.953 (24.20)	0.756 (19.20)	609-1946-ND†	.60	7.39	25.07	—	—	—	SLW18R-1C7LF	
20		1.031 (26.20)	0.835 (21.20)	609-1948-ND†	.57	7.09	23.04	—	—	—	SLW20R-1C7LF	
22		1.110 (28.20)	0.913 (23.20)	609-1950-ND†	.61	7.72	25.10	—	—	—	SLW22R-1C7LF	
24		1.189 (30.20)	0.992 (25.20)	609-1952-ND†	.62	7.57	25.68	—	—	—	SLW24R-1C7LF	
26		1.268 (32.20)	1.071 (27.20)	609-1954-ND†	.63	7.94	26.91	—	—	—	SLW26R-1C7LF	
28		1.346 (34.20)	1.150 (29.20)	609-1956-ND†	.50	5.99	19.97	—	—	—	SLW28R-1C7LF	
30		1.425 (36.20)	1.228 (31.20)	609-1958-ND†	.76	9.94	34.33	—	—	—	SLW30R-1C7LF	
<b>HLW Series — Side Entry PC Mount LIF</b>												
4		4	0.260 (6.60)	0.118 (3.00)	609-1814-ND†	.15	1.65	4.99	—	—	—	HLW4R-2C7LF
	5	0.300 (7.60)	0.157 (4.00)	609-1816-ND†	.18	1.96	5.89	—	—	—	HLW5R-2C7LF	
	6	0.339 (8.60)	0.197 (5.00)	609-1818-ND†	.18	1.97	6.10	—	—	—	HLW6R-2C7LF	
	8	0.417 (10.60)	0.276 (7.00)	609-1820-ND†	.20	2.18	6.97	—	—	—	HLW8R-2C7LF	
	10	0.496 (12.60)	0.354 (9.00)	609-1822-ND†	.22	2.11	6.53	—	—	—	HLW10R-2C7LF	
	12	0.575 (14.60)	0.433 (11.00)	609-1824-ND†	.22	2.35	7.73	—	—	—	HLW12R-2C7LF	
	14	0.654 (16.60)	0.512 (13.00)	609-1826-ND†	.23	2.54	8.17	—	—	—	HLW14R-2C7LF	
	15	0.693 (17.60)	0.551 (14.00)	609-1828-ND†	.41	5.09	16.28	—	—	—	HLW15R-2C7LF	
	16	0.732 (18.60)	0.591 (15.00)	609-1830-ND†	.25	2.80	8.99	—	—	—	HLW16R-2C7LF	
	18	0.811 (20.60)	0.670 (17.00)	609-1832-ND†	.25	2.93	9.39	—	—	—	HLW18R-2C7LF	
	20	0.890 (22.60)	0.748 (19.00)	609-1834-ND†	.27	3.11	9.79	—	—	—	HLW20R-2C7LF	
	22	0.969 (24.60)	0.827 (21.00)	609-1836-ND†	.28	3.25	10.19	—	—	—	HLW22R-2C7LF	
	24	1.047 (26.60)	0.906 (23.00)	609-1838-ND†	.28	3.30	10.38	—	—	—	HLW24R-2C7LF	
	26	1.126 (28.60)	0.984 (25.00)	609-1840-ND†	.30	3.50	10.99	—	—	—	HLW26R-2C7LF	
	28	1.205 (30.60)	1.063 (27.00)	609-1842-ND†	.30	3.56	11.39	—	—	—	HLW28R-2C7LF	
	30	1.283 (32.60)	1.142 (29.00)	609-1844-ND†	.30	3.62	11.58	—	—	—	HLW30R-2C7LF	
	<b>HFW Series — Top Entry SMT Non-ZIF</b>											
	5	4	0.276 (7.00)	0.118 (3.00)	609-1105-1-ND	.30	3.81	12.32	609-1105-2-ND	1,000	96.79	HFW4S-2STE1LF
5		0.315 (8.00)	0.157 (4.00)	609-1106-1-ND	.51	6.39	20.44	609-1106-2-ND	1,000	168.66	HFW5S-2STE1LF	
6		0.354 (9.00)	0.197 (5.00)	609-1107-1-ND	.30	3.81	12.32	609-1107-2-ND	1,000	123.19	HFW6S-2STE1LF	
7		0.394 (10.00)	0.236 (6.00)	609-1108-1-ND	.42	5.13	16.42	609-1108-2-ND	1,000	133.84	HFW7S-2STE1LF	
9		0.472 (12.00)	0.315 (8.00)	609-1110-1-ND	.28	3.42	10.95	609-1110-2-ND	1,000	89.23	HFW9S-2STE1LF	
10		0.512 (13.00)	0.354 (9.00)	609-1111-1-ND	.57	7.25	23.57	609-1111-2-ND	1,000	193.41	HFW10S-2STE1LF	
11		0.551 (14.00)	0.394 (10.00)	609-1112-1-ND	.49	6.05	19.34	609-1112-2-ND	1,000	136.44	HFW11S-2STE1LF	
12		0.591 (15.00)	0.433 (11.00)	609-1113-1-ND	.60	7.38	25.02	609-1113-2-ND	1,000	205.25	HFW12S-2STE1LF	
13		0.630 (16.00)	0.472 (12.00)	609-1114-1-ND	.44	5.38	17.21	609-1114-2-ND	1,000	140.23	HFW13S-2STE1LF	
14		0.670 (17.00)	0.512 (13.00)	609-1115-1-ND	.62	7.80	24.97	609-1115-2-ND	1,000	203.54	HFW14S-2STE1LF	
16		0.748 (19.00)	0.591 (15.00)	609-1117-1-ND	.73	8.76	29.21	609-1117-2-ND	2,000	238.10/M	HFW16S-2STE1LF	
18		0.827 (21.00)	0.670 (17.00)	609-1119-1-ND	.65	8.07	27.36	609-1119-2-ND	1,000	224.54	HFW18S-2STE1LF	
19		0.866 (22.00)	0.709 (18.00)	609-1120-1-ND	.50	6.11	20.34	609-1120-2-ND	1,000	165.79	HFW19S-2STE1LF	
23		1.024 (26.00)	0.866 (22.00)	609-1124-1-ND	.61	7.65	24.50	609-1124-2-ND	1,000	184.96	HFW23S-2STE1LF	
24		1.063 (27.00)	0.906 (23.00)	609-1125-1-ND	.57	7.04	23.46	609-1125-2-ND	1,000	187.71	HFW24S-2STE1LF	
26		1.142 (29.00)	0.984 (25.00)	609-1127-1-ND	.69	8.61	27.99	609-1127-2-ND	1,000	229.65	HFW26S-2STE1LF	
27		1.181 (30.00)	1.024 (26.00)	609-1128-1-ND	.65	8.07	26.23	609-1128-2-ND	1,000	215.24	HFW27S-2STE1LF	
28		1.220 (31.00)	1.063 (27.00)	609-1129-1-ND	.76	10.35	34.81	609-1129-2-ND	1,000	301.09	HFW28S-2STE1LF	
29		1.260 (32.00)	1.102 (28.00)	609-1130-1-ND	.71	9.01	29.29	609-1130-2-ND	1,000	231.62	HFW29S-2STE1LF	
<b>SFW Series — Top Entry SMT ZIF (Without Mounting Plate)</b>												
6		4	0.409 (10.40)	0.118 (3.00)	609-1132-1-ND	.68	8.58	27.89	609-1132-2-ND	1,000	228.84	SFW4S-2STE1LF
		5	0.449 (11.40)	0.157 (4.00)	609-1134-1-ND	.52	6.57	21.35	609-1134-2-ND	1,000	220.01	SFW5S-2STE1LF
		6	0.488 (12.40)	0.197 (5.00)	609-1136-1-ND	.68	8.36	28.37	609-1136-2-ND	1,000	232.78	SFW6S-2STE1LF
		8	0.567 (14.40)	0.276 (7.00)	609-1139-1-ND	.73	9.18	29.82	609-1139-2-ND	1,000	244.63	SFW8S-2STE1LF

† Bulk

(Continued)

Digi-Reel® Most SMT cutdown parts are available on a Digi-Reel®. For Digi-Reel part number, change 1-ND to 6-ND or CT-ND to DKR-ND. See Digi-Key® Services on page 2 for additional information.

**Free shipping on orders over £50! All prices are in British pound sterling and include duties.**

74 (UK091)

uk.digikey.com — FREEPHONE: 0-800-587-0991 • 0-800-904-7786 — FREEFAX: 0-800-587-0992 • 0-800-904-7783