

TEXAS INSTRUMENTS DigiKey Reel (Cont.) POWER SUPPLY PRODUCTS RoHS Compliant Parts Available					
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*	
				1	25 100
DCR011203P	DCR011203P-ND	DC/DC Converter, 12V to 3V	18-Dip	9.07	7.63 7.01
DCR011203U	296-9452-5-ND	1W Regulated DC/DC Converter	28-SOIC	9.07	7.63 7.01
DCR011205P	DCR011205P-ND	DC/DC Converter, 12V to 5V	18-Dip	9.07	7.63 7.01
DCR011205U	296-9453-5-ND	1W Regulated DC/DC Converter	28-SOIC	9.07	7.63 7.01
DCR012403P	296-9454-5-ND	1W Regulated DC/DC Converter	18-Dip	9.07	7.63 7.01
DCR012403U	296-9455-5-ND	1W Regulated DC/DC Converter	28-SOIC	9.07	7.63 7.01
DCR012405P	296-9456-5-ND	1W Regulated DC/DC Converter	18-Dip	9.07	7.63 7.01
DCR012405U	296-9457-5-ND	1W Regulated DC/DC Converter	28-SOIC	9.07	7.63 7.01
DCR021205P	296-9458-5-ND	2W Regulated DC/DC Converter	18-Dip	9.68	8.15 7.49
DCR021205P-U	296-18420-5-ND	2W Regulated DC/DC Converter	10-SOP	9.68	8.15 7.49
DCR022405P	296-9459-5-ND	2W Regulated DC/DC Converter	18-Dip	9.68	8.15 7.49
DCR022405P-U	296-17138-ND	2W Regulated DC/DC Converter	18-SOP	9.68	8.15 7.49
DCV010505DP	296-13450-5-ND	Mini, Isolated DC/DC Converter, 5V In, 5V Out	14-Dip	9.00	7.57 6.96
DCV010505P	DCV010505P-ND	Mini, Isolated DC/DC Converter, 5V In, 5V Out	14-Dip	9.00	7.57 6.96
DCV010505P-U	DCV010505P-U-ND	Mini, Isolated DC/DC Converter, 5V In, 5V Out	14-SOP	9.00	7.57 6.96
DCV010512DP	DCV010512DP-ND	Mini, Isolated DC/DC Converter, 5V In, Dual 12V Out	14-Dip	9.00	7.57 6.96
DCV010512DP-U	DCV010512DP-U-ND	Mini, Isolated DC/DC Converter, 5V In, Dual 12V Out	7-SOP	9.00	7.57 6.96
DCV010512P	DCV010512P-ND	Mini, Isolated DC/DC Converter, 5V In, 12V Out	14-Dip	9.00	7.57 6.96
DCV010512P-U	DCV010512P-U-ND	Mini, Isolated DC/DC Converter, 5V In, 12V Out	14-SOP	9.00	7.57 6.96
DCV010515DP	DCV010515DP-ND	Mini, Isolated DC/DC Converter, 5V In, Dual 15V Out	14-Dip	9.00	7.57 6.96
DCV010515DP-U	DCV010515DP-U-ND	Mini, Isolated DC/DC Converter, 5V In, Dual 15V Out	14-SOP	9.00	7.57 6.96
DCV010515P	DCV010515P-ND	Mini, Isolated DC/DC Converter, 5V In, 15V Out	14-Dip	9.00	7.57 6.96
DCV010515P-U	DCV010515P-U-ND	Mini, Isolated DC/DC Converter, 5V In, 15V Out	14-SOP	9.00	7.57 6.96
DCV011512DP	DCV011512DP-ND	Mini, Isolated DC/DC Converter, 15V In, Dual 12V Out	14-Dip	9.00	7.57 6.96
DCV011512DP-U	DCV011512DP-U-ND	Mini, Isolated DC/DC Converter, 15V In, Dual 12V Out	14-SOP	9.00	7.57 6.96
DCV011512DP-U/700	DCV011512DP-UTR-ND	Mini, Isolated DC/DC Converter, 15V In, Dual 12V Out	14-SOP	4150.03/700	
DCV011515DP	DCV011515DP-ND	Mini, Isolated DC/DC Converter, 15V In, Dual 15V Out	14-Dip	9.00	7.57 6.96
DCV011515DP-U	DCV011515DP-U-ND	Mini, Isolated DC/DC Converter, 15V In, Dual 15V Out	14-SOP	9.00	7.57 6.96
DCV011515DP-U/700	DCV011515DP-UTR-ND	Mini, Isolated DC/DC Converter, 15V In, Dual 15V Out	14-SOP	4150.03/700	
DCV012405P	DCV012405P-ND	Mini, Isolated DC/DC Converter, 24V In, 5V Out	14-Dip	9.00	7.57 6.96
DCV012405P-U	DCV012405P-U-ND	Mini, Isolated DC/DC Converter, 24V In, 5V Out	14-SOP	9.00	7.57 6.96
DCV012405P-U/700	DCV012405P-UTR-ND	Mini, Isolated DC/DC Converter, 24V In, 5V Out	14-SOP	4150.03/700	
DCV012415DP	DCV012415DP-ND	Mini, Isolated DC/DC Converter, 24V In, Dual 15V Out	14-Dip	9.00	7.57 6.96
DCV012415DP-U	DCV012415DP-U-ND	Mini, Isolated DC/DC Converter, 24V In, Dual 15V Out	7-SOP	9.00	7.57 6.96
DCV012415DP-U/700	DCV012415DP-UCT-ND	Mini, Isolated DC/DC Converter, 24V In, Dual 15V Out	7-SOP	9.40	7.98 7.36
DCV012415DP-U/700	DCV012415DP-UTR-ND	Mini, Isolated DC/DC Converter, 24V In, Dual 15V Out	7-SOP	4150.03/700	
LT1054CDW	296-9590-5-ND	Switched-Cap Voltage Conv. with Reg.	16-SOIC	2.13	1.72 1.57
LT1054CDWR	296-14618-1-ND	Switched-Cap Voltage Conv. with Reg.	16-SOIC	2.88	2.23 2.02
LT1054CDWR	296-14618-2-ND	Switched-Cap Voltage Conv. with Reg.	16-SOIC	2222.87/2,000	
LT1054CP	296-9591-5-ND	Switched-Cap Voltage Conv. with Reg.	8-Dip	2.95	2.37 2.16
LT1054D	296-9592-5-ND	Switched-Cap Voltage Conv. with Reg.	16-SOIC	2.13	1.72 1.57
LT1054DWR	296-17595-1-ND	Switched-Cap Voltage Conv. with Reg.	16-SOIC	2.18	1.69 1.53
LT1054DWR	296-17595-2-ND	Switched-Cap Voltage Conv. with Reg.	16-SOIC	1683.99/2,000	
LT1054IP	296-17596-5-ND	Switched-Cap Voltage Conv. with Reg.	8-Dip	1.94	1.56 1.43
REG10EVM-5	296-13557-ND	Evaluation Module for REG10-XX	—	34.65	—
REG10EVM-33	296-13556-ND	Evaluation Module for REG10-XX	—	34.65	—
REG710NA-2.5/250	296-12133-1-ND	2.5V, 30mA DC/DC Converter	SOT-23-6	1.34	1.03 94
REG710NA-2.5/250	296-12133-2-ND	2.5V, 30mA DC/DC Converter	SOT-23-6	190.58/250	
REG710NA-2.7/250	296-12134-1-ND	2.7V, 30mA DC/DC Converter	SOT-23-6	1.34	1.03 94
REG710NA-2.7/250	296-12134-2-ND	2.7V, 30mA DC/DC Converter	SOT-23-6	190.58/250	
REG710NA-3.3/250	296-12135-1-ND	3.3V, 30mA DC/DC Converter	SOT-23-6	1.34	1.03 94
REG710NA-3.3/250	296-12135-2-ND	3.3V, 30mA DC/DC Converter	SOT-23-6	190.58/250	
REG710NA-3/250	296-12136-1-ND	3.0V, 30mA DC/DC Converter	SOT-23-6	1.34	1.03 94
REG710NA-3/250	296-12136-2-ND	3.0V, 30mA DC/DC Converter	SOT-23-6	190.58/250	
REG710NA-5/250	296-12137-1-ND	5.0V, 30mA DC/DC Converter	SOT-23-6	1.34	1.03 94
REG710NA-5/250	296-12137-2-ND	5.0V, 30mA DC/DC Converter	SOT-23-6	190.58/250	
REG711EA-2.5/2K5	REG711EA2.5K5CT-ND	2.5V, 50mA Switched-Cap DC/DC Converter	8-MSOP	1.43	1.11 1.01
REG711EA-2.5/2K5	REG711EA2.5K5STR-ND	2.5V, 50mA Switched-Cap DC/DC Converter	8-MSOP	1380.80/2,500	
REG711EA-2.7/2K5	REG711EA2.7K5CT-ND	2.7V, 50mA Switched-Cap DC/DC Converter	8-MSOP	1.43	1.11 1.01
REG711EA-2.7/2K5	REG711EA2.7K5STR-ND	2.7V, 50mA Switched-Cap DC/DC Converter	8-MSOP	1380.80/2,500	
REG711EA-3/2K5	REG711EA3.2K5CT-ND	3V, 50mA Switched-Cap DC/DC Conv.	8-MSOP	1.43	1.11 1.01
REG711EA-3/2K5	REG711EA3.2K5STR-ND	3V, 50mA Switched-Cap DC/DC Conv.	8-MSOP	1380.80/2,500	
REG711EA-3.3/250	REG711EA3.3250CT-ND	3.3V, 50mA Switched-Cap DC/DC Converter	8-MSOP	1.73	1.33 1.21
REG711EA-3.3/250	REG711EA3.3250TR-ND	3.3V, 50mA Switched-Cap DC/DC Converter	8-MSOP	246.02/250	
REG711EA-5/2K5	REG711EA5.2K5CT-ND	5V, 50mA Switched-Cap DC/DC Conv.	8-MSOP	1.43	1.11 1.01
REG711EA-5/2K5	REG711EA5.2K5STR-ND	5V, 50mA Switched-Cap DC/DC Conv.	8-MSOP	1380.80/2,500	
REG711EVM-232	296-20536-ND	Evaluation Module for REG711-5	—	34.65	—
REG71050DDCT	296-17420-1-ND	60mA, 5V, Buck/Boost Charge Pump	TSOT-23-6	1.34	1.03 94
REG71050DDCT	296-17420-2-ND	60mA, 5V, Buck/Boost Charge Pump	TSOT-23-6	190.58/250	
REG71050DVR	296-23423-1-ND	60mA, 5V, Buck/Boost Charge Pump	6-SON	1.22	97 87
REG71050DVR	296-23423-2-ND	60mA, 5V, Buck/Boost Charge Pump	6-SON	1345.11/3,000	
REG71050DVRT	296-24144-1-ND	60mA, 5V, Buck/Boost Charge Pump*	6-SON	1.34	1.03 94
REG71050DVRT	296-24144-2-ND	60mA, 5V, Buck/Boost Charge Pump*	6-SON	333.68/500	
REG71050DDCT	296-15370-1-ND	60mA Switched-Cap Buck/Boost Conv.	TSOT-23-6	1.34	1.03 94

TEXAS INSTRUMENTS DigiKey Reel (Cont.) POWER SUPPLY PRODUCTS RoHS Compliant Parts Available					
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*	
				1	25 100
REG71055DDCT	296-15370-2-ND	60mA Switched-Cap Buck/Boost Conv.	TSOT-23-6	—	190.58/250
REG71055DDCRQ1	296-25155-1-ND	30mA Switched-Cap Buck/Boost Converter*	TSOT-23-6	1.34	1.03 94
REG71055DDCRQ1	296-25155-2-ND	30mA Switched-Cap Buck/Boost Converter*	TSOT-23-6	1544.70/3,000	
TL7660CDGKR	296-21855-1-ND	CMOS Voltage Converter	8-MSOP	1.11	88 79
TL7660CDGKR	296-21855-2-ND	CMOS Voltage Converter	8-MSOP	1018.71/2,500	
TL7660CDR	296-21856-1-ND	CMOS Voltage Converter	8-SOIC	1.05	84 75
TL7660CDR	296-21856-2-ND	CMOS Voltage Converter	8-SOIC	970.20/2,500	
TL7660CP	296-21857-5-ND	CMOS Voltage Converter	8-Dip	97	78 68
TL7660IDGKR	296-21858-1-ND	CMOS Voltage Converter	8-MSOP	1.19	94 85
TL7660IDGKR	296-21858-2-ND	CMOS Voltage Converter	8-MSOP	1091.48/2,500	
TL7660IDR	296-21859-1-ND	CMOS Voltage Converter	8-SOIC	1.19	94 85
TL7660IDR	296-21859-2-ND	CMOS Voltage Converter	8-SOIC	1091.48/2,500	
TL7660IP	296-21860-5-ND	CMOS Voltage Converter	8-Dip	1.09	88 77
TPS5102IDBT	296-2260-5-ND	Dual DC/DC Controller	30-TSSOP	4.94	4.05 3.66
TPS5103EVM-136	296-10924-ND	Evaluation Module for TPS5103	—	34.65	—
TPS5103IDB	296-2261-5-ND	Multimode DC/DC Controller	20-SSOP	3.40	2.73 2.49
TPS5120MDBTREP	296-21272-1-ND	Dual Output, 2-Phase Sync. Buck DC/DC Controller	30-TSSOP	8.48	7.19 6.64
TPS5120MDBTREP	296-21272-2-ND	Dual Output, 2-Phase Sync. Buck DC/DC Controller	30-TSSOP	9401.24/2,000	
TPS5120DDBTREP	296-18639-1-ND	Dual Output, 2-Phase Sync. Buck DC/DC Controller	30-TSSOP	7.82	6.50 5.91
TPS5120DDBTREP	296-18639-2-ND	Dual Output, 2-Phase Sync. Buck DC/DC Controller	30-TSSOP	7675.67/2,000	
TPS5120DDBTR01G4	296-22052-1-ND	Dual Output, 2-Phase Sync. Buck DC/DC Controller	30-TSSOP	6.06	5.04 4.58
TPS5120DDBTR01G4	296-22052-2-ND	Dual Output, 2-Phase Sync. Buck DC/DC Controller	30-TSSOP	5945.94/2,000	
TPS5124DBT	296-15863-5-ND	Dual Channel, Sync. Step-Down PWM Controller	30-TSSOP	4.66	3.75 3.41
TPS5124EVM	296-18960-ND	Evaluation Module for TPS5124	—	34.65	—
TPS5140PAG	296-12364-ND	Quad-Out High Efficiency DC/DC Cont.	64-TQFP	7.54	6.18 5.58
TPS5300AP	296-12508-5-ND	CPU Power Supply Controller	32-TSSOP	7.19	5.90 5.33
TPS5410D	296-20787-5-ND	1A Step-Down SWIFT™ Converter	8-SOIC	3.78	3.05 2.78
TPS5410EVM-203	296-22913-ND	Evaluation Module for TPS5410	—	34.65	—
TPS5410MDREP	296-25179-1-ND	1A Step-Down SWIFT™ Converter*	8-SOIC	5.88	4.88 4.44
TPS5410MDREP	296-25179-2-ND	1A Step-Down SWIFT™ Converter*	8-SOIC	7207.20/2,500	
TPS5410QDRQ1	296-25229-1-ND	1A Step-Down SWIFT™ Converter*	8-SOIC	3.95	3.23 2.90
TPS5420D	296-25229-2-ND	1A Step-Down SWIFT™ Converter*	8-SOIC	4378.03/2,500	
TPS5420D	296-19671-5-ND	2A Step-Down SWIFT™ Converter	8-SOIC	3.98	3.20 2.92
TPS5420EVM-175	296-21156-ND	Evaluation Module for TPS5420	—	7.07	—
TPS5420MDREP	296-22447-1-ND	2A Step-Down SWIFT™ Converter	8-SOIC	5.31	4.41 4.01
TPS5420MDREP	296-22447-2-ND	2A Step-Down SWIFT™ Converter	8-SOIC	6509.00/2,500	
TPS5420DQDRQ1	296-23226-1-ND	2A Step-Down SWIFT™ Converter	8-SOIC	4.16	3.40 3.05
TPS5420DQDRQ1	296-23226-2-ND	2A Step-Down SWIFT™ Converter	8-SOIC	4608.45/2,500	
TPS5430DDA	296-19447-5-ND	3A Step-Down SWIFT™ Converter	8-HSOIC	4.37	3.51 3.20
TPS5430EVM-136	296-19432-ND	Evaluation Module for TPS5430-136	—	6.99	—
TPS5430EVM-173	296-19640-ND	Evaluation Module for TPS5430	—	7.07	—
TPS5430MDAREP	296-24266-1-ND	3A Step-Down SWIFT™ Converter*	8-SOIC	6.80	5.65 5.13
TPS5430MDAREP	296-24266-2-ND	3A Step-Down SWIFT™ Converter*	8-SOIC	8333.33/2,500	
TPS5430QDARQ1	296-23177-1-ND	3A Step-Down SWIFT™ Converter	8-HSOIC	4.57	3.74 3.36
TPS5430QDARQ1	296-23177-2-ND	3A Step-Down SWIFT™ Converter	8-HSOIC	5069.30/2,500	
TPS5431DDA	296-19662-5-ND	3A Step-Down SWIFT™ Converter	8-HSOIC	4.07	3.28 2.99
TPS5431EVM-173	296-19710-ND	Evaluation Module for TPS5431-173	—	7.07	—
TPS5450DDA	296-21715-5-ND	5A Step-Down SWIFT™ Converter	8-HSOIC	4.68	3.84 3.47
TPS5450MDAREP	296-24950-1-ND	5A Step-Down SWIFT™ Converter*	8-SOIC	7.97	6.76 6.24
TPS5450MDAREP	296-24950-2-ND	5A Step-Down SWIFT™ Converter*	8-SOIC	11044.69/2,500	
TPS5450QDARQ1	296-23750-1-ND	5A Step-Down SWIFT™ Converter	8-SOIC	4.86	4.04 3.68
TPS5450QDARQ1	296-23750-2-ND	5A Step-Down SWIFT™ Converter	8-SOIC	5968.46/2,000	
TPS5602IDBT	296-2262-5-ND	Dual DC/DC Controller	30-SSOP	7.10	5.83 5.26
TPS6734EVM	296-10980-ND	Evaluation Module for TPS6734	—	34.65	—
TPS6734ID	296-3225-5-ND	12V, 120mA Boost Converter	8-SOIC	2.72	2.19 1.99