

| TEXAS INSTRUMENTS DigiReel (Cont.) TEMPERATURE SENSORS RoHS Compliant Parts Available | | | | |
|---|-------------------|---------------------------------------|----------|----------------|
| T.I. Part No. | Digi-Key Part No. | Description | Pkg. | Price Each* |
| | | | | 1 25 100 |
| TMP12AIDRLT | 296-24621-2-ND | Digital Temperature Sensor* | SOT-6 | 320.51/250 |
| TMP121AIDBVT | 296-15177-1-ND | Digital Temperature Sensor | SOT-23-6 | 2.18 1.79 1.61 |
| TMP121AIDBVT | 296-15177-2-ND | Digital Temperature Sensor | SOT-23-6 | 336.62/250 |
| TMP122AIDBVT | 296-15178-1-ND | Prog. Digital Temperature Sensor | SOT-23-6 | 2.39 1.96 1.76 |
| TMP122AIDBVT | 296-15178-2-ND | Prog. Digital Temperature Sensor | SOT-23-6 | 368.68/250 |
| TMP122EVM | 296-21136-ND | Evaluation Module for TMP122 | | 34.65 |
| TMP123AIDBVT | 296-15832-1-ND | Digital Temperature Sensor with SPI | SOT-23-6 | 2.18 1.79 1.61 |
| TMP123AIDBVT | 296-15832-2-ND | Digital Temperature Sensor with SPI | SOT-23-6 | 336.62/250 |
| TMP124AID | 296-16977-ND | Digital Temperature Sensor with SPI | 8-SOIC | 2.13 1.72 1.57 |
| TMP125AIDBVT | 296-17690-1-ND | Digital Temperature Sensor w/SPI | SOT-23-6 | 2.31 1.78 1.62 |
| TMP125AIDBVT | 296-17690-2-ND | Digital Temperature Sensor w/SPI | SOT-23-6 | 329.18/250 |
| TMP175AIDGKT | 296-19882-1-ND | Digital Temp. Sensor 2-Wire Interface | 8-MSOP | 2.08 1.70 1.50 |
| TMP175AIDGKT | 296-19882-2-ND | Digital Temp. Sensor 2-Wire Interface | 8-MSOP | 320.51/250 |
| TMP175AIDR | 296-17837-1-ND | Digital Temp. Sensor 2-Wire Interface | 8-SOIC | 2.07 1.60 1.45 |
| TMP175AIDR | 296-17837-2-ND | Digital Temp. Sensor 2-Wire Interface | 8-SOIC | 198.91/2,500 |
| TMP275AID | 296-21416-5-ND | 0.5°C Digital Out Temp. Sensor | 8-SOIC | 2.91 2.34 2.14 |
| TMP275AIDGKT | 296-19883-1-ND | 0.5°C Digital Out Temp. Sensor | 8-MSOP | 3.01 2.47 2.22 |
| TMP275AIDGKT | 296-19883-2-ND | 0.5°C Digital Out Temp. Sensor | 8-MSOP | 464.83/250 |
| TMP300AIDBVT | 296-24010-1-ND | 1.8V, Resistor Prog. Temp. Switch | SOT-23-6 | 1.46 1.13 1.02 |
| TMP300AIDBVT | 296-24010-2-ND | 1.8V, Resistor Prog. Temp. Switch | SOT-23-6 | 207.90/250 |
| TMP302ADRLLT | 296-25144-1-ND | 1.4V, Temperature Switch* | SOT563-6 | 91 .72 .65 |
| TMP302ADRLLT | 296-25144-2-ND | 1.4V, Temperature Switch* | SOT563-6 | 358.97/1,000 |
| TMP302DRLLT | 296-25145-1-ND | 1.4V, Temperature Switch* | SOT563-6 | 91 .72 .65 |
| TMP302DRLLT | 296-25145-2-ND | 1.4V, Temperature Switch* | SOT563-6 | 358.97/1,000 |
| TMP302CDRLT | 296-25146-1-ND | 1.4V, Temperature Switch* | SOT563-6 | 91 .72 .65 |
| TMP302CDRLT | 296-25146-2-ND | 1.4V, Temperature Switch* | SOT563-6 | 358.97/1,000 |
| TMP302DRLLT | 296-25147-1-ND | 1.4V, Temperature Switch* | SOT563-6 | 91 .72 .65 |
| TMP302DRLLT | 296-25147-2-ND | 1.4V, Temperature Switch* | SOT563-6 | 358.97/1,000 |
| TMP303ADRLLT | 296-25120-1-ND | 1.4V, Temp. Range Monitor* | SOT563-6 | 91 .72 .65 |
| TMP303ADRLLT | 296-25120-2-ND | 1.4V, Temp. Range Monitor* | SOT563-6 | 128.55/250 |
| TMP401AIDGKR | 296-20710-1-ND | Remote Digital Temperature Sensor | 8-MSOP | 2.07 1.60 1.45 |
| TMP401AIDGKR | 296-20710-2-ND | Remote Digital Temperature Sensor | 8-MSOP | 198.91/2,500 |
| TMP411AD | 296-22886-5-ND | ±1°C Remote/Local Temp. Sensor | 8-SOIC | 1.12 .90 .79 |
| TMP411ADGKR | 296-21417-1-ND | ±1°C Remote/Local Temp. Sensor | 8-MSOP | 1.00 .79 .71 |
| TMP411ADGKR | 296-21417-2-ND | ±1°C Remote/Local Temp. Sensor | 8-MSOP | 916.49/2,500 |
| TMP411BDGKR | 296-22887-5-ND | ±1°C Remote/Local Temp. Sensor | 8-SOIC | 1.12 .90 .79 |
| TMP411BDGKR | 296-21418-1-ND | ±1°C Remote/Local Temp. Sensor | 8-MSOP | 1.00 .79 .71 |
| TMP411CDR | 296-23546-1-ND | ±1°C Remote/Local Temp. Sensor | 8-SOIC | 1.00 .79 .71 |
| TMP411CDR | 296-23546-2-ND | ±1°C Remote/Local Temp. Sensor | 8-SOIC | 916.49/2,500 |
| TMP421AIDCNT | 296-21990-1-ND | Remote Temperature Sensor | SOT-23-8 | 1.58 1.22 1.11 |
| TMP421AIDCNT | 296-21990-2-ND | Remote Temperature Sensor | SOT-23-8 | 225.23/250 |
| TMP423AIDCNT | 296-23323-1-ND | ±1°C Remote/Local Temp. Sensor | SOT-23-8 | 2.18 1.69 1.53 |
| TMP423AIDCNT | 296-23324-1-ND | ±1°C Remote/Local Temp. Sensor | SOT-23-8 | 2.18 1.69 1.53 |
| TMP431ADGKT | 296-25148-1-ND | ±1°C Remote/Local Temp. Sensor* | 8-MSOP | 1.22 .97 .87 |
| TMP431ADGKT | 296-25148-2-ND | ±1°C Remote/Local Temp. Sensor* | 8-MSOP | 172.04/250 |
| TMP431BDGKT | 296-25149-1-ND | ±1°C Remote/Local Temp. Sensor* | 8-MSOP | 1.22 .97 .87 |
| TMP431BDGKT | 296-25149-2-ND | ±1°C Remote/Local Temp. Sensor* | 8-MSOP | 172.04/250 |
| TMP432ADGST | 296-25474-1-ND | ±1°C Remote/Local Temp. Sensor** | 10-MSOP | 1.34 1.03 .94 |
| TMP432ADGST | 296-25474-2-ND | ±1°C Remote/Local Temp. Sensor** | 10-MSOP | 190.59/250 |
| TMP432BDGST | 296-25475-1-ND | ±1°C Remote/Local Temp. Sensor** | 10-MSOP | 1.34 1.03 .94 |
| TMP432BDGST | 296-25475-2-ND | ±1°C Remote/Local Temp. Sensor** | 10-MSOP | 190.59/250 |
| TMP441AIDCNT | 296-24282-1-ND | ±1°C Remote/Local Temp. Sensor* | SOT-23-8 | 1.58 1.22 1.11 |
| TMP441AIDCNT | 296-24282-2-ND | ±1°C Remote/Local Temp. Sensor* | SOT-23-8 | 225.23/250 |
| TMP442ADCNT | 296-24283-1-ND | ±1°C Remote/Local Temp. Sensor* | SOT-23-8 | 1.82 1.41 1.28 |
| TMP442ADCNT | 296-24283-2-ND | ±1°C Remote/Local Temp. Sensor* | SOT-23-8 | 259.88/250 |
| TMP442BDCNT | 296-24284-1-ND | ±1°C Remote/Local Temp. Sensor* | SOT-23-8 | 1.82 1.41 1.28 |
| TMP442BDCNT | 296-24284-2-ND | ±1°C Remote/Local Temp. Sensor* | SOT-23-8 | 259.88/250 |

| TEXAS INSTRUMENTS DigiReel (Cont.) TIMERS RoHS Compliant Parts Available | | | | |
|--|-------------------|----------------------|---------|----------------|
| T.I. Part No. | Digi-Key Part No. | Description | Pkg. | Price Each* |
| | | | | 1 25 100 |
| NA555DR | 296-21752-1-ND | Precision Timer | 8-SOIC | .46 .32 .28 |
| NA555DR | 296-21752-2-ND | Precision Timer | 8-SOIC | 322.25/2,500 |
| NA555P | 296-21753-5-ND | Precision Timer | 8-Dip | .47 .35 .30 |
| NA556N | 296-21755-5-ND | Dual Precision Timer | 14-Dip | .42 .33 .29 |
| NE555D | 296-16792-ND | Precision Timer | 8-SOIC | .36 .24 .20 |
| NE555DR | 296-6501-1-ND | Precision Timer | 8-SOIC | .34 .23 .19 |
| NE555DR | 296-6501-2-ND | Precision Timer | 8-SOIC | 192.31/2,500 |
| NE555P | 296-1411-5-ND | Precision Timer | 8-Dip | .38 .26 .21 |
| NE555PSR | 296-6502-1-ND | Precision Timer | 8-SOP | .37 .25 .20 |
| NE555PSR | 296-6502-2-ND | Precision Timer | 8-SOP | 169.09/2,000 |
| NE555PW | 296-15086-5-ND | Precision Timer | 8-TSSOP | .40 .27 .22 |
| NE556D | 296-6503-5-ND | Dual Precision Timer | 14-SOIC | .40 .30 .25 |
| NE556D | 296-6504-5-ND | Dual Precision Timer | 14-Dip | .38 .27 .23 |
| NE56NSR | 296-13104-1-ND | Dual Precision Timer | 14-SOP | .42 .30 .26 |
| NE56NSR | 296-13104-2-ND | Dual Precision Timer | 14-SOP | 237.01/2,000 |
| SA555D | 296-9681-5-ND | Precision Timer | 8-SOIC | .40 .26 .22 |
| SA555P | 296-9682-5-ND | Precision Timer | 8-Dip | .49 .36 .31 |
| SE555D | 296-9683-5-ND | Precision Timer | 8-SOIC | .35 .27 .23 |
| SE555D G4 | 296-22062-5-ND | Precision Timer | 8-SOIC | .35 .27 .23 |
| SE555P | 296-9684-5-ND | Precision Timer | 8-Dip | .31 .23 .20 |
| TLC551CD | 296-11822-5-ND | CMOS Timer | 8-SOIC | 1.07 .87 .78 |
| TLC551CP | 296-10333-5-ND | CMOS Timer | 8-Dip | 1.07 .87 .78 |
| TLC552CD | 296-10334-5-ND | CMOS Timer | 14-SOIC | 2.09 1.69 1.52 |
| TLC552CN | 296-10335-5-ND | CMOS Timer | 14-Dip | 1.80 1.46 1.31 |
| TLC555CD | 296-1336-5-ND | LinCMOSTM Timer | 8-SOIC | 62 .48 .43 |
| TLC555CDR | 296-1336-1-ND | LinCMOSTM Timer | 8-SOIC | .56 .44 .39 |
| TLC555CDR | 296-1336-2-ND | LinCMOSTM Timer | 8-SOIC | 464.31/2,500 |
| TLC555CP | 296-1857-5-ND | LinCMOSTM Timer | 8-Dip | .51 .40 .35 |
| TLC555ID | 296-1337-5-ND | LinCMOSTM Timer | 8-SOIC | .67 .52 .45 |
| TLC555IDR | 296-1337-1-ND | LinCMOSTM Timer | 8-SOIC | .62 .48 .43 |
| TLC555IDR | 296-1337-2-ND | LinCMOSTM Timer | 8-SOIC | 509.96/2,500 |
| TLC555IDR | 296-1858-5-ND | LinCMOSTM Timer | 8-Dip | .56 .44 .38 |
| TLC555ODR | 296-10341-1-ND | LinCMOSTM Timer | 8-SOIC | .65 .51 .45 |
| TLC555ODR | 296-10341-2-ND | LinCMOSTM Timer | 8-SOIC | 535.34/2,500 |
| TLC555ODRQ1 | 296-22999-1-ND | LinCMOSTM Timer | 8-SOIC | 66 .51 .45 |
| TLC555ODRQ1 | 296-22999-2-ND | LinCMOSTM Timer | 8-SOIC | 542.27/2,500 |
| TLC556CD | 296-1338-5-ND | Dual CMOS Timer | 14-SOIC | 1.12 .90 .79 |
| TLC556CDR | 296-1338-1-ND | Dual CMOS Timer | 14-SOIC | .95 .75 .68 |
| TLC556CDR | 296-1338-2-ND | Dual CMOS Timer | 14-SOIC | 873.18/2,500 |
| TLC556CN | 296-1859-5-ND | Dual CMOS Timer | 14-Dip | .87 .70 .62 |

* RoHS Compliant

★ CALL FOR LOWER PRICING ON LARGER QUANTITIES! ★

(Continued)

Free shipping on orders over £50! All prices are in British pound sterling and include duties.

www.digikey.co.uk — FREEPHONE: 0-800-587-0991 • 0-800-904-7786 — FREEFAX: 0-800-587-0992 • 0-800-904-7783 (UK2011-EN) 989