

C

POWER INTEGRATIONS		DigiKey® (Cont.)		INTEGRATED POWER SWITCHING CONTROLLERS		
Power Integrations Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	25	100
LinkSwitch®-TN — RoHS Compliant						
LNK302DG-TL	596-1236-1-ND	Lowest Component Count, Energy Efficient Off-Line Switcher, Halogen Free	8-SOIC	.79	.66	.53
LNK302DG-TL	596-1236-2-ND	Lowest Component Count, Energy Efficient Off-Line Switcher, Halogen Free	8-SOIC	921.69/2,500		
LNK302GN-TL	596-1020-1-ND	Lowest Component Count, Energy Efficient Off-Line Switcher	8-SMD	.77	.65	.52
LNK302GN-TL	596-1020-2-ND	Lowest Component Count, Energy Efficient Off-Line Switcher	8-SMD	358.97/1,000		
LNK302PN	596-1021-5-ND	Lowest Component Count, Energy Efficient Off-Line Switcher	8-Dip	.71	.59	.48
LNK304DG-TL	596-1237-1-ND	Lowest Component Count, Energy Efficient Off-Line Switcher, Halogen Free	8-SOIC	.87	.73	.59
LNK304DG-TL	596-1237-2-ND	Lowest Component Count, Energy Efficient Off-Line Switcher, Halogen Free	8-SOIC	1018.71/2,500		
LNK304GN-TL	596-1022-1-ND	Lowest Component Count, Energy Efficient Off-Line Switcher	8-SMD	.85	.72	.57
LNK304GN-TL	596-1022-2-ND	Lowest Component Count, Energy Efficient Off-Line Switcher	8-SMD	397.78/1,000		
LNK304PN	596-1023-5-ND	Lowest Component Count, Energy Efficient Off-Line Switcher	8-Dip	.79	.66	.53
LNK305DG	596-1238-5-ND	Lowest Component Count, Energy Efficient Off-Line Switcher, Halogen Free	8-SOIC	1.00	.84	.67
LNK305GN-TL	596-1024-1-ND	Lowest Component Count, Energy Efficient Off-Line Switcher	8-SMD	1.00	.84	.67
LNK305GN-TL	596-1024-2-ND	Lowest Component Count, Energy Efficient Off-Line Switcher	8-SMD	465.70/1,000		
LNK305PN	596-1025-5-ND	Lowest Component Count, Energy Efficient Off-Line Switcher	8-Dip	.94	.78	.63
LNK306DG-TL	596-1239-1-ND	Lowest Component Count, Energy Efficient Off-Line Switcher, Halogen Free	8-SOIC	.99	.79	.60
LNK306DG-TL	596-1239-2-ND	Lowest Component Count, Energy Efficient Off-Line Switcher, Halogen Free	8-SOIC	1334.03/2,500		
LNK306GN-TL	596-1026-1-ND	Lowest Component Count, Energy Efficient Off-Line Switcher	8-SMD	.97	.78	.59
LNK306GN-TL	596-1026-2-ND	Lowest Component Count, Energy Efficient Off-Line Switcher	8-SMD	523.91/1,000		
LNK306PN	596-1027-5-ND	Lowest Component Count, Energy Efficient Off-Line Switcher	8-Dip	.92	.74	.56
LinkSwitch®-XT — RoHS Compliant						
LNK362DG	596-1241-5-ND	Energy Efficient, Low Power Off-Line Switcher, Halogen Free	8-SOIC	.81	.68	.55
LNK362PG	596-1240-5-ND	Energy Efficient, Low Power Off-Line Switcher, Halogen Free	8-Dip	.75	.63	.50
LNK363DG	596-1243-5-ND	Energy Efficient, Low Power Off-Line Switcher, Halogen Free	8-SOIC	.87	.73	.59
LNK363GN-TL	596-1087-1-ND	Energy Eff., Low Power Off-Line Switcher	8-SMD	.87	.73	.59
LNK363GN-TL	596-1087-2-ND	Energy Eff., Low Power Off-Line Switcher	8-SMD	407.48/1,000		
LNK363PG	596-1242-5-ND	Energy Efficient, Low Power Off-Line Switcher, Halogen Free	8-Dip	.81	.68	.55
LNK364DG	596-1245-5-ND	Energy Efficient, Low Power Off-Line Switcher, Halogen Free	8-SOIC	.91	.77	.61
LNK364GN-TL	596-1089-1-ND	Energy Eff., Low Power Off-Line Switcher	8-SMD	.91	.77	.61
LNK364PG	596-1244-5-ND	Energy Efficient, Low Power Off-Line Switcher, Halogen Free	8-Dip	.85	.72	.57
PeakSwitch® — RoHS Compliant						
PKS604FN	596-1123-5-ND	Enhanced, Energy Eff., Off-Line Switcher with Super Peak Power Performance	TO-262-7	1.39	1.11	.84
PKS604PN	596-1117-5-ND	Enhanced, Energy Eff., Off-Line Switcher with Super Peak Power Performance	8-Dip	1.11	.89	.67
PKS604YN	596-1120-5-ND	Enhanced, Energy Eff., Off-Line Switcher with Super Peak Power Performance	TO-220-7	1.39	1.11	.84
PKS605FN	596-1124-5-ND	Enhanced, Energy Eff., Off-Line Switcher with Super Peak Power Performance	TO-262-7	1.48	1.18	.89
PKS605YN	596-1121-5-ND	Enhanced, Energy Eff., Off-Line Switcher with Super Peak Power Performance	TO-220-7	1.48	1.18	.89
PKS606FN	596-1125-5-ND	Enhanced, Energy Eff., Off-Line Switcher with Super Peak Power Performance	TO-262-7	1.66	1.34	1.00
PKS606PN	596-1119-5-ND	Enhanced, Energy Eff., Off-Line Switcher with Super Peak Power Performance	8-Dip	1.44	1.16	.87
PKS606YN	596-1122-5-ND	Enhanced, Energy Eff., Off-Line Switcher with Super Peak Power Performance	TO-220-7	1.66	1.34	1.00
PKS607FN	596-1140-5-ND	Enhanced, Energy Eff., Off-Line Switcher with Super Peak Power Performance	TO-262-7	1.67	1.34	1.04
TinySwitch® — RoHS Compliant						
TNY253GN-TL	596-1040-1-ND	Energy Efficient, LP Off-Line Switcher	8-SMD	1.13	.91	.68
TNY253GN-TL	596-1040-2-ND	Energy Efficient, LP Off-Line Switcher	8-SMD	608.45/1,000		
TNY254GN-TL	596-1041-1-ND	Energy Efficient, LP Off-Line Switcher	8-SMD	1.13	.91	.68
TNY254GN-TL	596-1041-2-ND	Energy Efficient, LP Off-Line Switcher	8-SMD	608.45/1,000		
TNY255GN-TL	596-1042-1-ND	Energy Efficient, LP Off-Line Switcher	8-SMD	1.18	.95	.71
TNY255GN-TL	596-1042-2-ND	Energy Efficient, LP Off-Line Switcher	8-SMD	636.17/1,000		
TNY255PN	596-1170-5-ND	Energy Efficient, LP Off-Line Switcher	8-Dip	1.09	.88	.66
TinySwitch® Plus — RoHS Compliant						
TNY256PN	596-1171-5-ND	Energy Efficient, LP Off-Line Switcher	8-Dip	1.32	1.06	—
TNY256YN	596-1218-5-ND	Energy Efficient, LP Off-Line Switcher	TO-220-7	1.62	1.29	.97
TinySwitch®-II — RoHS Compliant						
TNY263PN	596-1045-5-ND	Enhanced, Energy Efficient, Low Power Off-Line Switcher	8-Dip	.94	.78	.63
TNY264GN-TL	596-1046-1-ND	Enhanced, Energy Efficient, Low Power Off-Line Switcher	8-SMD	.94	.75	.57
TNY264GN-TL	596-1046-2-ND	Enhanced, Energy Efficient, Low Power Off-Line Switcher	8-SMD	505.20/1,000		
TNY264PG	596-1255-5-ND	Enhanced, Energy Efficient, Low Power Off-Line Switcher, Halogen Free	8-Dip	1.02	.85	.68
TNY265PG	596-1256-5-ND	Enhanced, Energy Efficient, Low Power Off-Line Switcher, Halogen Free	8-Dip	.89	.71	.54
TNY266GN-TL	596-1050-1-ND	Enhanced, Energy Efficient, Low Power Off-Line Switcher	8-SMD	1.04	.84	.63
TNY266GN-TL	596-1050-2-ND	Enhanced, Energy Efficient, Low Power Off-Line Switcher	8-SMD	561.33/1,000		
TNY266PG	596-1257-5-ND	Enhanced, Energy Efficient, Low Power Off-Line Switcher, Halogen Free	8-Dip	.96	.77	.58
TNY267GN-TL	596-1052-1-ND	Enhanced, Energy Efficient, Low Power Off-Line Switcher	8-SMD	1.18	.95	.71

POWER INTEGRATIONS		DigiKey® (Cont.)		INTEGRATED POWER SWITCHING CONTROLLERS		
Power Integrations Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	25	100
TNY267GN-TL	596-1052-2-ND	Enhanced, Energy Efficient, Low Power Off-Line Switcher	8-SMD	636.17/2,000		
TNY267PN	596-1053-5-ND	Enhanced, Energy Efficient, Low Power Off-Line Switcher	8-Dip	1.09	.88	.66
TNY268GN-TL	596-1054-1-ND	Enhanced, Energy Efficient, Low Power Off-Line Switcher	8-SMD	1.28	1.03	.77
TNY268GN-TL	596-1054-2-ND	Enhanced, Energy Efficient, Low Power Off-Line Switcher	8-SMD	692.31/1,000		
TNY268PN	596-1055-5-ND	Enhanced, Energy Efficient, Low Power Off-Line Switcher	8-Dip	1.20	.96	.72
TinySwitch®-III — RoHS Compliant						
TNY274GN-TL	596-1109-1-ND	Energy Efficient, Off-Line Switcher with Enhanced Flexibility and Extended Pwr Range	8-SMD	1.00	.84	.67
TNY274GN-TL	596-1109-2-ND	Energy Efficient, Off-Line Switcher with Enhanced Flexibility and Extended Pwr Range	8-SMD	465.70/1,000		
TNY274PG	596-1258-5-ND	Energy Efficient, Off-Line Switcher with Enhanced Flexibility and Extended Pwr Range, Halogen Free	8-Dip	.94	.78	.63
TNY275GN-TL	596-1110-1-ND	Energy Efficient, Off-Line Switcher with Enhanced Flexibility and Extended Pwr Range	8-SMD	.87	.70	.52
TNY275GN-TL	596-1110-2-ND	Energy Efficient, Off-Line Switcher with Enhanced Flexibility and Extended Pwr Range	8-SMD	467.78/1,000		
TNY275PG	596-1259-5-ND	Energy Efficient, Off-Line Switcher with Enhanced Flexibility and Extended Pwr Range, Halogen Free	8-Dip	.98	.82	.66
TNY276GN-TL	596-1111-1-ND	Energy Efficient, Off-Line Switcher with Enhanced Flexibility and Extended Pwr Range	8-SMD	.92	.74	.56
TNY276GN-TL	596-1111-2-ND	Energy Efficient, Off-Line Switcher with Enhanced Flexibility and Extended Pwr Range	8-SMD	496.19/1,000		
TNY276PN	596-1092-5-ND	Energy Efficient, Off-Line Switcher with Enhanced Flexibility and Extended Pwr Range	8-Dip	.87	.70	.52
TNY277GN-TL	596-1112-1-ND	Energy Efficient, Off-Line Switcher with Enhanced Flexibility and Extended Pwr Range	8-SMD	1.00	.81	.61
TNY277GN-TL	596-1112-2-ND	Energy Efficient, Off-Line Switcher with Enhanced Flexibility and Extended Pwr Range	8-SMD	542.62/1,000		
TNY277PG	596-1260-5-ND	Energy Efficient, Off-Line Switcher with Enhanced Flexibility and Extended Pwr Range, Halogen Free	8-Dip	.96	.77	.58
TNY278GN-TL	596-1113-1-ND	Energy Efficient, Off-Line Switcher with Enhanced Flexibility and Extended Pwr Range	8-SMD	1.14	.92	.69
TNY278GN-TL	596-1113-2-ND	Energy Efficient, Off-Line Switcher with Enhanced Flexibility and Extended Pwr Range	8-SMD	617.46/1,000		
TNY278PN	596-1094-5-ND	Energy Efficient, Off-Line Switcher with Enhanced Flexibility and Extended Pwr Range	8-Dip	1.09	.88	.66
TNY279GN-TL	596-1114-1-ND	Energy Efficient, Off-Line Switcher with Enhanced Flexibility and Extended Pwr Range	8-SMD	1.30	1.04	.78
TNY279GN-TL	596-1114-2-ND	Energy Efficient, Off-Line Switcher with Enhanced Flexibility and Extended Pwr Range	8-SMD	702.01/1,000		
TNY279PN	596-1095-5-ND	Energy Efficient, Off-Line Switcher with Enhanced Flexibility and Extended Pwr Range	8-Dip	1.25	1.00	.75
TNY280GN-TL	596-1115-2-ND	Energy Efficient, Off-Line Switcher with Enhanced Flexibility and Extended Pwr Range	8-SMD	804.57/1,000		
TNY280PN	596-1096-5-ND	Energy Efficient, Off-Line Switcher with Enhanced Flexibility and Extended Pwr Range	8-Dip	1.44	1.16	.87
TinySwitch®-PK — RoHS Compliant						
TNY375PN	596-1142-5-ND	Energy Efficient, Off-Line Switcher with Enhanced Peak Power Performance	8-Dip	1.00	.84	.67
TNY376PN	596-1143-5-ND	Energy Efficient, Off-Line Switcher with Enhanced Peak Power Performance	8-Dip	.89	.71	.54
TNY377PN	596-1144-5-ND	Energy Efficient, Off-Line Switcher with Enhanced Peak Power Performance	8-Dip	.97	.78	.59
TOPSwitch® — RoHS Compliant						
TOP103YN	596-1147-5-ND	3-Terminal Off-Line PWM Switch	TO-220	2.87	2.30	1.79
TOP104YN	596-1148-5-ND	3-Terminal Off-Line PWM Switch	TO-220	3.01	2.42	1.88
TOP200YN	596-1149-5-ND	3-Terminal Off-Line PWM Switch	TO-220	2.05	1.64	1.28
TOP201YN	596-1150-5-ND	3-Terminal Off-Line PWM Switch	TO-220	2.50	2.00	1.56
TOP202YN	596-1151-5-ND	3-Terminal Off-Line PWM Switch	TO-220	3.06	2.45	1.91
TOP204YN	596-1153-5-ND	3-Terminal Off-Line PWM Switch	TO-220	3.73	2.99	2.53
TOP210PN	596-1154-5-ND	3-Terminal Off-Line PWM Switch	8-Dip	1.58	1.27	.99
TOP414GN-TL	596-1083-1-ND	3-Terminal DC/DC PWM Switch	8-SMD	2.26	1.81	1.41
TOP414GN-TL	596-1083-2-ND	3-Terminal DC/DC PWM Switch	8-SMD	1281.36/1,000		
TOPSwitch®-GX — RoHS Compliant						
TOP242GN-TL	596-1065-1-ND	Extended Power, Design Flexible, EcoSmart®, Integrated Off-Line Switcher	8-SMD	1.65	1.32	.99
TOP242GN-TL	596-1065-2-ND	Extended Power, Design Flexible, EcoSmart®, Integrated Off-Line Switcher	8-SMD	889.12/1,000		
TOP242PN	596-1066-5-ND	Extended Power, Design Flexible, EcoSmart®, Integrated Off-Line Switcher	8-Dip	1.56	1.25	.94
TOP243GN-TL	596-1068-1-ND	Extended Power, Design Flexible, EcoSmart®, Integrated Off-Line Switcher	8-SMD	1.70	1.36	1.06
TOP243GN-TL	596-1068-2-ND	Extended Power, Design Flexible, EcoSmart®, Integrated Off-Line Switcher	8-SMD	981.98/1,000		
TOP243PN	596-1069-5-ND	Extended Power, Design Flexible, EcoSmart®, Integrated Off-Line Switcher	8-Dip	1.62	1.30	1.01
TOP243YN	596-1070-5-ND	Extended Power, Design Flexible, EcoSmart®, Integrated Off-Line Switcher	TO-220-7	1.84	1.48	1.15
TOP244FN	596-1166-ND	Extended Power Design Flexible, EcoSmart®, Integrated Off-Line Switcher	TO-262-7	2.04	1.64	1.28

* RoHS Compliant

★ CALL FOR LOWER PRICING ON LARGER QUANTITIES! ★

(Continued)

Free shipping on orders over £50! All prices are in British pound sterling and include duties.

1062 (UK2011-EN) www.digikey.co.uk — FREEPHONE: 0-800-587-0991 • 0-800-904-7786 — FREEFAX: 0-800-587-0992 • 0-800-904-7783