





Wire Ferrules – Insulated

Material: Copper/Plastic. Surface: Tin-plated.



Twin-Wire Ferrules for Two Wires

Material: Copper/Plastic
Surface: Tin-plated



A

Size (mm ²)	AWG	Type	Color Code	Dimensions (mm)				Digi-Key Part No.	Pricing			AE Part No.
				A	B	C	D		10	50	100	
0.14	26	DIN	Gray	10.5	6	0.8	2.0	288-1001-ND*	1.68	7.37	12.63	1161014
				12.5	8	0.8	2.0	288-1002-ND*	1.80	7.88	13.50	1181014
		W	Gray	10.5	6	0.8	2.0	288-1039-ND*	1.68	7.37	12.63	1162014
0.25	24	DIN	Yellow	10.5	6	0.8	2.0	288-1003-ND*	1.68	7.37	12.63	11610025
				12.5	8	0.8	2.0	288-1004-ND*	1.80	7.88	13.50	11810025
		W	Blue	10.5	6	0.8	2.0	288-1041-ND*	1.68	7.37	12.63	11620025
				12.5	8	0.8	2.0	288-1042-ND*	1.80	7.88	13.50	11820025
0.34	22	DIN	Turquoise	10.5	6	0.8	2.0	288-1005-ND*	1.68	7.37	12.63	1161034
				12.5	8	0.8	2.0	288-1006-ND*	1.80	7.88	13.50	1181034
		W	Turquoise	10.5	6	0.8	2.0	288-1043-ND*	1.68	7.37	12.63	1162034
				12.5	8	0.8	2.0	288-1044-ND*	1.80	7.88	13.50	1182034
0.50	20	DIN	White	11.5	6	1.1	2.5	288-1007-ND	1.22	5.34	9.15	1161050
				13.5	8	1.1	2.5	288-1008-ND	.87	3.81	6.53	1181050
		W	Orange	11.5	6	1.1	2.5	288-1045-ND	1.22	5.34	9.15	1162050
				13.5	8	1.1	2.5	288-1046-ND	.87	3.81	6.53	1182050
				15.5	10	1.1	2.5	288-1047-ND	1.22	5.34	9.15	11102050
0.75	20	DIN	Gray	12.0	6	1.3	2.8	288-1010-ND	1.28	5.59	9.58	1161075
				14.0	8	1.3	2.8	288-1011-ND	.87	3.81	6.53	1181075
		W	White	12.0	6	1.3	2.8	288-1048-ND	1.28	5.59	9.58	1162075
				14.0	8	1.3	2.8	288-1049-ND	.87	3.81	6.53	1182075
1.00	18	DIN	Red	12.5	6	1.5	3.0	288-1014-ND	1.45	6.35	10.89	1161010
				14.5	8	1.5	3.0	288-1015-ND	.93	4.07	6.97	1181010
		W	Yellow	12.5	6	1.5	3.0	288-1052-ND	1.45	6.35	10.89	1162010
				14.5	8	1.5	3.0	288-1053-ND	.93	4.07	6.97	1182010
				16.5	10	1.5	3.0	288-1054-ND	1.45	6.35	10.89	11102010
				18.5	12	1.5	3.0	288-1055-ND	1.45	6.35	10.89	11122010
1.50	16	DIN	Black	12.5	6	1.8	3.4	288-1018-ND*	2.03	8.89	15.25	1161015
				14.5	8	1.8	3.4	288-1019-ND	1.28	5.59	9.58	1181015
		W	Red	12.5	6	1.8	3.4	288-1056-ND*	2.03	8.89	15.25	1162015
				14.5	8	1.8	3.4	288-1057-ND	1.28	5.59	9.58	1182015
				16.5	10	1.8	3.4	288-1058-ND	2.03	8.89	15.25	11102015
2.08	14	DIN	Yellow	14.5	8	2.05	3.6	288-1023-ND*	1.60	6.99	11.98	1181208
2.50	14	DIN	Blue	15.0	8	2.3	4.2	288-1024-ND	1.28	5.59	9.58	1181025
				19.0	12	2.3	4.2	288-1025-ND	1.74	7.62	13.07	11121025
		W	Blue	15.0	8	2.3	4.2	288-1062-ND	1.28	5.59	9.58	1182025
				19.0	12	2.3	4.2	288-1063-ND	1.74	7.62	13.07	11122025
4.00	12	DIN	Gray	17.5	10	2.9	4.8	288-1027-ND	2.09	9.15	15.68	11101040
				20.0	12	2.9	4.8	288-1028-ND	2.09	9.15	15.68	11121040
		W	Gray	17.5	10	2.9	4.8	288-1065-ND	2.09	7.84	10.45	11102040
				20.0	12	2.9	4.8	288-1066-ND	2.09	7.84	10.45	11122040
6.00	10	DIN	Yellow	20.0	12	3.6	6.2	288-1030-ND	2.76	10.35	13.79	11121060
				20.0	12	3.6	6.2	288-1068-ND	2.76	10.35	13.79	11122060
		W	Black	20.0	12	3.6	6.2	288-1032-ND	2.76	10.35	13.79	11121100
16.00	6	DIN	Blue	23.0	12	6.0	8.8	288-1034-ND	3.78	14.16	18.88	11121160
25.00	4	DIN	Yellow	29.0	16	7.5	11.0	288-1036-ND	9.58	35.94	47.92	11161250


* Does not conform to DIN 46228 Part 4

Note: For additional sizes, please visit our web site.

Size (mm ²)	AWG	Color	Dimensions (mm)				Digi-Key Part No.	Pricing			AE Part No.
			A	B	C	D		10	50	100	
2 x 0.50	2 x 20	White	15.0	8.0	1.5	2.3 / 4.5	288-1124-ND	1.16	5.08	8.71	1381050
2 x 0.75	2 x 20	Gray	15.0	8.0	1.8	2.6 / 5.1	288-1125-ND	1.16	5.08	8.71	1381075
2 x 0.75	2 x 20	Gray	17.0	10.0	1.8	2.6 / 5.1	288-1126-ND	1.48	6.48	11.11	13101075
2 x 1.00	2 x 18	Red	15.0	8.0	2.05	3.2 / 5.1	288-1127-ND	1.36	5.97	10.24	1381010
2 x 1.00	2 x 18	Red	17.0	10.0	2.05	3.2 / 5.1	288-1128-ND	1.89	8.26	14.16	13101010
2 x 1.50	2 x 16	Black	16.0	8.0	2.3	3.5 / 6.4	288-1129-ND	1.63	7.11	12.20	1381015
2 x 1.50	2 x 16	Black	20.0	12.0	2.3	3.5 / 6.4	288-1130-ND	2.32	10.16	17.42	13121015
2 x 2.50	2 x 14	Blue	18.5	10.0	2.9	4.0 / 7.5	288-1131-ND	2.32	10.16	17.42	13101025
2 x 2.50	2 x 14	Blue	21.5	13.0	2.9	4.0 / 7.5	288-1132-ND	2.32	10.16	17.42	13131025
2 x 4.00	2 x 12	Gray	23.0	12.0	3.8	4.9 / 8.6	288-1133-ND	4.21	15.79	21.05	13121040
2 x 6.00	2 x 10	Yellow	25.0	14.0	4.9	5.8 / 9.6	288-1134-ND	4.50	16.88	22.51	13141060
2 x 10.00	2 x 8	Red	26.0	14.0	6.5	7.0 / 12.6	288-1135-ND	5.52	20.69	27.52	13141100
2 x 16.00	2 x 6	Blue	31.0	16.0	8.5	8.8 / 16.6	288-1136-ND	14.52	63.53	108.90	13161160

Wire Ferrules – Non-Insulated

Material: Copper
Surface: Tin-plated



Size (mm ²)	AWG	Dimensions (mm)				Digi-Key Part No.	Pricing			AE Part No.
		A	B	C	D		10	50	100	
0.25	24	5	0.8	1.7	288-1077-ND*	.44	1.91	3.27	12510025	
		7	0.8	1.7	288-1078-ND*	.44	1.91	3.27	12710025	
0.34	22	5	0.9	1.8	288-1079-ND*	.46	2.03	3.48	12510034	
		7	0.9	1.8	288-1080-ND*	.46	2.03	3.48	12710034	
0.50	20	6	1.0	2.1	288-1081-ND	.49	2.16	3.70	12610050	
		8	1.0	2.1	288-1082-ND*	.52	2.29	3.92	12810050	
		10	1.0	2.1	288-1083-ND	.52	2.29	3.92	121010050	
0.75	20	6	1.2	2.3	288-1084-ND	.61	2.67	4.57	12610075	
		8	1.2	2.3	288-1085-ND*	.61	2.67	4.57	12810075	
		10	1.2	2.3	288-1086-ND	.64	2.80	4.79	121010075	
		12	1.2	2.3	288-1087-ND	.70	3.05	5.23	121210075	
1.00	18	6	1.4	2.5	288-1088-ND	.64	2.80	4.79	12610100	
		7	1.4	2.5	288-1089-ND	.64	2.80	4.79	12710100	
		8	1.4	2.5	288-1090-ND*	.64	2.80	4.79	12810100	
		10	1.4	2.5	288-1091-ND	.64	2.80	4.79	121010100	
		12	1.4	2.5	288-1092-ND*	.73	3.18	5.45	121210100	
1.50	16	7	1.7	2.8	288-1093-ND	.67	2.93	5.01	12710150	
		8	1.7	2.8	288-1094-ND	.67	2.93	5.01	12810150	
		10	1.7	2.8	288-1095-ND	.70	3.05	5.23	121010150	
		12	1.7	2.8	288-1096-ND	.78	3.43	5.88	121210150	
		15	1.7	2.8	288-1097-ND*	.78	3.43	5.88	121510150	
2.50	14	7	2.2	3.4	288-1099-ND	.84	3.69	6.32	12710250	
		8	2.2	3.4	288-1100-ND	.84	3.69	6.32	12810250	
		10	2.2	3.4	288-1101-ND	.84	3.69	6.32	121010250	
		12	2.2	3.4	288-1102-ND	.84	3.69	6.32	121210250	
4.00	12	9	2.8	4.0	288-1105-ND	.81	3.56	6.10	12910400	
		10	2.8	4.0	288-1106-ND	.81	3.56	6.10	121010400	
		12	2.8	4.0	288-1107-ND	.73	3.18	5.45	121210400	
6	10	10	3.5	4.7	288-1110-ND	1.63	7.11	12.20	121010600	
		12	3.5	4.7	288-1111-ND	1.63	7.11	12.20	121210600	
10.00	8	12	4.5	5.8	288-1114-ND	1.45	6.35	10.89	1212110	
25.00	4	12	7.3	9.5	288-1121-ND*	7.55	33.03	56.63	1212125	

* Does not conform to DIN 46228 Part 1

Assortment Boxes

288-1147-ND	Assortment Box 1 — 150 pieces DIN Type (30 pieces each of sizes 0.25, 0.34, 0.50, 0.75, and 1.00)	36.30
288-1153-ND	Assortment Box 1 — 150 pieces W Type (30 pieces each of sizes 0.25, 0.34, 0.50, 0.75, and 1.00)	36.30
288-1148-ND	Assortment Box 2 — 400 pieces DIN Type (50 pieces each of sizes 0.50 and 2.50; 100 pieces each of sizes 0.75, 1.00, and 1.50)	54.45
288-1154-ND	Assortment Box 2 — 400 pieces W Type (50 pieces each of sizes 0.50 and 2.50; 100 pieces each of sizes 0.75, 1.00, and 1.50)	54.45
288-1149-ND	Assortment Box 3 — 100 pieces DIN Type (50 pieces each of size 4.00; 20 pieces each of sizes 6.00 and 10.00; 10 pieces of size 16.00)	45.38
288-1155-ND	Assortment Box 3 — 100 pieces W Type (50 pieces each of size 4.00; 20 pieces each of sizes 6.00 and 10.00; 10 pieces of size 16.00)	45.38
288-		