

**DEMULATION AND CODING PRODUCT**

Intel Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	10	100
N2105CM	828541-ND	Digital CMOS QPSK Cable Demod... 68-PLCC	17.97	15.98	12.78	

**PERIPHERAL INTERFACE PRODUCTS**

Intel Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	10	100
GCIXB3208AA	831425-ND	8-Port, 32-Bit, IX Bus Peripheral Controller.....352-BGA	78.10	70.57	63.52	
EE87C42	863950-ND	8-Bit, Universal Peripheral Interface Slave Microcontroller*.....44-PLCC	12.71	11.95	8.90	

**MODEM CHIPSETS, CONTROLLERS, DSPs, AFEs**

Intel Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	10	100
MD5660AMS101	830882-ND	ISA/Serial Modem Chipset (MD4450CSCB, MD5660DTMA, MD1724T11VCB).....	6.76	—	—	
MD5661AMV101	830883-ND	PCMCIA Modem Chipset (MD4451CVCB, MD5661DTLA, MD1724T11VCB).....	10.68	8.44	—	
MD5662AMS101	830884-ND	ISA/Serial Modem Chipset (MD4450CSCB, MD5660DTMA, (MD1724T11VCB, 2pcs).....	9.95	—	—	
MD5675TS101	830885-ND	USB Modem Chipset (MD4470CSCB, MD5660DTMA, MD1724T11VCB).....	13.73	10.85	—	
DOMD4451CVCB	830839-ND	5V, 4451CV Controller.....128-LQFP	5.88	5.45	4.14	
FYMD4450CSCB	830837-ND	5V, 4450CS Controller.....128-SQFP	5.88	5.45	4.14	
FYMD4450CVCB	830890-ND	5V, 4450CV Controller.....128-SQFP	12.81	12.05	8.97	
FYMD4470CSCB	830849-ND	5V, 4470CS Controller.....128-SQFP	12.49	11.74	8.75	
DJMD5628DLB	830836-ND	3.3V, 5628 Digital Signal Proc.....100-LQFP	6.86	6.36	4.83	
DOMD5661DTLA	830848-ND	3.3V, 5661 Digital Signal Proc.....128-LQFP	5.88	5.45	4.14	
FYMD5660DTMA	830842-ND	3.3V, 5660 Digital Signal Proc.....128-SQFP	5.88	5.45	4.14	
FYMD8820	830850-ND	3.3V, 8820 Digital Signal Proc.....128-SQFP	36.50	34.68	26.47	
DYMD1724T11VCB	830851-ND	5V, Sigma-Delta Analog Front End....44-LQFP	2.18	2.00	1.53	

**XSCALE™ STORAGE PROCESSORS**

Intel Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	10	100
FW80219M600SL7CM	858207-ND	32-Bit, GP, High Perf. PCI Processor with Xscale™ Microarchitecture with 64-Bit PCI-X Interface, 600MHz.....544-BGA	44.83	40.12	32.45	
FW80321M600SL6R3	850667-ND	32-Bit, High Perf. PCI Processor with Xscale™ Microarchitecture with 64-Bit PCI-X Interface, 600MHz.....544-BGA	99.30	89.73	80.76	

**XSCALE™ NETWORK PROCESSORS**

Intel Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	10	100
FWIXP421BB	852277-ND	266MHz Network Processor with Xscale™ Core, 2 HSS Serial Ports.....492-BGA	23.51	20.90	16.72	
FWIXP425BB	852264-ND	266MHz, 2 HSS Ports, Crypto Processor Support, 2 Integrated 10/100 Ethernet MAC, Utupia 2 Interface.....492-BGA	28.16	25.04	20.03	
FWIXP425BD	852279-ND	533MHz, 2 HSS Ports, Crypto Processor Support, 2 Integrated 10/100 Ethernet MAC, Utupia 2 Interface.....492-BGA	45.67	40.87	33.06	

**FLASH MEMORY**

Numonyx Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	10	100
SLC Large Page Series — RoHS Compliant						
NAND01GR3B2ZA6E	NAND01GR3B2ZA6E-ND	1Gb NAND Flash.....63-VFBGA	7.91	7.00	5.65	
NAND01GW3B2BN6E	NAND01GW3B2BN6E-ND	1Gb NAND Flash.....48-TSOP	14.64	13.27	10.52	
NAND01GW3B2ZA6E	NAND01GW3B2ZA6E-ND	1Gb NAND Flash.....63-VFBGA	7.91	7.00	5.65	
NAND01GW3B2CN6E	NAND01GW3B2CN6E-ND	1Gb NAND Flash.....48-TSOP	5.95	4.73	4.12	
NAND02GR3B2DZA6E	NAND02GR3B2DZA6E-ND	2Gb NAND Flash.....63-VFBGA	11.64	10.31	8.32	
NAND02GW3B2DN6E	NAND02GW3B2DN6E-ND	2Gb NAND Flash.....48-TSOP	11.64	10.31	8.32	
NAND02GW3B2DZA6E	NAND02GW3B2DZA6E-ND	2Gb NAND Flash.....63-VFBGA	11.64	10.31	8.32	
NAND04GW3B2DN6E	NAND04GW3B2DN6E-ND	4Gb NAND Flash.....48-TSOP	14.45	13.10	10.39	
NAND08GW3B2CN6E	NAND08GW3B2CN6E-ND	8Gb NAND Flash.....48-TSOP	21.07	19.10	15.15	
NAND12BW3A2BN6E	NAND12BW3A2BN6E-ND	128Mb NAND Flash.....48-TSOP	4.90	4.02	3.40	
NAND512R3A2CZA6E	NAND512R3A2CZA6E-ND	512Mb NAND Flash...63-VFBGA	8.57	7.59	6.12	
NAND512W3A2CN6E	NAND512W3A2CN6E-ND	512Mb NAND Flash.....48-TSOP	8.57	7.59	6.12	
NAND512W3A2CZA6E	NAND512W3A2CZA6E-ND	512Mb NAND Flash...63-VFBGA	8.57	7.59	6.12	
C3 Series						
PC28F800C3BD70	870886-ND	8Mb, 3V, Flash Memory (1Mx8)*.....64-BGA	2.00	1.88	1.50	
GE28F160C3TD70	853978-ND	16Mb, 3V, Flash Memory (1Mx16).....46-BGA	2.72	2.50	1.91	
PC28F160C3BD70	865397-ND	16Mb, 3V, Flash Memory (1Mx16)*.....64-BGA	2.18	2.00	1.53	
PC28F160C3TD70	865400-ND	16Mb, 3V, Flash Memory (1Mx16)*.....64-BGA	2.18	2.00	1.53	
RD28F1604C3BD70855156	855156-ND	16Mb, 3V, Stacked Flash Memory.....66-EBGA	5.55	5.14	3.91	
JS28F160B3TD70	866262-ND	16Mb, 3V, Flash Memory (1Mx16)*.....48-TSOP	2.18	2.00	1.53	

Numonyx Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	10	100
JS28F160C3BD70	866264-ND	16Mb, 3V, Flash Memory (1Mx16)*.....48-TSOP	2.33	2.14	1.64	
JS28F160C3TD70	866265-ND	16Mb, 3V, Flash Memory (1Mx16)*.....48-TSOP	2.18	2.00	1.53	
PC28F320C3BD70	865363-ND	32Mb, 3V, Flash Memory (2Mx16)*.....64-BGA	3.03	2.78	2.12	
RC28F320C3TD70	851145-ND	32Mb, 3V, Flash Memory (2Mx16).....64-BGA	3.03	2.78	2.12	
JS28F320C3BD70	864836-ND	32Mb, 3V, Flash Memory (2Mx16)*.....48-TSOP	3.03	2.78	2.12	
JS28F320C3TD70	864838-ND	32Mb, 3V, Flash Memory (2Mx16)*.....48-TSOP	3.03	2.78	2.12	

**EMBEDDED FLASH**

Numonyx Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	10	100
J3D Series						
TE28F320J3D75 872335	872335-ND	32Mb, 3V, Embedded Flash.....56-TSOP	3.35	3.08	2.35	
JS28F320J3D75 S L8YL	876990CT-ND	32Mb, 3V, Embedded Flash*.....56-TSOP	2.80	2.48	1.92	
JS28F320J3D75 S L8YL	876990TR-ND	32Mb, 3V, Embedded Flash*.....56-TSOP	1724.98/1,600			
JS28F320J3D75 872337	872337-ND	32Mb, 3V, Embedded Flash.....56-TSOP	3.35	3.08	2.35	
JS28F320J3D75 872339	872339CT-ND	32Mb, 3V, Embedded Flash*.....56-TSOP	2.80	2.48	1.92	
JS28F320J3D75 872339	872339TR-ND	32Mb, 3V, Embedded Flash*.....56-TSOP	1724.98/1,600			
JS28F320J3D75 S L8YM	877042-ND	32Mb, 3V, Embedded Flash*.....56-TSOP	3.35	3.08	2.35	
RC28F320J3D75 S L8OS	872859CT-ND	32Mb, 3V, Embedded Flash.....64-EZBGA	2.80	2.48	1.92	
RC28F320J3D75 S L8OS	872859TR-ND	32Mb, 3V, Embedded Flash.....64-EZBGA	2044.42/2,000			
RC28F320J3D75 S L8ZR	877047-ND	32Mb, 3V, Embedded Flash.....64-EZBGA	2.40	2.20	1.68	
RC28F320J3D75 876045	876045-ND	32Mb, 3V, Embedded Flash.....64-EZBGA	2.40	2.20	1.68	
PC28F320J3D75 S L8OY	872833CT-ND	32Mb, 3V, Embedded Flash*.....64-EZBGA	2.80	2.48	1.92	
PC28F320J3D75 S L8OY	872833TR-ND	32Mb, 3V, Embedded Flash*.....64-EZBGA	2044.42/2,000			
PC28F320J3D75 876043	876043CT-ND	32Mb, 3V, Embedded Flash*.....64-EZBGA	2.80	2.48	1.92	
PC28F320J3D75 876043	876043TR-ND	32Mb, 3V, Embedded Flash*.....64-EZBGA	2044.42/2,000			
PC28F320J3D75 876051	876051-ND	32Mb, 3V, Embedded Flash*.....64-EZBGA	2.40	2.20	1.68	
PC28F320J3D75 S L8ZS	877053-ND	32Mb, 3V, Embedded Flash*.....64-EZBGA	3.35	3.08	2.35	
TE28F640J3D75 872332	872332CT-ND	64Mb, 3V, Embedded Flash.....56-TSOP	6.97	6.32	5.01	
TE28F640J3D75 872332	872332TR-ND	64Mb, 3V, Embedded Flash.....56-TSOP	4634.78/1,600			
TE28F640J3D75 872333	872333-ND	64Mb, 3V, Embedded Flash.....56-TSOP	5.55	5.14	3.91	
JS28F640J3D75 S L8YP	876722CT-ND	64Mb, 3V, Embedded Flash*.....56-TSOP	6.97	6.32	5.01	
JS28F640J3D75 S L8YP	876722TR-ND	64Mb, 3V, Embedded Flash*.....56-TSOP	4634.78/1,600			
JS28F640J3D75 872336	872336-ND	64Mb, 3V, Embedded Flash*.....56-TSOP	5.55	5.14	3.91	
JS28F640J3D75 872338	872338CT-ND	64Mb, 3V, Embedded Flash*.....56-TSOP	6.97	6.32	5.01	
JS28F640J3D75 872338	872338TR-ND	64Mb, 3V, Embedded Flash*.....56-TSOP	4634.78/1,600			
JS28F640J3D75 S L8YQ	876760-ND	64Mb, 3V, Embedded Flash*.....56-TSOP	5.55	5.14	3.91	
RC28F640J3D75 S L8ZQ	877050-ND	64Mb, 3V, Embedded Flash.....64-EZBGA	5.88	5.45	4.14	
RC28F640J3D75 872380	872380CT-ND	64Mb, 3V, Embedded Flash.....64-EZBGA	6.97	6.32	5.01	
RC28F640J3D75 872380	872380TR-ND	64Mb, 3V, Embedded Flash.....64-EZBGA	5553.90/2,000			
RC28F640J3D75 875775	875775-ND	64Mb, 3V, Embedded Flash.....64-EZBGA	5.55	5.14	3.91	
PC28F640J3D75 S L8OW	872860CT-ND	64Mb, 3V, Embedded Flash*.....64-EZBGA	6.97	6.32	5.01	
PC28F640J3D75 S L8OW	872860TR-ND	64Mb, 3V, Embedded Flash*.....64-EZBGA	5553.90/2,000			
PC28F640J3D75 875776	875776-ND	64Mb, 3V, Embedded Flash*.....64-EZBGA	5.88	5.45	4.14	
PC28F640J3D75 S L8ZT	877116-ND	64Mb, 3V, Embedded Flash*.....64-EZBGA	5.55	5.14	3.91	
TE28F128J3D75 872762	872762CT-ND	128Mb, 3V, Embedded Flash.....56-TSOP	10.53	10.17	7.99	
TE28F128J3D75 872762	872762TR-ND	128Mb, 3V, Embedded Flash.....56-TSOP	7550.40/1,600			
TE28F128J3D75 872764	872764-ND	128Mb, 3V, Embedded Flash.....56-TSOP	9.60	8.90	6.76	
JS28F128J3D75 872766	872766-ND	128Mb, 3V, Embedded Flash*.....56-TSOP	9.60	8.90	6.76	
JS28F128J3D75 872767	872767CT-ND	128Mb, 3V, Embedded Flash*.....56-TSOP	10.53	10.17	7.99	
JS28F128J3D75 872767	872767TR-ND	128Mb, 3V, Embedded Flash*.....56-TSOP	7550.40/1,600			
RC28F128J3D75 S L8QN	872828CT-ND	128Mb, 3V, Embedded Flash.....64-EZBGA	10.53	10.17	7.99	
RC28F128J3D75 S L8QN	872828TR-ND	128Mb, 3V, Embedded Flash.....64-EZBGA	9075.00/2,000			

*RoHS Compliant

(Continued)

★ CALL FOR LOWER PRICING ON LARGER QUANTITIES! ★

Free shipping on orders over £50! All prices are in British pound sterling and include duties.

uk.digikey.com — FREEPHONE: 0-800-587-0991 • 0-800-904-7786 — FREEFAX: 0-800-587-0992 • 0-800-904-7783

(UK091) 737

