

numonyx		Digi-Reel®		StrataFlash® (Continued)		
Numonyx Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	10	100
JS28F128P33B85 888018	888018-ND	128Mb, 3V StrataFlash® Memory*.....56-TSOP	7.08	6.56	4.98	
JS28F128P33T85 888019	888019-ND	128Mb, 3V StrataFlash® Memory*.....56-TSOP	7.08	6.56	4.98	
RC28F128P33B85 888066	888066-ND	128Mb, 3V StrataFlash® Memory*.....64-EZBGA	7.49	6.94	5.27	
RC28F128P33T85 888067	888067-ND	128Mb, 3V StrataFlash® Memory*.....64-EZBGA	7.08	6.56	4.98	
PC28F128P33B85 888064	888064-ND	128Mb, 3V StrataFlash® Memory*.....64-EZBGA	7.08	6.56	4.98	
PC28F128P33B85 S LA37	888020-ND	128Mb, 3V StrataFlash® Memory*.....64-EZBGA	7.08	6.56	4.98	
PC28F128P33B85 S LA4N	888347CT-ND	128Mb, 3V StrataFlash® Memory*.....64-EZBGA	10.53	10.17	7.99	
PC28F128P33B85 S LA4N	888347TR-ND	128Mb, 3V StrataFlash® Memory*.....64-EZBGA			9075.00/2,000	
PC28F128P33T85 S LALN	892799CT-ND	128Mb, 3V StrataFlash® Memory*.....64-EZBGA	10.53	10.17	7.99	
PC28F128P33T85 S LALN	892799TR-ND	128Mb, 3V StrataFlash® Memory*.....64-EZBGA			9075.00/2,000	
PC28F128P33T85 888065	888065-ND	128Mb, 3V StrataFlash® Memory*.....64-EZBGA	9.08	8.54	6.36	
PC28F128P33T85 S LALM	892798-ND	128Mb, 3V StrataFlash® Memory*.....64-EZBGA	7.08	6.56	4.98	
TE28F256P33B95 884142	884142-ND	256Mb, 3V StrataFlash® Memory*.....56-TSOP	9.33	8.77	6.54	
TE28F256P33T95 883590	883590-ND	256Mb, 3V StrataFlash® Memory*.....56-TSOP	9.33	8.77	6.54	
JS28F256P33B95 884143	884143-ND	256Mb, 3V StrataFlash® Memory*.....56-TSOP	9.33	8.77	6.54	
JS28F256P33T95 883593	883593-ND	256Mb, 3V StrataFlash® Memory*.....56-TSOP	9.86	9.27	6.90	
RC28F256P33B85 884144	884144-ND	256Mb, 3V StrataFlash® Memory*.....64-EZBGA	9.86	9.27	6.90	
RC28F256P33T85 883591	883591-ND	256Mb, 3V StrataFlash® Memory*.....64-EZBGA	9.33	8.77	6.54	
PC28F256P33B85 884145	884145-ND	256Mb, 3V StrataFlash® Memory*.....64-EZBGA	9.33	8.77	6.54	
PC28F256P33B85 S L9R6	884123CT-ND	256Mb, 3V StrataFlash® Memory*.....64-EZBGA	14.74	14.23	11.19	
PC28F256P33B85 S L9R6	884123TR-ND	256Mb, 3V StrataFlash® Memory*.....64-EZBGA			12705.00/2,000	
PC28F256P33B85 S LA8F	889994-ND	256Mb, 3V StrataFlash® Memory*.....64-EZBGA	9.33	8.77	6.54	
PC28F256P33T85 883595	883595-ND	256Mb, 3V StrataFlash® Memory*.....64-EZBGA	9.33	8.77	6.54	
JS48F4400POTB00887798	887798-ND	512Mb, 3V StrataFlash® Memory*.....56-TSOP	16.07	15.10	11.25	
TE48F4400POTB00887797	887797-ND	512Mb, 3V StrataFlash® Memory*.....56-TSOP	16.34	15.36	11.44	
RC48F4400POTB00885960	885960-ND	512Mb, 3V StrataFlash® Memory*.....64-EZBGA	16.34	15.36	11.44	
PC48F4400POTB00885967	885967-ND	512Mb, 3V StrataFlash® Memory*.....64-EZBGA	16.34	15.36	11.44	
PC48F4400POTB00S LAFB	891111-ND	512Mb, 3V StrataFlash® Memory*.....64-EZBGA	16.34	15.36	11.44	
PF38F3050M0Y3DE 896724	896724-ND	128Mb, 1.8V NOR Flash*.....56-SCSP	9.58	8.88	6.75	
PF38F4050M0Y3CF 891082	891082-ND	256Mb, 1.8V NOR Flash*.....107-SCSP	11.65	10.96	8.16	
PF38F5060M0Y0BE 886439	886439-ND	512Mb, 1.8V NOR Flash*.....105-SCSP	13.98	13.14	9.79	

numonyx		Digi-Reel®		MEMORY CARDS		
				RoHS Compliant		
Numonyx Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	25	100
SMC064BF6E	SMC064BF6E-ND	64Mb CompactFlash Card.....	33.69	31.37	25.56	
SMC128BF06E	SMC128BF06E-ND	128Mb CompactFlash Card.....	34.38	32.02	26.09	
SMC256BFJ6E	SMC256BFJ6E-ND	256Mb CompactFlash Card.....	39.58	36.86	30.03	
SMC512BFK6E	SMC512BFK6E-ND	512Mb CompactFlash Card.....	46.65	43.20	34.56	
SMC01GBFK6E	SMC01GBFK6E-ND	1Gb CompactFlash Card.....	41.16	38.12	30.50	
SMC02GBFK6E	SMC02GBFK6E-ND	2Gb CompactFlash Card.....	83.35	75.42	63.51	
SMC04GBFK6E	SMC04GBFK6E-ND	4Gb CompactFlash Card.....	139.40	123.91	108.42	

numonyx		Digi-Reel®		CODE STORAGE		
				RoHS Compliant		
Numonyx Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	10	100
<b>M25P Series</b>						
M25P05-AVMB6TP	M25P05-AVMB6TPCT-ND	512Kb, Serial Flash, 50MHz SPI Bus Interface.....8-UDFPN	1.09	.91	.77	
M25P05-AVMB6TP	M25P05-AVMB6TPTR-ND	512Kb, Serial Flash, 50MHz SPI Bus Interface.....8-UDFPN			1179.75/2,500	
M25P05-AVMN6TP	M25P05-AVMN6TPCT-ND	512Kb, Serial Flash, 50MHz SPI Bus Interface.....SO-8	1.09	.91	.77	
M25P05-AVMN6TP	M25P05-AVMN6TPTR-ND	512Kb, Serial Flash, 50MHz SPI Bus Interface.....SO-8			1270.50/2,500	
M25P05-AVMP6TG	M25P05-AVMP6TGCT-ND	512Kb, Serial Flash, 50MHz SPI Bus Interface.....8-VDFPN	1.09	.91	.77	
M25P05-AVMP6TG	M25P05-AVMP6TGTR-ND	512Kb, Serial Flash, 50MHz SPI Bus Interface.....8-VDFPN			2369.66/4,000	

Numonyx Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	10	100
M25P10-AVMB6TG	M25P10-AVMB6TGCT-ND	1Mb, Serial Flash, 50MHz SPI Bus Interface.....8-UDFPN	1.31	1.09	.92	
M25P10-AVMB6TG	M25P10-AVMB6TGTR-ND	1Mb, Serial Flash, 50MHz SPI Bus Interface.....8-UDFPN			1415.70/2,500	
M25P10-AVMN3P/X	M25P10-AVMN3P/X-ND	1Mb, Serial Flash, 50MHz SPI Bus Interface.....SO-8	13.1	1.09	.92	
M25P10-AVMN3TP/X	M25P10-AVMN3TP/XCT-ND	1Mb, Serial Flash, 50MHz SPI Bus Interface.....SO-8	1.31	1.09	.92	
M25P10-AVMN3TP/X	M25P10-AVMN3TP/XTR-ND	1Mb, Serial Flash, 50MHz SPI Bus Interface.....SO-8			1415.70/2,500	
M25P10-AVMN6TP	M25P10-AVMN6TPCT-ND	1Mb, Serial Flash, 50MHz SPI Bus Interface.....SO-8	1.20	1.00	.84	
M25P10-AVMN6TP	M25P10-AVMN6TPTR-ND	1Mb, Serial Flash, 50MHz SPI Bus Interface.....SO-8			1510.08/2,500	
M25P10-AVMP6TG	M25P10-AVMP6TGCT-ND	1Mb, Serial Flash, 50MHz SPI Bus Interface.....8-VDFPN	1.31	1.09	.92	
M25P10-AVMP6TG	M25P10-AVMP6TGTR-ND	1Mb, Serial Flash, 50MHz SPI Bus Interface.....8-VDFPN			2648.45/4,000	
M25P16-VME6G	M25P16-VME6G-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....8-VDFPN	2.87	2.36	1.99	
M25P16-VME6TG	M25P16-VME6TGCT-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....8-VDFPN	1.96	1.71	1.28	
M25P16-VME6TG	M25P16-VME6TGTR-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....8-VDFPN			4408.27/4,000	
M25P16-VMF6TP	M25P16-VMF6TPCT-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....SO-16	3.31	2.89	2.15	
M25P16-VMF6TP	M25P16-VMF6TPTR-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....SO-16			3648.15/2,500	
M25P16-VMN6P	M25P16-VMN6P-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....SO-8	2.83	2.33	1.97	
M25P16-VMN6P/ALT	M25P16-VMN6P/ALT-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....SO-8	1.96	1.71	1.28	
M25P16-VMN6TP	M25P16-VMN6TPCT-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....SO-8	1.96	1.71	1.28	
M25P16-VMN6TP	M25P16-VMN6TPTR-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....SO-8			2722.50/2,500	
M25P16-VMP6G	M25P16-VMP6G-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....8-VDFPN	3.11	2.56	2.16	
M25P16-VMP6TG	M25P16-VMP6TGCT-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....8-VDFPN	1.96	1.71	1.28	
M25P16-VMP6TG	M25P16-VMP6TGTR-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....8-VDFPN			4791.60/4,000	
M25P16-VMW6TG	M25P16-VMW6TGCT-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....SO-8	1.96	1.71	1.28	
M25P16-VMW6TG	M25P16-VMW6TGTR-ND	16Mb, Serial Flash, 75MHz SPI Bus Interface.....SO-8			4356.00/4,000	
M25P32-VME6G	M25P32-VME6G-ND	32Mb, LV, Serial Flash, 75MHz SPI Bus Interface.....8-VDFPN	4.65	3.81	3.22	
M25P32-VME6TG	M25P32-VME6TGCT-ND	32Mb, LV, Serial Flash, 75MHz SPI Bus Interface.....8-VDFPN	2.16	1.88	1.40	
M25P32-VME6TG	M25P32-VME6TGTR-ND	32Mb, LV, Serial Flash, 75MHz SPI Bus Interface.....8-VDFPN			7143.84/4,000	
M25P32-VMF6TP	M25P32-VMF6TPCT-ND	32Mb, LV, Serial Flash, 75MHz SPI Bus Interface.....SO-16	4.64	4.24	3.36	
M25P32-VMF6TP	M25P32-VMF6TPTR-ND	32Mb, LV, Serial Flash, 75MHz SPI Bus Interface.....SO-16			1928.26/1,000	
M25P32-VMP6G	M25P32-VMP6G-ND	32Mb, LV, Serial Flash, 75MHz SPI Bus Interface.....8-VDFPN	4.65	3.81	3.22	
M25P32-VMP6TG	M25P32-VMP6TGCT-ND	32Mb, LV, Serial Flash, 75MHz SPI Bus Interface.....8-VDFPN	2.16	1.88	1.40	
M25P32-VMP6TG	M25P32-VMP6TGTR-ND	32Mb, LV, Serial Flash, 75MHz SPI Bus Interface.....8-VDFPN			7143.84/4,000	
M25P32-VMW6G	M25P32-VMW6G-ND	32Mb, LV, Serial Flash, 75MHz SPI Bus Interface.....SO-8	4.39	3.61	3.04	
M25P32-VMW6TG	M25P32-VMW6TGCT-ND	32Mb, LV, Serial Flash, 75MHz SPI Bus Interface.....SO-8	2.16	1.88	1.40	
M25P32-VMW6TG	M25P32-VMW6TGTR-ND	32Mb, LV, Serial Flash, 75MHz SPI Bus Interface.....SO-8			2802.00/1,500	
M25P40-VMN3P/X	M25P40-VMN3P/X-ND	4Mb, LV, Serial Flash.....SO-8	1.74	1.46	1.22	
M25P40-VMN6TP	M25P40-VMN6TPCT-ND	4Mb, LV, Serial Flash.....SO-8	1.74	1.46	1.22	
M25P40-VMN6TP	M25P40-VMN6TPTR-ND	4Mb, LV, Serial Flash.....SO-8			2381.28/2,500	
M25P40-VMN3TP/X	M25P40-VMN3TP/XCT-ND	4Mb, LV, Serial Flash.....SO-8	1.74	1.46	1.22	
M25P40-VMN3TP/X	M25P40-VMN3TP/XTR-ND	4Mb, LV, Serial Flash.....SO-8			1887.60/2,500	
M25P40-VMN6TPMX	M25P40-VMN6TPMXCT-ND	4Mb, LV, Serial Flash.....SO-8	1.74	1.46	1.22	
M25P40-VMN6TPMX	M25P40-VMN6TPMXTR-ND	4Mb, LV, Serial Flash.....SO-8			1887.60/2,500	
M25P40-VMN6TPSO	M25P40-VMN6TPSOCT-ND	4Mb, LV, Serial Flash.....SO-8	1.74	1.46	1.22	
M25P40-VMN6TPSO	M25P40-VMN6TPSOCT-ND	4Mb, LV, Serial Flash.....SO-8			1887.60/2,500	
M25P40-VMP6G/TS	M25P40-VMP6G/TS-ND	4Mb, LV, Serial Flash.....8-VDFPN	1.74	1.46	1.22	
M25P40-VMP6G/TS	M25P40-VMP6G/TSCT-ND	4Mb, LV, Serial Flash.....8-VDFPN			174.146.122	
M25P40-VMP6G/TS	M25P40-VMP6G/TS-ND	4Mb, LV, Serial Flash.....8-VDFPN	1.74	1.46	1.22	
M25P40-VMP6G/TS	M25P40-VMP6G/TS-ND	4Mb, LV, Serial Flash.....8-VDFPN			3020.16/4,000	
M25P80-VMN3TP/4	M25P80-VMN3TP/4CT-ND	8Mb, LV, Serial Flash.....SO-8	1.96	1.64	1.38	
M25P80-VMN3TP/4	M25P80-VMN3TP/4TR-ND	8Mb, LV, Serial Flash.....SO-8			2123.55/2,500	
M25P80-VMN6TP	M25P80-VMN6TPCT-ND	8Mb, LV, Serial Flash.....SO-8	1.96	1.64	1.38	
M25P80-VMN6TP	M25P80-VMN6TPTR-ND	8Mb, LV, Serial Flash.....SO-8			2526.48/2,500	
M25P80-VMP6TG	M25P80-VMP6TGCT-ND	8Mb, LV, Serial Flash.....8-VDFPN	1.96	1.64	1.38	
M25P80-VMP6TG	M25P80-VMP6TGTR-ND	8Mb, LV, Serial Flash.....8-VDFPN			4228.22/4,000	
M25P80-VMW6TG	M25P80-VMW6TGCT-ND	8Mb, LV, Serial Flash.....SO-8	1.96	1.64	1.38	
M25P80-VMW6TG	M25P80-VMW6TGTR-ND	8Mb, LV, Serial Flash.....SO-8			1696.12/1,500	
M25P64-VME6TG	M25P64-VME6TGCT-ND	64Mb, LV, Serial Flash.....8-VDFPN	5.01	4.58	3.62	
M25P64-VME6TG	M25P64-VME6TGTR-ND	64Mb, LV, Serial Flash.....8-VDFPN			10367.28/4,000	
M25P64-VMF6TP	M25P64-VMF6TPCT-ND	64Mb, LV, Serial Flash.....SO-16	8.18	7.48	5.19	
M25P64-VMF6TP	M25P64-VMF6TPTR-ND	64Mb, LV, Serial Flash.....SO-16			2868.28/1,000	
M25P128-VME6G	M25P128-VME6G-ND	128Mb, LV, Serial Flash.....8-VDFPN	7.18	6.56	5.19	
M25P128-VMF6P	M25P128-VMF6P-ND	128Mb, LV, Serial Flash.....SO-16	10.93	9.68	7.81	
M25P128-VMF6PALT	M25P128-VMF6PALT-ND	128Mb, LV, Serial Flash.....SO-16	7.26	6.72	5.09	
M25P128-VMF6TP	M25P128-VMF6TPCT-ND	128Mb, LV, Serial Flash.....SO-16	7.26	6.72	5.09	
M25P128-VMF6TP	M25P128-VMF6TPTR-ND	128Mb, LV, Serial Flash.....SO-16			4994.88/1,000	

\*RoHS Compliant

★ CALL FOR LOWER PRICING ON LARGER QUANTITIES! ★

Free shipping on orders over £50! All prices are in British pound sterling and include duties.

uk.digikey.com — FREEPHONE: 0-800-587-0991 • 0-800-904-7786 — FREEFAX: 0-800-587-0992 • 0-800-904-7783

(UK091) 739