

numonyx		Digi+Reel		PARAMETER AND DATA STORAGE — RoHS Compliant		
Numonyx Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	10	100
M25PE Series						
M25PE10-VMN6P	M25PE10-VMN6P-ND	1Mb, Page-Erasable Serial Flash.....SO-8		1.52	1.20	1.02
M25PE10-VMN6TP	M25PE10-VMN6TPCT-ND	1Mb, Page-Erasable Serial Flash.....SO-8		1.31	1.09	.92
M25PE10-VMN6TP	M25PE10-VMN6TPTR-ND	1Mb, Page-Erasable Serial Flash.....SO-8		1452.00/2,500		
M25PE10-VMP6TG	M25PE10-VMP6TGCT-ND	1Mb, Page-Erasable Serial Flash.....8-VDFPN		1.31	1.09	.92
M25PE10-VMP6TG	M25PE10-VMP6TGTR-ND	1Mb, Page-Erasable Serial Flash.....8-VDFPN		2265.12/4,000		
M25PE20-VMN6P	M25PE20-VMN6P-ND	2Mb, Page-Erasable Serial Flash.....SO-8		2.23	1.75	1.49
M25PE20-VMN6TP	M25PE20-VMN6TPCT-ND	2Mb, Page-Erasable Serial Flash.....SO-8		1.52	1.28	1.07
M25PE20-VMN6TP	M25PE20-VMN6TPTR-ND	2Mb, Page-Erasable Serial Flash.....SO-8		2119.92/2,500		
M25PE20-VMP6G	M25PE20-VMP6G-ND	2Mb, Page-Erasable Serial Flash.....8-VDFPN		1.52	1.28	1.07
M25PE40-VMN6TP	M25PE40-VMN6TPCT-ND	4Mb, Page-Erasable Serial Flash.....SO-8		1.74	1.46	1.22
M25PE40-VMN6TP	M25PE40-VMN6TPTR-ND	4Mb, Page-Erasable Serial Flash.....SO-8		2642.64/2,500		
M25PE40-VMP6TG	M25PE40-VMP6TGCT-ND	4Mb, Page-Erasable Serial Flash.....8-VDFPN		1.54	1.29	1.08
M25PE40-VMP6TG	M25PE40-VMP6TGTR-ND	4Mb, Page-Erasable Serial Flash.....8-VDFPN		3280.36/4,000		
M25PE40-VMW6G	M25PE40-VMW6G-ND	4Mb, Page-Erasable Serial Flash.....SO-8		2.04	1.61	1.36
M25PE80-VMN6TP	M25PE80-VMN6TPCT-ND	8Mb, Page-Erasable Serial Flash.....SO-8		1.96	1.64	1.38
M25PE80-VMN6TP	M25PE80-VMN6TPTR-ND	8Mb, Page-Erasable Serial Flash.....SO-8		3239.78/2,500		
M25PE80-VMP6TG	M25PE80-VMP6TGCT-ND	8Mb, Page-Erasable Serial Flash.....8-VDFPN		1.96	1.64	1.38
M25PE80-VMP6TG	M25PE80-VMP6TGTR-ND	8Mb, Page-Erasable Serial Flash.....8-VDFPN		5183.64/4,000		
M25PE80-VMS6TG	M25PE80-VMS6TGCT-ND	8Mb, Page-Erasable Serial Flash.....8L-QFN		1.96	1.64	1.38
M25PE80-VMS6TG	M25PE80-VMS6TGTR-ND	8Mb, Page-Erasable Serial Flash.....8L-QFN		3397.68/4,000		
M25PE80-VMW6TG	M25PE80-VMW6TGCT-ND	8Mb, Page-Erasable Serial Flash.....SO-8		2.55	2.22	1.66
M25PE80-VMW6TG	M25PE80-VMW6TGTR-ND	8Mb, Page-Erasable Serial Flash.....SO-8		2060.82/1,500		
M25PE16-VMP6TG	M25PE16-VMP6TGCT-ND	16Mb, Page-Erasable Serial Flash.....8-VDFPN		1.96	1.71	1.28
M25PE16-VMP6TG	M25PE16-VMP6TGTR-ND	16Mb, Page-Erasable Serial Flash.....8-VDFPN		3717.12/4,000		
M25PE16-VMW6TG	M25PE16-VMW6TGCT-ND	16Mb, Page-Erasable Serial Flash.....SO-8		2.04	1.78	1.33
M25PE16-VMW6TG	M25PE16-VMW6TGTR-ND	16Mb, Page-Erasable Serial Flash.....SO-8		1848.58/1,500		

numonyx		Digi+Reel		CODE AND DATA STORAGE — RoHS Compliant		
Numonyx Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	10	100
M25PX Series						
M25PX80-VMW6G	M25PX80-VMW6G-ND	8Mb, Dual I/O, 4Kbyte Subsector Erase, Serial Flash.....SO-8		1.31	1.14	.88
M25PX32-VMF6F	M25PX32-VMF6FCT-ND	32Mb, Dual I/O, 4Kbyte Subsector Erase, Serial Flash.....SO-16		2.16	1.88	1.40
M25PX32-VMF6F	M25PX32-VMF6FTR-ND	32Mb, Dual I/O, 4Kbyte Subsector Erase, Serial Flash.....SO-16		1593.21/1,500		
M25PX32-VMP6E	M25PX32-VMP6E-ND	32Mb, Dual I/O, 4Kbyte Subsector Erase, Serial Flash.....8-VDFPN		3.09	2.54	2.14
M25PX64-VME6G	M25PX64-VME6G-ND	64Mb, Dual I/O, 4Kbyte Subsector Erase, Serial Flash.....8-VDFPN		5.01	4.58	3.62
M25PX64-VMF6P	M25PX64-VMF6P-ND	64Mb, Dual I/O, 4Kbyte Subsector Erase, Serial Flash.....SO-16		3.95	3.44	2.56
M25PX64-VMF6TP	M25PX64-VMF6TPCT-ND	64Mb, Dual I/O, 4Kbyte Subsector Erase, Serial Flash.....SO-16		5.01	4.58	3.62
M25PX64-VMF6TP	M25PX64-VMF6TPTR-ND	64Mb, Dual I/O, 4Kbyte Subsector Erase, Serial Flash.....SO-16		2776.95/1,000		

numonyx		Digi+Reel		INDUSTRY STANDARD BOOT BLOCK — RoHS Compliant		
Numonyx Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	10	100
M28W Series						
M28W160CB70N6E	M28W160CB70N6E-ND	16Mb (1Mbx16, Boot Block) 3V Supply Flash.....48-TSOP		3.96	3.26	2.75
M28W160CT70N6E	M28W160CT70N6E-ND	16Mb (1Mbx16, Boot Block) 3V Supply Flash.....48-TSOP		3.96	3.26	2.75
M28W160ECB70ZB6E	M28W160ECB70ZB6E-ND	16Mb (1Mbx16, Boot Block) 3V Supply Flash.....46-TFBGA		4.01	3.30	2.78
M28W160ECT70ZB6E	M28W160ECT70ZB6E-ND	16Mb (1Mbx16, Boot Block) 3V Supply Flash.....46-TFBGA		4.01	3.30	2.78
M28W160ECT70ZB6U	M28W160ECT70ZB6UCT-ND	16Mb (1Mbx16, Boot Block) 3V Supply Flash.....46-TFBGA		1.96	1.71	1.28
M28W160ECT70ZB6U	M28W160ECT70ZB6UTR-ND	16Mb (1Mbx16, Boot Block) 3V Supply Flash.....46-TFBGA		2323.20/2,500		

Numonyx Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	10	100
M28W320FCB70N6E	M28W320FCB70N6E-ND	32Mb (2Mbx16, Boot Block) 3V Supply Flash.....48-TSOP		4.96	4.07	3.44
M28W320FCB70ZB6E	M28W320FCB70ZB6E-ND	32Mb (2Mbx16, Boot Block) 3V Supply Flash.....47-TFBGA		5.66	4.65	3.93
M28W320FCT70N6E	M28W320FCT70N6E-ND	32Mb (2Mbx16, Boot Block) 3V Supply Flash.....48-TSOP		5.95	4.88	4.12
M28W320FCT70ZB6E	M28W320FCT70ZB6E-ND	32Mb (2Mbx16, Boot Block) 3V Supply Flash.....47-TFBGA		5.66	4.65	3.93
M28W640HC870N6F	M28W640HC870N6FCT-ND	64Mb (4Mbx16, Boot Block) 3V Supply Flash.....48-TSOP		5.01	4.58	3.62
M28W640HC870N6F	M28W640HC870N6FTR-ND	64Mb (4Mbx16, Boot Block) 3V Supply Flash.....48-TSOP		4165.43/1,500		
M28W640HC870ZB6F	M28W640HC870ZB6FCT-ND	64Mb (4Mbx16, Boot Block) 3V Supply Flash.....48-TFBGA		5.01	4.58	3.62
M28W640HC870ZB6F	M28W640HC870ZB6FTR-ND	64Mb (4Mbx16, Boot Block) 3V Supply Flash.....48-TFBGA		6860.70/2,500		
M28W640HCT70N6F	M28W640HCT70N6FCT-ND	64Mb (4Mbx16, Boot Block) 3V Supply Flash.....48-TSOP		5.01	4.58	3.62
M28W640HCT70N6F	M28W640HCT70N6FTR-ND	64Mb (4Mbx16, Boot Block) 3V Supply Flash.....48-TSOP		4165.43/1,500		
M28W640HCT70ZB6F	M28W640HCT70ZB6FCT-ND	64Mb (4Mbx16, Boot Block) 3V Supply Flash.....48-TFBGA		5.01	4.58	3.62
M28W640HCT70ZB6F	M28W640HCT70ZB6FTR-ND	64Mb (4Mbx16, Boot Block) 3V Supply Flash.....48-TFBGA		6860.70/2,500		

numonyx		Digi+Reel		AUTOMOTIVE STANDARD BOOT BLOCK		
Numonyx Part No.	Digi-Key Part No.	Description	Pkg.	Price Each ★		
				1	10	100
M29W Series						
M29DW128G60ZAG6E	M29DW128G60ZAG6E-ND	128Mb (8Mbx16, Multiple Bank, Page, Dual Boot) 3V Supply Flash*.....64-TBGA		7.26	6.72	5.09
M29DW128G70N6E	M29DW128G70N6E-ND	128Mb (8Mbx16, Multiple Bank, Page, Dual Boot) 3V Supply Flash*.....56-TSOP		7.26	6.72	5.09
M29DW128G70ZAG6E	M29DW128G70ZAG6E-ND	128Mb (8Mbx16, Multiple Bank, Page, Dual Boot) 3V Supply Flash*.....64-TBGA		7.26	6.72	5.09
M29DW323DB70N6E	M29DW323DB70N6E-ND	32Mb (4Mbx8 or 2Mbx16, Dual Bank 8:24, Boot Block) 3V Supply Flash*.....48-TSOP		6.37	5.23	4.42
M29DW323DB70ZE6E	M29DW323DB70ZE6E-ND	32Mb (4Mbx8 or 2Mbx16, Dual Bank 8:24, Boot Block) 3V Supply Flash*.....48-TFBGA		6.37	5.23	4.42
M29DW323DT70N6E	M29DW323DT70N6E-ND	32Mb (4Mbx8 or 2Mbx16, Dual Bank 8:24, Boot Block) 3V Supply Flash*.....48-TSOP		6.37	5.23	4.42
M29DW323DT70ZE6E	M29DW323DT70ZE6E-ND	32Mb (4Mbx8 or 2Mbx16, Dual Bank 8:24, Boot Block) 3V Supply Flash*.....48-TFBGA		6.37	5.23	4.42
M29W128GH70N6E	M29W128GH70N6E-ND	128Mb (16Mbx8 or 8Mbx16, Page, Uniform LBP) 3V Supply Flash*.....56-TSOP		5.26	—	3.16
M29W128GH70ZAG6E	M29W128GH70ZAG6E-ND	128Mb (16Mbx8 or 8Mbx16, Page, Uniform LBP) 3V Supply Flash*.....64-TBGA		7.26	6.72	5.09
M29W128GL70N6E	M29W128GL70N6E-ND	128Mb (16Mbx8 or 8Mbx16, Page, Uniform FB) 3V Supply Flash*.....56-TSOP		9.40	8.33	6.72
M29W128GL70ZAG6E	M29W128GL70ZAG6E-ND	128Mb (16Mbx8 or 8Mbx16, Page, Uniform FB) 3V Supply Flash*.....64-TBGA		9.40	8.33	6.72
M29W160EB70N6E	M29W160EB70N6E-ND	16Mb (2Mbx8 or 1Mbx16, Boot Block) 3V Supply Flash*.....48-TSOP		4.01	3.30	2.78
M29W160EB70ZAG6E	M29W160EB70ZAG6E-ND	16Mb (2Mbx8 or 1Mbx16, Boot Block) 3V Supply Flash*.....48-TFBGA		4.01	3.30	2.78
M29W160ET70N6E	M29W160ET70N6E-ND	16Mb (2Mbx8 or 1Mbx16, Boot Block) 3V Supply Flash*.....48-TSOP		4.01	3.30	2.78
M29W160ET70N6F	M29W160ET70N6FCT-ND	16Mb (2Mbx8 or 1Mbx16, Boot Block) 3V Supply Flash*.....48-TSOP		1.96	1.71	1.28
M29W160ET70N6F	M29W160ET70N6FTR-ND	16Mb (2Mbx8 or 1Mbx16, Boot Block) 3V Supply Flash*.....48-TSOP		2563.38/1,500		
M29W160ET70ZAG6E	M29W160ET70ZAG6E-ND	16Mb (2Mbx8 or 1Mbx16, Boot Block) 3V Supply Flash*.....48-TFBGA		4.01	3.30	2.78
M29W160FB70N3E	M29W160FB70N3E-ND	16Mb (x8 or x16, Boot Block) 3V Supply Flash*.....48-TSOP		1.96	1.71	1.28
M29W160FB70N3F	M29W160FB70N3FCT-ND	16Mb (x8 or x16, Boot Block) 3V Supply Flash*.....48-TSOP		1.96	1.71	1.28
M29W160FB70N3F	M29W160FB70N3FTR-ND	16Mb (x8 or x16, Boot Block) 3V Supply Flash*.....48-TSOP		1448.37/1,500		
M29W160FB80ZA3E	M29W160FB80ZA3E-ND	16Mb (x8 or x16, Boot Block) 3V Supply Flash*.....48-TFBGA		1.96	1.71	1.28
M29W160FT70N3E	M29W160FT70N3E-ND	16Mb (x8 or x16, Boot Block) 3V Supply Flash*.....48-TSOP		1.96	1.71	1.28
M29W160FT70N3F	M29W160FT70N3FCT-ND	16Mb (x8 or x16, Boot Block) 3V Supply Flash*.....48-TSOP		1.96	1.71	1.28
M29W160FT70N3F	M29W160FT70N3FTR-ND	16Mb (x8 or x16, Boot Block) 3V Supply Flash*.....48-TSOP		1448.37/1,500		
M29W320DB70N6E	M29W320DB70N6E-ND	32Mb (4Mbx8 or 2Mbx16, Non-Uniform Parameter Blocks, Boot Block)*.....48-TSOP		5.66	4.65	3.93
M29W320DB70ZE6E	M29W320DB70ZE6E-ND	32Mb (4Mbx8 or 2Mbx16, Non-Uniform Parameter Blocks, Boot Block)*.....48-TFBGA		5.66	4.65	3.93

*RoHS Compliant

(Continued)

★ CALL FOR LOWER PRICING ON LARGER QUANTITIES! ★

Free shipping on orders over £50! All prices are in British pound sterling and include duties.

740 (UK091)

uk.digikey.com — FREEPHONE: 0-800-587-0991 • 0-800-904-7786 — FREEFAX: 0-800-587-0992 • 0-800-904-7783