

T. I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*	1	25	100
SN74AVCH1T45YZPR	296-17372-2-ND	Tri-State Single-Bit Dual Supply Bus Transceiver.....	6-DSBGA	339.77/3,000			
SN74AVCH2T45DCTR	296-19108-1-ND	Tri-State Dual-Bit Dual Supply Bus Transceiver.....	SM8	52 40 30			
SN74AVCH2T45DCTR	296-19108-2-ND	Tri-State Dual-Bit Dual Supply Bus Transceiver.....	SM8	509.65/3,000			
SN74AVCH2T45DCUR	296-19109-1-ND	Tri-State Dual-Bit Dual Supply Bus Transceiver.....	US8	58 44 .33			
SN74AVCH2T45DCUR	296-19109-2-ND	Tri-State Dual-Bit Dual Supply Bus Transceiver.....	US8	566.28/3,000			
SN74AVCH2T45YZPR	296-21024-1-ND	Tri-State Dual-Bit Dual Supply Bus Transceiver.....	8-DSBGA	64 48 .36			
SN74AVCH2T45YZPR	296-21024-2-ND	Tri-State Dual-Bit Dual Supply Bus Transceiver.....	8-DSBGA	622.91/3,000			
SN74AVCH4T245DQVGR	296-18055-1-ND	Tri-State 4-Bit, Dual Supply, Bus Transceiver.....	16-TVSOP	65 55 .44			
SN74AVCH4T245DQVGR	296-18055-2-ND	Tri-State 4-Bit, Dual Supply, Bus Transceiver.....	16-TVSOP	579.35/2,000			
SN74AVCH4T245DR	296-18032-1-ND	Tri-State 4-Bit, Dual Supply, Bus Transceiver.....	16-SOIC	65 55 .44			
SN74AVCH4T245DR	296-18032-2-ND	Tri-State 4-Bit, Dual Supply, Bus Transceiver.....	16-SOIC	707.85/2,500			
SN74AVCH4T245PWR	296-18057-1-ND	Tri-State 4-Bit, Dual Supply, Bus Transceiver.....	16-TSSOP	65 55 .44			
SN74AVCH4T245PWR	296-18057-2-ND	Tri-State 4-Bit, Dual Supply, Bus Transceiver.....	16-TSSOP	579.35/2,000			
SN74AVCH4T245RGYR	296-18262-1-ND	Tri-State 4-Bit, Dual Supply, Bus Transceiver.....	16-QFN	72 60 .48			
SN74AVCH4T245RGYR	296-18262-2-ND	Tri-State 4-Bit, Dual Supply, Bus Transceiver.....	16-QFN	318.71/1,000			
SN74AVCH8T245DGV	296-17932-ND	Tri-State 8-Bit, Dual Supply, Bus Transceiver.....	24-TVSOP	.91 .73 .55			
SN74AVCH8T245PWR	296-19112-1-ND	Tri-State 8-Bit Dual Supply Bus Transceiver.....	24-TSSOP	.91 .73 .55			
SN74AVCH8T245PWR	296-19112-2-ND	Tri-State 8-Bit Dual Supply Bus Transceiver.....	24-TSSOP	943.80/2,000			
SN74AVCH8T245RHLR	296-22015-1-ND	Tri-State 8-Bit Dual Supply Bus Transceiver.....	24-QFN	.91 .73 .55			
SN74AVCH8T245RHLR	296-22015-2-ND	Tri-State 8-Bit Dual Supply Bus Transceiver.....	24-QFN	471.90/1,000			
SN74AVCH16T245GQLR	296-19102-1-ND	Tri-State 16-Bit Dual Supply Bus Transceiver.....	56-VFBGA	3.78 3.02 2.55			
SN74AVCH16T245GQLR	296-19102-2-ND	Tri-State 16-Bit Dual Supply Bus Transceiver.....	56-VFBGA	2359.50/1,000			
SN74AVCH16T245GR	296-18283-1-ND	Tri-State 16-Bit Dual Supply Bus Transceiver.....	48-TSSOP	2.40 1.93 1.50			
SN74AVCH16T245GR	296-18283-2-ND	Tri-State 16-Bit Dual Supply Bus Transceiver.....	48-TSSOP	2721.05/2,000			
SN74AVCH16T245VR	296-19103-1-ND	Tri-State 16-Bit Dual Supply Bus Transceiver.....	48-TVSOP	2.40 1.93 1.50			
SN74AVCH16T245VR	296-19103-2-ND	Tri-State 16-Bit Dual Supply Bus Transceiver.....	48-TVSOP	2721.05/2,000			
SN74AVCH20T245GR	296-17819-1-ND	Tri-State 20-Bit Dual Supply Bus Transceiver.....	56-TSSOP	2.58 2.07 1.61			
SN74AVCH20T245GR	296-17819-2-ND	Tri-State 20-Bit Dual Supply Bus Transceiver.....	56-TSSOP	2925.78/2,000			
SN74AVCH20T245KR	296-19106-1-ND	Tri-State 20-Bit Dual Supply Bus Transceiver.....	56-VFBGA	3.78 3.02 2.55			
SN74AVCH20T245KR	296-19106-2-ND	Tri-State 20-Bit Dual Supply Bus Transceiver.....	56-VFBGA	2359.50/1,000			
SN74AVCH20T245VR	296-19107-1-ND	Tri-State 20-Bit Dual Supply Bus Transceiver.....	56-TVSOP	2.58 2.07 1.61			
SN74AVCH20T245VR	296-19107-2-ND	Tri-State 20-Bit Dual Supply Bus Transceiver.....	56-TVSOP	2925.78/2,000			
SN74AVCH24T245GRGR	296-17663-1-ND	Tri-State 24-Bit Dual Supply Bus Transceiver.....	83-BGA	3.78 3.02 2.55			
SN74AVCH24T245GRGR	296-17663-2-ND	Tri-State 24-Bit Dual Supply Bus Transceiver.....	83-BGA	2359.50/1,000			
SN74AVCH24T245ZGR	296-17664-1-ND	Tri-State 24-Bit Dual Supply Bus Transceiver.....	83-BGA	2.86 2.29 1.78			
SN74AVCH24T245ZGR	296-17664-2-ND	Tri-State 24-Bit Dual Supply Bus Transceiver.....	83-BGA	1619.71/1,000			
SN74AVCH32T245KR	296-19110-1-ND	Tri-State 32-Bit Dual Supply Bus Transceiver.....	96-LFBGA	3.78 3.02 2.55			
SN74AVCH32T245KR	296-19110-2-ND	Tri-State 32-Bit Dual Supply Bus Transceiver.....	96-LFBGA	2359.50/1,000			
SN74AVCH32T245ZKER	296-19111-1-ND	Tri-State 32-Bit Dual Supply Bus Transceiver.....	96-LFBGA	2.93 2.34 1.82			
SN74AVCH32T245ZKER	296-19111-2-ND	Tri-State 32-Bit Dual Supply Bus Transceiver.....	96-LFBGA	1656.73/1,000			

BCT Family

SN64BCT125AD	296-9690-5-ND	Tri-State Quad Bus Buffer Gate.....	14-SOIC	1.45 1.17 .88			
SN64BCT757DW	296-9692-5-ND	Octal Buffer/Driver.....	20-SOIC	2.94 2.36 1.83			
SN64BCT25244NT	296-9691-5-ND	Tri-State Octal Bus Buffer/Driver.....	24-Dip	4.36 3.49 2.95			
SN74BCT244DWR	296-1152-1-ND	Octal Buffer/Driver.....	20-SOIC	2.43 1.95 1.52			
SN74BCT244DWR	296-1152-2-ND	Octal Buffer/Driver.....	20-SOIC	2754.09/2,000			
SN74BCT245DWR	296-1154-1-ND	Octal Bus Transceiver.....	20-SOIC	2.43 1.95 1.52			
SN74BCT245DWR	296-1154-2-ND	Octal Bus Transceiver.....	20-SOIC	2754.09/2,000			
SN74BCT374NSR	296-13177-1-ND	Tri-State Octal Edge-Triggered D-Type Flip-Flop.....	20-SOP	2.13 1.70 1.33			
SN74BCT374NSR	296-13177-2-ND	Tri-State Octal Edge-Triggered D-Type Flip-Flop.....	20-SOP	2407.42/2,000			
SN74BCT543DW	296-12335-5-ND	Tri-State Octal Register Transceiver with Output.....	24-SOIC	5.88 4.71 3.97			
SN74BCT623NSR	296-13178-1-ND	Tri-State Octal Bus Transceiver.....	20-SOP	2.29 1.83 1.43			
SN74BCT623NSR	296-13178-2-ND	Tri-State Octal Bus Transceiver.....	20-SOP	2591.82/2,000			
SN74BCT64QNSR	296-13179-1-ND	Tri-State Octal Bus Transceiver.....	20-SOP	2.57 2.06 1.60			
SN74BCT64QNSR	296-13179-2-ND	Tri-State Octal Bus Transceiver.....	20-SOP	2913.21/2,000			
SN74BCT652DWR	296-1155-1-ND	Octal Bus Transceiver.....	24-SOIC	5.08 4.07 3.44			
SN74BCT652DWR	296-1155-2-ND	Octal Bus Transceiver.....	24-SOIC	6352.50/2,000			
SN74BCT760MDWREP	296-22294-1-ND	Octal Buffer/Driver.....	20-SOIC	6.07 5.47 4.85			
SN74BCT760MDWREP	296-22294-2-ND	Octal Buffer/Driver.....	20-SOIC	9002.40/2,000			
SN74BCT2141DW	296-13176-5-ND	Memory Decoder with On-Chip Supply Voltage Monitor.....	20-SOIC	2.29 1.83 1.43			

T. I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*	1	25	100
Bus Switch Family (CBT)							
74CBTLV16211CGRDR	296-18211-1-ND	Low Voltage 24-Bit FET Bus Switch.....	54-LFBGA	2.16 1.73 1.35			
74CBTLV16211CGRDR	296-18211-2-ND	Low Voltage 24-Bit FET Bus Switch.....	54-LFBGA	1221.86/1,000			
74CBTLV16211CZDR	296-20802-1-ND	Low Voltage 24-Bit FET Bus Switch.....	54-BGA	1.60 1.28 .96			
74CBTLV16211CZDR	296-20802-2-ND	Low Voltage 24-Bit FET Bus Switch.....	54-BGA	830.54/1,000			
SN74CB3Q3125DBQR	296-19123-1-ND	Quad FET Bus Switch.....	16-QSOP	.61 .51 .41			
SN74CB3Q3125DBQR	296-19123-2-ND	Quad FET Bus Switch.....	16-QSOP	660.66/2,500			
SN74CB3Q3125DQVR	296-19124-1-ND	Quad FET Bus Switch.....	14-TVSOP	.61 .51 .41			
SN74CB3Q3125DQVR	296-19124-2-ND	Quad FET Bus Switch.....	14-TVSOP	540.14/2,000			
SN74CB3Q3125PWR	296-16804-1-ND	Quad FET Bus Switch.....	14-TSSOP	.72 .60 .48			
SN74CB3Q3125PWR	296-16804-2-ND	Quad FET Bus Switch.....	14-TSSOP	637.43/2,000			
SN74CB3Q3125RGYR	296-23248-1-ND	Quad FET Bus Switch.....	14-QFN	.72 .60 .48			
SN74CB3Q3125RGYR	296-23248-2-ND	Quad FET Bus Switch.....	14-QFN	318.71/1,000			
SN74CB3Q3244DBQR	296-19125-1-ND	8-Bit FET Bus Switch.....	20-QSOP	.61 .51 .41			
SN74CB3Q3244DBQR	296-19125-2-ND	8-Bit FET Bus Switch.....	20-QSOP	660.66/2,500			
SN74CB3Q3244DQVR	296-19125-1-ND	8-Bit FET Bus Switch.....	20-TVSOP	.61 .51 .41			
SN74CB3Q3244DQVR	296-19125-2-ND	8-Bit FET Bus Switch.....	20-TVSOP	540.14/2,000			
SN74CB3Q3244GQNR	296-17033-1-ND	8-Bit FET Bus Switch.....	20-VFBGA	1.04 .83 .63			
SN74CB3Q3244GQNR	296-17033-2-ND	8-Bit FET Bus Switch.....	20-VFBGA	537.97/1,000			
SN74CB3Q3244PWR	296-17824-1-ND	8-Bit FET Bus Switch.....	20-TSSOP	.72 .61 .49			
SN74CB3Q3244PWR	296-17824-2-ND	8-Bit FET Bus Switch.....	20-TSSOP	638.99/2,000			
SN74CB3Q3244RGYR	296-19127-1-ND	8-Bit FET Bus Switch.....	20-QFN	.83 .69 .56			
SN74CB3Q3244RGYR	296-19127-2-ND	8-Bit FET Bus Switch.....	20-QFN	366.63/1,000			
SN74CB3Q3244ZQNR	296-17034-1-ND	8-Bit FET Bus Switch.....	20-VFBGA	.83 .69 .56			
SN74CB3Q3244ZQNR	296-17034-2-ND	8-Bit FET Bus Switch.....	20-VFBGA	366.63/1,000			
SN74CB3Q3245DBQR	296-19128-1-ND	8-Bit FET Bus Switch.....	20-QSOP	.61 .51 .41			
SN74CB3Q3245DBQR	296-19128-2-ND	8-Bit FET Bus Switch.....	20-QSOP	660.66/2,500			
SN74CB3Q3245DQVR	296-19129-1-ND	8-Bit FET Bus Switch.....	20-TVSOP	.68 .57 .46			
SN74CB3Q3245DQVR	296-19129-2-ND	8-Bit FET Bus Switch.....	20-TVSOP	598.22/2,000			
SN74CB3Q3245GQNR	296-23249-1-ND	8-Bit FET Bus Switch.....	20-VFBGA	1.04 .83 .63			
SN74CB3Q3245GQNR	296-23249-2-ND	8-Bit FET Bus Switch.....	20-VFBGA	537.97/1,000			
SN74CB3Q3245PWR	296-19130-1-ND	8-Bit FET Bus Switch.....	20-TSSOP	.61 .51 .41			
SN74CB3Q3245PWR	296-19130-2-ND	8-Bit FET Bus Switch.....	20-TSSOP	540.14/2,000			
SN74CB3Q3245RGYR	296-19131-1-ND	8-Bit FET Bus Switch.....	20-QFN	.83 .69 .56			
SN74CB3Q3245RGYR	296-19131-2-ND	8-Bit FET Bus Switch.....	20-QFN	366.63/1,000			
SN74CB3Q3251DBQR	296-19132-1-ND	1-of-8 FET Mux/Demux.....	16-QSOP	.61 .51 .41			
SN74CB3Q3251DBQR	296-19132-2-ND	1-of-8 FET Mux/Demux.....	16-QSOP	660.66/2,500			
SN74CB3Q3251DQVR	296-19133-1-ND	1-of-8 FET Mux/Demux.....	16-TVSOP	.61 .51 .41			
SN74CB3Q3251DQVR	296-19133-2-ND	1-of-8 FET Mux/Demux.....	16-TVSOP	540.14/2,000			
SN74CB3Q3251PWR	296-18204-1-ND	1-of-8 FET Mux/Demux.....	16-TSSOP	.61 .51 .41			
SN74CB3Q3251PWR	296-18204-2-ND	1-of-8 FET Mux/Demux.....	16-TSSOP	540.14/2,000			
SN74CB3Q3253DBQR	296-17283-1-ND	Dual 1-of-4 FET Mux/Demux.....	16-QSOP	.61 .51 .41			
SN74CB3Q3253DBQR	296-17283-2-ND	Dual 1-of-4 FET Mux/Demux.....	16-QSOP	660.66/2,500			
SN74CB3Q3253DQVR	296-19134-1-ND	Dual 1-of-4 FET Mux/Demux.....	16-TVSOP	.73 .61 .49			
SN74CB3Q3253DQVR	296-19134-2-ND	Dual 1-of-4 FET Mux/Demux.....	16-TVSOP	641.30/2,000			
SN74CB3Q3253PWR	296-19135-1-ND	Dual 1-of-4 FET Mux/Demux.....	16-TSSOP	.72 .61 .49			
SN74CB3Q3253PWR	296-19135-2-ND	Dual 1-of-4 FET Mux/Demux.....	16-TSSOP	638.99/2,000			
SN74CB3Q3253RGYR	296-19136-1-ND	Dual 1-of-4 FET Mux/Demux.....	16-QFN	.83 .69 .56			
SN74CB3Q3253RGYR	296-19136-2-ND	Dual 1-of-4 FET Mux/Demux.....	16-QFN	366.63/1,000			
SN74CB3Q3257DBQR	296-17511-1-ND	4-Bit, 1-of-2 FET Mux/Demux.....	16-QSOP	.61 .51 .41			
SN74CB3Q3257DBQR	296-17511-2-ND	4-Bit, 1-of-2 FET Mux/Demux.....	16-QSOP	660.66/2,500			
SN74CB3Q3257DQVR	296-19137-1-ND	4-Bit, 1-of-2 FET Mux/Demux.....	16-TVSOP	.73 .61 .49			
SN74CB3Q3257DQVR	296-19137-2-ND	4-Bit, 1-of-2 FET Mux/Demux.....	16-TVSOP	641.30/2,000			
SN74CB3Q3257PWR	296-19138-1-ND	4-Bit, 1-of-2 FET Mux/Demux.....	16-TSSOP	.72 .61 .49			
SN74CB3Q3257PWR	296-19138-2-ND	4-Bit, 1-of-2 FET Mux/Demux.....	16-TSSOP	638.99/2,000			
SN74CB3Q3257RGYR	296-16834-1-ND	4-Bit, 1-of-2 FET Mux/Demux.....	16-QFN	.83 .69 .56			
SN74CB3Q3257RGYR	296-16834-2-ND	4-Bit, 1-of-2 FET Mux/Demux.....	16-QFN	366.63/1,000			
SN74CB3Q3305DCUR							